AP9563GH/J

Pb Free Plating Product

Advanced Power Electronics Corp.

P-CHANNEL ENHANCEMENT MODE POWER MOSFET

- ▼ **Lower On-resistance**
- ▼ **Simple Drive Requirement**
- ▼ **Fast Switching Characteristic**



BV_{DSS}	-40V
$R_{DS(ON)}$	40mΩ
I_D	-26A

TO-252(H)



TO-251(J)

Description

The TO-252 package is universally preferred for all commercial-industrial surface mount applications and suited for low voltage applications such as DC/DC converters. The through-hole version (AP9563GJ) is available for low-profile applications.

Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	-40	V
V_{GS}	Gate-Source Voltage	±25	V
I_D@T_C=25℃	Continuous Drain Current, V_{GS} @ 10V	-26	A
I_D@T_C=100℃	Continuous Drain Current, V_{GS} @ 10V	-16	A
I_{DM}	Pulsed Drain Current[1]	-64	A
P_D@T_C=25℃	Total Power Dissipation	44.6	W
	Linear Derating Factor	0.36	W/℃
T_{STG}	Storage Temperature Range	-55 to 150	℃
T_J	Operating Junction Temperature Range	-55 to 150	℃

Thermal Data

Symbol	Parameter		Value	Units
Rthj-c	Thermal Resistance Junction-case	Max.	2.8	℃/W
Rthj-a	Thermal Resistance Junction-ambient	Max.	110	℃/W

Electrical Characteristics@T_j=25°C(unless otherwise specified)

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Units
BV_{DSS}	Drain-Source Breakdown Voltage	V_{GS}=0V, I_D=-250uA	-40	-	-	V
$\Delta BV_{DSS}/\Delta T_j$	Breakdown Voltage Temperature Coefficient	Reference to 25℃, I_D=-1mA	-	-0.03	-	V/℃
$R_{DS(ON)}$	Static Drain-Source On-Resistance[2]	V_{GS}=-10V, I_D=-16A	-	-	40	mΩ
		V_{GS}=-4.5V, I_D=-12A	-	-	60	mΩ
$V_{GS(th)}$	Gate Threshold Voltage	V_{DS}=V_{GS}, I_D=-250uA	-1	-	-3	V
g_{fs}	Forward Transconductance	V_{DS}=-10V, I_D=-12A	-	18	-	S
I_{DSS}	Drain-Source Leakage Current (T_j=25°C)	V_{DS}=-40V, V_{GS}=0V	-	-	-1	uA
	Drain-Source Leakage Current (T_j=150°C)	V_{DS}=-32V, V_{GS}=0V	-	-	-25	uA
I_{GSS}	Gate-Source Leakage	V_{GS}= ±25V	-	-	±100	nA
Q_g	Total Gate Charge[2]	I_D=-12A	-	19	30	nC
Q_{gs}	Gate-Source Charge	V_{DS}=-32V	-	4	-	nC
Q_{gd}	Gate-Drain ("Miller") Charge	V_{GS}=-4.5V	-	9	-	nC
$t_{d(on)}$	Turn-on Delay Time[2]	V_{DS}=-20V	-	10	-	ns
t_r	Rise Time	I_D=-12A	-	37	-	ns
$t_{d(off)}$	Turn-off Delay Time	R_G=3.3Ω,V_{GS}=-10V	-	52	-	ns
t_f	Fall Time	R_D=1.6Ω	-	80	-	ns
C_{iss}	Input Capacitance	V_{GS}=0V	-	1460	2340	pF
C_{oss}	Output Capacitance	V_{DS}=-25V	-	230	-	pF
C_{rss}	Reverse Transfer Capacitance	f=1.0MHz	-	180	-	pF

Source-Drain Diode

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Units
V_{SD}	Forward On Voltage[2]	I_S=-12A, V_{GS}=0V	-	-	-1.2	V
t_{rr}	Reverse Recovery Time[2]	I_S=-12A, V_{GS}=0V,	-	40	-	ns
Q_{rr}	Reverse Recovery Charge	dI/dt=-100A/μs	-	54	-	nC

Notes:

1.Pulse width limited by safe operating area.

2.Pulse width ≤300us , duty cycle ≤2%.



Fig 1. Typical Output Characteristics



Fig 2. Typical Output Characteristics



Fig 3. On-Resistance v.s. Gate Voltage



Fig 4. Normalized On-Resistance v.s. Junction Temperature



Fig 5. Forward Characteristic of Reverse Diode



Fig 6. Gate Threshold Voltage v.s. Junction Temperature



Fig 7. Gate Charge Characteristics



Fig 8. Typical Capacitance Characteristics



Fig 9. Maximum Safe Operating Area



Fig 10. Effective Transient Thermal Impedance



Fig 11. Switching Time Waveform



Fig 12. Gate Charge Waveform