


PART NO.	"B"	THREAD	"C"	HEAD STYLE
NSS-4-#-01	.07 (1.8)	#4-40	.21 (5.3)	SLOTTED PAN
NSS-6-#-01	.08 (2.0)	#6-32	.27 (6.9)	
NSS-8-#-01	.08 (2.0)	#8-32	.32 (8.1)	
NSP-4-#-01	.08 (2.0)	#4-40	.21 (5.3)	PHILLIPS PAN
NSP-6-#-01	.09 (2.3)	#6-32	.26 (6.6)	
NSP-8-#-01	.11 (2.8)	#8-32	.32 (8.1)	



$-\#-$	${}^{\text{A}}\text{A}^{+0.000}_{-0.030}$ ($+0.00$ -0.76)
$-2-$	$1/8$ (3.2)
$-3-$	$3/16$ (4.8)
$-4-$	$1/4$ (6.4)
$-5-$	$5/16$ (7.9)
$-6-$	$3/8$ (9.5)
$-7-$	$7/16$ (11.1)
$-8-$	$1/2$ (12.7)
$-10-$	$5/8$ (15.9)
$-12-$	$3/4$ (19.1)
$-14-$	$7/8$ (22.2)
$-16-$	1.00 (25.4)

NOTES:

1. MATERIAL: NYLON 6/6 (RMS-01).
2. COLOR: NATURAL.

B	SEE ECN #1025 FOR CHANGES	SK 07.15.05
A	CHANGED FILE NO.	SM 08.16.02
REV	DESCRIPTION	ENGR DATE

TITLE: NYLON SCREWS					DWG IN IN(MM)	
TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=±1/64 ANG=±1°	FILE #	NSS-NSP	DWN: J.B.	APP:	FINAL	
	MAT'L:	SEE NOTES	DT: 01-16-97	DT:	PART #	PRINT TYPE
	RE:	RICHCO, INC.	RICHCO INC. PO BOX 804238, CHICAGO, 60680 (773) 539-4060		SEE TABLE	CA