

φ 2.0 mm Series

Conventional Part No. Global Part No. Lighting Color

LN282RPX LNG282RKR Red

LN382GPX LNG382GKG Green

LN482YPX LNG482YKX Amber

LN882RPX LNG882RKD Orange

■ 絶対最大定格 Absolute Maximum Ratings ($T_a = 25^\circ\text{C}$)

Lighting Color	P_D (mW)	I_F (mA)	I_{FP} (mA)*	V_R (V)	T_{opr} ($^\circ\text{C}$)	T_{stg} ($^\circ\text{C}$)
Red	70	25	150	4	-25 ~ +85	-30 ~ +100
Green	90	30	150	4	-25 ~ +85	-30 ~ +100
Amber	90	30	150	4	-25 ~ +85	-30 ~ +100
Orange	90	30	150	3	-25 ~ +85	-30 ~ +100

 I_{FP} の条件は $\text{duty } 10\%$ Pulse width 1 msec. The condition of I_{FP} is duty 10%, Pulse width 1 msec■ 電気的光学的特性 Electro-Optical Characteristics ($T_a = 25^\circ\text{C}$)

Conventional Part No.	Lighting Color	Lens Color	I_O		I_F	V_F		λ_P	$\Delta\lambda$	I_F	I_R	
			Typ	Min		Typ	Max	Typ	Typ		Max	V_R
LN282RPX	Red	Red Diffused	1.0	0.5	15	2.2	2.8	700	100	20	5	4
LN382GPX	Green	Green Diffused	1.2	0.5	20	2.2	2.8	565	30	20	10	4
LN482YPX	Amber	Amber Diffused	2.0	1.0	20	2.2	2.8	590	30	20	10	4
LN882RPX	Orange	Red Diffused	6.0	2.5	20	2.1	2.8	630	40	20	10	3
Unit	—	—	mcd	mcd	mA	V	V	nm	nm	mA	μA	V

