

Coaxial Amplifier

ZHL-2-8


50Ω Medium High Power 10 to 1000 MHz

Features

- wideband, 10 to 1000 MHz
- high IP3, +38 dBm typ.
- medium high power, 29 dBm min.

Applications

- test equipment
- cellular
- instrumentation
- laboratory
- VHF/UHF



BNC version shown
CASE STYLE: T34

Connectors	Model	Price	Qty.
BNC	ZHL-2-8	\$525.00	(1-9)
SMA	ZHL-2-8-S	\$535.00	(1-9)

Amplifier Electrical Specifications


MODEL NO.	FREQUENCY (MHz)		GAIN (dB)		MAXIMUM POWER (dBm)		DYNAMIC RANGE		VSWR (:1) Max.		DC POWER	
	f_L	f_U	Min.	Flatness Max.	Output (1 dB Compr. min.)	Input (no damage)	NF (dB) Typ.	IP3 (dBm) Typ.	In	Out	Volt (V) Nom.	Current (A) Max.
ZHL-2-8	10	1000	27	±1.0	+29	+5	10.0	+38	2.0	2.0	24	0.6

Open load is not recommended, potentially can cause damage.
With no load derate max input power by 20 dB

Maximum Ratings

Operating Temperature	-20°C to 65°C
Storage Temperature	-55°C to 100°C
DC Voltage	+25V Max.

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	S	T	wt
4.75	2.00	2.12	.19	4.375	.23	1.540	.144	.58	.34	.50	1.50	1.00	.12	.38	4.00	.30	2.60	grams
120.65	50.80	53.85	4.83	111.13	5.84	39.12	3.66	14.73	8.64	12.70	38.10	25.40	3.05	9.65	101.60	7.62	66.04	440.0



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

REV. OR
M98142
ZHL-2-8
060906
Page 1 of 2

FREQUENCY (MHz)	GAIN (dB)			DIRECTIVITY (dB)			VSWR (:1)		NOISE FIGURE (dB)	POUT at 1 dB COMPR. (dBm)
	23V	24V	24.5V	23V	24V	24.5V	IN	OUT	24V	24V
10.00	28.91	28.90	28.90	32.50	32.50	33.90	1.52	1.77	6.17	30.73
22.60	29.36	29.36	29.36	35.40	32.20	31.70	1.31	1.61	5.73	31.05
66.80	29.45	29.44	29.44	34.90	28.00	34.70	1.26	1.58	5.26	31.27
197.60	29.47	29.46	29.47	31.20	35.30	33.00	1.26	1.63	5.22	31.10
390.80	29.34	29.33	29.34	36.40	30.90	32.60	1.27	1.44	5.27	30.40
492.30	29.38	29.37	29.37	30.50	34.80	32.50	1.28	1.21	5.32	30.02
619.20	29.39	29.38	29.38	28.50	28.70	30.80	1.25	1.02	5.38	29.65
746.20	28.95	28.94	28.94	27.60	27.60	27.90	1.28	1.05	5.51	29.56
873.10	29.05	29.03	29.03	26.30	24.60	25.90	1.50	1.18	5.74	29.69
1000.00	29.06	29.05	29.05	21.70	23.10	22.20	1.26	1.82	6.09	29.32

