



English
日本語

Product Catalog	Engineering Info	Company Links	Contact Us
-----------------	------------------	---------------	------------

Fan Motors Engineering

Information

 DC Fans

1.Common Spec.

2.Numbering (Axial Fans)

3. Numbering (FB)

4. Numbering (Blowers BM)

5. Numbering (Blowers BG)

6. Numbering (FAL)

7.Sensors

8.Speed Control

AC Fans

Technical Information

Handling Precautions

Quality & Environment

DC Axial Fans Part Numbering System

To show details, place the mouse cursor on each item of the part number. Click "Display All" button to show all details.

24 10 M L - 04 W - B 1 0 - X 00
(1) (2) (3) (4) (5) (6) (7) (8) (9) (10) (11)

[Display All](#)

1. Size

10	25mm	28	70mm	04	10mm
12	30mm	31	80mm	06	15mm
14	35mm	36	92mm	08	20mm
16	40mm	47	119mm	10	25mm
20	50mm	50	127mm	12	32mm
21	52mm	59	150mm	15	38mm
24	60mm	68	172mm	20	50mm

2. Thickness

10mm
15mm
20mm
25mm
32mm
38mm
50mm

3. Series

P Series	S Series
M Series	F Series
N Series	
K Series	
H Series	

5. Input Voltage

01	5V	06	36V
02	6V	07	48V
03	9V	09	Custom
04	12V		voltage
05	24V		

4. Function

Brushless Type B Ball Bearing
DCM S Sleeve Bearing

7. Bearing

B Ball Bearing
S Sleeve Bearing

6. Termination 8. Speed

w	Lead Wires	1<2<3<4<5<6<7<8
T	Terminal Type	low high

9. Special Control Function

0 Standard type
9 Sensor type
8 2-speed type
7 Temperature detecting variable speed type/PWM control type
6 Temperature detecting variable speed type/Sensor type
5 2-speed type / Sensor type

11. Individual Specifications

Standard Type		Sensor Type	
00	Standard	00	Locked Rotor Alarm Signal(Standard)
01-99	Custom	01-49	Locked Rotor Alarm Signal(Custom)
		50	Tachometer Signal (Standard)
		51-99	Tachometer Signal (Custom)

10. Product No.

Item	Classification	Mounting Style	Item	Classification	Mounting Style	Item	Classification	Mounting Style
L	Standard Model	Rib Type	D	Standard Model	Flange Type	J	Value Model	One Side Rib Type
P	Standard Model	Flange Type	T	Value Model	Rib Type	H	Value Model	One Side Flange Type
B	Standard Model	Rib Type	S	Value Model	Flange Type	M	Value Model	Rib Type
E	Standard Model	Flange Type	C	Value Model	Rib Type	V	Value Model	Flange Type
G	Standard Model	Rib Type	F	Value Model	Flange Type	X	Vented casing	Flange Type