





REV.	DATE	ECR NO.	DESCRIPTION
A	06/20/12	2309	UPDATE DRAWING FORMAT



RECOMMENDED
CABLE STRIPPING DIM'S



1. IMPEDANCE: 50 OHM
2. FREQUENCY RANGE: DC 0–11 GHz
3. DIELECTRIC WITHSTANDING VOLTAGE: 1500 VRMS, MIN.
4. DURABILITY: 500 CYCLES MIN.
5. TEMPERATURE RANGE: –65°C to +165°C
6. CRIMPED FERRULE
HEX CRIMP SIZE .255"
7. CRIMPED CONTACT PIN
HEX CRIMP SIZE .068"

9	FERRULE	BRASS	NICKEL	1	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex										
8	CONTACT PIN	BRASS	GOLD	1		DRAWN	M.ZHANG						06/20/12	PART DESCRIPTION				
7	WASHER	BRASS	NICKEL	1		CHECKED								TNC CRIMP PLUG – 50 OHMS (FOR RG–59/U PLENUM, BELDEN 88241 CABLE)				
6	RING	DELTRIN	NATURAL	1		ISSUED			PART NO.									
5	RETAINER RING	BRASS	NICKEL	1		SHEET	1 OF 1		122114									
4	GASKET	RUBBER	RED	1					DWG. NO.									
3	INSULATOR	DELTRIN	NATURAL	1					122114.DWG									
2	BODY	BRASS	NICKEL	1					REV. A									
1	SHELL	BRASS	NICKEL	1					SIZE A									
DESCRIPTION		MATERIAL	FINISH	QTY				SCALE NA										

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[122114](#)