

Wire strippers and cutters

163

- Stripping and cutting, plus end nippers.
- For multi-core wire :
 - Ø mm 3.0 - 2.4 - 2.0 - 1.7 - 1.3 - 1.0 / Cutting Ø 3 mm
 - mm² : 7.0 - 4.5 - 3.0 - 2.3 - 1.3 - 0.8 / Cutting Ø 7 mm
 - AWG : 10.0 - 12.0 - 14.0 - 16.0 - 18.0 - 20.0 / Cutting Ø 10 mm
- 6 precision-machined notches.
- Return spring and catch.
- Length 150 mm.
- ΔΔ : 115 g.



► End strippers

End stripper

985760

- Opening spring and adjusting screw.
- PVC grips.
- For stripping wires 0.5 to 6 mm².




	 mm ²	AWG	 mm	ΔΔ g
985760	6	→ 10	7 → 18	160

Fine wire strippers

194.12

- Max. AWG 14.
- For light-gauge wire.
- Narrow blades.
- Cutting depth presetting.
- Burnished finish, PVC grips.
- Ø 1.5 mm single and multi-core wire.
- Cross section 1.8 mm².
- ΔΔ : 70 g.




Wire stripper

194.17CPE

- For single and multi-core wires 0.5 to 6 mm².
- 194.17 : Standard forged pliers.
- Knurled adjustment screw with locknut.
- Metal return spring.



	 mm ²	A mm	B mm	L mm	ΔΔ g
194.17CPE	0,5 - 6	17	8,5	170	185



Coated-wire strippers

173A

- Hardened steel. Plastic finger-pads for comfortable use.
- Burnished blades.
- 135 mm long x 10 mm wide.
- ΔΔ : 40 g.

