


LAYOUT





CIRCUIT: SPDT
CONTACT CONFIGURATION

SWITCH FUNCTION		
PDS. 1	PDS. 2	PDS. 3
		
DN	NONE	DN
2-3	OPEN	2-1

NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $XX.X = \pm 0.25$
3. TERM. NOS. FOR REF. ONLY
4. CONTACT RATING: 3A @120VAC OR 28VDC, 1A @250VAC
5. FIXED TERMINAL & MOVING CONTACT: Copper Alloy w/Gold over Nickel plate.
6. CONTACT RESISTANCE: 20mILLI OHMS max. initial
@2-4 VDC, 100mA for AG & Au
6. ELECTRIC LIFE: 30,000 make-and-break cycles
at full load.
7. INSULATION RESISTANCE: 1,000 M ohm min.
8. DIELECTRIC STRENGTH: 1,000 V RMS @sed level.
9. OPERATING TEMP. -30°C to 85°C
10. DESIGNATE MAJOR DIMENSION



9. OPERATING TEMP. -30°C to 85°C			
▲ 10. DESIGNATE MAJOR DIMENSION			
A	11592	RELEASED FOR PRODUCTION	8/2/01 CJB
REV.	ECN NO.	DESCRIPTION	DATE CHKD
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			
TITLE		E-SWITCH®	
200 MSP-1 T1 B1 M2 R E			
SCALE	DATE	DR	REV
2:1	8/2/01	CJB	A
		DWG	
		T211079	