




Relay Coupler



The universal foot of the Weidmüller **relay modules** allow them to be assembled on TS 32, TS 35 x 7.5 and TS 35 x 15 mounting rails in accordance with European standards EN 50 035 and EN 50 022.

An LED status indicator in the coil of the relay coupler indicates the relay switching status.

Contact material	Properties	Application	U/I
Fine silver AG 99 %	- inexpensive - average tendency to weld and average resistance to burn-off - subject to corrosion in sulphurous atmosphere	universal use up to medium-size loads	1 V...250 V 1 mA...5 A
Silver nickel ● AgNi 0.15	- high mechanical stability - low tendency to weld - low contact resistance - high resistance to burn-off	universal use at medium-size loads	≥ 12 V 5 mA...10 A
Hard silver AgCu3	- mechanical stability > AgNi - tendency to weld < AgNi - resistance to burn-off > AgNi - contact resistance > AgNi	for use with medium-size loads	≥ 12 V 10 mA...10 A
Silver cadmium oxide ● AgCdO	- very low tendency to weld - resistance to burn-off > AgCu3/Ni	suitable for switching inductive loads	≥ 12 V ≥ 100 mA
Silver-tin-oxide ● AgSnO ₂	- high thermal decomposition temperature - more arc-resistant with low material transfer	suitable for switching inductive loads	≥ 12 V ≥ 100 mA
Tungsten W	- very high resistance to burn-off - high switching rate with short closed times	circuits with extremely high on/off loads	≥ 60 V ≥ 1 A
Hard gold ● AuNi	- < lowest contact resistance - best resistance to corrosion	dry circuits in damp atmospheres	µV...60 V µA...0.2 V

● = preferred materials

Types of contact

The standard range comprises numerous types and combinations of contacts.

- 1 NC (EGR EG2, EGR EG7, RS 30)
- 1 NO (EGR EG2, EGR EG7, DKR, RS 30)
- 1 NC and 1 NO (EGR EG2, WRS)
- 2 NO (WRS)
- 3 NO (WRS)
- 1 Changeover (EGR EG2, EGR/RST EG7, WRS DKR PRS/PRZ MCZ R, RS 30, RS 31)
- 2 Changeover (EGR EG2, WRS, RS 32, PRS/PRZ)
- 4/8/16 Changeover (RSM)

Contact material

The all-round capability of Weidmüller relay modules is achieved by the choice of the contact material.

The contact is responsible for both the reliable transmission of the control signals and for switching power contactors. Weidmüller uses gold-plated or gold-flashed AgNi contacts for most applications. Gold-plated contacts permit the switching of the low-power applications up to 40 µW with a gold-plating thicker than 2 µm. For switching higher ratings we use AgSnO₂ or AgCdO contacts (RS 31).




Protective circuits of the contacts

Switching sparks may occur when switching inductive or capacitive loads that affect the operational life of the relay.

The following protective circuits offer the possibility of reducing contact wear:


Diode:



Advantage: can be used for all ratings, low overvoltage, minimum space requirements, economic

Disadvantage: very long drop-out delay


Diode and Z-diode:



Advantage: low overvoltage (determined by Z-diode), low drop-out delay

Disadvantage: not usable for high power ratings


RC combination:



Advantage: low overvoltage, low drop-out delay

Disadvantage: higher current loading on contacts at switch-on, complex and expensive for increased power rating

Varistor:



Advantage: low drop-out delay, economic

Disadvantage: not for all operating voltages and power ratings

U_S Voltage curve
1 Close
2 Open

Switching of small and large power ratings


For automation technology, Weidmüller offers the EGR EGR 7 relay coupler to switch ratings up to 40 μ W under resistive loads. This allows signals to be reliably relayed to control devices.

The switching of higher power ratings in power supply technology is achieved by the RS 31 relay coupler, which guarantees switching capacity up to 3.5 kVA under resistive loads.


Switching times of the relay modules

pick-up delay typ. < 10 ms
drop-out delay typ. < 12 ms


Switching behaviour/load limit curve (depending on type)



Contact life with resistive load



DC-limit with resistive load



Reduction factor with inductive load $\cos j < 1$
Switching no. eff. = switching no. (at $\cos j = 1$) x red. Factor F

Relay couplers with plugged relays

Relay couplers with plugged relays are only conditionally suitable for use in applications subject to heavy vibrations. Relay couplers with soldered relays are to be preferred.


Derating curves

The contact resistance is largely responsible for heat development within the relay. This link is demonstrated by a derating curve as a function of the permissible current subject to the ambient temperature.

We determine the current (curve a) for the following operating conditions:

- continuous operation
- rated input voltage + 10 %
- several relay modules operating under load, mounted horizontally in a row without spacing on mounting rail

A higher load is applicable when modules are mounted with a gap of 20 mm as shown in curve "b". In addition, the function of curve "b" shows the max. values for a switching or short-time operation when assembled horizontally on the mounting rail.



Notes for usage

The characteristic data of the actuation are to be meticulously observed when using UC variants in DC circuitry. UC variants have a higher current input at the moment of switching due to their series circuitry. The internal current limiter of commercially available initiators can result in the operated relay coupler not being switched through.

RC combination

Long supply cables are particularly open to electrical and electro-mechanical influences. These can lead to disturbances of the function or even failure of the relay module. A remedy for this problem is an RC combination in series that filters out unwanted disturbances. RC combinations are available for all customary relay couplers: pluggable (PLUGSERIES) or as terminal block (WDU 12C and DKU 12C).

Protective separation

All equipment required to guarantee "protective separation" must be constructed in such a way that, for example, a mechanical defect cannot reduce the level of insulation. In the case of a relay, this means that if a mechanical defect occurs (bent solder pin, break in winding conductor or broken spring), "protective separation" must be guaranteed.

Relays are specified and tested according to IEC 255 and VDE 0435. Neither standard contains any reference to EN 50 178 (Equipping power installations with electronic equipment) nor is "protective separation" defined. To compound matters the test voltages quoted for the relays are based on different measurement conditions. The test voltages cannot be applied to EN 50 178 or DIN VDE 0106 Part 101. As more and more users employ only equipment that guarantees "protective separation", a lot of manufacturers of relays refer to DIN VDE 0106 and test their products accordingly. Consequently, the quoted values correspond to the requirements for "protective separation".

Standards

The following standards are fulfilled:
EN 50 178

Equipping power installations with electronic equipment

DIN VDE 0106 Part 101

Protection against flow of dangerous currents through the human body; basic requirements for protective separation within electrical equipment.

DIN VDE 0109

Insulation co-ordination within low-voltage system including clearance and creepage distances for assembled PCBs.

DIN VDE 0435

Electrical relays, all-or-nothing relays


Input circuit

Input voltage [V]	Reference voltage at which the relay coupler operates. Typical reference voltages: => 5 V DC, 12, 24, 48, 60, 115, 230 V AC/DC
Input current [mA]	Quotient resulting from input voltage and input resistance. Input resistance => coil resistance + resistance of drive (R, LED, rect. ...)
Rated power consumption [W/VA]	Input voltage x input current AC/DC with tolerance of +/- 10% or +/-15% Typical range for relay coupler: 250 mW > P _v > 1 W 0.4 VA > P _v > 1.2 VA
Pull-in voltage [V]	Smallest input voltage that relay coupler requires in order to respond (T _{amb} = 293 K)
Pick-up current [mA]	Smallest input current required to switch relay from inoperative to operating position (T _{amb} = 293 K)
Pull-in power [W/VA]	Product of pull-in voltage and pick-up current
Drop-out voltage [V]	Voltage level at which relay has definitely released
Self reset current [mA]	Input current level at which relay has definitely released

Output circuit

Output voltage [V]	Max. voltage that can be applied to relay contact
Switching current [A]	Current that can flow for max. of 4 sec. after relay contact has closed
Continuous current [A]	Current that flows continuously after contact has closed
Switching power [W/VA]	Product of output voltage and switching current with resistive, inductive and capacitive load
Min. switching power [mW]	Smallest amount of power that can be switched via contact
Service life	Number of switching operations before contact fails - mechanical => with no electric load - electrical => with resistive or inductive AC/DC load
Pick-up lag [ms]	Length of time from application of energizing voltage until contact closes/opens
Drop-out lag [ms]	Length of time from breaking the energizing circuit until contact closes/opens
Contact bounce time [ms]	Length of time between first and last closing/opening of contact when relay picks up or drops out
Switching frequency [Hz]	Switching operations per sec. with a duty factor of 1 : 2 (t _{on} = t _{off})
Withstand voltage [kV]	Max. test voltage between input and output circuits which does not cause any discharge
Reliable separation	Feature of relay coupler that conform to VDE 0160 and VDE 0106 Part 101
Electric arc	Current flow between contact surfaces as they open, caused by ionization
Contact wear	Switching inductive loads leads to considerable changes in the composition of the materials used. The results are: => formation of pits or peaks on the surface of contacts => failure due to interlocking of contacts
Spark absorption	Limitation of transient overvoltages by connecting supplementary circuit across inductive loads => RC combinations => Z-diodes/suppressor diodes => varistors
Reduction factor	Factor by which service life is reduced when switching inductive loads

Types of Housings for Relay Coupler



Component housing EG

Weidmüller coupling modules are enclosed in housings appropriate for industrial applications. The housings are suitable for fitting onto mounting rails TS 32, TS 35 x 7.5 or TS 35 x 15 in accordance with European standards EN 50 035 and EN 50 022.

Weidmüller component housings **EG 1** and **EG 2** are 18 mm wide.

The fully enclosed EG housings are equipped with clamping yoke screw connections or push-on connections to connect conductors. Conductors with the following cross-sections can be connected: solid core: 0.5...4 mm² or flexible: 0.5...2.5 mm².

The component housing **EG 7** has a special status. It has been specifically designed to accommodate 10-mm slim relays and optocouplers.

EG 7 relay couplers can be optionally mounted onto TS 32 or TS 35 rails.

The RST EG 7 locking socket is also available for use with the pluggable relays couplers.

The enclosed EG 7 housing are equipped with clamping yoke screw connections. The following conductor cross-sections can be connected: NO/NC: 0.5...1.5 mm² Changeover (RST): 0.5...2.5 mm².



Component housing WAVEBOX

It is important to provide modern electronics components with housings suitable for the function. Setting and operating functions must be guaranteed; technical requirements with respect to heat dissipation and EMC properties are to be supported.

An ideal design saves space and wiring costs in the switchgear cabinet. In addition, ergonomics and design are becoming increasingly important for high-quality relay coupler interfaces.

The WAVEBOX fulfils these criteria and is further distinguished by the following:

- Optimal width for any application (12.5 mm, 17.5 mm, **22.5 mm**)
- Large component assembly surface; SMDs mountable on solder side
- No tools required for assembly
- Pluggable PCBs
- Pluggable cross-connection via ZQV 2.5 N
- Hinged, transparent cover
- Screw/plug and socket connector BLZ 5.08
- Optional tension clamp/plug and socket connector BLFZ 5.08
- Marking option with WS tags
- Mount onto TS 35

Connection systems

BLZ screw/plug-in connectors and BLZF tension clamp/plug-in systems for flexible conductors up to 2.5 mm², to guarantee maximum wiring flexibility.

Removing printed circuit boards

Accomplished by depressing the locking clips at the side of the headpiece, and withdrawing the terminal level and PCB from the housing. This is not permitted when the supply is connected.


Cross-connection

The ZQV 2.5 N/2 cross-connector can connect housings of the same family at the base of the housing. The cross-connection can be loaded with a current of up to 8 A. This allows the supply voltage to be cross-connected from one electronics module to another.

The voltage at the cross-connection must not exceed 50 V.

Ventilation vents

Ventilation vents, arranged at an angle, temper and ventilate the lower side of the housings.



Modular system PLUGSERIES/PLUGRELAY

is a new generation of pluggable relay couplers. The core of this system is an innovative relay socket **PXS** or **PXZ**. Weidmüller has combined the functionality and experience from its relay and terminal block business in this product.

The PLUGRELAY is the ideal connection technology between the relay and the application.


Modular system principle

The PLUGSERIES is particularly service friendly.

Commercially available relays are plugged; retainer and release clips ensure stability, LED indicators with free-wheeling diodes can be easily plugged.

- Relays can be easily plugged
 - suitable for small electric circuits standard design and BGD
- Independent connection technology: screw or tension clamp rated cross-section 0.5...2.5 mm²
- Robust design of retainer / release clip
- One or two changeover contacts Max. current switched 16 A
- Low wiring costs thanks to ZQV 25N cross-connectors (pluggable)
- Service-friendly modular system
 - relay socket, LED indicators, retainer clips and relays
 - mount onto TS 35
 - marking options with WS markers on retainer clips
- Pluggable LED indicator with free-wheeling diode

Types of Housings for Relay Coupler



Weidmüller RS locking socket

Locking sockets with relays RS 30, 31, 32 are either 11.2 mm or 25 mm wide depending on version. The open profile makes the use of pluggable relays possible.

Modules mounted onto the locking sockets are provided with clamping yoke screw connections or push-on connectors for wiring conductors.

Conductors with the following cross-sections can be connected:


solid core: 0.5...4 mm²
flexible: 0.5...2.5 mm².

Locking sockets with multiple interfaces

RSM multiple interfaces can be optionally assembled with 4, 8 or 16 relays. To save wiring costs on the input side, variants are offered with joint positive and negative potentials.

The PCB connectors are provided with clamping yoke screw connections for conductors with the following cross-sections:
solid core: 0.5...4 mm² or
flexible: 0.5...2.5 mm².

Some versions of the RSM coupler have a male connector block available for connecting pre-assembled cables on the input side in accordance with IEC 603-1/DIN 41 651.



Minicoupler DK

All DKR mini coupler components fulfil demands for slimmest possible design. The sensational width of only 6 mm is achieved by using state-of-the-art surface mountable components SMDs. 4 and 5 screw-connections are offered for 0.5...4 mm² conductor cross-sections. The mini couplers offer a wide spectrum for coupling digital sensor/actuator signals between automation devices and the field process. DKR relay couplers can receive and standardise signals with varying voltages from the field.

Miniconditioner MCZ

The 6-mm MCZ housing is one of the slimmest of its kind. It has the following distinguishing features:

- Z-spring reduces mounting costs
- integrated cross-connection options in the input and outputs minimise wiring costs

MCZR miniconditioner (relay coupler) are available with 4 or 5 Z-spring connections. The clampable conductor cross-section is 0.5...1.5 mm².



MICROSERIES

The relay coupler and optocoupler variants from the **MICROSERIES** are used in applications in industrial automation to isolate and couple digital input and output signals. Their compact design means that they are particularly suitable for use on sub-distribution boards as well as in switchgear cabinets where they help the user to make optimum use of valuable switching space. With its compact design, the **MICROSERIES** elegantly combines the functionality of the classic coupling level and the terminal level.

- 6.1-mm mounting width
- Pluggable cross-connections of four potentials in the inputs and outputs
- Proven cross-connection system ZQV 4 N
- Wide input voltage spectrum from 5 ... 230 V
- LED-indicator reverse-connect protection free-wheeling diode
- Housing material: WEMID
Flammability class: V0 in accordance with UL 94
- Innovative retaining and release system
- Marking surfaces for fitting standard WS 12/6 markers


CE-marking

Weidmüller relay couplers are marked with the CE symbol and comply with the requirements of EN 50 081 Part 1 and EN 50 082 Part 2. They can therefore be used for both industrial as well as for applications in residential, commercial and light industry.

Appropriate ESD measures should be taken during installation. If supply cables are particularly long, overvoltage protection should be provided to prevent interference from electrical disturbance in the atmosphere.

Relay Coupler

Electromechanical switching

Output										
24 V 										
				2 x		3 x		2 x	4 x	8 x
										16 x
Housing										
EG	● 0133660000 Page 72	● 0133560000 Page 72						● 0160260000 Page 73		
	● 0536260000 Page 72	● 0542660000 Page 72						● 0123060000 Page 73		
WAVESERIES WRS			● 8275350000 ● 8286280000 ● 8416210000 ● 8418220000 ● 8418230000 Page 74	● 8418240000 ● 8418250000 Page 76	● 8418270000 ● 8418280000 Page 77	● 8418330000 Page 79	● 8418300000 ● 8418310000 ● 8418320000 Page 78			
EG 7*	● 8216520000 ● 8147120000 ● 8092340000 Page 80	● 8216530000 ● 8147140000 ● 8092350000 Page 80	● 8216570000 ● 8216560000 ● 8216580000 Page 80							
PLUGSERIES PRS / PRZ			● 8530621001 ● 8530691001 ● 8536530000 ● 8536650000 Page 82				● 8530631001 ● 8530701001 ● 8536560000 ● 8536680000 Page 82			
RS 30	● 1101661001 ● 1101611001 ● 1101621001 ● 1101761001 ● 1101711001 ● 1101721001 Page 91	● 1100961001 ● 1100911001 ● 1100921001 ● 1101061001 ● 1101011001 ● 1101021001 Page 91	● 1181511001 ● 1181521001 ● 1100260000 ● 1100210000 ● 1100220000 ● 1100360000 Page 91							
RS 31			● 1128361001 ● 1128331001 ● 1128311001 Page 92							
RS 32							● 9406121001 ● 9406221001 Page 94			
RSM							● 1173461001 ● 1113361001 ● 1113461001 ● 1112361001 ● 1112761001 Page 97	● 1113161001 ● 1100061001 ● 1113561001 ● 1113661001 ● 1107761001 ● 1112661001 ● 1113861001 ● 1173561001 Page 97	● 1113261001 ● 1100161001 ● 1113761001 ● 8018221001 ● 1107861001 ● 1113061001 ● 1173661001 Page 97	
DKR 32	● 8016620000 ● 8008110000 Page 70									
DKR 35	● 8016610000 ● 8008170000 Page 70 ● 8215620000 Page 71		● 8181980000 ● 8181970000 Page 71							
DKR 35/32			● 9454910000 Page 71							
MCZ R			● 8365980000 ● 8442960000 ● 8390590000 Page 68							
MICROSERIES MRS / MRZ			● 8533640000 ● 8533660000 ● 8556050000 ● 8556120000 Page 87							

* Approval by Germanischer Lloyd

Reliable
separation



● 24 V dc
● 24 V_{uc}/ac

Relay Coupler

Electromechanical switching

Output

48 V



Housing

EG	● 0662660000 Page 72	● 0662460000 Page 72					● 0160360000 ● 0123260000 Page 73			
WAVESERIES WRS			● 8286280000 Page 74	● 8418250000 Page 76	● 8418280000 Page 77		● 8418310000 Page 78			
EG 7*	● 8092370000 Page 81	● 8092380000 Page 81	● 8216590000 Page 81							
RS 30	● 1101861001 ● 1101811001 ● 1101821001 ● 1101961001 ● 1101911001 ● 1101921001 Page 91	● 1101161001 ● 1101111001 ● 1101121001 ● 1101261001 ● 1101211001 ● 1101221001 Page 91	● 1100460000 ● 1100410000 ● 1100420000 ● 1100560000 Page 91							
RS 31			● 1150761001 Page 92							
RS 32							● 9406321001 Page 94 ● 9406421001 ● 1122661001 Page 95			
RSM							● 1114061001 ● 1113961001 ● 1112461001 ● 1173761001 Page 97	● 1114161001 ● 1114261001 Page 97	● 1114361001 ● 1114461001 Page 97	
MICROSERIES MRS / MRZ			● 8556040000 ● 8556110000 Page 87							
115 V										
EG							● 0141360000 ● 0160460000 Page 73			
WAVESERIES WRS			● 8418220000 Page 75	● 8418260000 Page 76	● 8418290000 Page 77					
EG 7*	● 8092430000 Page 81	● 8092440000 Page 81	● 8216610000 Page 81							
PLUGSERIES PRS / PRZ			● 8536510000 ● 8536610000 ● 8530640000 ● 8530790000 Page 82				● 8536520000 ● 8536630000 ● 8530660000 ● 8530720000 Page 82			
RS 30	● 1155161001 ● 1155111001 ● 1155121001 ● 1102161001 ● 1102111001 ● 1102121001 Page 91	● 1155211001 ● 1155261001 ● 1155221001 ● 1101461001 ● 1101411001 ● 1101421001 Page 91								
RS 31			● 1150361001 ● 1150461001 Page 92							
RS 32							● 1122761001 ● 9406621001 Page 95			
RSM							● 1114561001 Page 97	● 1114661001 Page 97	● 1114761001 Page 97	
MCZ R			● 8420880000 ● 8467470000 Page 61							
MICROSERIES MRS / MRZ			● 8556030000 ● 8556100000 Page 87							

* Approval by Germanischer Lloyd

Reliable
separation

● Vdc
● Vuc/ac


Digital signal
processing

Relay Coupler

Electromechanical switching

Output

230 V



Housing

EG	● 0543860000 Page 72	● 0543660000 Page 72					● 0142460000 Page 73		
WAVESERIES WRS			● 8418230000 Page 75	● 8418260000 Page 76	● 8418290000 Page 77	● 8418340000 Page 79	● 8418320000 Page 78		
EG 7*	● 8092460000 Page 81	● 8092470000 Page 81	● 8216620000 Page 81						
PLUGSERIES PRS / PRZ			● 8530671001 Page 82				● 8530681001 Page 82		
RS 30	● 1102261001 Page 91	● 1101561001 Page 91	● 1100860000 Page 91						
RS 31			● 1128461001 Page 93						
RS 32							● 9406721001 Page 95		
RSM							● 1114861001 Page 97	● 1114961001 Page 97	● 1115061001 Page 97
MCZ R			● 8237710000 Page 69						
MICROSERIES MRS / MRZ			● 8556020000 Page 87						
240 V									
RS 30	● 1128561001 Page 91	● 1128661001 Page 91							

* Approval by Germanischer Lloyd

Reliable
separation

● 230 Vuc/ac

Relay Coupler

Electromechanical switching

		Output									
12 V											
Housing											
EG								● 0160160000 Page 73			
WAVESERIES WRS					● 8418240000 Page 76	● 8418270000 Page 77		● 8418300000 Page 78			
EG 7*		● 8092310000 Page 80	● 8092320000 Page 80	● 8216550000 Page 80							
PLUGSERIES PRS / PRZ				● 8536471001 ● 8536571001 Page 82				● 8536501001 ● 8536591001 Page 82			
RS 30		● 1129421001 Page 91	● 1129521001 Page 91	● 1129660000 Page 91							
RS 32								● 9406021001 Page 94			
DKR 35		● 8171100000 Page 70									
MICROSERIES MRS / MRZ				● 8556070000 ● 8556140000 Page 86							

		Output									
4...60 V											
Housing											
WAVESERIES WRS 2, 4...24 V				● 8275320000 Page 74							
WAVESERIES WRS 60 V				● 8418210000 Page 74							
EG 7*, 60 V		● 8092400000 Page 81	● 8092410000 Page 81	● 8216600000 Page 81							
RS 30, 60 V		● 1102061001 ● 1102011001 ● 1102021001 Page 91		● 1100660000 ● 1100610000 ● 1100620000 Page 91				● 9406521001 Page 94			
DKR 32, 5 V		● 8019600000 Page 70									
DKR 35, 5 V		● 8019610000 Page 70									
MCZ R, 60 V				● 8470380000 Page 68							
MICROSERIES MRS / MRZ, 5 V				● 8556080000 ● 8556150000 Page 86							
MICROSERIES MRS / MRZ, 60 V				● 8556060000 ● 8556130000 Page 87							

* Approval by Germanischer Lloyd

Reliable
separation

● Vdc
● Vuc/ac

Digital signal
processing

Relay Couplers in Component Housings

Miniconditioners MCZ R

MCZ R 24 Vdc


MCZ R 24 Vdc/Au

MCZ R 24 Vac/dc


MCZ R 60 Vdc



Limit diagram







Derating curve



Schematic circuit diagram

This module can be used as a universal interface between the controller and actuator for switching medium-sized loads.

- Reduces installation and commissioning times by use of the proven Z-spring connection technology
- Pluggable cross-connections in input and output minimise wiring costs
- 6-mm width



Ordering data	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.
for TS 35	MCZ R 24 Vdc	8365980000	MCZ R 24 Vdc/Au	8442960000	MCZ R 24 Vac/dc	8390590000	MCZ R 60 Vdc	8470380000
Technical data								
Input								
Input voltage	24 Vdc $\pm 20\%$ (19.2...28.8 V)		24 Vdc $\pm 20\%$ (19.2...28.8 V)		24 Vac/dc $\pm 10\%$ (21.6...26.4 V)		60 Vdc $\pm 20\%$ (48...72 V)	
Input current at U_N	6.3 mA $\pm 10\%$ (5.7...6.9 mA)		6.3 mA $\pm 10\%$ (5.7...6.9 mA)		ac: 10.8 mA $\pm 15\%$ (9.2...12.4 mA) dc: 6.1 mA $\pm 15\%$ (5.2...7.1 mA)		3 mA $\pm 20\%$ (12.4...3.6 mA)	
Max. input power	156 mW $\pm 10\%$		156 mW $\pm 10\%$		ac: 160 mVA $\pm 10\%$ dc: 151 mW $\pm 10\%$		180 mW $\pm 45\%$	
Making threshold	12 V...19 V		12 V...19 V		ac: ca. 17 V / dc: ca. 19 V		ca. 38 V	
Cut-out threshold	4 V...5.5 V		4 V...5.5 V		ac: ca. 7 V / dc: ca. 4 V		ca. 14 V	
Reaction time at U_N (typ.)	4.5 ms		4.5 ms		5 ms		4.5 ms	
Release at U_N (typ.)	10 ms		10 ms		30 ms		10 ms	
Capacity working resistance to reduction at dissipated energy	no		no		no		no	
Functionality	operating indication reverse polarity protect. diode free wheel diode		operating indication reverse polarity protect. diode free wheel diode		operating indication bridge rectifier		operating indication reverse polarity protect. diode free wheel diode	
Cross-connection on pin	2, 3, 4		2, 3, 4		2, 3, 4		2, 3, 4	
Output								
Switching voltage	1 changeo. cont. (AgSnO ₂) max. 300 Vdc / 400 Vac		1 changeo. cont. (5 μ Au) max. 300 Vdc / 400 Vac		1 changeo. cont. (AgSnO ₂) max. 300 Vdc / 400 Vac		1 changeo. cont. (AgSnO ₂) max. 300 Vdc / 400 Vac	
ac: continuous current/switching power (see derating diagram)	max. 6 A / max. 1500 VA		max. 6 A* / max. 1500 VA		max. 6 A / max. 1500 VA		max. 6 A / max. 1500 VA	
Min. switching current	100 mA (at U = 10 V)		1) 0.1 mA		100 mA (at U = 10 V)		100 mA (at U = 10 V)	
Switch-on current	max. 6 A		max. 6 A*		max. 6 A		max. 6 A	
dc: Continuous current/switching power	see limit diagram		see limit diagram		see limit diagram		see limit diagram	
Mechanical service life	20 x 10 ⁶ switching operations		20 x 10 ⁶ switching operations		20 x 10 ⁶ switching operations		20 x 10 ⁶ switching operations	
Max. switching frequency at nominal load	0.1 Hz		0.1 Hz		0.1 Hz		0.1 Hz	
Insulation coordination acc. to EN 50178								
Rated voltage	300 V		300 V		300 V		300 V	
Rated impulse voltage	4 kV		4 kV		4 kV		4 kV	
Overvoltage category	III		III		III		III	
Pollution severity	2		2		2		2	
Clearances and creepage distances	≥ 5.5 mm		≥ 5.5 mm		≥ 5.5 mm		≥ 5.5 mm	
Insulation coord.- and voltage proof, input/output mounting rail	4 kV _{eff} / 1 min		4 kV _{eff} / 1 min		4 kV _{eff} / 1 min		4 kV _{eff} / 1 min	
Ambient temperature	-25 °C...+50 °C		-25 °C...+50 °C		-25 °C...+50 °C		-25 °C...+50 °C	
Storage temperature	-40 °C...+60 °C		-40 °C...+60 °C		-40 °C...+60 °C		-40 °C...+60 °C	
Conductor	AWG 22...12		AWG 22...12		AWG 22...12		AWG 22...12	
Conductor cross-section	1.5 mm ²		1.5 mm ²		1.5 mm ²		1.5 mm ²	
Approvals	CE, UL, CSA, GL		CE, UL, CSA, GL		CE, UL, CSA, GL		CE, UL, CSA	
Overall width	6 mm		6 mm		6 mm		6 mm	
Accessories	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.
End plate	AP MCZ 1.5	8389030000	AP MCZ 1.5	8389030000	AP MCZ 1.5	8389030000	AP MCZ 1.5	8389030000
Further accessories, dimensions and connection data see	Page 305		Page 305		Page 305		Page 305	

¹⁾ depends on load conditions

* the hard-gold plating is resistant for parameters 36 Vdc, 50 mA with 10⁶ cycles


Relay Couplers in Component Housings

MCZ R 110 Vdc

MCZ R 120 Vac



MCZ R 230 Vac

Limit diagram



Derating curve

— rowed without clearances on the mounting rail
- - - rowed with 20 mm spacing



Type	Cat. No.	Type	Cat. No.	Type	Cat. No.
MCZ R 110 Vdc	8467470000	MCZ R 120 Vac	8420880000	MCZ R 230 Vac	8237710000
110 Vdc ±10%		120 Vac -15 %/+10 %		230 Vac ±10%	
2.85 mA ±25%		7 mA ±15 %		9.5 mA ±15 % (8...11mA)	
340 mW ±25%		0.85 VA ±15 % (380 mW ±15 %)		2.1 VA ±15 %	
ca. 68 V / 1.6 mA		ca. 70 V / 4 mA		ca. 115 V / 5 mA	
ca. 19 V / 0.4 mA		ca. 22 V / 1.3 mA		ca. 60 V / 2.5 mA	
4.5 ms		8 ms		8 ms	
10 ms		30 ms		30 ms	
no		yes		no	
operating indication		operating indication		operating indication	
bridge rectifier		bridge rectifier		bridge rectifier	
2, 3, 4		2,3, 4		2,3, 4	
1 changeo. cont. (AgSnO ₂)		1 changeo. cont. (AgSnO ₂)		1 changeo. cont. (AgSnO ₂)	
max. 300 Vdc / 400 Vac		max. 300 Vdc / 400 Vac		max. 300 Vdc / 400 Vac	
max. 6 A / max. 1500 VA		max. 6 mA / max. 1500 VA		max. 6 A / max. 1500 VA	
100 mA (at U = 10 V)		100 mA (at U = 10 V)		100 mA (at U = 10 V)	
max. 6 A		max. 6 A		max. 6 A	
see limit diagram		see limit diagram		see limit diagram	
20 x 10 ⁶ switching operations		20 x 10 ⁶ switching operations		20 x 10 ⁶ switching operations	
0.1 Hz		0.1 Hz		0.1 Hz	
300 V		300 V		300 V	
4 kV		4 kV		4 kV	
III		III		III	
2		2		2	
≥ 5.5 mm		≥ 5.5 mm		≥ 5.5 mm	
4 kV _{eff} / 1 min		4 kV _{eff} / 1 min		4 kV _{eff} / 1 min	
-25 °C...+50 °C		-25 °C...+50 °C		-25 °C...+50 °C	
-40 °C...+60 °C		-40 °C...+60 °C		-40 °C...+60 °C	
AWG 22...12		AWG 22...12		AWG 22...12	
1.5 mm ²		1.5 mm ²		1.5 mm ²	
CE, UL, CSA		CE, UL, CSA		CE, UL, CSA	
6 mm		6 mm		6 mm	
Type	Cat. No.	Type	Cat. No.	Type	Cat. No.
AP MCZ 1.5	8389030000	AP MCZ 1.5	8389030000	AP MCZ 1.5	8389030000
Page 305		Page 305		Page 305	

Relay Couplers in Component Housings Mini coupler DKR

These modules are used for protective separation of input signals and adjustment of signal levels


- Cost-effective solution for adjustment of power and potential
- Low input power
- Screw connection technology
- 6-mm width

DKR 5 Vdc





DKR 12 Vdc

DKR 24 Vac/dc

DKR 24 Vdc




Schematic circuit diagram



Ordering data		Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.
for TS 32	Y	DKR 5 Vdc	8019600000			DKR 24 Vac/dc	8008110000	DKR 24 Vdc	8016620000
for TS 35	W	DKR 5 Vdc	8019610000	DKR 12 Vdc	8171100000	DKR 24 Vac/dc	8016610000	DKR 24 Vdc	8008170000
With combination foot TS 32/TS 35									
Technical data		Input: bottom		Input: bottom		Input: bottom		Input: bottom	
Input voltage		5 Vdc $\pm 5\%$		12 Vdc $\pm 10\%$		24 Vac/dc $\pm 20\%$		24 Vdc $\pm 20\%$	
Input current		12.5 mA		12 mA		11.5 mAac/9 mAac		9.3 mA	
Input current, limited = SPS able									
Input power		65 mW		144 mW		300 mVA/220 mW		225 mW	
Pick-up lag		typ. 0.7...2.5 ms		typ. 0.7...2.5 ms		0.6...4.5 ms ac/0.9...1.3 ms dc		typ. 0.7...2.5 ms	
Turn off delay		typ. 0.2...2.0 ms		typ. 0.2...2.0 ms		12.7...25 ms ac/14.4...16.4 ms dc		typ. 0.2...2.0 ms	
Max. switch-on current		500 mA		500 mA		500 mA		500 mA	
Max. switching capacity		10 W/10 VA		10 W/10 VA		10 W/10 VA		10 W/10 VA	
Max. output voltage		100 V		175 V		170 V		100 V	
Max. output current		500 mA		500 mA		500 mA		500 mA	
Min. output current									
Max. switching frequency		200 Hz		25 Hz		5 Hz		20 Hz	
Contact material		RH/RU		RH/RU		RH/RU		RH/RU	
Contacts		1 normally-open contact		1 normally-open contact		1 normally-open contact		1 normally-open contact	
Service life	mechanical	10 ⁹ switching operations		10 ⁹ switching operations		10 ⁹ switching operations		10 ⁹ switching operations	
	at I _L = 10 mA	5 x 10 ⁸ switching operations		5 x 10 ⁸ switching operations		5 x 10 ⁸ switching operations		5 x 10 ⁸ switching operations	
Insulation coordination acc. to EN 50178									
Rated voltage		150 V		150 V		150 V		150 V	
Rated impulse voltage		1.5 kV		1.5 kV		1.5 kV		1.5 kV	
Overvoltage category		III		III		III		III	
Pollution severity		2		2		2		2	
Clearances and creepage distances		≥ 3 mm		≥ 3 mm		≥ 3 mm		≥ 3 mm	
Operating temperature	without clearance	-25 °C...+40 °C		-25 °C...+40 °C		-25 °C...+40 °C		-25 °C...+40 °C	
	with clearance	-25 °C...+50 °C		-25 °C...+50 °C		-25 °C...+50 °C		-25 °C...+50 °C	
Storage temperature		-40 °C...+60 °C		-40 °C...+60 °C		-40 °C...+60 °C		-40 °C...+60 °C	
Conductor		AWG 22...12		AWG 22...12		AWG 22...12		AWG 22...12	
Conductor cross-section		0.5...4 mm ²		0.5...4 mm ²		0.5...4 mm ²		0.5...4 mm ²	
Overall width		6 mm		6 mm		6 mm		6 mm	
Accessories		Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.
End plate		AP DKT4	0687560000	AP DKT4	0687560000	AP DKT4	0687560000	AP DKT4	0687560000
Further accessories, dimensions and connection data see		Page 305		Page 305		Page 305		Page 305	

Relay Couplers in Component Housings Mini coupler DKR

DKR 24 Vac/dc







DK5R-1U



DKR 24 Vdc



DKR 24 Vac/dc



Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.
DKR 24 Vdc	8215620000	DK5R-1U	9454910000	DKR 24 Vdc	8181980000	DKR 24 Vac/dc	8181970000
Input: top		Input: bottom		Input: bottom		Input: bottom	
24 Vdc ±20 %		24 Vac/dc ±20 %		24 Vdc ±20 %		24 Vac/dc ±20 %	
9.3 mA		9 mAac/7 mAac		11.5 mA		20 mAac/16 mAac	
		max. 240 mA				max. 100 mA	
225 mW		6 ms		384 mW		480 mWac/400 mWdc	
typ. 0.7...2.5 ms		15 ms ac/dc					
typ. 0.2...2.0 ms							
500 mA		4 A		5 A		5 A	
10 W/10 VA		1.5 kVA/140 W		2 kVA/192 W		2 kVA/192 W	
175 Vac/dc		250 Vac/dc		250 Vac/dc		250 Vac/dc	
500 mA		6 A		8 A		8 A	
25 Hz		20 Hz		100 mA		100 mA	
RH/RU		Ag Ni		25 Hz		ac: 5 Hz dc: 25 Hz	
1 normally-open contact		1 changeover contact		AgCdO		1 changeover contact	
10 ⁹ switching operations		2x10 ⁷ switching operations		1 changeover contact		≥10 ⁷ switching operations	
5 x 10 ⁸ switching operations				≥10 ⁷ switching operations		≥3 x 10 ⁶ switching operations	
				≥3 x 10 ⁶ switching operations			
150 V		300 V		300 V		300 V	
1.5 kV		4 kV		6 kV		6 kV	
III		III		IV		IV	
2		2		2		2	
≥3 mm		≥8 mm		≥8 mm		≥8 mm	
-25 °C...+40 °C		-40 °C...+60 °C		-25 °C...+40 °C		-25 °C...+40 °C	
-25 °C...+50 °C		-40 °C...+60 °C		-25 °C...+50 °C		-25 °C...+50 °C	
-40 °C...+60 °C		-40 °C...+60 °C		-40 °C...+60 °C		-40 °C...+60 °C	
AWG 22...12		AWG 22...12		AWG 22...12		AWG 22...12	
0.5...4 mm ²		0.5...4 mm ²		0.5...4 mm ²		0.5...4 mm ²	
6 mm		6 mm		18 mm		18 mm	

Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.
AP DKT4	0687560000	AP DK5	8268870000	AP DKT4	0687560000	AP DKT4	0687560000
Page 305		Page 305		Page 305		Page 305	

Relay Coupler in Component Housings EG 2

with 1 NO or 1 NC

EGR EG 2 24 V

AC/DC voltage



EGR EG 2 24 V

Direct and alternating voltage



EGR EG 2 48 V






EGR EG 2 230 V

AC voltage



Schematic circuit diagram



Ordering data

Type	Cat. No.
NC	0133560000¹⁾
NO	0133660000¹⁾

Type	Cat. No.
NC	0542660000
NO	0536260000

Type	Cat. No.
NC	0662460000
NO	0662660000

Type	Cat. No.
NC	0543660000
NO	0543860000

Rated data

Input voltage

Rated consumption – (W)

Rated consumption ~ (VA)

Drop-out current of the relay** (at 20 °C)






Max. output voltage

Continuous current

Derating curve

a = mounted horizontally on rail without clearance

b = mounted horizontally on rail with clearance x 20 mm



Switch-on current

Max. switching capacity with resistor load

Min. switching capacity/switching current

Bounce times

Switching times, typical

–, pick-up lag

–, turn off delay

Max. switching frequency

Contact material

Service life, mechanical

–, 24 V–, 1 A, resistive load

–, 230 V–, 3 A, resistive load

Status indicator

Storage temperature

Ambient temperature

–, mounted on rail without clearance

–, mounted on rail with clearance ≥ 20 mm

Approvals

Insulation coordination acc. to EN 50178

Overvoltage category

Pollution severity

Accessories, dimensions and connection data see

** Larger values on request

5 A
600 VA/120 W
40 µW
< 2 ms
< 5.3 ms
< 8.3 ms
50 Hz
AgNi, gold-plated
> 10 ⁷ switching operations
> 6 x 10 ⁵ switching operations
> 10 ⁵ switching operations
Green LED
–40 °C...+60 °C
–25 °C...+40 °C
–25 °C...+50 °C
CSA (013366)

5 A
600 VA/120 W
40 µW
< 2 ms
< 8 ms
< 22 ms
30 Hz
AgNi, gold-plated
> 10 ⁷ switching operations
> 6 x 10 ⁵ switching operations
> 10 ⁵ switching operations
Green LED
–40 °C...+60 °C
–25 °C...+40 °C
–25 °C...+50 °C

5 A
600 VA/120 W
40 µW
< 2 ms
< 9 ms
< 12 ms
37 Hz
AgNi, gold-plated
> 10 ⁷ switching operations
> 6 x 10 ⁵ switching operations
> 10 ⁵ switching operations
Green LED
–40 °C...+60 °C
–25 °C...+40 °C
–25 °C...+50 °C

5 A
600 VA/120 W
40 µW
< 2 ms
< 5 ms
< 7 ms
40 Hz
AgNi, gold-plated
> 10 ⁷ switching operations
> 6 x 10 ⁵ switching operations
> 10 ⁵ switching operations
Green LED
–40 °C...+60 °C
–25 °C...+40 °C
–25 °C...+50 °C

III
3
Page 306, Fig. II

III
3
Page 306, Fig. II

III
2
Page 306, Fig. II

III
2
Page 306, Fig. II

¹⁾ no output varistor

Relay Coupler in Component Housings EG 2

with 2.8-mm tab connection

EGR EG 2

DC voltage
2 changeover contacts




EGR EG 2


AC/DC voltage
2 changeover contacts



Schematic circuit diagram




LED is parallel
to coil in 12 V DC
and 24 V DC
versions



Ordering data

Rated data

Input voltage
Rated consumption ~ (W)
Rated consumption ~ (VA)
Drop-out current of the relay** (at 20 °C)
Max. output voltage
Continuous current
Derating curve
a = mounted horizontally on rail without clearance
b = mounted horizontally on rail with clearance x 20 mm



Switch-on current
Max. switching capacity with resistor load
Min. braking capacity/switching current
Bounce times
Switching times, typical
–, pick-up lag
–, turn off delay
Max. switching frequency
Contact material
Service life, mechanical
–, 24 V–, 1 A, resistive load
–, 230 V–, 3 A, resistive load
Status indicator
Storage temperature
Ambient temperature
–, mounted on rail without clearance
–, mounted on rail with clearance ≥ 20 mm

Insulation coordination acc. to EN 50178

Overvoltage category	III
Pollution severity	2
Accessories, dimensions and connection data see	Page 306, Fig. III

** Larger values on request


Type	Cat. No.
EGR 2 RT (12 V~)	0160160000
EGR 2 RT (24 V~)	0160260000

Type	Cat. No.
EGR 2 RT (48 V~)	0160360000
EGR 2 RT (115 V~)	0160460000


Type	Cat. No.
EGR 2 RT (24 V0)	0123060000
EGR 2 RT (48 V0)	0123260000

Type	Cat. No.
EGR 2 RT (115 V0)	0141360000
EGR 2 RT (230 V0)	0142460000

Type	Cat. No.
EGR 2 RT (12 V~)	0160160000
EGR 2 RT (24 V~)	0160260000



Type	Cat. No.
EGR 2 RT (24 V0)	0123060000
EGR 2 RT (48 V0)	0123260000



Type	Cat. No.
EGR 2 RT (115 V0)	0141360000
EGR 2 RT (230 V0)	0142460000

014246	
15 A/200 ms	15 A/200 ms
1100 VA/144 W	1100 VA/144 W
5 A	5 A
4 ms	4 ms
23 ms	17 ms
18 ms	13 ms
25 ms	17 ms
19 ms	18 ms
19 Hz	24 Hz
21 Hz	22 Hz
Ag, gold-flashed	Ag, gold-flashed
30 x 10 ⁶	30 x 10 ⁶
10 ⁵ (1100 VA, cos φ = 1)	10 ⁵ (1100 VA, cos φ = 1)

Red LED	Red LED
–40 °C...+85 °C	–40 °C...+85 °C
–25 °C...+40 °C	–25 °C...+40 °C

Overvoltage category	III
Pollution severity	2
Accessories, dimensions and connection data see	Page 306, Fig. III

** Larger values on request

WAVESERIES Relay Coupler in Component Housings

With 1 changeover contact

Relay couplers in the WAVEBOX

- Independent connection technology
 - pluggable connection unit
 - screw or tension clamp technology
- Fast commissioning and after-sales-service service
 - pluggable PCBs
- Save wiring tasks
 - cross-connections possible at input and output

WRS 1 2.4-24 VDC



WRS 1 24 VDC






WRS 1 24/48 VUC



WRS 1 24/60 VUC



Schematic circuit diagram




Ordering data	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.
Screw connection	WRS 1 2.4-24 Vdc	8275320000	WRS 1 24 Vdc	8275350000	WRS 1 24/48 Vuc	8286280000	WRS 1 24/60 Vuc	8418210000
Tension clamp connection	WRZ 1	8430170000	WRZ 1	8430180000	WRZ 1	8430190000	WRZ 1	8430200000
Input								
Input voltage	2.4...24 Vdc +10 %		24 Vdc±10 %		24 Vuc±10 % / 48 Vuc±10%		24 Vuc±10% / 60 Vuc±10%	
Input current	4.6 mA _{dc} ±15% at U _e 12 V		9 mA _{dc} ±15%		14 mA _{uc} ±15% at U _e 24 V		11 mA _{ac} ±15% at U _e =60 V	
					14 mA _{uc} ±15% at U _e 48V		10 mA _{dc} ±15% at U _e =60 V	
							10.2 mA _{ac} ±15% at U _e =24 V	
							9 mA _{dc} ±15% at U _e =24 V	
Input power	6 mW ±15% at U _e 2.4 V		220 mW±15%		0.5 VA (W)±15% at U _e =48V		0.7 VA ±15% at U _e =60 V	
					0.35 VA (W)±15% at U _e =24V		0.34 VA±15% at U _e =24 V	
							0.6 W ±15% at U _e =60 V	
							0.22 W±15% at U _e =24 V	
Output								
Switching voltage	max. 150 Vdc /250 Vac		max. 150 Vdc /250 Vac		max. 150 Vdc /250 Vac		max. 150 Vdc/250 Vac	
Continuous current AC / Switching power AC	max. 5 A /max. 1250 VA*		max. 5 A /max. 1250 VA*		max. 5A /max. 1250 VA*		max. 5 A/max. 1250 VA*	
Switch-on current	max. 10 A		max. 10 A		max. 10 A		max. 10 A	
Min. switching	100 mA/5 Vdc		100 mA/5 Vdc		100 mA/5Vdc		100 mA/5 Vdc	
Contact material	Ag-alloy		Ag-alloy		Ag-alloy		Ag-alloy	
Contact resistance (when new)	max. 30 mΩ/max. 100 mΩ at 1 A/6 Vdc		max. 30 mΩ/max. 100 mΩ at 1 A/6 Vdc		max. 30 mΩ/max. 100 mΩ at 1 A/6 Vdc		max. 30 mΩ/max. 100 mΩ at 1 A / 6 Vdc	
Pick-up delay at nominal voltage	typ. 7 ms (NO) / 4.5 ms (NC)		typ. 7 ms (NO) / 4.5 ms (NC)		typ. 7 ms (NO) / 4.5 ms (NC)		typ. 5.4 ms (NO) / 4.2 ms (NC)	
Turn off delay	typ. 6.3 ms (NO) / 5.5 ms (NC)		typ. 6.3 ms (NO) / 5.5 ms (NC)		typ. 6.3 ms (NO) / 5.5 ms (NC)		typ. 4.4 ms (NO) / 5.4 ms (NC)	
Mechanical service life	20 x 10 ⁶ switching operations		20 x 10 ⁶ switching operations		20 x 10 ⁶ switching operations		20 x 10 ⁶ switching operations	
Electrical service life	150 x 10 ³ switching operations		150 x 10 ³ switching operations		1.5 x 10 ⁵ switching operations		150 x 10 ³ switching operations	
Max. switching frequency at nominal voltage	0.1 Hz		0.1 Hz		0.1 Hz		0.1 Hz	
Ambient temperature	-25 °C...+50 °C		-25 °C...+50 °C		-25 °C...+50 °C		-25 °C...+50 °C	
Storage temperature	-40 °C...+60 °C		-40 °C...+60 °C		-40 °C...+60 °C		-40 °C...+60 °C	
Approvals	UL/CSA		UL/CSA		UL/CSA		UL/CSA	
Insulation coordination acc. to EN 50178								
Rated voltage	300 V		300 V		300 V		300 V	
Rated impulse voltage	4 kV (1.2/50 μ)		4 kV (1.2/50 μ)		4 kV (1.2/50 μ)		4 kV (1.2/50 μ)	
Overvoltage category	III		III		III		III	
Pollution severity	2		2		2		2	
Implemented clearance and creepage path	≥ 5.5 mm		≥ 5.5 mm		≥ 5.5 mm		≥ 5.5 mm	
Insulation and voltage strength								
Insulation and voltage strength of entire circuit to mounting rail	4 kV _{eff} 1 min		4 kV _{eff} 1 min		4 kV _{eff} 1 min		4 kV _{eff} 1 min	
Testing								
Input/output high voltage test	4 kV _{eff} 1 s		4 kV _{eff} 1 s		4 kV _{eff} 1 s		4 kV _{eff} 1 s	
Accessories, dimensions and connection data see	Page 298 + 308		Page 298 + 308		Page 298 + 308		Page 298 + 308	

* at ambient temperature 20°C

WAVESERIES Relay Coupler in Component Housings

WRS 1 24/115 VUC WRS 1 24 VUC 230 VAC




Type	Cat. No.	Type	Cat. No.
WRS 1 24/115 Vuc	8418220000	WRS 1 24 Vuc/230 Vac	8418230000
WRZ 1	8430210000	WRZ 1	8430220000

24 Vuc±10% / 115 Vuc±10%	24 Vuc±10% / 230 Vac±10%
11 mAac±15% at Ue=115 V	15 mAac±15% at Ue=230 V
10.5mAac±15% at Ue=115 V	14 mAac±15% at Ue=24 V
10.2 mAac±15% at Ue=24 V	13 mAac±15% at Ue=24 V
9 mAac±15% at Ue=24 V	
1.3 VA ±15% at Ue=115 V	3.5 VA ±15% at Ue=230 V
0.34 VA±15% at Ue=24 V	0.34 VA±15% at Ue=24 V
1.2 W ±15% at Ue=115 V	0.32 W±15% at Ue=24 V
0.22 W±15% at Ue=24 V	


max. 150 Vdc/250 Vac	max. 150 Vdc/250 Vac
max. 5 A/max. 1250 VA*	max. 5 A/max. 1250 VA*
max. 10 A	max. 10 A
100 mA/5 Vdc	100 mA/5 Vdc
Ag-alloy	Ag-alloy
max. 30 mΩ/max. 100 mΩ	max. 30 mΩ/max. 100 mΩ
at 1 A / 6 Vdc	at 1 A / 6 Vdc
typ. 5.4 ms (NO) /	typ. 5.4 ms (NO) /
4.2 ms (NC)	4.2 ms (NC)
typ. 4.4 ms (NO) /	typ. 4.4 ms (NO) /
5.4 ms (NC)	5.4 ms (NC)
20 x 10 ⁶ switching operations	20 x 10 ⁶ switching operations
150 x 10 ³ switching operations	150 x 10 ³ switching operations
0.1 Hz	0.1 Hz
-25 °C...+50 °C	-25 °C...+50 °C
-40 °C...+60 °C	-40 °C...+60 °C
UL/CSA	UL/CSA

300 V	300 V
4 kV (1.2/50 μ)	4 kV (1.2/50 μ)
III	III
2	2
≥ 5.5 mm	≥ 5.5 mm
4 kV _{eff} 1 min	4 kV _{eff} 1 min


4 kV _{eff} 1 s	4 kV _{eff} 1 s
Page 298 + 308	Page 298 + 308




WRS 1 2.4-24 VDC • 8275320000




WRS 1 24/48 VUC • 8286280000



WRS 1 24/60 VUC • 8418210000




WRS 1 24/115 VUC • 8418220000




WRS 1 24 VUC/230 VAC • 8418230000

WAVESERIES Relay Coupler in Component Housings


with 2 NO contacts



WRS 2 12/24 VDC • 8418240000



WRS 2 24/48 VUC • 8418250000



WRS 2 115 VUC/ 230 VAC • 8418260000

Ordering data

Screw connection

Tension clamp connection

Input

Input voltage

Input current

Input power

Output

Switching voltage

Continuous current AC / Switching power AC

Switch-on current

Min. switching

Contact material

Contact resistance (when new)

Pick-up delay at nominal voltage

Turn off delay

Mechanical service life

Electrical service life

Max. switching frequency at nominal voltage

Ambient temperature

Storage temperature

Approvals

Insulation coordination acc. to EN 50178

Rated voltage

Rated impulse voltage

Overtoltage category

Pollution severity

Implemented clearance and creepage path

Insulation and voltage strength

Insulation and voltage strength of entire circuit to mounting rail

Testing

Input/output high voltage test


Accessories, dimensions and connection data see

* at ambient temperature 20°C

WRS 2 12/24 VDC



Schematic circuit diagram



Type Cat. No.

WRS 2 12/24 Vdc

8418240000

WRZ 2 8430230000

12 Vdc±10 % / 24 Vdc±10 %
21 mAac±15% at Ue=24 V
20 mAac±15%bei Ue=12 V

0.5 W±15% at Ue=24 V
0.24 W±15% at Ue=12 V

max. 250 Vdc / 250 Vac
(UL → 13300/12300)

max. 5 A / max. 1250 VA*

max. 8 A

100 mA / 5 Vdc

AgSnO₂

max. 30 mΩ/max. 100 mΩ

at 1 A/6 Vdc

typ. 5 ms

typ. 6.3 ms (NO) /

5.5 ms (NC)

50 x 10⁶ switching operations

1 x 10⁵ switching operations

0.1 Hz

-25 °C...+50 °C

-40 °C...+60 °C

UL/CSA

300 V

4 kV (1.2/50 μ)

III

2

≥ 8 mm

4 kVeff 1 min


4 kVeff 1 s

Page 298 + 308

WRS 2 24/48 VUC



Schematic circuit diagram



Type Cat. No.

WRS 2 24/48 Vuc

8418250000

WRZ 2 8430240000

24 Vuc±10 % / 48 Vuc±10 %
10 mAac±15% at Ue=48 V
11.5 mAac±15% at Ue=24 V
8.5 mAac±15% at Ue=48 V
7.2 mAac±15% at Ue=24 V

0.48 VA±15% at Ue=48 V
0.21 VA±15% at Ue=24 V
0.4 W±15% at Ue=48 V
0.17 W±15% at Ue=24 V

max. 250 Vdc / 250 Vac
(UL → 13300/12300)

max. 5 A / max. 1250 VA*

max. 8 A

100 mA / 5 Vdc

AgSnO₂

max. 30 mΩ/max. 100 mΩ

at 1 A/6 Vdc

typ. 5 ms

50 x 10⁶ switching operations

1 x 10⁵ switching operations

0.1 Hz

-25 °C...+50 °C

-40 °C...+60 °C

UL/CSA

300 V

4 kV (1.2/50 μ)

III

2

≥ 8 mm

4 kVeff 1 min


4 kVeff 1 s

Page 298 + 308

WRS 2 115 VUC/ 230 VAC



Schematic circuit diagram



Type Cat. No.

WRS 2 115 Vuc/230 Vac

8418260000

WRZ 2 8430250000

115 Vuc±10%/ 230 Vac±10 %
11 mAac±15% at Ue=230 V
8.5 mAac±15% at Ue=115 V
8 mAac±15% at Ue=115 V

2.5 VA±15% at Ue=230 V
1 VA±15% at Ue=115 V
0.9 W±15% at Ue=115 V

max. 250 Vdc / 250 Vac
(UL → 13300/12300)

max. 5 A / max. 1250 VA*

max. 8 A

100 mA / 5 Vdc

AgSnO₂

max. 30 mΩ/max. 100 mΩ

at 1 A/6 Vdc

50 x 10⁶ switching operations

1 x 10⁵ switching operations

0.1 Hz

-25 °C...+50 °C

-40 °C...+60 °C

UL/CSA (nur 115 Vuc)

300 V

4 kV (1.2/50 μ)

III

2

≥ 8 mm


4 kVeff 1 min

4 kVeff 1 s


Page 298 + 308

WAVESERIES Relay Coupler in Component Housings


with 1NC / 1 NO



WRS 2 12/24 VDC • 8418270000



WRS 2 24/48 VUC • 8418280000



WRS 2 115 VUC/230 VAC • 8418290000

Ordering data

Screw connection

Tension clamp connection

Input

Input voltage

Input current

Input power

Output

Switching voltage

Continuous current AC / Switching power AC

Switch-on current

Min. switching

Contact material

Contact resistance (when new)

Pick-up delay at nominal voltage

Turn off delay

Mechanical service life

Electrical service life

Max. switching frequency at nominal voltage

Ambient temperature

Storage temperature

Approvals

Insulation coordination acc. to EN 50178

Rated voltage

Rated impulse voltage

Overvoltage category

Pollution severity

Implemented clearance and creepage path

Insulation and voltage strength

Insulation and voltage strength of entire circuit to mounting rail

Testing

Input/output high voltage test


Accessories, dimensions and connection data see

* at ambient temperature 20 °C

WRS 2 12/24 VDC



Schematic circuit diagram



Type	Cat. No.
WRS 2 12/24 Vdc	8418270000
WRZ 2	8430260000

12 Vdc±10% / 24 Vdc±10%
19.7 mAcd±15% at Ue=12 V
20.5 mAcd±15% at Ue=24 V

0.5 W±15% at Ue=24 V
0.24 W±15% at Ue=12 V

max. 250 Vdc/250 Vac
max. 5 A/max. 1250 VA*
max. 8 A
100 mA/5 V
AgSnO₂
max. 30 mΩ/max. 100 mΩ
at 1 A/6 Vdc
typ. 5ms

50 x 10⁶ switching operations
1 x 10⁵ switching operations
0.1 Hz
-25 °C...+50 °C
-40 °C...+60 °C
UL/CSA

300 V

4 kV (1.2/50 μ)

III

2


≥ 8 mm

4 kVeff 1 min

4 kVeff 1 s

Page 298 + 308

WRS 2 24/48 VUC



Type	Cat. No.
WRS 2 24/48 Vuc	8418280000
WRZ 2	8430270000

24 Vuc±10% / 48 Vuc±10%
10 mAcd±15% at Ue=48 V
11.5 mAcd±15% at Ue=24 V
8.5 mAcd±15% at Ue=48 V
7.2 mAcd±15% bei Ue=24 V
0.48 VA±15% at Ue=48 V
0.21 VA±15% at Ue=24 V
0.4 W±15% at Ue=48 V
0.17 W±15% at Ue=24 V

max. 250 Vdc/250 Vac
max. 5 A/max. 1250 VA*
max. 8 A
100 mA/5 V
AgSnO₂
max. 30 mΩ/max. 100 mΩ
at 1 A/6 Vdc

50 x 10⁶ switching operations
1 x 10⁵ switching operations
0.1 Hz
-25 °C...+50 °C
-40 °C...+60 °C
UL/CSA

300 V

4 kV (1.2/50 μ)

III

2


≥ 8 mm

4 kVeff 1 min

4 kVeff 1 s

Page 298 + 308

WRS 2 115 VUC/230 VAC



Type	Cat. No.
WRS 2 115 Vuc/230 Vac	8418290000
WRZ 2	8430280000

115 Vuc±10% / 230 Vac±10%
11 mAcd±15% at Ue=230 V
10 mAcd±15% at Ue=115 V
8 mAcd±15% at Ue=115 V

2.5 VA±15% at Ue=230 V
1 VA±15% at Ue=115 V
0.9 W±15% at Ue=115 V

max. 250 Vdc/250 Vac
max. 5 A/max. 1250 VA*
max. 8 A
100 mA/5 V
AgSnO₂
max. 30 mΩ/max. 100 mΩ
at 1 A/6 Vdc

50 x 10⁶ switching operations
1 x 10⁵ switching operations
0.1 Hz
-25 °C...+50 °C
-40 °C...+60 °C
UL/CSA (nur 115 Vuc)

300 V

4 kV (1.2/50 μ)

III

2

≥ 8 mm


4 kVeff 1 min

4 kVeff 1 s


Page 298 + 308

WAVESERIES Relay Coupler in Component Housings


with 2 changeover contacts



WRS 2 12/24 VDC • 8418300000



WRS 2 24/48 VUC • 8418310000



WRS 2 24 VUC/ 230 VAC • 8418320000

Ordering data

Screw connection

Tension clamp connection

Input

Input voltage

Input current

Input power

Output

Switching voltage

Continuous current AC / Switching power AC

Switch-on current

Min. switching

Contact material

Contact resistance (when new)

Pick-up delay at nominal voltage

Turn off delay

Mechanical service life

Electrical service life

Max. switching frequency at nominal voltage

Ambient temperature

Storage temperature

Approvals

Insulation coordination acc. to EN 50178

Rated voltage

Rated impulse voltage

Overvoltage category

Pollution severity

Implemented clearance and creepage path

Insulation and voltage strength

Insulation and voltage strength of entire circuit to mounting rail

Testing

Input/output high voltage test


Accessories, dimensions and connection data see

* at ambient temperature 20°C

WRS 2 12/24 VDC




Schematic circuit diagram



WRS 2 24/48 VUC




Schematic circuit diagram



WRS 2 24 VUC/ 230 VAC



Schematic circuit diagram



Type	Cat. No.
WRS 2 12/24 Vdc	8418300000
WRZ 2	8430290000

Type	Cat. No.
WRS 2 24/48 Vuc	8418310000
WRZ 2	8430300000

Type	Cat. No.
WRS 2 24 VUC/230 Vac	8418320000
WRZ 2	8430310000

12 Vdc±10% /24 Vdc±10 %
21 mAac±15% at Ue=12 V
22 mAac±15% at Ue=24 V

0.26 W±15% at Ue=12 V
0.53 W±15% at Ue=24 V

max. 150 Vdc /250 Vac
max. 5 A/max. 1250 VA*
max. 10 A
100 mA/5 Vdc
Ag-alloy
max. 30 mΩ / max. 100 mΩ
at 1 A / 6 Vdc
typ. 6.5 ms (NO) /
4.5 ms (NC)
typ. 8 ms (NO) /
11 ms (NC)
20 x 10 ⁶ switching operations
1.5 x 10 ⁵ switching operations
0.1 Hz
-25 °C...+50 °C
-40 °C...+60 °C
UL/CSA

24 Vuc±10% /48 Vuc±10 %
14 mAac±15% at Ue=48 V
14 mAac±15% at Ue=24 V

0.7 VA(W)±15% at Ue=48 V
0.35 VA(W)±15% at Ue=24 V

max. 150 Vdc /250 Vac
max. 5 A/max. 1250 VA*
max. 10 A
100 mA/5 Vdc
Ag-alloy
max. 30 mΩ / max. 100 mΩ
at 1 A / 6 Vdc
typ. 6.5 ms (NO) /
4.5 ms (NC)
typ. 8 ms (NO)/
11 ms (NC)
20 x 10 ⁶ switching operations
1.5 x 10 ⁵ switching operations
0.1 Hz
-25 °C...+50 °C
-40 °C...+60 °C
UL/CSA

24 Vuc±10% /230 Vac±10%
15 mAac±15% at Ue=230 V
14 mAac±15% at Ue=24 V

0.35 W±15% at Ue=24 V
3.45 VA ±15% at Ue=230 V

max. 150 Vdc /250 Vac
max. 5 A/max. 1250 VA*
max. 10 A
100 mA / 5 Vdc
Ag-alloy
max. 30 mΩ / max. 100 mΩ
at 1 A / 6 Vdc
typ. 6 ms (NO)/4.2 ms
(NO)/Eingang: 24 Vuc/230 Vac
typ. 4.4 ms (NO)/
5.4 ms (NC)
20 x 10 ⁶ switching operations
150 x 10 ³ switching operations
0.1 Hz
-25 °C...+50 °C
-40 °C...+60 °C


Rated voltage
Rated impulse voltage
Overvoltage category
Pollution severity
Implemented clearance and creepage path

Insulation and voltage strength of entire circuit to mounting rail


4 kVeff 1 min
4 kVeff 1 s
Page 298 + 308

WAVESERIES Relay Coupler in Component Housings

with 3 NO contacts



WRS 2 24 VUC • 8418330000



WRS 2 230 VAC • 8418340000

WRS 2 24 VUC



Schematic circuit diagram



WRS 2 230 VAC



Ordering data	Type	Cat. No.	Type	Cat. No.
Screw connection	WRS 2 24 Vuc	8418330000	WRS 2 230 Vac	8418340000
Tension clamp connection	WRZ 2	8430320000	WRZ 2	8430330000
Input				
Input voltage	3fach 24 Vac ±10 %		3 x 230 Vac ±10 %	
Input current	10.5 mAac ±15 % at U _{nom} (per channel)		10.3 mAac ±15 % at U _{nom} (per channel)	
Input power	0.3 VA ±15 % (per channel) 0.25 W ±15 %		2.4 VA ±15 % (per channel)	
Output				
Switching voltage	max. 250 Vdc /250 Vac		max. 250 Vdc / 250 Vac	
Continuous current AC / Switching power AC	max. 4 A/max. 1500 VA*		max. 4 A/max. 1500 VA*	
Switch-on current	max. 6 A		max. 6 A	
Min. switching	12 V/10 mA		12 V/10 mA	
Contact material	AgSnO ₂		AgSnO ₂	
Contact resistance (when new)	max. 100 mΩ at 1 A/24 Vdc		max. 100 mΩ at 1 A/24 Vdc	
Pick-up delay at nominal voltage	typ. 5 ms		typ. 8 ms	
Turn off delay	typ. 21 ms		typ.11 ms	
Mechanical service life	20 x 10 ⁶ switching operations		20 x 10 ⁶ switching operations	
Electrical service life	1 x 10 ⁶ switching operations		1 x 10 ⁶ switching operations	
Max. switching frequency at nominal voltage	0.1 Hz		0.1 Hz	
Ambient temperature	-25 °C...+50 °C		-25 °C...+50 °C	
Storage temperature	-40 °C...+60 °C		-40 °C...+60 °C	
Approvals	UL/CSA			
Insulation coordination acc. to EN 50178				
Rated voltage	300 V		300 V	
Rated impulse voltage	4 kV (1.2/50 μ)		4 kV (1.2/50 μ)	
Overvoltage category	III		III	
Pollution severity	2		2	
Implemented clearance and creepage path	≥ 5.5 mm		≥ 5.5 mm	
Insulation and voltage strength				
Insulation and voltage strength of entire circuit to mounting rail	4 kVeff 1 min		4 kVeff 1 min	
Testing				
Input/output high voltage test	4 kVeff 1 s		4 kVeff 1 s	
Accessories, dimensions and connection data see	Page 298 + 308		Page 298 + 308	

* at ambient temperature 20°C

Relay Couplers in Components Housings EG 7

- Plugs on to locking socket RS EG 7 with combination foot TS 32, 35
- Overall width: 10 mm
- With combination foot for TS 15, TS 32 or TS 35
- Versions with 12 V, 24 V and 48 V full protective separation in accordance with VDE 0160, Part 101
- All EGR EG 7 and RST EG 7 are approved by Germanischer Lloyd. Approval No. 35962 HH**

EGR EG 7 RST EG 7 RS EG 7

EGR EG 7



RST EG 7






RS EG 7

Schematic circuit diagram

Derating curve

a = mounted horizontally on rail without clearance

b = mounted horizontally on rail, rowed with clearances



Ordering data

Combination foot for TS 15, TS 32, TS 35	1 NO
	1 NC
EGR EG 7 spare relays, without connection unit	
Plug-in relay-coupl., without engagem. socket, 1 changeo. cont.	
Engage.socket f. plug-in relay coupler w. combin.foot TS 32, 35	

Rated data of the coil

Input voltage	12 V0 +15 % -10 %
Rated consumption	320 mW +20 % -10 %
Max. switch-on current	120 mA
Combination foot for drop current	≤ 3 mA
Connection	- NO and NC
	- changeover contacts

Rated data der Contacts

Max. output voltage	250 V
Continuous current	5 A
Max. switch-on current	8 A
Min. switching capacity/switching current	100 mW/10 mA
Bounce times	≤ 1 ms
Contact material ²⁾	AgNi 0.15 gold-flashed
Bounce times	≤ 1 ms
Switching times	
pick up delay	≤ 8 ms
drop-out delay	≤ 6 ms
Service life, mechanical	> 15 x 10 ⁶ switching operations
-, 24 V-, 1.1 A, inductive load	≥ 2 x 10 ⁶ switching operations with free wheel diode
-, 230 V-, 5 A, resistive load	> 2 x 10 ⁵ switching operations
Status indicator	Green LED
Storage temperature	-40 °C...+60 °C
Ambient temperature	-25 °C...+60 °C

Insulation coordination acc. to EN 50178

Safe isolation according to VDE 0106 part 101	DIN VDE 0106
Rated impulse voltage	8 kV
Clearances and creepage distances	≥ 8 mm
Overvoltage category	III
Pollution severity	2

Accessories

Cross-connection comb. 16fold	QB 16/10.16
Accessories, dimensions and connection data see	Page 304

1) Serves only as a spare part for NO and NC

Type	Cat. No.
EGR EG7	8092310000
EGR EG7	8092320000
EGR EG7	8092330000¹⁾
RST EG7	8216550000
RS EG7	8193830000

12 V0 +15 % -10 %
320 mW +20 % -10 %
120 mA
≤ 3 mA
Screw connection
0.5...1.5 mm ²
AWG-Conductor 26...16
0.5...2.5 mm ²

250 V
5 A
8 A
100 mW/10 mA
≤ 1 ms
AgNi 0.15 gold-flashed
≤ 1 ms
≤ 8 ms
≤ 6 ms
> 15 x 10 ⁶ switching operations
≥ 2 x 10 ⁶ switching operations with free wheel diode
> 2 x 10 ⁵ switching operations
Green LED
-40 °C...+60 °C
-25 °C...+60 °C

DIN VDE 0106
8 kV
≥ 8 mm
III
2
QB 16/10.16
Page 304

Type	Cat. No.
EGR EG7	8216520000
EGR EG7	8216530000
EGR EG7	8218200000¹⁾
RST EG7	8216570000
RS EG7	8193830000

24 V- +15 % -10 %
280 mW +20 % -10 %
12 mA
≤ 3 mA
Screw connection
0.5...1.5 mm ²
AWG-Conductor 26...16
0.5...2.5 mm ²

250 V
5 A
8 A
100 mW/10 mA
≤ 1 ms
AgNi 0.15 gold-flashed
≤ 1 ms
≤ 8 ms
≤ 6 ms
> 15 x 10 ⁶ switching operations
≥ 2 x 10 ⁶ switching operations with free wheel diode
> 2 x 10 ⁵ switching operations
Green LED
-40 °C...+60 °C
-25 °C...+60 °C

DIN VDE 0106
8 kV
≥ 8 mm
III
2
QB 16/10.16
Page 304

Type	Cat. No.
EGR EG7	8147120000
EGR EG7	8147140000
EGR EG7	8160030000¹⁾
RST EG7	8216560000
RS EG7	8193830000

24 V- +15 % -10 %
280 mW +20 % -10 %
12 mA
≤ 3 mA
Screw connection
0.5...1.5 mm ²
AWG-Conductor 26...16
0.5...2.5 mm ²

250 V
5 A
8 A
40 μW ²⁾
≤ 1 ms
AgNi 0.15 5 μ Au
≤ 1 ms
≤ 8 ms
≤ 6 ms
> 15 x 10 ⁶ switching operations
≥ 2 x 10 ⁶ switching operations with free wheel diode
> 2 x 10 ⁵ switching operations
Green LED
-40 °C...+60 °C
-25 °C...+60 °C

DIN VDE 0106
8 kV
≥ 8 mm
III
2
QB 16/10.16
Page 304

Type	Cat. No.
EGR EG7	8092340000
EGR EG7	8092350000
EGR EG7	8092360000¹⁾
RST EG7	8216580000
RS EG7	8193830000

24 V0 +15 % -10 %
280 mW +20 % -10 %
240 mA
≤ 3 mA
Screw connection
0.5...1.5 mm ²
AWG-Conductor 26...16
0.5...2.5 mm ²

250 V
5 A
8 A
100 mW/10 mA
≤ 1 ms
AgNi 0.15 gold-flashed
≤ 2.4 ms
≤ 11 ms
≤ 10 ms
> 15 x 10 ⁶ switching operations
≥ 2 x 10 ⁶ switching operations with free wheel diode
> 2 x 10 ⁵ switching operations
Green LED
-40 °C...+60 °C
-25 °C...+60 °C


DIN VDE 0106
8 kV
≥ 8 mm
III
2
QB 16/10.16
Page 304

²⁾ The following ratings can safely be switched:
a) 100 mV...60 V ac/dc/100 μA...300 mA

b) 5 V... 24 V dc/10 mA... 1.2 A
c) 24 V... 60 V dc/10 mA... 500 mA
d) 10 V...250 V ac/10 mA... 5 A

After switching higher powers (b...d) lower powers (a) can no longer be switched.

Relay Couplers in Components Housings EG 7





48 V0

60 V~

115 V0

230 V~

230 V~



Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.
EGR EG7	8092370000	EGR EG7	8092400000	EGR EG7	8092430000	EGR EG7	8092460000	EGR EG7	8178200000
EGR EG7	8092380000	EGR EG7	8092410000	EGR EG7	8092440000	EGR EG7	8092470000		
EGR EG7	8092390000¹⁾	EGR EG7	8092420000¹⁾	EGR EG7	8092450000¹⁾	EGR EG7	8092480000¹⁾		
RST EG7	8216590000	RST EG7	8216600000	RST EG7	8216610000	RST EG7	8216620000	RST EG7	8216630000
RS EG7	8193830000	RS EG7	8193830000	RS EG7	8193830000	RS EG7	8193830000	RS EG7	8193830000
48 V0 +15 % -10 %		60 V0 +15 % -10 %		115 V0 +15 % -10 %		230 V~ +15 % -10 %		230 V~ +15 % -10 %	
280 mW +15 % -10 %		280 mW +15 % -10 %		330 mW +15 % -10 %		280 mW +15 % -10 %		280 mW +15 % -10 %	
480 mA		600 mA		160 mA		185 mA		185 mA	
≤ 3 mA		≤ 3 mA		≤ 3 mA		≤ 3 mA		≤ 3 mA	
Screw connection		Screw connection		Screw connection		Screw connection		Screw connection	
0.5...1.5 mm ²		0.5...1.5 mm ²		0.5...1.5 mm ²		0.5...1.5 mm ²		0.5...1.5 mm ²	
AWG-Conductor 26...16		AWG-Conductor 26...16		AWG-Conductor 26...16		AWG-Conductor 26...16		AWG-Conductor 26...16	
0.5...2.5 mm ²		0.5...2.5 mm ²		0.5...2.5 mm ²		0.5...2.5 mm ²		0.5...2.5 mm ²	
250 V		250 V		250 V		250 V		250 V	
5 A		5 A		5 A		5 A		5 A	
8 A		8 A		8 A		8 A		8 A	
100 mW/10 mA		100 mW/10 mA		100 mW/10 mA		100 mW/10 mA		40 μW ²⁾	
≤ 1 ms		≤ 1 ms		≤ 1 ms		≤ 1 ms		≤ 1 ms	
AgNi 0.15 gold-flashed		AgNi 0.15 gold-flashed		AgNi 0.15 gold-flashed		AgNi 0.15 gold-flashed		AgNi 0.15 5 μ Au	
≤ 2.5 ms		≤ 3.8 ms		≤ 3.8 ms		≤ 2 ms		≤ 2 ms	
≤ 12 ms		≤ 12 ms		≤ 12 ms		≤ 12 ms		≤ 12 ms	
≤ 10 ms		≤ 10 ms		≤ 10 ms		≤ 10 ms		≤ 10 ms	
> 15 x 10 ⁶ switching operations		> 15 x 10 ⁶ switching operations		> 15 x 10 ⁶ switching operations		> 15 x 10 ⁶ switching operations		> 15 x 10 ⁶ switching operations	
≥ 2 x 10 ⁶ switching operations		≥ 2 x 10 ⁶ switching operations		≥ 2 x 10 ⁶ switching operations		≥ 2 x 10 ⁶ switching operations		≥ 2 x 10 ⁶ switching operations	
with free wheel diode		with free wheel diode		with free wheel diode		with free wheel diode		with free wheel diode	
> 2 x 10 ⁵ switching operations		> 2 x 10 ⁵ switching operations		> 2 x 10 ⁵ switching operations		> 2 x 10 ⁵ switching operations		> 2 x 10 ⁵ switching operations	
Green LED		Green LED		Green LED		Green LED		Green LED	
-40 °C...+60 °C		-40 °C...+60 °C		-40 °C...+60 °C		-40 °C...+60 °C		-40 °C...+60 °C	
-25 °C...+60 °C		-25 °C...+60 °C		-25 °C...+60 °C		-25 °C...+60 °C		-25 °C...+60 °C	
DIN VDE 0106									
8 kV		8 kV		8 kV		8 kV		8 kV	
≥ 8 mm		≥ 8 mm		≥ 8 mm		≥ 8 mm		≥ 8 mm	
III		III		III		III		III	
2		2		2		2		2	
QB 16/10.16	1650330000	QB 16/10.16	1650330000	QB 16/10.16	1650330000	QB 16/10.16	1650330000	QB 16/10.16	1650330000
Page 304		Page 304		Page 304		Page 304		Page 304	

PLUGSERIES Relays on Sockets




PRZ/PRS



PRZ/PRS



PRS/PRZ xxx 1CO PRS/PRZ xxx 2CO



- Modular system comprising:
 - Relay socket for mounting rails
 - LED indicator unit / RC combination
 - retainer clip
 - pluggable relays
- Independent connection technology: screw or tension clamp technology
- Compatible with low power relays type RT / Standard with 1 or 2 CO contacts
- Coil and root-contacts cross-connectable with cross-connection type ZQV 2.5 N
- Available as complete module or as spare parts

DC-Version



Type/Version	Cat. No.	Qty.
Screw connection		
PRS 12Vdc LD 1CO	8536471001	10
PRS 12Vdc LD 2CO	8536501001	10
PRS 24Vdc LD 1CO	8530621001	10
PRS 24Vdc LD 2CO	8530631001	10
PRS 115Vdc LD 1CO	8536510000	10
PRS 115Vdc LD 2CO	8536520000	10
PRS 24Vdc LD 2CO SGR 282	8596000000	10
with gold-plated relay contacts:		
PRS 24Vdc LD 2CO AU	8561760000	10
Tension clamp connection		
PRZ 12Vdc LD 1CO	8536571001	10
PRZ 12Vdc LD 2CO	8536591001	10
PRZ 24Vdc LD 1CO	8530691001	10
PRZ 24Vdc LD 2CO	8530701001	10
PRZ 115Vdc LD 1CO	8536610000	10
PRZ 115Vdc LD 2CO	8536630000	10
PRZ 24Vdc LD 2CO SGR 282	8595970000	10
with gold-plated relay contacts:		
PRZ 24Vdc LD 2CO AU	8552440000	10
Other variants on request		
Technical data		
Input voltage	12 V dc ... 24Vdc ... 115Vdc	
Rated consumption, typ	400 mW	
Status indicator	pluggable LED-housing, green LED	
Output	1 CO / 2 CO contacts	
Contact version	1 x UM / 2 x UM	
Max. output voltage	250Vuc	
Max. switching current	16A / 2 x 8A	
Continuous current	10A	
Rated braking capacity	4kVA / 2 x 2kVA	
Service life, mech.	30 x 10 ⁶	
Input/output		
Clearance and creepage path	> 8mm	
Protective separation	DIN VDE 0106 T. 101	
Dielectric strength	> 4kV eff	
Insulation coordinates acc. to EN 50178	III / 2	
Miscellaneous data		
Ambient temperature	-40°C ... +50°C	
Protection class	IP 20	
Rated cross-section	0.5...2.5mm ²	
Flammability	V0	
Relay type	Schrack RT1 / RT2	
Dimensions WxHxT	15.2 x 91 x 85	
Approvals	CE, UL recognized, cUL	
Rail mounted	TS 35	
Accessories		
Cross-connection		
2-pole black	ZQV 2.5N/4-2 SW1784270000	60
2-pole red	ZQV 2.5N/4-2 RT 1784280000	60
2-pole blue	ZQV 2.5N/4-2 BL 1784290000	60
Marking tags		
WS 10/5	1060860000	
WS 15/5	1609880000	

AC-Version

Type/Version	Cat. No.	Qty.
Screw connection		
PRS 24Vac LD 1CO	8536530000	10
PRS 24Vac LD 2CO	8536560000	10
PRS 120Vac LD 1CO	8530641001	10
PRS 120Vac LD 2CO	8530661001	10
PRS 230Vac LD 1CO	8530671001	10
PRS 230Vac LD 2CO	8530681001	10
with gold-plated relay contacts:		
PRS 120Vac LD 2CO AU	8595960000	10
PRS 230Vac LD 2CO AU	8595990000	10
Tension clamp connection		
PRZ 24Vac LD 1CO	8536651001	10
PRZ 24Vac LD 2CO	8536681001	10
PRZ 120Vac LD 1CO	8530710000	10
PRZ 120Vac LD 2CO	8530720000	10
PRZ 230Vac LD 1CO	8530731001	10
PRZ 230Vac LD 2CO	8530741001	10
with gold-plated relay contacts:		
PRZ 120Vac LD 2CO AU	8575940000	10
PRZ 230Vac LD 2CO AU	8575950000	10
Other variants on request		
Technical data		
Input voltage	24Vac ... 120Vac ... 230Vac	
Rated consumption, typ	760 VA	
Status indicator	pluggable LED-housing, green LED	
Output	1 CO / 2 CO contacts	
Contact version	1 x UM / 2 x UM	
Max. output voltage	250Vuc	
Max. switching current	16A / 2 x 8A	
Continuous current	10A	
Rated braking capacity	4kVA / 2 x 2kVA	
Service life, mech.	5 x 10 ⁶	
Input/output		
Clearance and creepage path	> 8mm	
Protective separation	DIN VDE 0106 T. 101	
Dielectric strength	> 4kV eff	
Insulation coordinates acc. to EN 50178	III / 2	
Miscellaneous data		
Ambient temperature	-40°C ... +50°C	
Protection class	IP 20	
Rated cross-section 0.5 mm ²	0.5...2.5mm ²	
Flammability	V0	
Relay type	Schrack RT1 / RT2	
Dimensions WxHxT	15.2 x 91 x 85	
Approvals	CE, UL recognized, cUL	
Rail mounted	TS 35	
Accessories		
Cross-connection		
2-pole black	ZQV 2.5N/4-2 SW1784270000	60
2-pole red	ZQV 2.5N/4-2 RT 1784280000	60
2-pole blue	ZQV 2.5N/4-2 BL 1784290000	60
Marking tags		
WS 10/5	1060860000	
WS 15/5	1609880000	

PLUGSERIES Relays on Sockets

Accessories



Empty base for rail mounted TS 35

Screw connection
Tension clamp connection

Technical data

Rated current
Rated voltage
Dielectric strength coil/contacts
Protection class
Rated cross-section
Insulation stripping length
- Screw connection
- Tension clamp connection
Ambient temperature
Flammability class UL 94

Type	Cat. No.	Qty.
PXS35	8533771001	10
PXZ35	8536691001	10

Holding clamp

Type	Cat. No.	Qty.
PRC	8536700000	100

Operating indication

LED indicator with free-wheeling diode

6 ... 24 Vdc	PLED 24 Vdc	8536710000	20
6 ... 24 Vdc	PLED 24 Vdc red	8611010000	20
48 ... 60 Vdc	PLED 48 Vdc	8536720000	20
115 Vdc	PLED 115 Vdc	8536730000	20
12 ... 24 Vac	PLED 24 Vac	8536750000	20
115 Vac	PLED 120 Vac	8536760000	20
230 Vac	PLED 230 Vac	8536780000	20
230 Vac	PLED 230 Vac red	8611000000	20
RC combination 120...230 VAC/DC	PLRC 200 nF/200Ω	8566530000	20

Pluggable cross-connectionen


2-pole black	ZQV 2.5N/4-2SW	1784270000	60
2-pole red	ZQV 2.5N/4-2RT	1784280000	60
2-pole blue	ZQV 2.5N/4-2BL	1784290000	60

Marking tags


10 x 5 mm	WS 10/5	1060860000	200
	WS 15/5	1609880000	96

Operating indication

DC-Version



AC-Version




PLUGSERIES Relays on Sockets


Pluggable relay types

Print figure/circuit diagram Relay type RT/SGR


16 A, Pinning 5 mm





1 changeover contact



2 changeover contacts



SCHRACK RT



Pluggable relay

12 Vdc 1 changeover contact
12 Vdc 2 changeover contacts
24 Vdc 1 changeover contact
24 Vdc 1 changeover contact AU
24 Vdc 2 changeover contacts
24 Vdc 2 changeover contacts AU
48 Vdc 1 changeover contact
48 Vdc 2 changeover contacts
60 Vdc 2 changeover contacts
110 Vdc 1 changeover contact
110 Vdc 2 changeover contacts
24 Vac 1 changeover contact
24 Vac 2 changeover contacts
115 Vac 1 changeover contact
115 Vac 1 changeover contact AU
115 Vac 2 changeover contacts
115 Vac 2 changeover contacts AU
230 Vac 1 changeover contact
230 Vac 1 changeover contact AU
230 Vac 2 changeover contacts
230 Vac 2 changeover contacts AU

Type Schrack RT	Cat. No.	Qty.
RT 314012	4058470000	20
RT 424012	4058560000	20
RT 314024	4058480000	20
RT 315024	4058490000	20
RT 424024	4058570000	20
RT 425024	4058580000	20
RT 314048	4058740000	20
RT 424048	4058750000	20
RT 424060	4058760000	20
RT 314110	4058500000	20
RT 424110	4058590000	20
RT 315524	4058510000	20
RT 424524	4058600000	20
RT 314615	4058520000	20
RT 315625	4058530000	20
RT 424615	4058610000	20
RT 425615	4058620000	20
RT 314730	4058540000	20
RT 315730	4058550000	20
RT 424730	4058630000	20
RT 425730	4058640000	20

Technical data


Contact number and type	1 changeover contact or 2 changeover contacts
Contact material	AgNi 90/10, AgNi 0.15 htv
Switching current	16 A 1We/2 x 8 A 2We
Switching voltage	250 V ac
Braking capacity	4 kVA
Min. switching current / braking capacity	10 mA /100 mW
Min. braking capacity AU contact	40 µW
Rated consumption	400 mW dc/0.55 VA ac
Dielectric strength Sp./Kont.	5 kV
Response / drop out time:	DC coil typ. 7/3 ms AC coil 9/45 ms
Bounce time NO contact/normally closed contact	typ. 1/3 ms
Mechanical service life:	DC coil > 30 x 10 ⁶ switching operations AC coil > 30 x 10 ⁸ switching operations
Braking capacity	1-pole DC 13 1.25A, L/R = 80 ms 2.3 x 10 ⁵ 2-pole DC 13 1.25A, L/R = 80 ms 2.8 x 10 ⁵ 2-pole AC 15 1.2A, cosL/R = 0.3 6050x

Miscellaneous data

Protection class	IP 40
Flammability class UL	V0
Ambient temperature	DC coil -40°C ... +85°C AC coil -40°C ... +70°C
Weight	14 g
Approvals	UL, CSA, VDE, ÖVE

Relay Couplers on Sockets MICROSERIES in Terminal Format


MICRORELAY MRS/MRZ




This module can be used as a universal interface between the controller and actuator for switching small to medium-sized loads.

- Pluggable cross-connection in the input and output reduces wiring costs
- 6-mm width
- Flexible thanks to screw and tension clamp connection versions

Limit diagram



Current temperature-rise curve



Ambient temperature [°C]



Schematic circuit diagram

MRS 5 Vdc 1CO

MRZ 5 Vdc 1CO

MRS 12 Vdc 1CO

MRZ 12 Vdc 1CO



Ordering data

for TS 35

Screw connection

Tension clamp connection

Type Cat. No.

MRS 5 Vdc 1CO **8556080000**

MRZ 5 Vdc 1CO **8556150000**

Type Cat. No.

MRS 12 Vdc 1CO **8556070000**

MRZ 12 Vdc 1CO **8556140000**

Technical data

Input

Input voltage

Input voltage ac with U_{Nenn}

Input voltage dc with U_{Nenn}

Input power

Making threshold, (typ.)

Cut-out threshold (typ.)

Status indicator

Reaction time at U_N (typ.)

Release at U_N (typ.)

Voltage of relay coil

5 Vdc $\pm 20\%$ (4...6 V)

12 Vdc $\pm 20\%$ (9.6...14.4 V)

38.5 mAdc $\pm 10\%$

193 mW $\pm 10\%$

3.2 V / 21.6 mA

1.6 V / 8 mA

Green LED

6.2 ms

3.9 ms

5 V

17.2 mAdc $\pm 10\%$

210 mW $\pm 10\%$

6.4 V / 8.4 mA

2.5 V / 2.4 mA

Green LED

5.8 ms

6.9 ms

12 V

Functionality

Operating indication

Reverse polarity protection

Free wheel diode

yes

yes

yes

yes

yes

yes

Output

Switching voltage

ac: continuous current/switching power (see derating diagram)

Switch-on current

dc: Continuous current/switching power

Min. braking capacity

Contact material

Mechanical service life

Max. switching frequency at nominal voltage

1 changeover contact

250 Vac acc. to VDE

240 Vac acc. to UL/CSA

max. 6 A / max. 1500 VA

max. 6 A

see limit diagram

12 V / 10 mA

AgSnO

20 x 10⁶ switching operations

0.1 Hz

1 changeover contact

250 Vac acc. to VDE

240 Vac acc. to UL/CSA

max. 6 A / max. 1500 VA

max. 6 A

see limit diagram

12 V / 10 mA

AgSnO

20 x 10⁶ switching operations

0.1 Hz

Ambient temperature

Storage temperature

Climate

-25 °C...+50 °C

-40 °C...+60 °C

40 °C / 93 % rel. humidity,

no condensation

CE, cUL

-25 °C...+50 °C

-40 °C...+60 °C

40 °C / 93 % rel. humidity,

no condensation

CE, cUL

Insulation coordination acc. to EN 50178

Rated voltage

Rated impulse voltage

Overvoltage category

Pollution severity

Insulation coord.- and voltage proof, input/output mounting rail

Achieved clearances and creepage distances

300 V

4 kV (1.2 / 50 μ s)

III

2

4 kV_{eff} / 1 min

≥ 5.5 mm

300 V

4 kV

III

2

4 kV_{eff} / 1 min

≥ 5.5 mm

Relay Couplers on Sockets MICROSERIES in Terminal Format

MRS 24 Vdc 1CO

MRS 24 Vuc 1CO

MRS 48 Vuc 1CO

MRS 60 Vdc 1CO

MRS 120 Vuc 1CO

MRS 230 Vac 1CO

MRZ 24 Vdc 1CO







MRZ 24 Vuc 1CO

MRZ 48 Vuc 1CO

MRZ 60 Vdc 1CO

MRZ 120 Vuc 1CO

MRZ 230 Vac 1CO




Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.
MRS 24 Vdc 1CO	8533640000	MRS 24 Vuc 1CO	8556050000	MRS 48 Vuc 1CO	8556040000	MRS 60 Vdc 1CO	8556060000	MRS 120 Vuc 1CO	8556030000	MRS 230 Vac 1CO	8556020000
MRZ 24 Vdc 1CO	8533660000	MRZ 24 Vuc 1CO	8556120000	MRZ 48 Vuc 1CO	8556110000	MRZ 60 Vdc 1CO	8556130000	MRZ 120 Vuc 1CO	8556100000	MRZ 230 Vac 1CO	8556090000
24 Vdc ± 20 % (19.2...28.8 V)		24 Vuc ±10% (21.6...26.4 V)		48 Vuc ±10% (43.2...52.8 V)		60 Vdc ±20% (48...72 V)		120 Vuc +10%/-15% (102...132 V)		230 Vac ±10% (207...253 V)	
6.6 mAdc ±10 %		11 mA ±10 %		5 mA ±20 %		3.3 mAdc ±20 %		3.5 mA ±15 %		7.6 mA ±15%	
160 mW ±10%		6.4 mA ±20 %		4 mA ±20 %		200 mW ±10 %		0.42 VA ±15 %		1.55 VA ±15 %	
15.4 V / 4 mA		154 mW ±10 %		190 mW ±20 %		35 V / 1.6 mA		71 V / 1.8 mA		103 V / 5 mA	
6.5 V / 1.2 mA		15.8 V / 3.6 mA		29 V / 2.2 mA		11 V / 0.6 mA		22 V / 0.5 mA		49 V / 2.5 mA	
Green LED		7 V / 1.3 mA		11 V / 1.3 mA		Green LED		Green LED		Green LED	
6.6 ms		Green LED		Green LED		5.9 ms		6.7 ms		13 ms	
5.8 ms		7.3 ms		6.1 ms		6.5 ms		8.1 ms		11 ms	
24 V		9 ms		5.8 ms		60 V		60 V		24 V	
		24 V		48 V							
yes						yes		yes		yes	
yes		yes		yes		yes		yes		-	
yes		yes		yes		yes		yes		-	
1 changeover contact		1 changeover contact		1 changeover contact		1 changeover contact		1 changeover contact		1 changeover contact	
250 Vac acc. to VDE		250 V ~ acc. to VDE		250 Vac acc. to VDE		250 Vac acc. to VDE		250 V ~ acc. to VDE		250 V ~ acc. to VDE	
240 Vac acc. to UL/CSA		240 V ~ acc. to UL/CSA		240 Vac acc. to UL/CSA		240 Vac acc. to UL/CSA		240 V ~ acc. to UL/CSA		240 V ~ acc. to UL/CSA	
max. 6 A / max. 1500 VA		max. 6 A / max. 1500 VA		max. 6 A / max. 1500 VA		max. 6 A / max. 1500 VA		max. 6 A / max. 1500 VA		max. 6 A / max. 1500 VA	
max. 6 A		max. 6 A		max. 6 A		max. 6 A		max. 6 A		max. 6 A	
see limit diagram		see limit diagram		see limit diagram		see limit diagram		see limit diagram		see limit diagram	
12 V /10 mA		12 V /10 mA		12 V /10 mA		12 V /10 mA		12 V /10 mA		12 V /10 mA	
AgSnO		AgSnO		AgSnO		AgSnO		AgSnO		AgSnO	
20 x 10 ⁶ switching operations		20 x 10 ⁶ switching operations		20 x 10 ⁶ switching operations		20 x 10 ⁶ switching operations		20 x 10 ⁶ switching operations		20 x 10 ⁶ switching operations	
0.1 Hz		0.1 Hz		0.1 Hz		0.1 Hz		0.1 Hz		0.1 Hz	
-25 °C...+50 °C		-25 °C...+50 °C		-25 °C...+50 °C		-25 °C...+50 °C		-25 °C...+50 °C		-25 °C...+50 °C	
-40 °C...+60 °C		-40 °C...+60 °C		-40 °C...+60 °C		-40 °C...+60 °C		-40 °C...+60 °C		-40 °C...+60 °C	
40 °C / 93 % rel. humidity, no condensation		40 °C / 93 % rel. humidity, no condensation		40 °C / 93 % rel. humidity, no condensation		40 °C / 93 % rel. humidity, no condensation		40 °C / 93 % rel. humidity, no condensation		40 °C / 93 % rel. humidity, no condensation	
CE, cUL		CE, cUL		CE, cUL		CE, cUL		CE, cUL		CE, cUL	
300 V		300 V		300 V		300 V		300 V		300 V	
4 kV		4 kV		4 kV		4 kV		4 kV		4 kV	
III		III		III		III		III		III	
2		2		2		2		2		2	
4 kV _{eff} / 1 min		4 kV _{eff} / 1 min		4 kV _{eff} / 1 min		4 kV _{eff} / 1 min		4 kV _{eff} / 1 min		4 kV _{eff} / 1 min	
≥ 5.5 mm		≥ 5.5 mm		≥ 5.5 mm		≥ 5.5 mm		≥ 5.5 mm		≥ 5.5 mm	


Relay Couplers on Sockets MICROSERIES in Terminal Format

Accessories

Tension clamp version MRZ




Screw version MRS



General technical data		Tension clamp version		Screw version			
Clampable conductor:							
Solid H07V-U	mm²	0.5...2.5		0.5...4			
Fsolid H07V-K	mm²	0.5...2.5		0.5...2.5			
„f“ with ferrules acc. to DIN 46 228/1*	mm²	0.5...1.5		0.5...1.5			
„f“ with ferrules with plastic collar*	mm²	0.5...1.5		0.5...1.5			
Max. clampable range in mm² /gauge pin acc. to IEC 60 947-1 Size		0.13...2.5	A 2	0.13...4	A 3		
Rated torque		-		0.6 Nm			
Continuous current of cross-connection 2-pole	A	10		10			
Continuous current of cross-connection multipole	A	10		10			
Insulation stripping length	mm	10		7			
Protection class		IP 20		IP 20			
Housing material		Wemid		Wemid			
Flammability class UL 94		V0		V0			
Rated current		6 A		6 A			
Rated voltage		250 V		250 V			
Cross-connection		Type	Cat. No.	Qty.	Type	Cat. No.	Qty.
Pluggable cross-connection							
ZQV	yellow	ZQV 4N / 2 GE	1758250000	60	ZQV 4N / 2 GE	1758250000	60
		ZQV 4N / 3 GE	1762630000	60	ZQV 4N / 3 GE	1762630000	60
		ZQV 4N / 4 GE	1762620000	60	ZQV 4N / 4 GE	1762620000	60
		ZQV 4N / 10 GE	1758260000	20	ZQV 4N / 10 GE	1758260000	20
		ZQV 4N / 41 GE	1758270000	10	ZQV 4N / 41 GE	1758270000	10
	red	ZQV 4N / 2 RT	1793950000	60	ZQV 4N / 2 RT	1793950000	60
		ZQV 4N / 3 RT	1793980000	60	ZQV 4N / 3 RT	1793980000	60
		ZQV 4N / 4 RT	1794010000	60	ZQV 4N / 4 RT	1794010000	60
		ZQV 4N / 10 RT	1794040000	20	ZQV 4N / 10 RT	1794040000	20
		ZQV 4N / 41 RT	1794070000	10	ZQV 4N / 41 RT	1794070000	10
	blue	ZQV 4N / 2 BL	1793960000	60	ZQV 4N / 2 BL	1793960000	60
		ZQV 4N / 3 BL	1793990000	60	ZQV 4N / 3 BL	1793990000	60
		ZQV 4N / 4 BL	1794020000	60	ZQV 4N / 4 BL	1794020000	60
		ZQV 4N / 10 BL	1794050000	20	ZQV 4N / 10 BL	1794050000	20
		ZQV 4N / 41 BL	1794080000	10	ZQV 4N / 41 BL	1794080000	10
	black	ZQV 4N / 2 SW	1793970000	60	ZQV 4N / 2 SW	1793970000	60
		ZQV 4N / 3 SW	1794000000	60	ZQV 4N / 3 SW	1794000000	60
		ZQV 4N / 4 SW	1794030000	60	ZQV 4N / 4 SW	1794030000	60
		ZQV 4N / 10 SW	1794060000	20	ZQV 4N / 10 SW	1794060000	20
		ZQV 4N / 41 SW	1794090000	10	ZQV 4N / 41 SW	1794090000	10
Markings		Type	Cat. No.	Qty.	Type	Cat. No.	Qty.
12 x 6 mm		WS 10/6	1060960000	200	WS 10/6	1060960000	200
		WS 12/6	1061160000	200	WS 12/6	1061160000	200
Screwdriver		Type	Cat. No.	Qty.	Type	Cat. No.	Qty.
		SD 0.6 x 3.5 x 100	9008330000	10	SD 0.6 x 3.5 x 100	9008330000	10



Relay Couplers on Sockets MICROSERIES in Terminal Format

Accessories



Contact service life

Material AgSnO₂



Pluggable relay

Coil voltage 5 V, 1 changeover contact
Coil voltage 12 V, 1 changeover contact
Coil voltage 24 V, 1 changeover contact
Coil voltage 48 V, 1 changeover contact
Coil voltage 60 V, 1 changeover contact
Coil voltage 24 V, 1 changeover contact, 5 μAU
Coil voltage 60 V, 1 changeover contact, 5 μAU

Technical data (of relay manufacturer)

Contact number and type
Contact version
Switching current
Switching voltage / max. Switching voltage
Braking capacity
Contact material
Recommended min. load
Typ. bounce time NO contact
Typ. bounce time normally closed contact

Miscellaneous data

Flammability class UL
Ambient temperature
Max. switching operations with rated load / without load
Response / drop out time
Bounce time NO contact / normally closed contact
Protection class Housing

For further data see also

Type NAIS APE...	Cat. No.	Qty.
... 30005V	4061580000	20
... 30012V	4061610000	20
... 30024V	4060120000	20
... 30048V	4061620000	20
... 30060V	4061630000	20
... 30124V	4061590000	20
... 30160V	4061600000	20

1 changeover contact
Single contact
6 A
300 Vdc / 400 Vac
1500 VA
AgSnO ₂
≥ 100 mA, 12 V
1 ms
5 ms


V-0
-40 ... +85 °C
6/1200 switching operations per minute
5 / 2.5 ms
1.5 / 5 ms
IP 67

www.matsushita.de

Relay Couplers on Sockets RS 30

1 NC, 1 NO
or 1 changeover contact

Schematic circuit diagram



Rated data

Input voltage 5...60 V ± 10%; 115 V/230 V + 5% – 15%

Rated consumption – (W)

Rated consumption ~ (VA)

Drop-out current of the relay (at 20 °C)

Drop-out current of the relay (at 20 °C)

Pick-up current


Max. output voltage

Continuous current

Derating curve



a = mounted horizontally on rail without clearance

b = mounted horizontally on rail with clearance x 20 mm



5 VTTL	12 V~	24 V~	24 V0	48 V~	48 V0	60 V~	115 V~	115 V~	230 V~ ²⁾	240 V~
0.45 W ¹⁾	0.45 W	0.45 W	0.45 W	0.45 W	0.45 W	0.45 W	–	0.82 W	–	–
–	–	–	0.7 VA	–	0.6 VA	–	0.8 VA	–	0.8 VA	1.2 VA
–	3 mA	3 mA	2.5 mA~	2 mA	2.5 mA~	1 mA~	–	2 mA~	–	0.5 mA~
–	–	–	3.5 mA~	–	4.5 mA~	–	1 mA~	–	1 mA~	1 mA~
–	–	12 mA	–	10 mA	–	–	6 mA	4.3 mA	–	–
250 V	250 V	250 V	250 V	250 V	250 V	250 V	250 V	250 V	250 V	250 V
5 A	6 A	6 A	6 A	6 A	5 A	5 A	5 A	5 A	3 A	3 A

Continuous current



Switch-on current	8 A
Switching capacity with resistive load	2000 VA/100 W
Min. switching capacity/switching current	250 mW/10 mA
Bounce times	≤ 3 ms
Switching times, typical	
–, pick-up lag	≤ 8 ms
–, turn off delay	≤ 7 ms
Max. switching frequency	70 Hz
Contact material	AgNi, gold-flashed
Service life, mechanical	>10 ⁷ switching operations
–, 24 V~, 1 A, resistive load	> 5 x 10 ⁵ switching operations
–, 230 V~, 3 A, resistive load	>7 x 10 ⁵ switching operations
Storage temperature	–40 °C...+60 °C
Ambient temperature	
–, mounted on rail without clearance	–25 °C...+40 °C
–, mounted on rail with clearance ≥ 20 mm	–25 °C...+50 °C

Insulation coordination acc. to EN 50178

Overvoltage category	III
Pollution severity	2
Dimensions	
Mounting width	11.2 mm NO/NC, 25 mm changeover contacts
Length (perpendicular to mounting rail)	70 mm (74 mm BL/SL version)
Height TS 32/TS 35 x 7.5	56 mm/51.5 mm

¹⁾ Rated consumption with 24 VDC auxiliary voltage.

²⁾ 230 V~ on request

Relay Couplers on Sockets RS 30

RS 30

Screw connection

1 NO

1 NC



5

RS 30

Screw connection

1 changeover contact



6

RS 30

Disconnect plug with

screw connection

1 changeover contact








8

RS 30 TTL

Disconnect plug with

screw connection

1 NO and 1 NC



Ordering data

Connection method

Screw connection (LP)

Disconnect plug with screw connection (BL/SL)

Schematic circuit diagram

1 2 3 4 5

6 7 8 8

Contact

NO NO NC NC changeo. c.

changeo. c. changeo. c. NO NC

Input voltage

Function indicator

5 V~

TTL

None

12 V~

None

Red LED

1129421001 1129521001

1101661001 1100961001

24 V~

Green LED

Red LED

1101611001 1100911001 1181511001

1101621001 1100921001 1181521001

24 Vb

None

Green LED

Red LED

1101761001 1101061001

1101711001 1101011001

1101721001 1101021001

48 V~

None

Green LED

Red LED

1101861001 1101161001

1101811001 1101111001

1101821001 1101121001

48 Vb

None

Green LED

Red LED

1101961001 1101261001

1101911001 1101211001

1101921001 1101221001

60 V~

None

Green LED

Red LED

1102061001

1102011001

1102021001

115 V~

None

Green LED

Red LED

1155161001 1155261001

1155111001 1155211001

1155121001 1155221001

115 V~

None

Green LED

Red LED

1102161001 1101461001

1102111001 1101411001

1102121001 1101421001

230 V~

None

Green LED

Red LED

1102261001 1101561001

1102211001 1101511001

1102221001 1101521001

240 V~

None

Green LED

Red LED

1128561001 1128661001

1128511001 1128611001

1128521001 1128621001

1167760000 1167660000

1129660000

1100260000

1100210000

1100220000

1100360000

1100460000

1100410000

1100420000

1100560000

1100660000

1100610000

1100620000

1100760000

1100860000

Relay Couplers on Sockets RS 30

1 changeover contact



- Usable for high switching-power
- Suitable for switching inductive loads

RS 31

with power contacts



Schematic circuit diagram





Ordering data

Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.
RS 31, 24 V~	1128361001	RS 31, 48 V~	1150761001	RS 31, 115 V~	1150361001	RS 31, 115 V~	1150461001
RS 31, 24 V~	1128331001						
RS 31, 24 V~	1128311001						

Rated data

Input voltage	24 V~, ±10 %	48 V~, ±10 %	115 V~, +5 % -15 %	115 V~, +5 % -15 %
Rated consumption – (W)	1 W	1 W	1 W	–
Rated consumption – (VA)	–	–	–	1 VA
Drop-out current of the relay (at 20 °C)	11.5 mA~	13.5 mA~	5.5 mA~	–
Drop-out current of the relay (at 20 °C)	–	–	–	1.5 mA~
Max. output voltage	250 V	250 V	250 V	250 V
Continuous current	16 A	16 A	16 A	16 A

Derating curve
mounted horizontally on rail without clearance




Switch-on current	60 A/200 ms	60 A/200 ms	60 A/200 ms	60 A/200 ms
Max. switching capacity with resistor load	3.5 kVA/480 W	3.5 kVA/480 W	3.5 kVA/480 W	3.5 kVA/480 W
Min. switching capacity/switching current	1 W/100 mA	1 W/100 mA	1 W/100 mA	1 W/100 mA
Bounce times	< 3 ms	< 6 ms	< 6 ms	< 6 ms
Switching times, typical				
–, pick-up lag	< 9 ms	< 12 ms	< 10 ms	< 4 ms
–, turn off delay	< 10 ms	< 8 ms	< 12 ms	< 11 ms
Max. switching frequency				
Contact material	AgCdO	AgCdO	AgCdO	AgCdO
Service life, mechanical	3 x 10 ⁷ switching operations	3 x 10 ⁷ switching operations	3 x 10 ⁷ switching operations	3 x 10 ⁷ switching operations
– 230 V, 50 Hz, 3.5 kV A	2.5 x 10 ⁵ switching operations	2.5 x 10 ⁵ switching operations	2.5 x 10 ⁵ switching operations	2.5 x 10 ⁵ switching operations
Status indicator	Red LED Yellow LED Green LED	1128361001 1128331001 1128311001	1150761001 1150361001	1150461001
Storage temperature	–40 °C...+60 °C	–40 °C...+60 °C	–40 °C...+60 °C	–40 °C...+60 °C
Ambient temperature	–25 °C...+40 °C	–25 °C...+40 °C	–25 °C...+40 °C	–25 °C...+40 °C
Insulation coordination acc. to EN 50178				
Overvoltage category	III	III	III	III
Pollution severity	2	2	2	2
Dimensions				
Mounting width	25 mm	25 mm	25 mm	25 mm
Length (perpendicular to mounting rail)	70 mm	70 mm	70 mm	70 mm
Height with TS 32/TS 35 x 7.5	58 mm/53.5 mm	58 mm/53.5 mm	58 mm/53.5 mm	58 mm/53.5 mm


Relay Coupler on Locking Socket Profile RS 31

RS 31

with power contacts



Type	Cat. No.	
RS 31, 230 V~	1128461001	
RS 31, 230 V~	1128431001	
RS 31, 230 V~	1128411001	
230 V~, +5 % -15 %		
-		
1 VA		
-		
2.2 mA~		
250 V		
16 A		




60 A/200 ms	
3.5 kVA/480 W	
1 W/100 mA	
< 6 ms	
< 10 ms	
< 8 ms	
AgCdO	
3 x 10 ⁷ switching operations	
2.5 x 10 ⁵ switching operations	
1128461001	
1128431001	
1128411001	
-40 °C...+60 °C	
-25 °C...+40 °C	
III	
2	
25 mm	
70 mm	
58 mm/53.5 mm	


Relay Couplers on Sockets RS 32

with 2 changeover contacts


RS 32




RS 32



Schematic circuit diagram



9406021001



9406121001

9406321001

9406521001

Ordering data

Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.
------	----------	------	----------	------	----------	------	----------

RS 32 9406021001


RS 32 9406121001

RS 32 9406221001

RS 32 9406321001

Rated data


Input voltage	12 V-, $\pm 10\%$	24 V-, $\pm 10\%$	24 V0, $\pm 10\%$	48 V-, $\pm 10\%$
Rated consumption - (W)	0.6 W	0.6 W	0.6 W	0.6 W
Rated consumption ~ (VA)	-	-	0.9 VA	-
Drop-out current of the relay** (at 20 °C)	9.5 mA	5 mA	24 V-: 4.5 mA	2 mA
Drop-out current of the relay** (at 20 °C)	-	-	24 V-: 2.5 mA	-
Max. output voltage	250 V	250 V	250 V	250 V
Continuous current	2 x 4 A	2 x 4 A	2 x 4 A	2 x 4 A
Derating curve	mounted horizontally on rail without clearance			




Switch-on current	2 x 6 A	2 x 6 A	2 x 6 A	2 x 6 A
Max. switching capacity with resistor load	1400 VA	1400 VA	1400 VA	1400 VA
Min. switching capacity/switching current	-	-	-	-
Bounce times	≤ 4 ms	≤ 4 ms	≤ 4 ms	≤ 4 ms
Switching times, typical	-	-	-	-
- , pick-up lag	≤ 13 ms	≤ 13 ms	≤ 13 ms	≤ 13 ms
- , turn off delay	≤ 10 ms	≤ 10 ms	≤ 10 ms	≤ 10 ms
Max. switching frequency	-	-	-	-
Contact material	AgNi0.15, gold-flashed	AgNi0.15, gold-flashed	AgNi0.15, gold-flashed	AgNi0.15, gold-flashed
Service life, mechanical	> 30x10 ⁶ switching operations	> 30x10 ⁶ switching operations	> 30x10 ⁶ switching operations	> 30x10 ⁶ switching operations
- , 24 V-, 1 A, resistive load	-	-	-	-
- , 230 V-, 3 A, resistive load	-	-	-	-
Status indicator	Red LED	Red LED	Red LED	Red LED
Storage temperature	-40 °C...+60 °C	-40 °C...+60 °C	-40 °C...+60 °C	-40 °C...+60 °C
Ambient temperature	-25 °C...+40 °C	-25 °C...+40 °C	-25 °C...+40 °C	-25 °C...+40 °C
Approvals	-	CSA	-	CSA
Insulation coordination acc. to EN 50178	-	-	-	-
Overvoltage category	III	III	III	III
Pollution severity	2	2	2	2
Dimensions	-	-	-	-
Mounting width	25 mm	25 mm	25 mm	25 mm
Length (perpendicular to mounting rail)	70 mm	70 mm	70 mm	70 mm
Height with TS 32/TS 35 x 7.5	68 mm/63.5 mm	68 mm/63.5 mm	68 mm/63.5 mm	68 mm/63.5 mm

Relay Couplers on Sockets RS 32

RS 32




9406221001
9406421001
9406621001
9406721001



1122661001
1122761001

Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.
RS 32	9406421001	RS 32	9406521001	RS 32	9406621001	RS 32	9406721001	RS 32	1122661001	RS 32	1122761001
48 V ₀ , ±10 %		60 V ₀ , ±10 %		115 V ₀ , +5 % -15 %		230 V ₀ , +5 % -15 %		24 V/48 V ₀ , ±10 %		115 V/230 V ₀ , +5 % -15 %	
0.6 W		0.6 W		0.5 W		1 W		0.5 W/0.6 W		0.5 W/1 W	
0.9 VA		—		0.6 VA		1 VA		0.7 VA/0.9 VA		0.6 VA/1 VA	
48 V~: 2 mA		1.5 mA		115 V~: 1 mA		230 V~: 1.2 mA		~: 5 mA/2 mA		~: 1 mA/1.2 mA	
48 V~: 4.5 mA		—		115 V~: 1.5 mA		230 V~: 2 mA		~: 3 mA/4.5 mA		~: 1.5 mA/2 mA	
250 V		250 V		250 V		250 V		250 V		250 V	
2 x 4 A		2 x 4 A		2 x 4 A		2 x 4 A		2 x 4 A		2 x 4 A	



2 x 6 A	2 x 6 A	2 x 6 A	2 x 6 A	2 x 6 A	2 x 6 A
1400 VA	1400 VA	1400 VA	1400 VA	1400 VA	1400 VA
≤ 4 ms	≤ 4 ms	≤ 4 ms	≤ 4 ms	≤ 4 ms	≤ 4 ms
≤ 13 ms	≤ 10 ms	≤ 13 ms	≤ 13 ms	≤ 13 ms	≤ 13 ms
≤ 10 ms	≤ 10 ms	≤ 10 ms	≤ 10 ms	≤ 10 ms	≤ 10 ms
AgNi0.15, gold-flashed	AgNi0.15, gold-flashed	AgNi0.15, gold-flashed	AgNi0.15, gold-flashed	AgNi0.15, gold-flashed	AgNi0.15, gold-flashed
> 30x10 ⁶ switching operations	> 30x10 ⁶ switching operations	> 30x10 ⁶ switching operations	> 30x10 ⁶ switching operations	> 30x10 ⁶ switching operations	> 30x10 ⁶ switching operations
Red LED	Red LED	Red LED	Red LED	Green LED	Green LED
-40 °C...+60 °C	-40 °C...+60 °C	-40 °C...+60 °C	-40 °C...+60 °C	-40 °C...+60 °C	-40 °C...+60 °C
-25 °C...+40 °C	-25 °C...+40 °C	-25 °C...+40 °C	-25 °C...+40 °C	-25 °C...+40 °C	-25 °C...+40 °C
III	III	III	III	III	III
2	2	2	2	2	2
25 mm	25 mm	25 mm	25 mm	25 mm	25 mm
70 mm	70 mm	70 mm	70 mm	70 mm	70 mm
68 mm/63.5 mm	68 mm/63.5 mm	68 mm/63.5 mm	68 mm/63.5 mm	68 mm/63.5 mm	68 mm/63.5 mm

Multiple Socket Interface RSM

(Relay Coupler)


with one changeover contact each

RSM 4 R 4 relays, soldered

RSM 4 RS 4 relays, plug-in

RSM 8 R 8 relays, soldered

RSM 8 RS 8 relays, plug-in




Also available as opto-coupler (max. 48 V),
See page 120/121

Schematic circuit diagram

Fixing feet can also be mounted turned through 180°

DC voltage, positive switching



Rated data




Input voltage	
Rated consumption ~ (W)	soldered relay
	plug-in relay
Rated consumption ~ (VA)	soldered relay
	plug-in relay
Pick-up current ~ (mA)	soldered relay
– (mA)	plug-in relay
Pick-up current ~ (mA)	soldered relay
– (mA)	plug-in relay

Drop-out current of the relay (at 20 °C)	2 mA
Max. output voltage	250 V
Continuous current	6 A

Derating-curve

a = mounted horizontally on rail without clearance

b = mounted horizontally on rail with clearance ≥ 20 mm



Switching times, typical

–, pick-up lag (–/–)

–, turn off delay (–/–)

Bounce times

Switch-on current

Switching capacity with resistive load

Min. switching capacity/switching current

Contact material

Service life, mechanical

–, 24 V–, 1 A, resistive load

–, 230 V–, 3 A, resistive load

Storage temperature

Ambient temperature

Insulation coordination acc. to EN 50178

Overvoltage category

Pollution severity

Dimensions

Conductor cross-section (screw connection)

Spare relay (pluggable)

for 24 V-RSM types

for 48 V-RSM types

for 115 V, 230 V-RSM types

≤ 8 ms	≤ 10 ms/10 ms	≤ 12 ms	≤ 10 ms/12 ms	≤ 10 ms	≤ 8 ms/10 ms	≤ 10 ms	≤ 8 ms/10 ms
≤ 7 ms	≤ 15 ms/20 ms	≤ 11 ms	≤ 15 ms/20 ms	≤ 10 ms	≤ 5 ms/8 ms	≤ 10 ms	≤ 7 ms/8 ms
≤ 3 ms	≤ 3 ms	≤ 3 ms	≤ 3 ms	≤ 3 ms	≤ 3 ms	≤ 3 ms	≤ 3 ms

8 A	8 A	8 A	8 A	8 A	8 A	8 A	8 A
2000 VA	2000 VA	2000 VA	2000 VA	2000 VA	2000 VA	2000 VA	2000 VA
250 mW/10 mA							
AgNi 90/10, AgNiO,15, gold-flashed							
> 30x10 ⁶ switching operations							
> 5 x 10 ⁵ switching operations							
> 7 x 10 ⁵ switching operations							
–40 °C...+60 °C							
–25 °C...+50 °C							

III
2

Input voltage	Contact material	Cat. No.	Notes
24 V–	AgNi 90/10	8630780000	RT 314024 with yoke
24 V–	AgNi 90/10	4058480000	RT 314024 without yoke
48 V–	AgNi 90/10	8630790000	RT 314048 with yoke
48 V–	AgNi 90/10	4058740000	RT 314048 without yoke
115 V–	AgNi 90/10	8630770000	RT 314110 with yoke
115 V–	AgNi 90/10	4058500000	RT 314110 without yoke
115 V–	Au 5	4156970000	ZLT input relay KHU/BV 1680




Multiple Socket Interface RSM

RSM 16 RS

16 relays, plug-in



Red LEDs, further colours on request



Ordering data

[illegible]

Spare relays
on request

1) Common negative potential, positive is switched
2) Common negative potential, negative is switched

³⁾ Approval by the Germanischer Lloyd

Relay Socket Module for Industry Relays


Weidmüller relay sockets for mounting rails enable plug-in relays most commonly used in industry to be mounted; they make possible installations in which the control section and power section are perfectly separated. The coil terminals and the connection terminals are located on opposite sides of the locking socket modules.

The conductors are connected via screw terminals; the securing in the terminal is achieved by a clamping yoke system. This method has been used by Weidmüller for many years, and is the only method that guarantees a reliable connection in industrial applications.


Thanks to their combination foot, these modules can be mounted onto TS 32, TS 35x7.5, TS 35x15 mounting rails in accordance with European standards EN 50035 and EN 50022.

The connections are marked according to European Standard EN 50005. The modules are designed for DC relays (with a damping diode parallel to the coil, as well as a protection diode for reverse polarity protection) and AC relays.

They can be provided with an LED on request.



DC voltage



Ac voltage


The input terminals are doubled, in order to pick off the poles. Note the following for DC current operation:

A1 = +

A2 = -

The contacts available at the output are:
2, 3 or 4 changeover contacts.

The marking of the contacts in the following diagram corresponds to European standard EN 50005.



The standard range of relay socket modules is divided as follows:

Group 1:

RS 3 (2 changeover contacts)

RS 4, RS 14 (4 changeover contacts)

For relays of the type "international"

Group 2:

RS 6 (2 changeover contacts) Size 1

RS 7, 17 (3 changeover cont.) Size 2

RS 8, 18 (4 changeover cont.) Size 2

RS 9 (2 changeover cont.) Size 2

For relays of the type "European".

Relays with 4 changeover contacts (size 2) can be secured to RS 7, RS 17 and RS 9; however, only 3 or 2 changeover contacts are connected to the terminals, which results in space savings.

Group 3:

RS 21 (2 changeover contacts)

RS 23 (3 changeover contacts)

RS 24 (2 x 3 changeover cont.)

For relays with one socket with 8 or 11 pins.

The table on page 87 offers an overview of the most important manufacturers of relays in groups 2, 3 and 4. The list is provided for information purposes only, and does not claim to be complete

List of Plug-in Relays for Weidmüller Relay Socket Modules

Manufacturer	Group 1	Group 2	Group 3
	International relays	European relays	Relays with socket oktal
	• RS 3 2 changeover contacts • RS 4, RS 14 4 changeover contacts	• RS 6 2 changeover contacts (Size 1) • RS 7, RS 17 3 changeover cont. (Size 2) • RS 8, RS 18 4 changeover cont. (Size 2) • RS 9 2 changeover cont. (Size 2)	• RS 21 2 changeover contacts • RS 23 3 changeover contacts • RS 24 2x3 changeover contacts
Relay type	Relay type	Relay type	Relay type
EBERLE	• – • –	• – • Type 40701 • Type 40701 • – • – • – • – • – • –	• – • Type 41454 • Type 41454
ELESTA	• – • –	• – • – • –	• SKR 085 • SKR 115
FEME	• – • –	• – • – • – • –	• RCP 8 • RCP 11 • RCP 11
GRUNER	• – • –	• Series 9065 G • Series 9059 G/9066 G • Series 9059 G/9066 G • Series 9059 G/9066 G	• Series 668 B 2 changeover contacts • Series 668 A 3 changeover contacts • Series 668 A 3 changeover contacts
HALLER	• – • –	• Series H-561 Size 1 • Series H-561 Size 2 • Series H-561 Size 2 • Series H-561 Size 2	• HB-1/1 • HB-1/2 • HB-1/2
ITT (MTI)	• MAT 2 • MAT 4	• Type 24 • Type 25 • Type 25 • Type 25	• – • – • –
FUJITSU	• FRL 263-02 • FRL 263-04	• – • – • – • –	• FRL 256-02 • FRL 256-04 • FRL 256-04
KUHNKE	• – • Type 111 A4	• – • – • – • –	• Universal relays-M/-H/-U • Universal relays-M/-H/-U • Universal relays-M/-H/-U
KUKE	• – • –	• Miniature relays Type 01 • Miniature relays Type 02 • Miniature relays Type 02 • Miniature relays Type 02	• – • – • –
NATIONAL	• HC 2 • HC 4	• – • – • – • –	• – • – • –
OMRON	• MY 2 • MY 4	• MHS-2 • MHS-4 • MHS-4 • MHS-4	• MK 2 • MK 3 • MK 3
POTTER & BRUMFIELD	• – • Series KH	• – • Series R 10 • Series R 10 • Series R 10	• Series KAP • Series KAP • Series KAP
RAPA	• – • –	• Series 012 Size 1 • Series 012 Size 2 • Series 012 Size 2 • Series 012 Size 2	• Series C-Type CKR • Series C-Type CKR • Series C-Type CKR
Tyco/SCHRACK	• ZT 4 • PT 4	• Relays N, S, W Size 1 • Relays N, S, W Size 2 • Relays N, S, W Size 2 • Relays N, S, W Size 2	• Series RN/RC • Series RN/RC • Series RN/RC
SDS	• HC 2 • HC 4	• K 2 • K 4 • K 4 • K 4	
TEC	• – • Type 1301	• Type 1350 • Type 1360 • Type 1360 • Type 1360	• Type 1210 • Type 1210 • Type 1210
ZETTLER	• – • TEC 1401	• AZ E 20, AZ 420, AZ 420 W • AZ E 21, AZ 421, AZ 421 W • AZ E 21, AZ 421, AZ 421 W • AZ E 21, AZ 421, AZ 421 W	• AZ 1010 – AZ 509 2 C • AZ 1010 – AZ 509 3 C • AZ 1010 – AZ 509 3 C

Relay Sockets for Industry Relays

PT 4 industry relays

4-pole, with test button



Rated data

Contact data	
Contact number and type	4 changeover contacts
Contact version	Single contacts
Contact material	AgNi 90/10, AgNi 90/10 htv
Max. braking capacity AC	1500 VA
Rated voltage	250 V~
Continuous current	6 A / contact
Switch-on current	12 A / contact
Min. contact rating	24V, 10 mA / 20 m, 1 mA htv
Mechanical service life	DC coil > 30x10 ⁶ AC coil > 20x10 ⁶
Response / drop out time	15/10 ms
Bounce time	5 ms
Test voltage	2.5 kV _{eff} coil / contact
Isolation acc. to IEC664	B, 60 V~/75 V
Rated voltage	250 V
Pollution severity	2
Overvoltage category	III
Insulation group / reference voltage	B/250
Approvals	VDE, UL, CSA

Miscellaneous data

Protection class	IP50
Flammability class UL 94	V-0
Ambient temperature	DC coil -40 ... + 70 °C AC coil -40 ... + 70 °C
Weight	30g

Correspond. relay socket

- Relay sockets Type RS 3, RS 4 and RS 14
- Alternatives to ZT 4 see table on page 99

Ordering data


	Type (ZT 4)	Best.-Nr
6 V~	PT 570006	8074650000
12 V~	PT 570012	8054360000
24 V~	PT 570024	1180700000
48 V~	PT 570048	8074670000
60 V~	PT 570060	8074680000
115 V~	PT 570110	8074700000
6 V~	PT 570506	8074710000
12 V~	PT 570512	8074730000
24 V~	PT 570524	1181800000
48 V~	PT 570548	1180900000
60 V~	PT 570560	8074760000
115 V~	PT 570615	1180800000
230 V~	PT 570730	1181100000
Retainer clip for SIEMENS-Relays	PT 28800	8572170000

Relay Sockets for Industry Relays


RS 3

RS 4


RS 14



Relay sockets for DC and AC voltage relays
with fixing foot for TS 32/TS 35x7.5 and TS 35x15



0125661001



Relay type*	Schrack	Schrack	Schrack
	Type PT 5	Type PT 5	Type PT 5
	4-pole	4-pole	4-pole
Contacts on module	2 changeover contacts	4 changeover contacts	4 changeover contacts
Ordering data	Sockettyp	RS 3	RS 4
Relay socket for AC relays (without diode)		0115161001	0116261001
With red LED (230 V~)			
Relay socket for DC relays with suppressor diode and reserve voltage protection (diode 1 N 4007)		0115061001	0116161001
With red LED (24 V~)			0116121001
With green LED (24 V~)		0115011001	
Dimensions			
Relay socket width	35 mm	65 mm	45 mm
Insulation stripping length	7 mm	7 mm	7 mm
Connection data			
Screw connection, solid	0.5...4 mm ²	0.5...4 mm ²	0.5...4 mm ²
Screw connection, flexible	0.5...2.5 mm ²	0.5...2.5 mm ²	0.5...2.5 mm ²
Conductor cross-section	AWG 26...14	AWG 26...14	AWG 26...14
Rated data			
Coil voltage (types without LED)	250 V ₀	250 V ₀	250 V ₀
Contact voltage	250 V~	125 V~	125 V~
Contact current	5 A	5 A	5 A
Accessories	Type	Cat. No.	Qty.
Mounting rail (2 m lengths)	TS 32	0122800000	–
	TS 35x7.5	0383400000	–
	TS 35x15	0498000000	–
End bracket (thickness mm)	EWK 2	0199360000	50
	EW 35	0383560000	50
Insert tag (blanc)**	ESo 7	0515200000	–
Protective strip, transparent**	SSt 7	0515300000	100
Retainer clip for Schrack relays	ZG 28800	0116000000	25


* Relay not included in delivery

Relay Coupler, Relay Sockets Module for Industry Relays

RS 21 RS 23 RS 24



0167161001



Plug-in relay for	Plug-in relay for
Octal socket	submagnal socket
8-pole	11-pole
2 changeov. c. 3 changeov. c. 2 x 3 changeov. c.	

RS 21	RS 23	RS 24
on request	8010061001	on request
0167161001	0188661001	on request

35 mm	40 mm	75.5 mm
7 mm	7 mm	7 mm
0.5...4 mm ²	0.5...4 mm ²	0.5...4 mm ²
0.5...2.5 mm ²	0.5...2.5 mm ²	0.5...2.5 mm ²
AWG 26...14	AWG 26...14	AWG 26...14

250 V0	250 V0	250 V0
250 V~	250 V~	250 V~
6 A	6 A	6 A
Type	Cat. No.	Qty.
TS 32	0122800000	-
TS 35x7.5	0383400000	-
TS 35x15	0498000000	-
EWK 2	0199360000	50
EW 35	0383560000	50
ESo 7	0515200000	-
SSt 7	0515300000	100





With increasing automation, potential separation between the control and field sides of circuits is becoming increasingly important. The control unit being the core of the automation must be electrically safe and free from feedback when coupled with the various sensors and actuators. Opto-coupler are being used in a growing number of applications. They offer the necessary safety and have further advantages such as:


- low power uptake on control side
- high switching frequency
- no contact bounce
- wear-free switching
- insensitive to vibration
- use independent of location
- no mechanical parts
- long life
- high insulation voltage

Because of these features, opto-coupler are an alternative to conventional, mechanical relay interfaces.

For industrial usage, Weidmüller offers modules with various input voltages and housings.

Basic construction of the opto-coupler interface:

The heart of the system is the opto-electronic component (opto-coupler) that effects the coupling.



An important parameter of this type of modules is the CTR = current transfer rate.


The CTR is given in % and is the ratio between the input current I_F and the maximum available output current I_C .

Example: $I_F = 10 \text{ mA}$; $\text{CTR} = 100\%$
 $\Rightarrow I_C = 10 \text{ mA}$.

The CTR is affected by a number of parameters such as:

- Ambient temperature
- efficiency of the luminescence diode
- geometric dimensions within the module

It also drops with time. The result is that the switching levels change due to ageing.




CTR as a function of operating life

To eliminate these effects where possible, Weidmüller opto-coupler use almost exclusively semiconductors which have a long life in terms of CTR.

Moreover, the insulation of a module is highly important, since the actual coupling of the input and output circuits takes place optically. Thus the optical component has to guarantee separation of both circuits even in case of a defect.

Weidmüller opto-coupler comply with DIN VDE 0884 to provide a maximum level of safety.

Appropriate switching circuits need to be included to ensure that the entire component provides reliable separation in accordance with DIN VDE 0106, Part 101.



Circuit diagram of an opto-coupler

Opto-coupler for protective separation or galvanic isolation


The most important precondition for achieving protective separation with opto-electronic coupling modules is the partial discharge test in accordance with DIN VDE 0884. Double or reinforced insulation for protective separation must be discharge proof. High voltage tests, as are usual with relays, cannot be carried out with semi-conductors, because they could lead to the destruction of the semi-conductor. Safe separation for the given rated voltage is applicable to coupling modules that are integrated into opto-couplers if:

- the opto-couplers are tested according to DIN VDE 0884
- clearance and creepage distances on the PCB and connection elements correspond to EN 50 178, DIN VDE 0106 and 0109.


Control side of the opto-coupler interface

3 basic circuits are to be differentiated on the input side of the opto-coupler's interface:

- as a pure **DC input** with polarity protection diode which prevents the opto-coupler from being destroyed if the input polarity is reversed.




- as an **AC/DC input:**



Wrong polarity of the DC input signal is not possible with this switching. The disadvantage of an AC/DC input circuit (driven by DC signal) is the low switching rate since the charging capacitor (CL, necessary for AC-input signal) lowers the max. switching rate.

- pure **AC-Input:**



* Sample circuit

Here, too, the charging capacity lowers the max. switching rate considerably. Weidmüller opto-coupler with AC/DC or AC input signals are designed for 40...60 Hz power supply. With AC-signal input the max. switching rate is below half the power supply frequency.

A high switching rate is not possible, otherwise continuous switching in tune with the power frequency would occur.

Output side of the opto-coupler

Weidmüller opto-coupler are designed and sized for a wide variety of applications. Demands regarding the load side of opto-coupler modules could be:

- power amplification
- signal conditioning
- AC/DC, DC/AC
- short-circuit protection
- interference proof, etc.


To fulfil these requirements, the opto-coupler must contain additional electronic components which determine the functionality of the opto-coupler.

Thus there are 2 basic output variations for opto-coupler

Output as

- 2 pole and
- 3 pole circuits

2-pole DC output



* Wiring example

The 2-pole DC output is comparable to a conventional switch. With this type it is immaterial where the load is in the output circuit. It is, however, important to provide the necessary output supply voltage with the right polarity.




Opto-couplers are normally given with an output voltage supply from 5...48 VDC. These values should not be cut or exceeded on any occasion.

The load current should not be higher than the stated max. output current. Continuously exceeding this value will destroy the output stage.

The derating curve shows the dependency of the output current as a function of the Ambient temperature (see under the respective product on the following pages).

2-pole AC output




A special semiconductor element (TRIAC) in the output stage of the opto-coupler is used to switch AC voltages.

As for the DC-versions the appropriate parameters (such as voltage, frequency, max. load current, ambient temperature) should be given consideration.

A neutral voltage switch ensures that the load is switched only in the voltage zero. To protect against voltage spikes, the modules are always fitted with appropriate protection elements (varistors, RC-combination).

3-pole DC output



This type of output stage requires for safe function a potential-linked output voltage supply with an output that is either positive switching (common reference potential is GND or 0 V) or negative switching (common reference potential is the positive voltage pole).

Standards

Weidmüller opto-coupler comply with the following standards:

EN 50 178
Furnishing of power engineering systems with electronic equipment
DIN VDE 0106 Part 101
Protection against flow of dangerous currents into the human body; basic requirements for reliable separation within electrical equipment.


DIN VDE 0884
Optoelectronic coupling devices for reliable separation

DIN VDE 0109
Insulation coordination within low-voltage system including clearance and creepage distances for equipment


Protective circuit

All opto-coupler have a protective circuit in the output (generally a free-wheeling diode).

To prevent decoupling of interference signals to other leads the load side should be protected.




Protective circuit for DC output




Protective circuit for AC output

Application example



Types of housing for opto-coupler



Weidmüller coupler modules are enclosed in housings that are appropriate for industrial applications. The housings are suitable for fitting onto mounting rails TS 32, TS 35 x 7.5 or TS 35 x 15 in accordance with European Standards EN 50 035 and EN 50 022.

Component housing EG

Weidmüller component housings **EG 1** and **EG 2** are 18 mm wide. The fully enclosed EG housings are fitted with clamping yoke screw connections or push-on blade connectors for attaching wires. Conductors with the following cross-sectional dimensions can be connected:

solid conductors: 0.5...4 mm² or
flexible conductors: 0.5...2.5 mm².

The component housing EG 7 has a special status. It has been specifically designed to accommodate 10-mm slim opto-couplers.

EG 7 opto-coupler modules can be mounted onto TS 32 or TS 35 rails.

The RS EG7 locking socket is also available for the OST opto-couplers.

The fully-enclosed EG 7 housing is fitted with clamping yoke connections.

Conductors with the following cross-sections can be connected:

Component housing EG7: 0.5...1.5 mm²
Locking socket: 0.5...2.5 mm².

Component Housing WAVEBOX

Component housing WAVEBOX

It is important for modern electronics to create a functional housing. Setting and operating functions must be guaranteed, technical demands regarding heat dissipation and EMC properties are to be supported. The ideal design saves space and mounting costs in the switchgear cabinet. Moreover, ergonomics and the design are gaining in importance for high-quality opto-couplers interfaces. The WAVEBOX fulfils these criteria and has the following distinguishing features:

The WAVEBOX is characterised by:

- Optimal width for any application (12.5 mm, 17.5 mm, **22.5 mm**)
- Large component assembly surface; SMD's can be mounted on the solder side
- No tools required for assembly
- Plug-in printed circuit board
- Plug-in cross-connection via ZQV 2.5 N
- Hinged, transparent cover
- BLZ 5.08 screw/plug and socket connector
- BLZF 5.08 optional tension clamp/plug and socket connector
- Marking option with WS tags
- Suitable for snap-fitting on TS 35

Connection systems

Available are BLZ screw-type connectors as well as the BLZF tension clamp system for up to 2.5 mm² flexible conductors for maximum wiring flexibility.

Printed-circuit board removal

This takes place by pushing in the locking hooks in way of the cover and with drawing of the terminal level and printed circuit board from the housing. This must not take place with the supply connected.

Cross-connection

Housings of the same family arranged side by side, can be cross-connected in the base of the housing with the ZQV 2.5 N/2 cross-connector. The cross-connection can be loaded with a current of up to 8 A. By means of this arrangement, the supply voltage can be cross-connected from one electronic module to another. The voltage transferred from the cross-connection to the terminal level must not exceed 50 V.

Air vents

Slanted air vents control the temperature and ventilate the housing base.

Modular system

PLUGSERIES/PLUGOpto

is a new generation of pluggable SSR. The core is an innovative relay socket **PXS** or **PXZ**.


Both products combine Weidmüller functionality and experience gained from the relay and terminal business.

The PLUGOpto is the ideal connection technology between SSR and the application.

Modular principle

The new PLUGSERIES is particularly service friendly. Commercially available SSRs are simply plugged: holding / dismantling clamps guarantee secure mounting; LED indicators with free-wheeling diode can be simply plugged.

- Easy plugging of SSR
 - suitable for the standard design and RT
- Independent connection technology: screw or tension clamp
- Rated cross-section 0.5 2.5 mm²
- Robust holding / dismantling clamp
- Control voltage 24 Vac/Vdc
- Rated switching voltage 24 Vdc, 24 Vac/Vdc, 230 Vac
- Up to 5 A continuous current
- Low wiring costs thanks to ZQV 2.5N (pluggable) cross-connectors
- Service-friendly modular system
 - relay socket, LED indicator
 - holding clamp and SSR
 - mount onto TS 35
 - marking options with WS marking tags and holding clamps
- Pluggable LED indicator with free-wheeling diode



Weidmüller locking socket RS

The locking socket with opto-couplers RS 40 have a width of 11.2 mm. The modules on locking socket profiles are equipped with clamping yoke (screw connection) units for conductor connection.

Connectable are:

solid conductors: 0.5...4 mm²

flexible conductors: 0.5...2.5 mm².

Locking socket with multiple interfaces

Multiple interfaces RSM are optionally available assembled with 4, 8 or 16 plug-gable opto-couplers. Versions are available with joint positive and negative potentials in order to reduce wiring on the input side.

PCB clamping yoke screw connector elements have clamping yoke units for connecting conductors with the following cross-sections:

solid conductors: 0.5...4 mm²


flexible conductors: 0.5...2.5 mm²

Variants of the RSM couplers have male connector blocks on the input side for connecting pre-assembled cables, in accordance with IEC 603-1/DIN 41651.



Mini-coupler

All parts of the mini-coupler DKR and DKO meet the specifications for a design that is as slim as possible. The sensational width of a mere 6 mm can be achieved by employing the latest surface-mounted devices (SMD). There are 4 or 5 screw connections available which accept conductors with cross-sectional dimensions from 0.5...4 mm². The mini-coupler offer a wide range of options for coupling digital sensor/actuator signals between automation devices and the process stage. With DKO opto-coupler, signals from the field with different voltages can be picked up and unified.



Miniconditioner MCZ

The MCZ-housing is distinguished as one of the slimmest component-housings. A tool width of only 6 mm reduces space requirements in cabinets.

The MCZ is characterized by:

- Tension-clamp connection
 - integrated cross-connection option for input and output minimise wiring costs.
- The mini conditioner MCZO (opto-couplers) have 4 and 5 Z-tension spring connections. The clampable conductor cross-section is 0.5...1.5 mm².

CE-marking

Weidmüller opto-coupler are marked with the CE symbol and comply with the requirements of EN 50 081 Part 1 and EN 50 082 Part 2. They can therefore be used for both industrial as well as for commercial and light industry.

Appropriate ESD measures should be taken during installation. If connecting wires are particularly long, overvoltage protection should be provided in order to prevent interference from electrical disturbance in the atmosphere.

Opto-coupler

Electronic switching

Output											
24 V											
		5 - 48 V ≤ 20 mA	5 - 48 V ≤ 0.1 A	5 - 48 V ≤ 0.5 A	5 - 48 V ≤ 20 mA	5 - 48 V ≤ 2.5 A	5 - 48 V ≤ 5 A	24 - 250 V ≤ 3.5 A	5 - 48 V ≤ 0.1 A	5 - 48 V ≤ 0.1 A	5 - 48 V ≤ 0.1 A
Housing		5 - 48 V ≤ 20 mA	5 - 48 V ≤ 0.1 A	5 - 48 V ≤ 0.5 A	5 - 48 V ≤ 20 mA	5 - 48 V ≤ 2.5 A	5 - 48 V ≤ 5 A	24 - 250 V ≤ 3.5 A	5 - 48 V ≤ 0.1 A	5 - 48 V ≤ 0.1 A	5 - 48 V ≤ 0.1 A
EG		● 0558160000 Page 122	● 0609860000 Page 123				● 8220870000 Page 130				
WAVESERIES WOS							● 8275190000 Page 126		● 8237720000 Page 128		
EG 7						● 8269050000 Page 131	● 8281720000 Page 131				
RS 40			● 8092530000 ● 8234580000 Page 132								
		● 1160961001 ● 1161761001 ● 1177860000 Page 137	● 1117461001 ● 8065031001 ● 1119460000 Page 137								
RSM									● 1123861001 ● 1123761001 ● 1125161001 ● 8017581001 ● 1124900000 ● 1170200000 ● 1153200000 ● 1121300000 Page 139	● 1124261001 ● 1125261001 ● 8003671001 ● 1124900000 ● 1170200000 ● 1153200000 ● 1121300000 ● 8021391001 ● 1124900000 ● 1170200000 ● 1153200000 ● 1121300000 Page 139	● 1124661001 ● 8018220000 ● 1124900000 ● 1153200000 ● 1121300000 ● 8082471001 ● 1124900000 ● 1170200000 ● 1153200000 ● 1121300000 Page 139
DKO 32		● 8008090000 Page 116		● 8019580000 Page 117							
DKO 35		● 8008150000 Page 116 ● 8028300000 ● 8215640000 ● 8248790000 Page 117		● 8019590000 Page 117 ● 8215630000 Page 118		● 8215600000 ● 8181990000 Page 118					
DKO 35/32		● 8228640000 Page 119				● 8228630000 Page 118					
MCZ O		● 8365940000 Page 114	● 8398940000 Page 115			● 8287730000 Page 114					
PLUGSERIES POS/POZ		● 8324610000 (5 V TTL) Page 115									
							● 8610840000 ● 8610920000 ● 8610900000 ● 8610970000 ● 8610890000 ● 8610960000 ● 8615600000 ● 8615640000 ● 8615620000 ● 8615650000 Page 134	● 8610860000 ● 8610930000 ● 8610910000 ● 8610980000 ● 8615590000 ● 8615630000 Page 134			

Reliable
separation

● 24 V dc
● 24 Vuc/ac

● Replacement opto-coupler dc and ac/dc
● Empty socket

Opto-coupler

Electronic switching

		Output									
											
Housing		5 - 48 V ≤ 20 mA	5 - 48 V ≤ 0.1 A	5 - 48 V ≤ 0.5 A	5 - 48 V ≤ 20 mA	5 - 48 V ≤ 2.5 A	5 - 48 V ≤ 5 A	24 - 250 V ≤ 3.5 A	5 - 48 V ≤ 0.1 A	5 - 48 V ≤ 0.1 A	5 - 48 V ≤ 0.1 A
EG 7			● 8092550000 Page 132								
			● 8234590000 Page 132								
RS 40			● 1161061001 Page 137								
			● 1161860000 Page 137								
DKO 35		● 8151230000 Page 120									

		Output									
											
Housing		5 - 48 V ≤ 20 mA	5 - 48 V ≤ 0.1 A	5 - 48 V ≤ 0.5 A	5 - 48 V ≤ 20 mA	5 - 48 V ≤ 2.5 A	5 - 48 V ≤ 5 A	24 - 250 V ≤ 3.5 A	5 - 48 V ≤ 0.1 A	5 - 48 V ≤ 0.1 A	5 - 48 V ≤ 0.1 A
EG			● 0131860000 Page 123								
WAVESERIES WOS				● 8235180000 Page 125			● 8296250000 Page 126	● 8259950000 Page 127	● 8275360000 Page 128		
EG 7			● 8092570000 ● 8234600000 ● 8397420000 ● 8315590000 Page 133								
RS 40			● 1161161001 ● 1161960000 Page 137								
DKO 32		● 8027980000 Page 119									
DKO 35		● 8077860000 Page 119 ● 8131660000 Page 120									
MCZ O			● 8421060000 Page 114								

Opto-coupler

Electronic switching

		Output									
		230 V 									
Housing		5 - 48 V ≤ 20 mA	5 - 48 V ≤ 0.1 A	5 - 48 V ≤ 0.5 A	5 - 48 V ≤ 20 mA	5 - 48 V ≤ 2.5 A	5 - 48 V ≤ 5 A	24 - 250 V ≤ 3.5 A	5 - 48 V ≤ 0.1 A	5 - 48 V ≤ 0.1 A	5 - 48 V ≤ 0.1 A
EG			● 0546360000 Page 123								
WAVESERIES WOS				● 8275380000 Page 125			● 8275220000 Page 126	● 8275400000 Page 127	● 8275340000 Page 128		
EG 7			● 8092590000 ● 8234610000 ● 8387580000 ● 8394990000 Page 133								
RS 40			● 1161461001 ● 1162060000 ● 8182690000 Page 137								
DKO 32	● 8008100000 Page 119										
DKO 35	● 8008160000 Page 119										
MCZ O	● 8421380000 Page 114										

● 230 V_{uc/ac}

Opto-coupler

Electronic switching

Housing	Output									
	5 - 48 V ≤ 20 mA	5 - 48 V ≤ 0.1 A	5 - 48 V ≤ 0.5 A	5 - 48 V ≤ 20 mA	5 - 48 V ≤ 2.5 A	5 - 48 V ≤ 5 A	24 - 250 V ≤ 3.5 A	5 - 48 V ≤ 0.1 A	5 - 48 V ≤ 0.1 A	5 - 48 V ≤ 0.1 A
EGO	● 8011250000 Page 122	● 0114260000 Page 122								
WAVESERIES WOS			● 8275500000 Page 124							
EGO 7		● 8092510000 ● 8234570000 Page 132								
RS 40		● 1118760000 ● 1161660000 Page 137								
RSM O								● 8017581001 ● 1121200000 ● 1124800000 Page 139	● 8003671001 ● 1121200000 ● 1124800000 ● 8021391001 ● 1121200000 ● 1124800000 Page 139	● 8018221001 ● 1121200000 ● 1124800000 ● 8082471001 ● 1121200000 ● 1124800000 Page 139
DKO 35		● 8184030000 Page 116								
3...60 V										
EGO, 3...5 V	● 0266160000 Page 122									
EGO, 3...12 V	● 8011250000 Page 122									
WAVESERIES WOS 5 V					● 8275430000 Page 124					
WAVESERIES WOS 5 V TTL		● 8275210000 Page 129								
WAVESERIES WOS 3.5 - 15 V		● 8275390000 Page 124								
WAVESERIES WOS 12 - 28 V		● 8275450000 Page 129								
WAVESERIES WOS 15 - 60 V		● 8237730000 Page 124	● 8237730000 Page 124				● 8275440000 Page 127			
EGO, 7.5 V			● 8092490000 ● 8234560000 Page 132							
RS 40, 5 V	● 1118861001 ● 1161560000 Page 137									
RSM, 5 V								● 1123661001 ● 1121100000 Page 139	● 1124061001 ● 1121100000 Page 139	● 1124461001 ● 1121100000 Page 139
DKO 32	● 8018620000 Page 116									
DKO 35	● 8018630000 Page 116	● 8067100000 Page 120								
DKO 32/35		● 8228650000 Page 116								

Reliable
separation


● 12 Vdc
● 12 Vuc/ac

● Replacement opto-coupler dc and ac/dc
● Empty socket

Digital signal
processing

Opto-coupler in component housing mini coupler MCZ

Opto-couplers MCZ O



Schematic circuit diagram

- This module can be used:
- between controller and sensor, for feedback of different statuses.
 - for direct switching of load currents up to a Adc, but also provides "online" information about the behaviour of the load current.



The MCZ-O modules do have following features:

- Reduction of installation- and power-up times by using the proved tension-clamp technology
- Pluggable cross-connection units in the input side reduce wiring costs
- 6 mm width

MCZ O 24 Vac/dc 20 mA



Derating curve
rated to ambient temperature

a = rowed without clearances on the mounting rail
b = rowed with clearances ≥ 20 mm





MCZ O 24 Vac/dc 2 A²



Output current



MCZ O 120 Vac/dc



MCZ O 230 Vac



Ordering data


For TS 35

Technical data

Input	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.
Input voltage	MCZ O 24 Vac/dc	8365940000	MCZ O 24 Vac/dc	8287730000	MCZ O 120 Vac/dc	8421060000	MCZ O 230 Vac	8421380000
Making threshold	24 Vac/dc $\pm 10\%$ (21.6...26.4ac/dc)		24 Vac/dc $\pm 20\%$ (19.2...28.8ac/dc)		120 Vac/dc -15 % +5 %		230 Vac -15 % +5 %	
Input current at U_{nom}	ac: 14.1 Vac / dc: 16.8 Vdc		approx. 16 Vac/dc		approx. 65 Vac/approx. 70 Vdc		approx. 170 Vac	
Rated input consumption	ac: 11.4 mA / dc: 9.6 mA		ac: 13 mA / dc: 12 mA		approx. 3 mA		ac: 10 mA	
Max. input frequency	ac: 5 Hz duty factor 1:2		ac: approx. 220 mW					
Capacity working resistance to reduction at dissipated energy	dc: 10 Hz duty factor 1:2		dc: ca. 195 mW		ac: 5 Hz duty factor 1:2		ac: 5 Hz duty factor 1:2	
Functionality	no		ac: ≤ 10 Hz duty factor 1:2		dc: 20 Hz duty factor 1:2		no	
Output	operating indication		dc: ≤ 30 Hz duty factor 1:2		no		yes	
Supply voltage	5...48 Vdc		operating indication		operating indication		operating indication	
Max. output current	20 mA		24 Vdc $\pm 20\%$ (19.2...28.8 Vdc)		5...48 Vdc		5...48 Vdc	
Voltage drop at max. load current	≤ 1 V		2 A		50 mA		20 mA	
Pulse duration, limiting overload current (not periodic)	≤ 150 mA / 10 ms				< 1.6 V		< 1.6 V	
Reverse current (close-circuit current) at $U_{out} = 48$ V	max. 0.16 mA				< 150 mA / 10 ms		< 150 mA / 10 ms	
Reverse polarity protection					max. 0.16 mA		max. 0.16 mA	
Free-wheel diode	present		present					
- typ. Switch-on delay (at ac phase position dependent)	ac: ≤ 10 ms / dc: ≤ 20 ms		external necessary		present		present	
- typ. Switch-off delay (at ac phase position dependent)	ac: ≤ 45 ms / dc: ≤ 40 ms				≤ 30 ms			
Short-circuit proof			yes		≤ 40 ms			
Insulation coordin./Reliable separation acc. to EN 50 178								
Rated voltage	300 V		300 V		300 V		300 V	
Rated impulse voltage	6 kV		6 kV		6 kV		6 kV	
Overvoltage category	III		III		III		III	
Pollution severity	2		2		2		2	
Clearances and creepage distances	≥ 5.5 mm		≥ 5.5 mm		≥ 5.5 mm		≥ 3 mm	
Insulation coordin.- and voltage proof, input/output mounting rail	4 kV _{eff} / 1 min		4 kV _{eff} / 1 min		4 kV _{eff} / 1 min		4 kV _{eff} / 1 min	
Opto-coupler	acc. to VDE 0884		acc. to VDE 0884		acc. to VDE 0884		acc. to VDE 0884	
Ambient temperature rowed on mounting rail without clearances	-25 °C...+50 °C		-25 °C...+40 °C		-25 °C...+40 °C		-25 °C...+50 °C	
Ambient temperature rowed with clearances ≥ 20 mm	-25 °C...+50 °C		-25 °C...+50 °C		-25 °C...+50 °C		-25 °C...+50 °C	
Storage temperature	-40 °C...+85 °C		-40 °C...+60 °C		-40 °C...+60 °C		-40 °C...+85 °C	
Conductor	AWG 22...12		AWG 22...12		AWG 22...12		AWG 22...12	
Conductor cross-section	1.5 mm ²		1.5 mm ²		1.5 mm ²		1.5 mm ²	
Approvals	CE, UL, CSA		CE, UL, CSA		CE, UL, CSA		CE, UL, CSA	
Overall width	6 mm		6 mm		6 mm		6 mm	
Accessories	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.
End plate	AP MCZ 1.5	8389030000	AP MCZ 1.5	8389030000	AP MCZ 1.5	8389030000	AP MCZ 1.5	8389030000
Further accessories, dimensions and connection data	Page 305		Page 305		Page 305		Page 305	

Opto-coupler in component housing mini coupler MCZ

Opto-couplers MCZ O



This module can be used:




- 1* - between controller and actuator, for the signal conversion of 24 Vdc to 5 VTTL
- 2* - between controller and actuator, for the signal conversion of 5 VTTL to 5...48 Vdc

MCZ O 24 Vdc/5 VTTL^{1*}




Derating curve
rated to ambient temperature

a = rowed on the mounting rail without clearances
b = rowed with clearances ≥ 20 mm

MCZ O 5 V TTL/5...48 Vdc^{2*}



Schematic circuit diagram



Ordering data

For TS 35

Type Cat. No.
MCZ O 24 Vdc **8324610000**

Type Cat. No.
MCZ O 24 Vdc **8398940000**

Technical data

Input

Supply voltage	
Input voltage	24 Vdc $\pm 16\%$ (20...28 Vdc)
Making threshold	approx. 17 Vdc
Input current at U_{nom}	4.7 mA (2.9...6.5 mA)
Rated input consumption	dc: 112 mW
Max. input frequency	100 kHz switching ratio 1:2 50 kHz switching ratio 1:10
Min. input impulse width	2 µs

Output

Supply voltage	5 V (4.75...5.25 V)
Output voltage	5 V TTL (4.75...5.25 V)
Max. output current	8 mA, Fan Out = 20 LS-TTL
Voltage drop at max. load current	
Pulse duration, limiting overload current (not periodic)	
Reverse current (static current) at $U_{out} = 48$ V	
Reverse polarity protection	
Free-wheel diode	
- typ. switch-on delay	1 µs (at 20 Vdc)
- typ. switch-off delay	2.5 µs (at 28 Vdc)

5 Vdc $\pm 5\%$
5 V TTL
$I_{LE} = 1 \mu A / I_{HI} = 8 \mu A$
2.4 kHz
5...48 Vdc
100 mA
≤ 1.8 V
present (input)
present
approx. 27 µs
approx. 210 µs

Insulation coordin./Reliable separation acc. to EN 50178

Rated voltage	300 V	300 V
Rated impulse voltage	6 kV	6 kV
Overvoltage category	III	III
Pollution severity	2	2
Clearances and creepage distances	≥ 5.5 mm	≥ 5.5 mm
Insulation coordination/dielectric strength I/O to TS	4 kV _{eff} / 1 min	4 kV _{eff} / 1 min
Opto-coupler	acc. to VDE 0884	acc. to VDE 0884
Ambient temperature rowed on mounting rail without clearances	-25 °C...+40 °C	-25 °C...+50 °C
Ambient temperature rowed with clearances ≥ 20 mm	-25 °C...+50 °C	-25 °C...+50 °C
Storage temperature	-40 °C...+60 °C	-40 °C...+85 °C
Conductor	AWG 22...12	AWG 22...12
Conductor cross-section	1.5 mm ²	1.5 mm ²
Approvals	CE, UL, CSA	CE, UL, CSA
Overall width	6 mm	6 mm
Accessories	Type Cat. No.	Type Cat. No.
End plate	AP MCZ 1.5 8389030000	AP MCZ 1.5 8389030000
Further accessories, dimensions and connection data	Page 305	Page 305

Opto-coupler in component housing mini coupler DK

Opto-couplers DKO


DKO 5 Vdc

DKO 5 VTTL






DKO 12 Vdc

DKO 24 Vac/dc

- Coupling of digital sensor-/actuator-signals between PLC and process
- Low cost solution for level- and potential-equalization
- Low input power
- Screw clamp connection technology
- 6 mm width



Schematic circuit diagram



Ordering data	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.
For TS 32	Y	DKO 5 Vdc 8018620000					DKO 24 Vac/dc 8008090000	
For TS 35	W	DKO 5 Vdc 8018630000			DKO 12 Vdc 8184030000		DKO 24 Vac/dc 8008150000	
With combination foot TS 32/TS 35								
Technical data	Input: bottom		Input: bottom		Input: bottom		Input: bottom	
Input voltage	5 Vdc $\pm 5\%$		5 VTTL		12 Vdc $\pm 20\%$		24 Vac/dc $\pm 10\%$	
Switch-on voltage	2.4 Vdc				approx. 7 V		112.8 Vac/16.8 Vdc	
Input current	≤ 10 mA		1 μ A		11 mA		11.4 mAac/9.6 mAac	
Max. input power	50 mW				130 mW		280 mVA/230 mW	
Output voltage	5...48 Vdc		5...48 Vdc		24 Vdc $\pm 10\%$		5...48 Vdc	
Max. output current	20 mA		100 mA		50 mA		20 mA	
Min. output current	50 μ A		50 μ A		50 μ A		50 μ A	
Max. switching frequency; switching ratio 1: 2	20 Hz		3 kHz		10 kHz		ac: 5 Hz dc: 10 Hz	
Switch-on delay	≤ 15 μ s		approx. 27 μ s		1 μ s		≤ 15 ms at dc	
Switch-off delay	≤ 70 μ s		approx. 35 μ s		2.5 μ s		≤ 25 ms at dc	
Voltage drop at max. load	≤ 1.6 V		≤ 1.6 V		≤ 1 V		≤ 1 V	
Insulation coordination to EN 50 178								
Rated voltage	150 V		300 V		300 V		300 V	
Rated impulse voltage	4 kV		6 kV		6 kV		4 kV	
Overvoltage category	IV		IV		IV		III	
Pollution severity	2		2		2		2	
Clearances and creepage distances	≥ 4 mm		≥ 5.5 mm		≥ 5.5 mm		≥ 4 mm	
Operating temperature	without clearances	-25 °C...+50 °C	-25 °C...+50 °C		-25 °C...+50 °C		-25 °C...+40 °C	
	with clearances	-25 °C...+50 °C	-25 °C...+50 °C		-25 °C...+50 °C		-25 °C...+50 °C	
Storage temperature		-40 °C...+85 °C	-40 °C...+85 °C		-40 °C...+85 °C		-40 °C...+85 °C	
Conductor		AWG 22...12	AWG 22...12		AWG 22...12		AWG 22...12	
Conductor cross-section		0.5...4 mm ²	0.5...4 mm ²		0.5...4 mm ²		0.5...4 mm ²	
Overall width		6 mm	6 mm		12 mm		6 mm	
Accessories	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.
End plate	AP DKT4	0687560000	AP DK5	8268870000	AP DKT4	0687560000	AP DKT4	0687560000
Further accessories, dimensions and connection data	Page 305		Page 305		Page 305		Page 305	

Opto-coupler in component housing mini coupler DK


Opto-couplers DKO

DKO 24 Vdc






DKO 24 Vdc

DKO 24 Vdc

DKO 24 Vdc



Schematic circuit diagram



Ordering data	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.
For TS 32	Y							
For TS 35	W							
Technical data	DKO 24 Vdc	8028300000	DKO 24 Vdc	8215640000	DKO 24 Vdc	8248790000	DKO 24 Vdc	8019580000
Input voltage	24 Vdc ±10 %		24 Vdc ±10 %		24 Vdc ±10 %		24 Vdc ±10 %	
Switch-on voltage	approx.19 V/7.5 mA		approx.19 V/7.5 mA		approx.19 V/7.5 mA		approx.17 V	
Input current	≤15 mA		≤15 mA		≤8.5 mA		6 mA	
Max. input power	360 mW		360 mW		204 mW		145 mW	
Output voltage	5...48 Vdc		5...48 Vdc		5...48 Vdc		5...48 Vdc	
Max. output current	20 mA		20 mA		20 mA		500 mA	
Min. output current	50 µA		50 µA		50 µA		50 µA	
Max. switching frequency; switching ratio 1: 2	3 kHz		3 kHz		3 kHz		200 Hz	
Switch-on delay	approx.50 µs		approx.50 µs		approx.50 µs		approx.40 µs	
Switch-off delay	approx.80 µs		approx.80 µs		approx.80 µs		approx.65 µs	
Voltage drop at max. load	≤900 mV		≤900 mV		≤900 mV		≤800 mV	
Insulation coordination to EN 50 178								
Rated voltage	300 V		300 V		300 V		300 V	
Rated impulse voltage	4 kV		4 kV		4 kV		4 kV	
Overvoltage category	II		II		III		II	
Pollution severity	2		2		2		2	
Clearances and creepage distances	≥4 mm		≥4 mm		≥4 mm		≥4 mm	
Operating temperature	without clearances	-25 °C...+40 °C	-25 °C...+40 °C		-25 °C...+40 °C		-25 °C...+40 °C	
	with clearances	-25 °C...+50 °C	-25 °C...+50 °C		-25 °C...+50 °C		-25 °C...+50 °C	
Storage temperature		-40 °C...+85 °C	-40 °C...+85 °C		-40 °C...+85 °C		-40 °C...+85 °C	
Conductor		AWG 22...12	AWG 22...12		AWG 22...12		AWG 22...12	
Conductor cross-section		0.5...4 mm ²	0.5...4 mm ²		0.5...4 mm ²		0.5...4 mm ²	
Overall width		6 mm	6 mm		6 mm		6 mm	
Accessories	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.
End plate	AP DKT4	0687560000	AP DKT4	0687560000	AP DKT4	0687560000	AP DKT4	0687560000
Further accessories, dimensions and connection data	Page 305		Page 305		Page 305		Page 305	

Opto-coupler in component housing mini coupler DK

Opto-couplers DKO


- Coupling of digital sensor-/actuator-signals between PLC and process
- Low cost solution for level- and potential-equalization
- Low input power
- Screw clamp connection technology
- 6 mm width

DKO 24 Vdc





DKO 24 Vdc

DKO 24 Vdc


DKO 24 Vac/dc



Schematic circuit diagram



Mode: green → Load current $\geq 500\text{mA}$
yellow → Idling
red → Short circuit



Ordering data	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.
For TS 32	Y							
For TS 35	W							
With combination foot TS 32 / TS 35								
Technical data	DKO 24 Vdc	8215630000	DKO 24 Vdc	8181990000	DKO 24 Vdc	8215600000	DKO 24 Vac/dc	8228630000
Input voltage	24 Vdc $\pm 10\%$		24 Vdc $\pm 10\%$		24 Vdc $\pm 10\%$		24 Vdc/dc $\pm 20\%$	
Switch-on voltage	approx. 17 Vdc		approx. 18 Vdc		approx. 18 Vdc		approx. 16 Vdc/dc	
Input current	6 mA		12 mA		12 mA		13 mAac/12 mAac	
Max. input power	145 mW		290 mW		290 mW		220 mVA/195 mW	
Output voltage	5...48 Vdc		24 Vdc $\pm 10\%$		24 Vdc $\pm 10\%$		24 Vdc $\pm 20\%$	
Max. output current	500 mA		2 A		2 A		2 A	
Min. output current	50 μA							
Max. switching frequency; switching ratio 1: 2	200 Hz		100 Hz		100 Hz		ac: 10 Hz dc: $\leq 30\text{ Hz}$	
Switch-on delay	approx. 40 μs						2 ms	
Switch-off delay	approx. 65 μs						7 ms	
Voltage drop at max. load	$\leq 800\text{ mV}$							
Insulation coordination to EN 50 178								
Rated voltage	300 V		300 V		300 V		300 V	
Rated impulse voltage	4 kV		4 kV		4 kV		6 kV	
Overvoltage category	III		III		III		IV	
Pollution severity	2		2		2		2	
Clearances and creepage distances	$\geq 4\text{ mm}$		$\geq 3\text{ mm}$		$\geq 3\text{ mm}$		$\geq 5.5\text{ mm}$	
Operating temperature	without clearances with clearances	-25 °C...+40 °C -25 °C...+50 °C	-25 °C...+40 °C -25 °C...+50 °C	-25 °C...+40 °C -25 °C...+50 °C	-25 °C...+40 °C -25 °C...+50 °C	-25 °C...+40 °C -25 °C...+50 °C	-25 °C...+40 °C -25 °C...+50 °C	
Storage temperature		-40 °C...+85 °C	-40 °C...+85 °C	-40 °C...+85 °C	-40 °C...+85 °C	-40 °C...+85 °C	-40 °C...+85 °C	
Conductor	AWG 22...12		AWG 22...12		AWG 22...12		AWG 22...12	
Conductor cross-section	0.5...4 mm ²		0.5...4 mm ²		0.5...4 mm ²		0.5...4 mm ²	
Overall width	6 mm		12 mm		12 mm		6 mm	
Accessories	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.
End plate	AP DKT4	0687560000	AP DKT4	0687560000	AP DKT4	0687560000	AP DK 5	8268870000
Further accessories, dimensions and connection data	Page 305		Page 305		Page 305		Page 305	


Opto-coupler in component housing mini coupler DK

Opto-couplers DKO





DKO DK5 24 Vdc

DKO 115 Vac/dc

DKO 230 Vac/dc





Schematic circuit diagram






Ordering data		Type	Cat. No.	Type	Cat. No.	Type	Cat. No.
For TS 32	Y			DKO 115 Vac/dc	8027980000	DKO 230 Vac/dc	8008100000
For TS 35	W			DKO 115 Vac/dc	8077860000	DKO 230 Vac/dc	8008160000
With combination foot TS 32/TS 35		DKO 24 Vdc	8228640000				
Technical data		Input: top		Input: bottom		Input: bottom	
Input voltage		24 Vdc $\pm 20\%$		115 Vac/dc $\pm 5\%$ -15 %		230 Vac/dc $\pm 5\%$ -15 %	
Switch-on voltage		approx. 17 Vdc		approx. 65 Vac/approx. 66 Vdc		approx. 130 Vac/approx. 140 Vdc	
Input current		4.7 mA		2.65 mAac/3 mAac		1.8 mAac/1.7 mAac	
Max. input power		112 mW		390 mVA/350 mW		395 mVA/370 mW	
Output voltage		5 VTTL		5...48 Vdc		5...48 Vdc	
Max. output current		8 mA, Fan Out = 20 LS-TTL		50 mA		20 mA	
Min. output current						50 μ A	
Max. switching frequency; switching ratio 1: 2		100 kHz 1:2/50 kHz 1:10		ac: 5 Hz/dc: 20 Hz		ac: 5 Hz/dc: 20 Hz	
Switch-on delay		1 μ s		17.4 ms		20 ms	
Switch-off delay		2.5 μ s		27.4 ms		20 ms	
Voltage drop at max. load				<1.6 V		<1.6 V	
Insulation coordination to EN 50 178							
Rated voltage		300 V		300 V		300 V	
Rated impulse voltage		4 kV		6 kV		4 kV	
Overvoltage category		III		IV		III	
Pollution severity		2		2		2	
Clearances and creepage distances		≥ 5.5 mm		≥ 5.5 mm		≥ 3 mm	
Operating temperature	without clearances	-25 °C...+40 °C		-25 °C...+40 °C		-25 °C...+50 °C	
	with clearances	-25 °C...+50 °C		-25 °C...+50 °C		-25 °C...+50 °C	
Storage temperature		-25 °C...+85 °C		-40 °C...+85 °C		-40 °C...+85 °C	
Conductor		AWG 22...12		AWG 22...12		AWG 22...12	
Conductor cross-section		0.5...4 mm ²		0.5...4 mm ²		0.5...4 mm ²	
Overall width		6 mm		6 mm		6 mm	
Accessories		Type	Cat. No.	Type	Cat. No.	Type	Cat. No.
End plate		AP DK5	8268870000	AP DKT4	0687560000	AP DKT4	0687560000
Further accessories, dimensions and connection data		Page 305		Page 305		Page 305	

DKO 35 125 Vdc



Schematic circuit diagram



Ordering data	
For TS 32	y
For TS 35	w
With combination foot TS 32 / TS 35	
Technical data	
Input voltage	48 Vdc ±10 %
Input current	3.7 mA ±20 %
Input nominal power	178 mW
Total power loss	400 mW
Making threshold	approx.32 Vdc
Input reverse voltage	max. 1 kV
Output voltage	5...28 Vdc
Output current	max. 20 mA
Voltage drop at max. load	1.6 V
Feature of output circuit	Disconnection plug
Indication	LED red
Dielectric strength input/output	3.75 kV _{eff} / 5.3 kVdc
Dielectric strength to mounting rail	4 kV _{eff}
Clearances and creepage distances	>5 mm
Operating temperature	-25 °C...+50 °C
Storage temperature	-40 °C...+60 °C
Conductor	AWG 22...12
Conductor cross-section	0.5...4 mm²
Overall width	6 mm
Accessories	
End plate	Type Cat. No.
	AP DKT4 0687560000

Opto-coupler in component housing mini coupler DK

Opto-couplers DKO S0 signal sensor

Application example:

Signals for consumers are normally transferred via an interface. Generally, this interface must conform with DIN 43867 (interface for signal transmission). There must be a differentiation between the passive interface and active S0 interface. The actual signals, that are correspondingly proportional to the relevant consumption (electrical energy, gas consumption, water, district heating, etc.) are shown at measuring sensors (electric meter, etc.) The interface itself is purely passive (acceptor) and must be supplied via a source. The source for providing the current is built into the active interface. The following threshold values are specified:

$$I_{\max} = 27 \text{ mAdc}$$

$$U_{\max} = 27 \text{ Vdc}$$

$$f_{\max} = 16.66 \text{ Hz}$$


For the recognition of the corresponding consumption signals, the following currents are integrated:

ON (active) -> 10...27 mA
Off (inactive) -> 0...2 mA


The module accepts the input from the signal sensor and outputs the opto-decoupled output signal, i. e. galvanically isolated.

DKO switching amplifiers/opto-couplers for Namur initiators

DKO DK4 S0




Schematic circuit diagram



DKO

Schematic circuit diagram



Ordering data	
For TS 32	y
For TS 35	w
With combination foot TS 32 / TS 35	
Technical data	
Input	
Input voltage	24 Vdc $\pm 10\%$
Input current	$\leq 13 \text{ mA}$
Pulse generator	Specification acc. to DIN 43864 (current interface for connection to pulse generator acc. to DIN 43864)
Output	
Output voltage	5...48 Vdc
Output current	max. 100 mA
Voltage proof input-output/mounting rail	4 kV _{eff}
Insulation coordination to DIN VDE 0160, Draft 11/94	
Rated voltage	300 V
Rated impulse voltage	6 kV
Overvoltage category	IV
Pollution severity	2
Clearances and creepage distances	$\geq 5.5 \text{ mm}$
Operating temperature	without clearances -25 °C...+40 °C with clearances -25 °C...+50 °C
Storage temperature	-40 °C...+60 °C
Conductor	AWG 22...12
Conductor cross-section	0.5...4 mm ²
Overall width	12 mm
Accessories	
End plate	AP DKT4 0687560000

Type	Cat. No.
DKO DK4 S0	8467030000
DKO DK4 S0	8100180000
Technical data	
Input	
Input voltage	24 Vdc $\pm 10\%$
Input current	$\leq 13 \text{ mA}$
Reverse polarity protection	Specification acc. to DIN 43864 (current interface for connection to pulse generator acc. to DIN 43864)
NAMUR-Input (N+ and N-)	
Switching frequency	
Switch-on delay	
Switch-off delay	
Input (E+ and 0)	
Switch-on point	
Switch off-point	
Current consumption	
Max. switching frequency	
Switch-on delay	
Switch-off delay	
Output (A+ and A-)	
Output voltage	5...30 Vdc
Output current	max. 100 mA
Switching capacity	max. 3 W
Internal voltage drop	max. 1 V
Protective measure	Free-wheel. diode btwn. A+...A-
Voltage proof input-output/mounting rail	4 kV _{eff}
Operating temperature	without clearances -25 °C...+40 °C with clearances -25 °C...+50 °C
Storage temperature	-40 °C...+60 °C
Conductor	AWG 22...12
Conductor cross-section	0.5...4 mm ²
Overall width	12 mm
Accessories	
End plate	AP DKT4 0687560000

Ordering data	
For TS 32	y
For TS 35	w
With combination foot TS 32 / TS 35	
Technical data	
Input	
Input voltage	24 Vdc $\pm 20\%$
Input current	$\leq 35 \text{ mA}$
Reverse polarity protection	up to 1 kV available
NAMUR-Input (N+ and N-)	
Switching frequency	300 Hz f. pulse duty factor 1:1
Switch-on delay	approx. 45 μs
Switch-off delay	approx. 450 μs
Input (E+ and 0)	
Switch-on point	approx. 18 V
Switch off-point	ca 15 V
Current consumption	< 5 mA
Max. switching frequency	300 Hz f. pulse duty factor 1:1
Switch-on delay	approx. 20 μs
Switch-off delay	approx. 400 μs
Output (A+ and A-)	
Output voltage	5...30 Vdc
Output current	max. 100 mA
Switching capacity	max. 3 W
Internal voltage drop	max. 1 V
Protective measure	Free-wheel. diode btwn. A+...A-
Voltage proof input-output/mounting rail	4 kV _{eff}
Operating temperature	without clearances -25 °C...+40 °C with clearances -25 °C...+50 °C
Storage temperature	-40 °C...+60 °C
Conductor	AWG 22...12
Conductor cross-section	0.5...4 mm ²
Overall width	12 mm
Accessories	
End plate	AP DKT4 0687560000

Type	Cat. No.
DKO	8164250000
Technical data	
Input	
Input voltage	24 Vdc $\pm 20\%$
Input current	$\leq 35 \text{ mA}$
Reverse polarity protection	up to 1 kV available
NAMUR-Input (N+ and N-)	
Switching frequency	300 Hz f. pulse duty factor 1:1
Switch-on delay	approx. 45 μs
Switch-off delay	approx. 450 μs
Input (E+ and 0)	
Switch-on point	approx. 18 V
Switch off-point	ca 15 V
Current consumption	< 5 mA
Max. switching frequency	300 Hz f. pulse duty factor 1:1
Switch-on delay	approx. 20 μs
Switch-off delay	approx. 400 μs
Output (A+ and A-)	
Output voltage	5...30 Vdc
Output current	max. 100 mA
Switching capacity	max. 3 W
Internal voltage drop	max. 1 V
Protective measure	Free-wheel. diode btwn. A+...A-
Voltage proof input-output/mounting rail	4 kV _{eff}
Operating temperature	without clearances -25 °C...+40 °C with clearances -25 °C...+50 °C
Storage temperature	-40 °C...+60 °C
Conductor	AWG 22...12
Conductor cross-section	0.5...4 mm ²
Overall width	12 mm
Accessories	
End plate	AP DKT4 0687560000

Opto-coupler in component housing EG

Opto-couplers EGO

EGO 1 5 V

For low voltage
alternatively positive
or negative switching

EGO 1 5 V


EGO 1 12 V

EGO 1 24 V




Schematic circuit diagram

Switching ratio



Switching ratio $\frac{t_1}{t_3} = \frac{1}{2} = 1 : 2$



* Wiring option

Ordering data	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.
	EGO 1, 5 V	0266160000	EGO 1, 12 V	8011250000 ³⁾	EGO 1, 12 V	0114260000	EGO 1, 24 V	0558160000
Rated data								
Input voltage	3...5 V⁻²⁾		3...12 V⁻		12 V₀, ±10 %		24 V⁻, ±10 %	
Rated consumption – (W)	9...45 mW		30...280 mW		0.35 W		0.6 W	
Rated consumption – (VA)	–		–		0.45 VA		–	
Output supply voltage	5...48 V ⁻¹⁾		5...48 V ⁻¹⁾		5...48 V ⁻¹⁾		5...48 V ⁻¹⁾	
Voltage drop at max. load current	<1 V		<1 V		<1.6 V		<1 V	
Output current	20 mA		20 mA		100 mA		20 mA	
Derating curve								
a = mounted on rail without clearance								
b = mounted on rail without clearance ≥ 20 mm								
Continuous current								
Ambient temperature								
Impulse loading, max. current (not periodic)	0.2 A/10 ms		0.2 A/10 ms		0.8 A/10 ms		0.2 A/10 ms	
Max. reverse current (quiescent current) at U = 48 V	0.16 mA		0.16 mA		0.16 mA		0.16 mA	
Switch-on time (cyclic operation)	≤12 μs		22 μs		≤6 ms		≤30 μs	
Switching-off time (cyclic operation)	≤180 μs		44 μs		≤13 ms		≤100 μs	
Max. switching frequency, DC	100 Hz		5000 Hz/5000 Hz		20 Hz		3000 Hz	
Max. switching frequency, AC					<10 Hz			
Switching ratio	1 : 2		1 : 2/1 : 4		1 : 2		1 : 2	
Min. input impulse width			50 μs					
Storage temperature	–40 °C...+60 °C		–40 °C...+85 °C		–40 °C...+85 °C		–40 °C...+85 °C	
Ambient temperature								
–, rowed on mounting rail without clearances	–25 °C...+60 °C		–25 °C...+60 °C		–25 °C...+60 °C		–25 °C...+60 °C	
–, rowed with clearances ≥ 20 mm	–25 °C...+60 °C		–25 °C...+60 °C		–25 °C...+60 °C		–25 °C...+60 °C	
Insulation coordination to EN 50 178								
Overvoltage category	III		III		III		III	
Pollution severity	2		2		2		2	
Accessories, dimensions and connection data see	Page 306, Fig. I		Page 306, Fig. I		Page 306, Fig. I		Page 306, Fig. I	

¹⁾ Not TTL-compatible

²⁾ Conditionally level-compatible

³⁾ At U_e ≤ 5 V, the LED only lights weakly or not at all.
Output switching function is not affected.

Opto-coupler in component housing EG


EGO 1 24 V




EGO 2 115 V0
for low voltage




EGO 2 230 V0



* Wiring option



In the case of inductive or capacitive electrical noise, it is recommended to connect an RC network (DK 4 RC) upstream or to use EGO 3.



Type	Cat. No.
EGO 1, 24 V	0609860000

24 V0, $\pm 10\%$

0.5 W

0.6 VA

5...48 V⁻¹)

<1.6 V

100 mA

Type	Cat. No.
EGO 2, 115 V0	0131860000

117 V0, $\pm 10\%$

0.8 W

0.9 VA

5...48 V⁻¹)

<1.6 V

100 mA

Type	Cat. No.
EGO 2, 230 V0	0546360000

230 V0, $\pm 5\%$ -15 %


1.2 W

1.4 VA

5...48 V⁻¹)

<1.6 V

100 mA



0.8 A/10 ms

0.16 mA

≤ 2 ms

≤ 15 ms

20 Hz

<10 Hz

1 : 2

-40 °C...+85 °C


-25 °C...+60 °C

-25 °C...+60 °C

III

2

Page 306, Fig. I



0.8 A/10 ms

0.16 mA

≤ 5 ms

≤ 22 ms

20 Hz

< 10 Hz

1 : 2

-40 °C...+85 °C


-25 °C...+40 °C

-25 °C...+50 °C

III

2

Page 306, Fig. I



0.8 A/10 ms

0.16 mA

≤ 13 ms

≤ 10 ms

20 Hz

< 10 Hz

1 : 2

-40 °C...+85 °C

-25 °C...+40 °C

-25 °C...+50 °C

III

2

Page 306, Fig. I

Digital signal processing

Opto-coupler in component housing WAVESERIES

Opto-couplers WAVESERIES

Opto-coupler in WAVEBOX:

- Independent connection technology
 - pluggable connection unit optionally available with screw or tension clamp connection technology
- Fast commissioning and after-sales service
 - pluggable replacement PCBs
- Save wiring
 - cross-connection option at input / output
- Fast switching
 - high frequency output, up to 100 kHz
- Reliable power output
 - short-circuit and overload proof
- Space-saving components
 - 4-channel opto-couplers

WOS 1 5 VDC

negative switching



WOS 1 3.5-15 VDC







WOS 1 12 VDC



WOS 1 15-60 VDC



Schematic circuit diagram



Ordering data	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.
Screw connection	WOS 1 5 Vdc	8275430000	WOS 1 3.5-15 Vdc	8275390000	WOS 1 12 Vdc	8275500000	WOS 1 15-60 Vdc	8237730000
Tension clamp connection	WOZ 1	8430030000	WOZ 1	8430040000	WOZ 1	8429990000	WOZ 1	8430090000
Input								
Input voltage	4.0 Vdc... 5 Vdc ...6.0 Vdc		3.5 Vdc...15 Vdc		10 Vdc... 12 Vdc ...14 Vdc		15 Vdc...60 Vdc ¹⁾	
Input current	7.5 mA at 4.0 V 13.5 mA at 5.0 V 19.0 mA at 6.0 V		10.5 mA at 3.5.0 V 12.5 mA at 5.0 V 25.0 mA at 15 V		15.3 mA ac at 12 V 12.4 mA dc at 12 V		1.4 mA at 15 V 2.5 mA at 24 V 4.1 mA at 48 V ...60 V	
Making threshold	approx.2.2 V		approx.2.5 V		approx.8 V		ca.12 V	
Breaking threshold	approx.2.0 V		approx.1.5 V		approx.7 V		approx.9 V	
Input frequency	100 Hz		5 kHz				1 kHz	
Switch-on delay	100 us		8 us		10 ms ac and 4 ms dc		90 us	
Switch-off delay	1 ms		35 us		20 ms ac and 18 ms dc		250 us	
Status indicator	LED green in input		LED green in input		LED green in output		LED green in output	
Output								
Output current range	negative switching				short-circuit protection		short-circuit protection	
Nominal output current	max. 2 A*		max. 100 mA		10 mA...0.6 A		10 mA...0.6 A	
Output voltage	18 Vdc... 24 Vdc ...30 Vdc		5 Vdc...48 Vdc		max. 500 mA		max. 500 mA	
Response threshold					12 Vdc... 24 Vdc ...28 Vdc		12 Vdc... 24 Vdc ...28 Vdc	
Residual voltage	≤ 300 mV		≤ 1.5 V at 100 mA		typ. 0.7 A ... 1.8 A		typ. 0.7 A ... 1.8 A	
Protection circuit	Varistor		Varistor, integr. free-wh. diode		min. 0.7 A; max. 2.4 A		min.0.7 A; max. 2.4 A	
Voltage supply					≤ 0.5 V, at 500 mA		≤ 0.5 V at 500 mA	
Short-circuit in output	no		no		Polarity protection, varistor		Polarity protection, varistor	
Temperature					12Vdc... 24Vdc ...28Vdc		12 Vdc... 24 Vdc ...28 Vdc	
Operating temperature**	-25 °C...+50 °C rowed		-25 °C...+60 °C rowed		yes / max. 96 h		yes / max. 96 h	
Storage temperature	-40 °C...+85 °C		-40 °C...+85 °C					
Mechanical data								
Overall width	22.5 mm		22.5 mm					
Housing material	Polyamide PA 66		Polyamide PA 66					
Approvals	UL/CSA		UL/CSA					
Reliable separation according to EN 50 178								
Coordination of insulation according to EN 50 178								
Opto-coupler according to VDE 0884								
Rated voltage	300 V		300 V					
Rated impulse voltage	4 kV		4 kV					
Overvoltage category	III		III					
Pollution severity	2		2					
Clearance/creepage path	≥ 5.5 mm		≥ 5.5 mm					
Accessories, dimensions and connection data see	Page 298 + 308		Page 298 + 308					

* at ambient temperature 20 °C/horizontal installation

¹⁾ **Caution:** Cross-connections may only be used for voltages ≤ **50 Vdc** (extra-low voltage).

Opto-coupler in component housing WAVESERIES




Opto-couplers WAVESERIES

WOS 1 115 VUC

WOS 1 230 VUC



Schematic circuit diagram



WOS 1 230 VUC • 8275380000

Ordering data	Type	Cat. No.	Type	Cat. No.
Screw connection	WOS 1 115 Vuc	8235180000	WOS 1 230 Vuc	8275380000
Tension clamp connection	WOZ 1	8430100000	WOZ 1	8430050000
Input				
Input voltage	115 Vuc, max. 130 Vuc		230 V, max. 250 Vuc	
Input current	3.1 mA ac at 115 V 2.9 mA dc at 115 V		11.5 mA ac at 230 V 1.8 mA dc at 230 V	
Making threshold	ca.75 V ac and 71 dc		ca.170 V ac and 140 V dc	
Breaking threshold	ca.70 Vuc		ca.130 V ac and 135 V dc	
Input frequency	-		-	
Switch-on delay	10 ms ac 10 ms dc		25 ms ac 15 ms dc	
Switch-off delay	15 ms ac 15 ms dc		25 ms ac 20 ms dc	
Status indicator	LED green in output		LED green in output	
Output	short-circuit protection		short-circuit protection	
Output current range	10 m A...0.6 A		10 mA...0.6 A	
Nominal output current	max. 500 mA		max. 500 mA	
Output voltage	12 Vdc... 24 Vdc ...28 Vdc		12 Vdc... 24 Vdc ...28 Vdc	
Response threshold	typ. 0.7 A ... 1.8 A min.0.7 A; max. 2.4 A		typ. 0.7 A ... 1.8 A min.0.7 A; max. 2.4 A	
Residual voltage	≤ 0.5 V at 500 mA		≤ 0.5 V at 500 mA	
Protection circuit	Polarity protection, varistor		Polarity protection, varistor	
Voltage supply	12 Vdc... 24 Vdc ...28 Vdc		12 Vdc... 24 Vdc ...28 Vdc	
Short-circuit in output	yes / max. 96 h		yes / max. 96 h	
Temperature				
Operating temperature**	-25 °C...+60 °C rowed		-25 °C...+60 °C rowed	
Storage temperature	-40 °C...+85 °C		-40 °C...+85 °C	
Mechanical data				
Overall width	22.5 mm		22.5 mm	
Housing material	Polyamide PA 66		Polyamide PA 66	
Approvals	UL/CSA		UL/CSA	
Reliable separation according to EN 50 178				
Coordination of insulation according to EN 50 178				
Opto-coupler according to VDE 0884				
Rated voltage	300 V		300 V	
Rated impulse voltage	4 kV		4 kV	
Overvoltage category	III		III	
Pollution severity	2		2	
Clearance/creepage path	≥ 5.5 mm		≥ 5.5 mm	
Accessories, dimensions and connection data see	Page 298 + 308		Page 298 + 308	

* at ambient temperature 20 °C/horizontal installation

Opto-coupler in component housing WAVESERIES

Opto-couplers WAVESERIES

with power output
(short-circuit proof and overload proof)

WOS 2 24 VUC




WOS 2 115 VUC



WOS 2 230 VUC



Schematic circuit diagram



WOS 2 230 VUC • 8275220000

Ordering data

Screw connection

Tension clamp connection

Input

Input voltage

Input current

Making threshold

Breaking threshold

Switch-on delay

Switch-off delay

Status indicator normal operation

Status indicator short-circuit, underload, overload

Underload

Output

Output current

Closed supply-circuit current (output not switched)

Voltage supply

Residual voltage

Protection circuit

Short-circuit in output

Temperature

Operating temperature**

Storage temperature

Mechanical data

Overall width

Housing material

Approvals

Reliable separation according to EN 50 178

Coordination of insulation according to EN 50 178

Opto-coupler according to VDE 0884

Rated voltage

Rated impulse voltage

Overvoltage category

Pollution severity

Clearance/creepage path

Accessories, dimensions and connection data see

* at ambient temperature 20 °C/horizontal installation

Type Cat. No.

WOS 2 24 Vuc **8275190000**

WOZ 2 **8430080000**

Type Cat. No.

WOS 2 115 Vuc **8296250000**

WOZ 2 **8429980000**

Type Cat. No.

WOS 2 230 Vuc **8275220000**

WOZ 2 **8430060000**

21.6 V...**24 V**...26.4 V
16.3 mA **ac** at 24 V
13.5 mA **dc** at 24 V

ca.16 V
ca.11 V
8 ms ac 7 ms dc
25 ms ac 25 ms dc
LED green in output
LED red in output*¹⁾
min. 2 mA...max. 1.5 A at Tb
25 °C...150 °C
min. 2 mA...max. 1.9 A at Tb
-40 °C...25 °C
Tb: temperature in module
direct at output driver
BTS442

short-circuit protection

5 Adc*
approx.15 mA at 28.8 V
19.2 Vdc...**24 Vdc**...28.8 Vdc
max. 400 mV
Polarity protection, varistor
yes / max. 96 h

-25 °C...+50 °C rowed
-40 °C...+85 °C

22.5 mm

Polyamide PA 66

UL/CSA

300 V

4 kV

III

2

≥ 5.5 mm

Page 298 + 308

115 V, max. 130 Vuc
3.1 mA **ac** at 115 V
2.8 mA **dc** at 115 V

ca.70 V
ca.55 V
10 ms ac 15 ms dc
30 ms ac 30 ms dc
LED green in output
LED red in output*¹⁾
min. 2 mA...max. 1.5 A at Tb
25 °C...150 °C
min. 2 mA...max. 1.9 A at Tb
-40 °C...25 °C
Tb: temperature in module
direct at output driver
BTS442

short-circuit protection

5 Adc*
approx.15 mA at 28.8 V
19.2 Vdc...**24 Vdc**...28.8 Vdc
max. 400 mV
Polarity protection, varistor
yes / max. 96 h

-25 °C...+50 °C rowed
-40 °C...+85 °C

22.5 mm

Polyamide PA 66

UL/CSA

300 V

4 kV

III

2

≥ 5.5 mm

Page 298 + 308

230 V, max. 250 Vuc
12.0 mA **ac** at 230 V
1.8 mA **dc** at 230 V

ca.140 V ca.100 V
ca.100 V ca.120 V
10 ms ac 15 ms dc
30 ms ac 30 ms dc
LED green in output
LED red in output*¹⁾
min. 2 mA...max. 1.5 A at Tb
25 °C...150 °C
min. 2 mA...max. 1.9 A at Tb
-40 °C...25 °C
Tb: temperature in module
direct at output driver
BTS442

short-circuit protection

5 Adc*
approx.15 mA at 28.8 V
19.2 Vdc...**24 Vdc**...28.8 Vdc
max. 400 mV
Polarity protection, varistor
yes / max. 96 h

-25 °C...+50 °C rowed
-40 °C...+85 °C

22.5 mm

Polyamide PA 66

UL/CSA

300 V

4 kV

III

2

≥ 5.5 mm

Page 298 + 308

*¹⁾ LED red:

hard short-circuit,
LED permanently lit.
The output is switched off and
does **not** reset itself. To reset,
the output or input must be
temporarily disconnected from
the supply voltage or input
signal.

Overload: LED cycles,
Rate: approx. 2 sec. on,
approx. 30 sec. off.
Module resets itself after the
overload is removed.

Underload: LED permanently
lit.

When an underload reco-
gnised, both LEDs are lit.
The output is switched
through

Opto-coupler in component housing WAVESERIES

Opto-coupler WAVESERIES

with AC voltage output and
zero voltage switch


WOS 2 15-60 VUC



WOS 2 115 VUC






WOS 2 230 VUC



WOS 2 15-60 VUC • 8275440000

Schematic circuit diagram



Ordering data

Screw connection

Tension clamp connection

Input

Input voltage

Input current

Making threshold

Breaking threshold

Switch-on delay

Switch-off delay

Status indicator normal operation

Type Cat. No.

WOS 2 15-60 Vuc **8275440000**

WOZ 2 **8430010000**

15 Vuc...60 Vac/66 Vdc

3.3 mA **ac** at 15 V

3.8 mA **dc** at 15 V

4.0 mA **ac** at 24 V

4.6 mA **dc** at 24 V

5.3 mA **ac** at 60 V

5.6 mA **dc** at 60 V

approx.11 V **dc** approx.15 V **ac**

approx.5 V **dc** approx.14 V **ac**

max. 20 ms

max. 20 ms

LED green in input

Type Cat. No.

WOS 2 115 Vuc **8259950000**

WOZ 2 **8430160000**

115 Vuc max. 130 Vuc

7.2 mA **ac** at 115 V

3.8 mA **dc** at 115 V

approx.90 V **dc** approx.90 V **ac**

approx.70 V **dc** approx.70 V **ac**

max. 20 ms

max. 20 ms

LED green in input

Type Cat. No.

WOS 2 230 VUC **8275400000**

WOZ 2 **8430150000**

230 Vuc max. 250 Vuc

11.8 mA **ac** at 230 V

3.3 mA **dc** at 230 V

approx.180 V **dc** approx.200 V **ac**

approx.150 V **dc** approx.140 V **ac**

max. 25 ms

max. 25 ms

LED green in input

Output

Output current

Closed supply-circuit current (output not switched)

Voltage supply

Residual voltage

Protection circuit

Short-circuit in output

Temperature

Operating temperature**

Storage temperature

Mechanical data

Overall width

Housing material

Approvals

Reliable separation according to EN 50 178

Coordination of insulation according to EN 50 178

Opto-coupler according to VDE 0884

Rated voltage

Rated impulse voltage

Overvoltage category

Pollution severity

Clearance/creepage path

Accessories, dimensions and connection data see

* at ambient temperature 20 °C/horizontal installation

AC voltage output

max. 230 V/3.5 A ac*

2 mA

24 Vac...250Vac (50Hz-60Hz)

max. 1.6 V

RC-combination with varistor

-

-25 °C...+50 °C rowed

-40 °C...+85 °C

22.5 mm

Polyamide PA 66

UL/CSA

300 V

4 kV

III

2

≥ 5.5 mm

Page 298 + 308

AC voltage output

max. 230 V/3.5 A ac*

2 mA

24Vac...250 Vac (50Hz-60Hz)

max. 1.6 V

RC-combination with varistor

-

-25 °C...+50 °C rowed

-40 °C...+85 °C

22.5 mm

Polyamide PA 66

UL/CSA

300 V

4 kV

III

2

≥ 5.5 mm

Page 298 + 308

AC voltage output

max. 230V/3.5A ac*

2 mA

24 Vac...250 Vac (50Hz-60Hz)

max. 1.6 V

RC-combination with varistor

-

-25 °C...+50 °C rowed

-40 °C...+85 °C

22.5 mm

Polyamide PA 66

UL/CSA

300 V

4 kV

III

2

≥ 5.5 mm

Page 298 + 308

Opto-coupler in component housing WAVESERIES

Opto-coupler WAVESERIES

(4-channel, short-circuit proof)


WOS 2 24 VUC

WOS 2 115 VUC



WOS 2 230 VUC



Schematic circuit diagram



WOS 2 230 VUC • 8275340000



Ordering data
Screw connection
Tension clamp connection

Type	Cat. No.
WOS 2 24 Vuc	8237720000
WOZ 2	8430110000

Type	Cat. No.
WOS 2 115 Vuc	8275360000
WOZ 2	8430130000

Type	Cat. No.
WOS 2 230 Vuc	8275340000
WOZ 2	8430140000

Input
Input voltage
Input current
Making threshold
Breaking threshold
Switch-on delay
Switch-off delay
Status indicator normal operation
Status indicator short-circuit, underload, overload

18 Vuc ... 30 Vuc	
2.8 mA ac at 24 V	
3.7 mA dc at 24 V	
ca.13 V dc	ca.14 V ac
ca.10 V dc	ca.13 V ac
20 ms ac 7.0 ms dc	
46 ms ac 50 ms dc	
LED green in output	
LED red in output*	

115 Vuc, max. 130 Vuc	
1.4 mA ac at 115 V	
2.0 mA dc at 115 V	
ca.60 V dc	ca.60 V ac
ca.50 V dc	ca.50 V ac
40 ms ac 15 ms dc	
60 ms ac 70 ms dc	
LED green in output	
LED red in output*	

230 V, max. 250 V	
1.4 mA ac at 230 V	
2.0 mA dc at 230 V	
ca.150 V dc	ca.120 V ac
ca.110 V dc	ca.110 V ac
40 ms ac 14 ms dc	
95 ms ac 140 ms dc	
LED green in output	
LED red in output*	

* LED red, one LED for all channels

Output ¹⁾
Output current
Output total current
Voltage supply
Response threshold
Residual voltage
Protection circuit
Synchronisation factor
Lamp load

short-circuit protection
max. 500 mA per channel
max. 2 A
12 Vdc... 24 Vdc ...28 Vdc
typ. 0.9 A
min. 0.65 A, max. 1.2 A, R _L 2Ω
≤ 0.65 V, at 500 mA
Polarity protection, varistor
100 %
max. 3 W

short-circuit protection
max. 500 mA per channel
max. 2 A
12 Vdc... 24 Vdc ...28 Vdc
typ. 0.9 A
min. 0.65 A, max. 1.2 A, R _L 2Ω
≤ 0.65 V, at 500 mA
Polarity protection, varistor
100 %
max. 3 W

short-circuit protection
max. 500 mA per channel
max. 2 A
12 Vdc... 24 Vdc ...28 Vdc
typ. 0.9 A
min. 0.65 A, max. 1.2 A, R _L 2Ω
≤ 0.65 V, at 500 mA
Polarity protection, varistor
100 %
max. 3 W

Temperature
Operating temperature
Storage temperature

-25 °C...+50 °C rowed
-40 °C...+85 °C

-25 °C...+50 °C rowed
-40 °C...+85 °C

-25 °C...+50 °C rowed
-40 °C...+85 °C

Mechanical data
Overall width
Housing material
Approvals

22.5 mm
Polyamide PA 66
UL/CSA

22.5 mm
Polyamide PA 66
UL/CSA

22.5 mm
Polyamide PA 66
UL/CSA

Reliable separation according to EN 50 178

Coordination of insulation according to EN 50 178

Opto-coupler according to VDE 0884

Rated voltage
Rated impulse voltage
Overvoltage category
Pollution severity
Clearance/creepage path

150 V
2.5 kV
III
2
≥ 3 mm

150 V
2.5 kV
III
2
≥ 3 mm

300 V
4 kV
III
2
≥ 5.5 mm

Accessories, dimensions and connection data see

Page 298 + 308

Page 298 + 308

Page 298 + 308

¹⁾ Protection circuit for output load necessary, page 107

Opto-coupler in component housing WAVESERIES

Opto-coupler WAVESERIES


with high switching frequency

WOS 1 5 VTTL
50 kHz



WOS 1 12-28 VDC
100 kHz



Schematic circuit diagram



WOS 1 5 VTTL 50 kHz • 8275210000



Ordering data

Screw connection

Tension clamp connection

Input

Input voltage

Input current

Supply voltage

Input resistance

Making threshold

Breaking threshold

Input frequency

Switch-on delay

Switch-off delay

Status indicator normal operation

Type Cat. No.

WOS 1 5 VTTL 50 kHz

8275210000

WOZ 2 **8430070000**

5 VTTL

11.8 mA at 4.75 V

13.6 mA at 5 Vdc

15.5 mA at 5.25 Vdc

4.75 Vdc ... 5.25 Vdc

110 KΩ

50 kHz at $R_{load} = 470 \Omega$

1 μs

7 μs

LED green in input circuit

Type Cat. No.

WOS 1 12-28 Vdc/100 kHz

8275450000

WOZ 2 **8430000000**

12V dc...28 Vdc

5.5 mA at 12 Vdc

7.9 mA at 24 Vdc

8.8 mA at 28 Vdc

approx. 5 V dc

approx. 4 V dc

100 kHz at $R_{load} = 470 \Omega$

1 μs

3 μs

LED green in input circuit

Output

Voltage supply

Supply nominal current

Output current

Residual voltage

Protection circuit

21.6 Vdc...**24 Vdc**...26.4 Vdc

approx. 5.4 mA, output not

switched

≤ 50 mA

≤ 1.5 V at 50 mA

Polarity protection, varistor

21.6 Vdc...**24 Vdc**...26.4 Vdc

approx. 5.4 mA, output not

switched

≤ 50 mA

≤ 1.5 V at 50 mA

Polarity protection, varistor

Temperature

Operating temperature

Storage temperature

Mechanical data

Overall width

Housing material

Approvals

Reliable separation according to EN 50 178

Coordination of insulation according to EN 50 178

Opto-coupler according to VDE 0884

Rated voltage

Rated impulse voltage

Overvoltage category

Pollution severity

Clearance/creepage path

Accessories, dimensions and connection data see

-25 °C...+60 °C rowed

-40 °C...+85 °C

22.5 mm

Polyamide PA 66

UL/CSA

≥ 5.5 mm

Page 298 + 308

-25 °C...+60 °C rowed

-40 °C...+85 °C

22.5 mm

Polyamide PA 66

UL/CSA

≥ 5.5 mm

Page 298 + 308

Opto-coupler in component housing EG5


power opto-couplers

With "online" check-back indication of the load ratio

- Power opto-couplers for load currents up to 4 A.
- Short-circuit proof
- Patented "online" load indication and check-back indication
 - optical indication
 - status indication via 3-coloured LEDs
 - electrical indication
 - 2-bit "online" data signal for check-back indication of the load performance to a PLC or similar
- Module fulfils protective separation in accordance with VDE 0106 Part 101 and EN 50 178 (rated voltage 300 V)
- Internal opto-coupler according to with DIN VDE 0884
- Insulation voltage 4 kV_{eff}
- Clearance and creepage distances ≥ 8 mm

Schematic circuit diagram

EGO 5 PKR 24 Vac/dc



Indication and check-back indication of load ratio

Input	Load Indication	LI 1	LI 2	LED	Output
Low	x x x	L	L	off	low
High	Normal	L	H	green	high
High	Error ¹⁾	H	L	red	low
High	Open Load ²⁾	H	H	yellow	high

Ordering data

Type	Cat. No.
EGO 5 PKR	8220870000

Rated data

Input	Screw connection 0.5...4 mm ²
Input voltage	24 Vac/dc, min 20 Vac/dc, max 30 Vac/dc
Input current (at U _N)	12 mA (24 Vdc) 13 mA (24 Vac)
Rated input consumption	195 mW, 220 mVA
Max. input frequency dc	≤ 30 Hz, switching ratio 1 : 2
Typ. switch-on delay	2 ms
Typ. switch-off delay	7 ms
Max. input frequency ac	≤ 10 Hz
Output	Screw connection 0.5...4 mm ²
Supply voltage	20...30 Vdc
Max. output current	4 A
Reverse polarity protection	present
Short-circuit conditions	short-circuit-protected (switches output off immediately; auto switch-on when short-circuit eliminated)
Thermal short-circuit	≤ 12 A. output switches off and on again automatically after certain time.
Load Indication LI 1, LI 2	
Supply voltage	5...48 Vdc
Max. current	100 mA
Max. voltage drop	1.6 V
Storage temperature	-40 °C...+60 °C
Ambient temperature	
- rowed on mounting rail without clearances	-20 °C...+40 °C
- rowed with clearances	-20 °C...+50 °C
Insulation coordination EN 50 178	
Overvoltage category	IV
Pollution severity	2
Accessories, dimensions and connection data see	Page 307, Fig. VII

¹⁾ Error: short-circuit, overload, over- or under voltage at output, overtemperature in the module

²⁾ Open load: Underload recognition at active input: type 500 mA (max. 1.5 A) at 25 °C. Open load will be indicated at I_{Load} ≥ 500 mA depending on switching status.

Opto-coupler in component housing EG7

power opto-couplers


- Pluggable on socket RS EG 7 with combination foot TS 32, 35
- Overall width **10 mm**

OST EG7 2 A



- Short circuit protected and over load-safe output
- 3-colour status-LED for output current indication
- Reliable separation acc. to DIN VDE 0884



OST EG7 4 A



Schematic circuit diagram



Ordering data		Type	Cat. No.	Type	Cat. No.
Pluggable opto-coupler, without socket		OST EG7 2 A	8269050000	OST EG7 4 A	8281720000
socket for pluggable opto-coupler with combin. foot TS 32, 35		RS EG7	8193830000	RS EG7	8193830000
Rated data		Cat. No.		Cat. No.	
Conductor connection		Lugs for socket RS EG7		Lugs for socket RS EG7	
		8193830000		8193830000	
Input voltage		24 Vac/dc $\pm 20\%$		21.6 Vdc	
Input current		dc: 5.5 mA ac: 6 mA		10.5 mA	
Input power		dc: 132 mW ac: 145 mW		230 mW	
Reliably switched on		19.2 V		21.6 V	
Reliably switched off		2.4 V		2 V	
Status indicator		LED green, yellow, red		LED green	
Reverse polarity protection		-		present	
Switch-on delay		12 ms		typ. 10 μ s	
Switch-off delay		17 ms		typ. 45 μ s	
Max. Switching frequency		100 Hz (resistive load/2 A/ Switching ratio 1 : 2)		100 Hz (resistive load/4 A/ Switching ratio 1 : 2)	
Output supply voltage		24 Vdc $\pm 30\%$		21.6...26.4 Vdc	
Switching current		2 A		4 A	
Voltage drop at max. load current		≤ 0.2 V, short-circuit proof and overload proof		≤ 0.2 V, not short-circuit proof and not overload proof	
Status indicator:		Green LED output set		output set	
		Yellow LED output set, no activity, < 500 mA		normal function	
		Red LED output set, short-circuit			
		LED off output not set			
Storage temperature		- 25...+ 60 °C		- 25...+ 60 °C	
Operating temperature		0...+ 40 °C		0...+ 40 °C	
- rowed on mounting rail without clearances		0...+ 50 °C		0...+ 50 °C	
- rowed with clearances					
Insulation coordination to EN 50 178					
Reliable separation		according to DIN VDE 0884		-	
Overvoltage category		III		III	
Pollution severity		2		2	
Accessories, dimensions and connection data see		Page 304		Page 304	

Opto-coupler in component housing EG7

Opto-couplers

- With combination foot for TS 15, TS 32 or TS 35
- Pluggable on socket RS EG 7 with combination foot TS 32, 35
- Overall width **10 mm**
- **Reliable separation according to DIN VDE 0884**

EGO EG 7 OST EG 7 RS EG 7

EGO EG 7



OST EG 7



RS EG 7


Schematic circuit diagram

5 V~

12 V0

24 V0

48 V0



Ordering data	Type	Cat. No.	Type	Cat. No.	Type	Best.-EGO	Type	Cat. No.
Combination foot for TS 15, TS 32, TS 35	EGO EG7	8092490000	EGO EG7	8092510000	EGO EG7	8092530000	EGO EG7	8092550000
Plug-in opto-coupler, without engagement socket	OST EG7	8234560000	OST EG7	8234570000	OST EG7	8234580000	OST EG7	8234590000
Engage. socket for opto-coupler with combin. foot TS 32, 35	RS EG7	8193830000	RS EG7	8193830000	RS EG7	8193830000	RS EG7	8193830000
Rated data	5 V~ ±20 %		12 V0 ±20 %		24 V0 ±20 %		48 V0 ±20 %	
Input voltage	5 V~ ±20 %		12 V0 ±20 %		24 V0 ±20 %		48 V0 ±20 %	
Switch-on current	3 V~		12 V/4.5 mA for max. 10 ms		12 V/4.5 mA for max. 10 ms		12 V/4.5 mA for max. 10 ms	
Making threshold, typical	6.5 V~		6.5 V~		15.5 V~		31.5 V~	
	7.5 V~		7.5 V~		16.5 V~		45 V~	
Rated input current DC	3 mA		3 mA		2.8 mA		2.8 mA	
Rated input current AC	33.5 mA		33.5 mA		3.4 mA		3.2 mA	
Rated input consumption	40 mW/50 mVA		40 mW/50 mVA		70 mW/90 mVA		135 mW/155 mVA	
Output supply voltage	5...48 V~		5...48 V~		5...48 V~		5...48 V~	
Output current	100 mA		100 mA		100 mA		100 mA	
Max. output current	300 mA		300 mA		300 mA		300 mA	
Switch-on time (first time)	6 ms for U _N = 5 V~		6 ms for U _N = 12 V~		5 ms for U _N = 24 V~		5 ms for U _N = 48 V~	
Switch-off time	12 ms for U _N = 5 V~		12 ms for U _N = 12 V~		15 ms for U _N = 24 V~		15 ms for U _N = 48 V~	
Switching frequency	15 Hzdc		15 Hzdc		15 Hzdc		15 Hzdc	
Storage temperature	-40...+60 °C		-40...+60 °C		-40...+60 °C		-40...+60 °C	
Ambient temperature	-25...+60 °C		-25...+60 °C		-25...+60 °C		-25...+60 °C	
Connection								
Insulation coordination to EN 50 178								
Protective separation	acc. to DIN VDE 0884		acc. to DIN VDE 0884		acc. to DIN VDE 0884		acc. to DIN VDE 0884	
Clearances and creepage distances	≥ 5.5 mm		≥ 5.5 mm		≥ 5.5 mm		≥ 5.5 mm	
Rated impulse voltage	6 kV		6 kV		6 kV		6 kV	
Overvoltage category	III		III		III		III	
Pollution severity	2		2		2		2	
Accessories	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.
Cross connection comb 16-pole	QB 16/10.16	1650330000	QB 16/10.16	1650330000	QB 16/10.16	1650330000	QB 16/10.16	1650330000
Further accessories, dimensions and connection data see	Page 304		Page 304		Page 304		Page 304	

Opto-coupler in component housing EG7

EGO EG 7




EGO EG 7

115 V₀

230 V₉

230 V_{dc}



Type Cat. No.
EGO EG7 **8092570000**

OST EG7 **8234600000**
RS EG7 **8193830000**

115 V₀ ±20 %
115 V/90 mA for 5 ms
70 V~
72 V~
3.3 mA
5.5 mA
400 mW/500 mVA
5...48 V~
100 mA
300 mA

5 ms for U_N = 115 V~
18 ms for U_N = 115 V~
15 Hzdc

-40...+60 °C
-25...+60 °C

acc. to DIN VDE 0884
≥ 5.5 mm
6 kV
III
2

Type Cat. No.
QB 16/10.16 **1650330000**

Page 304

Type Cat. No.
EGO EG7 **8092590000**

OST EG7 **8234610000**
RS EG7 **8193830000**

230 V~ ±20 %
230 V/110 mA for 2 ms
140 V~
-
3.8 mA
-
836 mVA
5...48 V~
100 mA
300 mA

5 ms for U_N = 230 V~
18 ms for U_N = 230 V~
12 Hz

-40...+60 °C
-25...+60 °C

acc. to DIN VDE 0884
≥ 5.5 mm
6 kV
III
2

Type Cat. No.
QB 16/10.16 **1650330000**

Page 304

Type Cat. No.
OST EG7 **8621190000**

230 V_{dc} ±20 %
230 V~ /110 mA for 2 ms
140 V~ (for testing only)
-
1.8 mA
-
100 mA
300 mA

-40...+60 °C
-25...+60 °C
Screw connection
0.5...1.5mm², AWG 22...16

acc. to DIN VDE 0884
≥ 5.5 mm
6 kV
III
2

Type Cat. No.
QB 16/10.16 **1650330000**

Page 304

Opto-couplers for long control cables

- with combination foot for TS 15, TS 32 or TS 35
- plugs onto locking socket RS EG 7 with combination TS 32, 35
- overall width **10 mm**
- **protective separation acc. to DIN VDE 0884**
- RC-input for suppressing noise signals
- reliable switching performance by interference on the control side

EGO EG 7 RC/ OST EG 7 RC




OST EG 7 RC

RS EG 7 RC

115 V₀

230 V₉

Schematic circuit diagram



Ordering data

Combination foot for TS 15, TS 32, TS 35
Pluggable opto-coupler, without locking socket
Locking socket for pluggable opto-coupler with combin. foot TS 32, 35

Rated data

Input voltage
Switch-on current
Making threshold, typ.

Rated input current DC
Rated input current AC
Rated input consumption
Output supply voltage
Output current
Max. output current
Switch-on time (first time)
Switch-off time
Switching frequency

Storage temperature
Ambient temperature

Insulation coordination to

Reliable separation
Clearances / creepage distances
Rated impulse voltage
Overvoltage category
Pollution severity

Accessories

Cross connec. comb 16-pole

Futher Accessories, dimensions and connection data see

Type Cat. No.
EGO EG7 **8397420000**

OST EG7 **8315590000**

RS EG7 8193830000
115 V₀ ±20 %
115 V/90 mA for 5 ms
70 V~
72 V~
3.3 mA
9 mA/90 mA (5 ms)
400 mW/500 mVA
5...48 V~
100 mA
300 mA

9 ms for U_N = 115 V~
25 ms for U_N = 115 V~
12 Hzdc

-40...+60 °C
-25...+60 °C

EN 50 178

acc. to DIN VDE 0884
≥ 5.5 mm
6 kV
III
2

Type Cat. No.
QB 16/10.16 **1650330000**

Page 304

Type Cat. No.
EGO EG7 **8387580000**

OST EG7 **8394990000**

RS EG7 8193830000
230 V~ ±20 %
230 V/110 mA for 2 ms
140 V~
-
14 mA/110 mA (2 ms)
-
836 mVA
5...48 V~
100 mA
300 mA

15 ms for U_N = 230 V~
15 ms for U_N = 230 V~
12 Hz

-40...+60 °C
-25...+60 °C


acc. to DIN VDE 0884
≥ 5.5 mm
6 kV
III
2

Type Cat. No.
QB 16/10.16 **1650330000**

Page 304

Solid State relay on locking socket PLUGSERIES

Complete module




Accessories SSR Standard




- Compact dimensions (29 x 25.4 x 12.7)
- Combines with PLUGSERIES socket PXS / PXZ, LED indicator PLED and PRC holding clamp to a complete functioning unit.
- Fully compatible with electromechanical relays in standard design
- Control voltage 24 VAC / DC
- Rated switching current 24 VDC, 24 VAC/DC, or 230 VAC
- Up to 5 A continuous current
- Mounts onto PCB or socket
- High mounting density possible

DC version



AC version




DC version

Type/Version	Cat. No.
Screw connection	
POS 24Vdc/24Vdc 2.5A	8610840000
POS 24Vdc/230Vac 2A	8610860000
POS 24Vdc/24Vdc 1A	8610890000
POS 24Vdc/24Vdc 5A	8610900000
POS 24Vdc/230Vac 4A	8610910000
Tension clamp connection	
POZ 24Vdc/24Vdc 2.5A	8610920000
POZ 24Vdc/230Vac 2A	8610930000
POZ 24Vdc/24Vdc 1A	8610960000
POZ 24Vdc/24Vdc 5A	8610970000
POZ 24Vdc/230Vac 4A	8610980000

AC version

Type/Version	Cat. No.
Screw connection	
POS 24Vac/24Vdc 2.5A	8615600000
POS 24Vac/24Vdc 5A	8615620000
POS 24Vac/230Vac 4A	8615590000
Tension clamp connection	
POZ 24Vac/24Vdc 2.5A	8615640000
POZ 24Vac/24Vdc 5A	8615650000
POZ 24Vac/230Vac 4A	8615630000

Dimensions



Ordering data

Type	Cat. No.
SSR 24 VUC/24VDC 5A	8576350000

Technical data

Input (typical values at 20 °C)
Input voltage min. AC/DC
Input voltage max. AC/DC
Input current min. AC/DC
Input current max. AC/DC
Drop-out voltage AC/DC
Resistance

Output

max. switching current DC
max. switching current AC
min. switching current DC
min. switching current AC
Rated switching voltage DC
Rated switching voltage AC

Switch voltage range DC
Switch voltage range AC

max. forward anode voltage at max. switching current DC
max. forward anode voltage at max. switching current AC

max. switch-on time DC
max. switch-on time AC (50 Hz)

max. switch-off time DC
max. switch-off time AC (50 Hz)

Insulation

Test voltage control circuit - switching circuit DC
Test voltage control circuit - switching circuit AC

Further data

Operating temperature range
Weight
Approvals
Celduc
Further accessories, dimensions and connection data

Type	Cat. No.
SSR 24 VUC/24VDC 5A	8576350000
SSR 24 VUC/230VAC 4A	8576360000

DC Version

15 V
30 V
6.1 mA
12 mA
2.5 V
2.100 Ω

5 A

1 mA
24 V
0...30 V
0.3 V
2 ms
18 ms
2.5 kV _{eff}

0...30 V

12...275 V
1.1 V

2 ms

12 ms
20 ms

18 ms

4 kV _{eff}

-40 °C...+50 °C

approx. 18 g
cUL, UL recognized
SPD07505
see page 83

AC Version

15 V
30 V
6.1 mA
12 mA
2.5 V
2.100 Ω

3 A (4 A at 20 °C)

50 mA
230 V ~
12...275 V
1.1 V
12 ms
20 ms
4 kV _{eff}

12...275 V

1.1 V

12 ms

20 ms

20 ms

4 kV _{eff}

-40 °C...+50 °C


approx. 18 g
cUL, UL recognized
SPA07420
see page 83

Solid State relay on locking socket PLUGSERIES

Accessories SSR / RT




Dimensions




- Compact dimensions (29 x 15.7 x 12.7)
- Combines with PLUGSERIES socket PXS / PXZ, LED indicator PLED and PRC holding clamp to a complete functioning unit.
- Fully compatible with standard electromechanical relays RT
- Control voltage 24 VAC / DC
- Rated switching current 24 VDC, 24 VAC/DC, or 230 VAC
- Up to 5 A continuous current
- Mounts onto PCB or socket
- High mounting density possible


AC version



DC version



AC/DC version





Ordering data	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.
	SSR 24 VUC/24VDC 2.5A	8576340000	SSR 24 VUC/230VAC 2A	8576370000	SSR 24 VUC/24VUC 1A	8576380000
Technical data	DC Version	AC Version	AC/DC Version			
Input (typical values at 20 °C)						
Input voltage min. AC/DC	15 V	15 V	15 V			
Input voltage max. AC/DC	30 V	30 V	30 V			
Input current min. AC/DC	6.1 mA	6.1 mA	6.1 mA			
Input current max. AC/DC	12 mA	12 mA	12 mA			
Drop-out voltage AC/DC	2.5 V	2.5 V	2.5 V			
Resistances	2.100 Ω	2.100 Ω	2.100 Ω			
Output						
max. switching current DC	2.5 A					
max. switching current AC		2A				
max. switching current AC/DC			1A			
min. switching current DC	1mA					
min. switching current AC		50mA				
min. switching current AC/DC			1mA			
Rated switching voltage DC	24 V					
Rated switching voltage AC		230 V				
Rated switching voltage AC/DC			24 V			
Switch voltage range DC	0...30 V					
Switch voltage range AC		12...275 V				
Switch voltage range AC/DC			0...30 V			
max. forward anode voltage at max. switching current DC	0.5 V					
max. forward anode voltage at max. switching current AC		1 V				
max. forward anode voltage at max. switching current AC/DC			0.9 V			
max. switch-on time DC	2 ms					
max. switch-on time AC (50 Hz)		12 ms				
max. switch-on time AC/DC (50 Hz)			5 ms			
max. switch-off time DC	18 ms					
max. switch-off time AC (50 Hz)		20 ms				
max. switch-off time AC/DC (50 Hz)			12 ms			
Insulation						
Test voltage control circuit - switching circuit DC	2.5 kV _{eff}					
Test voltage control circuit - switching circuit AC		4 kV _{eff}				
Test voltage control circuit - switching circuit AC/DC			4 kV _{eff}			
Further data						
Operating temperature range	-40 °C...+50 °C	-40 °C...+50 °C	-40 °C...+50 °C			
Weight	approx.11 g	approx.11 g	approx.11 g			
Approvals	cUL, UL recognized	cUL, UL recognized	cUL, UL recognized			
Celduc	STD07205	STA07220	STN07105			
Further accessories, dimensions and connection data	see page 83	see page 83	see page 83			

Opto-coupler on locking socket profile RS 40

Opto-couplers for signal input

RS 40



Rated data

Input voltage

Rated consumption ~ (W)

Rated consumption ~ (VA)

Output supply voltage



Voltage drop at max. load current

Output current

Derating curve

a = rowed on mounting rail without clearances

b = rowed with clearances ≥ 20 mm



Pulse duration, limiting overload current (not periodic)

Sperrstrom (Ruhestrom), max. at $U = 48$ V

Switch-on time (cyclic operation)

Switch-off time (cyclic operation)

Max. switching frequency DC voltage

Max. switching frequency AC voltage

Switching ratio

Insulation coordination to EN 50 178

Rated voltage

Rated impulse voltage

Overvoltage category

Pollution severity

Clearances and creepage distances

Opto-coupler

Test voltage (corresponds 100% module test)

Module is immune to interference

Insulation voltage

Input – output/mounting rail

Storage temperature

Ambient temperature

–, rowed on mounting rail without clearances

–, rowed with clearances ≥ 20 mm

	5 V ²⁾	12 V ₀ ± 10 %	24 V ₀ ± 10 %	24 V ₀ ± 10 %	48 V ₀ ± 10 %	115 V ₀ , +5%-15%	230 V ₀ , +5%-15%
Rated consumption ~ (W)	0.045 W	0.25 W	0.51 W	0.34 W	0.55 W	0.33 W	
Rated consumption ~ (VA)		0.32 VA		0.5 VA	0.65 VA	0.65 VA	0.52 VA
Output supply voltage	5...48 V ¹⁾	5...48 V ¹⁾	5...48 V ¹⁾	5...48 V ¹⁾	5...48 V ¹⁾	5...48 V ¹⁾	5...48 V ¹⁾
Voltage drop at max. load current	< 0.9 V	< 1.6 V	< 0.9 V	< 1.6 V	< 1.6 V	< 1.5 V	< 1.5 V
Output current	20 mA	100 mA	20 mA	100 mA	100 mA	100 mA	100 mA
Pulse duration, limiting overload current (not periodic)	0.2 A/10 ms	0.8 A/10 ms	0.2 A/10 ms	0.8 A/10 ms	0.8 A/10 ms	0.8 A/10 ms	0.8 A/10 ms
Sperrstrom (Ruhestrom), max. at $U = 48$ V	0.16 mA	0.16 mA	0.16 mA	0.16 mA	0.16 mA	0.16 mA	0.16 mA
Switch-on time (cyclic operation)	≤ 12 μs	≤ 6 ms	≤ 30 μs	≤ 2 ms	≤ 5 ms	≤ 10 ms	≤ 6 ms
Switch-off time (cyclic operation)	≤ 15 μs	≤ 13 ms	≤ 60 μs	≤ 15 ms	≤ 20 ms	≤ 23 ms	≤ 18 ms
Max. switching frequency DC voltage	3 kHz	20 Hz	3 kHz	20 Hz	< 20 Hz	10 Hz	
Max. switching frequency AC voltage		< 10 Hz			< 10 Hz		
Switching ratio	1 : 2	10 Hz 1 : 2	1 : 2	10 Hz 1 : 1	10 Hz 1 : 1	10 Hz 1 : 1	10 Hz 1 : 1
Rated voltage	300 V	300 V	300 V	300 V	300 V	300 V	300 V
Rated impulse voltage	6 kV	6 kV	6 kV	6 kV	6 kV	6 kV	6 kV
Overvoltage category	IV	IV	IV	III	IV	IV	IV
Pollution severity	2	2	2	2	2	2	2
Clearances and creepage distances	≥ 5.5 mm	≥ 5.5 mm	≥ 5.5 mm	≥ 5.5 mm	≥ 5.5 mm	≥ 5.5 mm	≥ 5.5 mm
Opto-coupler	according to DIN VDE 0884	according to DIN VDE 0884	according to DIN VDE 0884	according to DIN VDE 0884	according to DIN VDE 0884	according to DIN VDE 0884	according to DIN VDE 0884
Test voltage (corresponds 100% module test)	according to DIN VDE 0884	according to DIN VDE 0884	according to DIN VDE 0884	according to DIN VDE 0884	according to DIN VDE 0884	according to DIN VDE 0884	according to DIN VDE 0884
Module is immune to interference	non-destructive test 1 kV	non-destructive test 1 kV	non-destructive test 1 kV	non-destructive test 1 kV	non-destructive test 1 kV	non-destructive test 1 kV	non-destructive test 1 kV
Insulation voltage	acc. to IEC 801-4 severity 4	acc. to IEC 801-4 severity 4	acc. to IEC 801-4 severity 4	acc. to IEC 801-4 severity 4	acc. to IEC 801-4 severity 4	acc. to IEC 801-4 severity 4	acc. to IEC 801-4 severity 4
Input – output/mounting rail	4 kV~eff 1 min.					4 kV~eff 1 min.	
Storage temperature	–40 °C...+85 °C					–40 °C...+70 °C	
Ambient temperature	–25 °C...+60 °C					–25 °C...+40 °C	
–, rowed on mounting rail without clearances	–25 °C...+60 °C					–25 °C...+45 °C	
–, rowed with clearances ≥ 20 mm							

¹⁾ Not TTL-compatible

²⁾ Conditionally level-compatible

Opto-coupler on locking socket profile RS 40

RS 40



Ordering data				
Connection method	Input voltage	Function indicator	Screw connection (GSE)	Disconnect plug with screw connection (BL/SL)
	5 V ²⁾	Yellow LED	1118861001	1161560000
	12 V ₀	Green LED	1118761001	1161660000
	24 V~	Yellow LED	1160961001	1161760000 1177860000 ¹⁾
	24 V ₀	Yellow LED Green LED	1117461001 8065031001	1119460000
	48 V ₀	Green LED	1161061001	1161860000
	115 V ₀	Green LED	1161161001	1161960000
	230 V~	Green LED	1161461001	1162060000
	230 V~	Red LED		8182690000

Connection data				
Insulation stripping length			7 mm	6 mm
Conductor cross-section		0.5...2.5 mm ²	0.5...1.5 mm ²	
			AWG 26...14	AWG 26...16
Dimensions				
Mounting width			11.2 mm	11.2 mm
Length (perpendicular to mounting rail)			70 mm	74 mm
Height TS/TS 35 x 7.5			56 mm/51.5 mm	56 mm/51.5 mm

¹⁾ Output 5 VTTL-compatible
²⁾ Conditionally level-compatible

Opto coupler on locking socket with multiple interface RSM

(Opto-couplers)

RSM 4 OS

4 opto-couplers


RSM 8 OS

8 opto-couplers

Note!

During operation and maintenance
please observe the relevant ESD
measures.


(ESD endangered area)



Also available as relay coupler, see page 84/85

Schematic circuit diagram


Opto coupler 24 Vdc / 2 A



Rated data	
Input voltage	5 V ⁻¹ ±10 %
Rated consumption ~ (W)	60 mW
Rated consumption ~ (VA)	–
Output operating voltage	5...48 V ¹⁾
Voltage drop at max. load current	<1.6 V
Output current	0.1 A

Derating curve
a = Continuous operation

b = Switching mode




Pulse duration, limiting overload current (not periodic)	0.8 A/10 ms
Max. reverse current (static current), at U	0.16 mA
Switching frequency	100 Hz
Storage temperature	–40 °C...+85 °C
Ambient temperature	–25 °C...+60 °C
–, rowed on mounting rail without clearances	–25 °C...+60 °C
–, rowed with clearances x 20 mm	–25 °C...+60 °C

Dimensions	
Mounting width	
RSM 4	75 mm
RSM 8	145 mm
RSM 16	285 mm
Length (perpendicular to mounting rail)	87 mm

DC voltage/positive switching (joint negative)


Standard Opto coupler 5...48 Vdc / 100 mA



Rated data	
Input voltage	24 V ⁻ ±10 %
Rated consumption ~ (W)	400 mW
Rated consumption ~ (VA)	–
Output operating voltage	5...48 V ¹⁾
Voltage drop at max. load current	<1.6 V
Output current	0.1 A

Derating curve
a = Continuous operation

b = Switching mode



Pulse duration, limiting overload current (not periodic)	0.8 A/10 ms
Max. reverse current (static current), at U	0.16 mA
Switching frequency	100 Hz
Storage temperature	–40 °C...+85 °C
Ambient temperature	–25 °C...+60 °C
–, rowed on mounting rail without clearances	–25 °C...+60 °C
–, rowed with clearances x 20 mm	–25 °C...+60 °C


Dimensions	
Mounting width	
RSM 4	75 mm
RSM 8	145 mm
RSM 16	285 mm
Length (perpendicular to mounting rail)	87 mm

¹⁾ Not TTL-compatible


Opto coupler on locking socket with multiple interface RSM

RSM 16 OS


16 Opto couplers



DC/negative switching (common positive)



DC/AC voltage



Ordering data										
Conn. method	Input voltage	RSM 4 OS		RSM 8 OS		RSM 16 OS		Positive switching ³⁾	Negative switching ⁴⁾	Cat. No.
Input/output		w/o. optocoupl.	4 optocoupl.	w/o. optocoupl.	8 optocoupl.	w/o. optocoupl.	16 optocoupl.			Mount. width (mm)
Screw/			•					•		1123661001
	5 V ⁻²⁾				•			•		1124061001
							•	•		1124461001
		•						•		8017581001
			•*					•		1123861001
			•*						•	1123761001
	24 V ⁻			•				•		8003671001
				•					•	8021391001
					•*			•		1124261001
						•		•		8018221001
						•			•	8082471001
							•*	•		1124661001
	24 V ⁰		•*							1125161001
					•*					1125261001

* equipped as standard with opto-coupler 5...48 Vdc / 100 mA

Connection data

Insulation stripping length	7 mm				
Conductor cross-section	0.5...2.5 mm ² /AWG 26...14				
Replacement opto-c.	Type	Input voltage	Output voltage	Output current	Cat. No.
	OS	5 V ⁻⁵⁾ ±10 %	24 V ⁻ ±20 %	0.1 A	1121100000
	OS	12 V ⁻⁵⁾ ±10 %	5...48 V ⁻	0.1 A	1124800000
	OS	12 V ⁰ ±10 %	5...48 V ⁻	0.1 A	1121200000
	OS	24 V ⁻⁵⁾ ±10 %	5...48 V ⁻	0.1 A	1124900000
	OS	24 V ⁻⁵⁾ ±10 %	24 V ⁻ +10 %	2.0 A	1170200000
	OS	24 V ⁻⁵⁾ ±10 %	250 V ⁻	0.1 A	1153200000
	OS	24 V ⁰ ±10 %	5...48 V ⁻	0.1 A	1121300000

²⁾ 5 V TTL Input voltage on request

³⁾ Common negative potential, positive is switched

⁴⁾ Common positive potential, negative is switched

⁵⁾ Not suitable for DC/AC version

Opto coupler, locking socket for semi-conductor relays

Single and multiple socket interface-unit

Advantages of semiconductor relays:


- Wear-free switching also with high switching frequencies
- Bounce-free switching
- No electromagnetic interferences
- High insulation-voltage between load and control circuit

Note!
The relevant ESD measures are to be observed during commissioning and maintenance (ESD endangered area)


RS 1 HR



RSM 4 HR






RSM 8 HR



RSM 8 HR-100

RSM 16 HR-100

Schematic circuit diagram



Ordering data	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.
	RS 1 HR	1166961001	RSM 4 HR	1167061001 ³⁾	RSM 8 HR	1167161001 ³⁾	RSM 8 HR-100	1166261001 ³⁾	RSM 16 HR-100*	1167261001 ³⁾
Rated data (with input module)¹⁾										
Input voltage, max.	250 V~		250 V~		250 V~		250 V~		250 V~	
Input current (per channel)	25 mA		25 mA		25 mA		25 mA		25 mA	
Max. output voltage	24 V0		24 V0		24 V0		24 V0		24 V0	
Output current (per channel), max.	Depending on module		Depending on module		Depending on module		Depending on module		Depending on module	
Rated data (with output module)¹⁾										
Input voltage, max.:	24 V0		24 V0		24 V0		24 V0		24 V0	
Input current (per channel)	Depending on module		Depending on module		Depending on module		Depending on module		Depending on module	
Max. output supply voltage	250 V		250 V		250 V		250 V		250 V	
Max. output current (per channel)	Depending on module		Depending on module		Depending on module		Depending on module		Depending on module	
Auxiliary voltage	24 V- ±10 %		24 V- ±10 %		24 V- ±10 %		24 V- ±10 %		24 V- ±10 %	
Status indicator	LED red		LED red		LED red		LED red		LED red	
Fuse	5x20, 5 A quick		5x20, 5 A quick		5x20, 5 A quick		5x20, 5 A quick		5x20, 5 A quick	
Storage temperature	-40 °C...+70 °C		-40 °C...+70 °C		-40 °C...+70 °C		-40 °C...+70 °C		-40 °C...+70 °C	
Ambient temperature	-25 °C...+70 °C		-25 °C...+70 °C		-25 °C...+70 °C		-25 °C...+70 °C		-25 °C...+70 °C	
	Dependent on semiconductor relay used		Dependent on semiconductor relay used		Dependent on semiconductor relay used		Dependent on semiconductor relay used		Dependent on semiconductor relay used	
Connection data										
Conductor cross-section	0.5...2.5 mm ²		0.5...2.5 mm ²		0.5...2.5 mm ²		0.5...2.5 mm ²		0.5...2.5 mm ²	
Screw connection	–		–		–		–		–	
Male connect. block DIN 41651 ²⁾	–		–		10-pole		10-pole		20-pole	
„Sub-D“-connection ²⁾	–		–		15-pole		15-pole		25-pole	
Dimensions										
Mounting width	35 mm		130 mm		249 mm		156 mm		305 mm	
Length (perpendicular to mounting rail)	87 mm		87 mm		87 mm		109 mm		109 mm	

¹⁾ The rating data depend on the used module
²⁾ on request

³⁾ Mixed placement of input and output modules is not valid.

Semi-conductor relays


**Solid state relays
for signal input
and output**

**Input module
HRE 24**
DC/DC






Input module HRE 115/HRE 230
AC/DC

**Output module
HRA 230**
DC/AC

**Output module
HRA 60**
DC/DC



Schematic circuit diagram



Ordering data	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.	Type	Cat. No.
	HRE 24	117440000	HRE 115	1174500000	HRE 230	1174600000	HRA 230	1174100000	HRA 60	1174300000
Rated data										
Input voltage	10...32 V- (process)		90...140 V₀ (process)		180 V...280 V₀ (process)		18...32 V- (Logic)		18...32 V- (Logic)	
Input current at max. V	21.33 mA		10 mA		6.4 mA		—		—	
Input resistance	1.5 kΩ		14 kΩ		44 kΩ		2.2 kΩ		2.2 kΩ	
Switch-on voltage	—		—		—		3 V		3 V	
Switch-off voltage	—		—		—		1 V		1 V	
Max. output operating voltage	18...32 V (Logic) ¹⁾		18...32 V (Logic) ¹⁾		18...32 V (Logic) ¹⁾		24...250 V~ ¹⁾²⁾ (process)		5...60 V~ ¹⁾²⁾ (process)	
Voltage drop at max. load current	0.4 V		0.4 V		0.4 V		—		—	
Max. output current (Continuous test)	100 mA		100 mA		100 mA		3 A		3 A, resistive load	
Derating curve a = self-cooling b = mounted on 2 k/W heat sink Continuous current										
Ambient temperature										
Min. Load current	—		—		—		20 mA		—	
Leakage current in off-condition at rated load voltage	max. 100 µA		max. 100 µA		max. 100 µA		6 mA		1 mA	
Surge current	—		—		—		75 A/20 ms		5 A/1 s	
Switch-on time	5 ms		20 ms		20 ms		≤ 1/2 Period		100 µs	
Switch-off time	5 ms		20 ms		20 ms		≤ 1/2 Period		750 µs	
Input impulse	—		—		—		unlimited, t _{min} 100 µs		unlimited, t _{min} 100 µs	
Storage temperature	-40 °C...+100 °C		-40 °C...+100 °C		-40 °C...+100 °C		-40 °C...+100 °C		-40 °C...+100 °C	
Ambient temperature	-20 °C...+ 70 °C		-25 °C...+ 70 °C		-25 °C...+ 70 °C		-25 °C...+ 70 °C		-25 °C...+ 70 °C	

¹⁾ 250 V max. in connection with HR modules.
Only negative-switching when used on HR-socket!

²⁾ For inductive loads the module must be protected with diode or varistor.



Timers

The IT product family of electronic delay timers from Weidmüller are the optimum solution for industrial tasks.

The product family IT offers:

- Response delay (ITR)
- Wiping contact without control input (ITWo)
- Wiping contact with control input (ITWw)
- Turn-off delay without control input (ITTo)
- Turn off delay without control input (ITTTo)
- Pulse generator (ITTT)
- Multifunction (ITM)
- Multifunction (ITMF)

Designation of types:

I = Industry

T = Timer

R = Response Delay

Wo = Wiping contact relay without control input

Ww = Wiping contact relay with control input

To = Turn -off delay without control input

Tw = Turn-off delay with control input

TT = Two Times

M = Multifunction

MF = Multifunction Four

Time ranges and supply voltages of delay timer relays




The modules' functions for 4 or 7 time can be precisely selected via the rotary button.

The multiple voltage ranges of the supply voltage allow for a wide area of use in industry (see table).

Product	Time	Range	Voltage supply
ITR	0.1 s - 100 h	0.1 s - 1 s	1 min - 10 min
ITWo, ITTT		1 s - 10 s	0.1 h - 1 h
ITTW		0.1 min - 1 min	1 h - 10 h
ITWw		10 h - 100 h	
ITMF, ITM			
ITTo	0.06 s - 160 s	0.06 s - 0.6 s	2 s - 20 s
		0.25 s - 2.5 s	16 s - 160 s
			24 V - 240 VAC
			24 VDC

Output of the timing relays



The load in every module is switched by a changeover relay (250 V, 8 A). The multifunction module (ITM) switches both changeover relays immediately or, one changeover relay immediately and the other changeover relay delayed.



Characteristic data of output contacts

Limit values by resistive load

Service life of contacts by resistive load



Functions of the Timers

Response delay ITR timer relay

As soon as the operating voltage is applied, the preset delay period T begins. After time period T has expired, output R connects the load.



Wiping contact timer relay without control input ITWo

When the operating voltage is applied, output R connects the load immediately. After the preset delay period T has expired, output R disconnects the load.



Wiping contact timer relay with control input ITWw

As soon as the operating voltage is applied, a pulse (e. g. 50 ms) or a voltage is applied to control input Y1. Output R connects the load immediately. After the preset delay period T has expired, output R disconnects the load.




Turn-off delay timer relay without control input ITTo

As soon as the operating voltage is applied, output R connects the load. Delay period T does not begin until the operating voltage is switched off. After delay period T has expired, output R disconnects the load.




Turn-off delay timer relay with control input ITTw

After the operating voltage has been applied and control input Y1 has been activated, output R connects the load for an indefinite period of time. When the control input is opened and after the preset time period T has expired, the output disconnects the load.




Pulse generator ITTT

The repeat cycles starts with two individually adjustable times after applying the supply voltage. There is a different starting state for each delay.



Multifunction ITM/ITMF

Function A: Response delay




As soon as the operating voltage is applied, the preset delay period T begins. After time period T has expired, output R connects the load.

Function Ac: Response delay and turn-off delay



As soon as operating voltage has been applied and control input Y1 has closed, delay period T begins. After time period T has expired, output R connects the load (delayed response). When control input Y1 is opened, the output disconnects the load after the preset time period has expired (delayed turn-off).

Function At: Additive response delay




As soon as the operating voltage has been applied and delay period T has expired, output R connects the load. At control input Y1 the contact break intervals are accumulated (additive process). As soon as the operating voltage is switched off, the load at output R is disconnected.

Function B: Wiping contact with control input




As soon as the operating voltage has been applied, a pulse (min 50 ms) or a voltage can be applied to control input Y1. Output R connects the load immediately. After delay period T has expired, output R disconnects the load.

Function Bw: Wiping function



The operating voltage must be applied. As soon as a voltage is applied to control input Y1, output R connects the load for the preset time T. After time period T has expired, output R disconnects the load. As soon as the control input is opened, output R once more connects the load for the duration of time period T. After time period T has expired, output R disconnects the load.

Function C: Turn-off delay with control input




As soon as the operating voltage has been applied and control input Y1 has been activated, output R connects the load for an indefinite period of time. When the control input is opened and after the preset time period T has expired, the output disconnects the load.

Function D: Pulse generator (begins in the zero position)




As soon as the operating voltage has been applied, output R simultaneously switches the load alternately between the zero position and operating position for the period of the preset time T. With this function, the cycle begins at the zero position.

Function Di: Pulse generator (begins in the operating position)




As soon as the operating voltage has been applied, output R simultaneously switches the load alternately between the zero position and operating position for the period of the preset time T. With this function, the cycle begins at the operating position.

Function H: Wiping contact without control input



As soon as the operating voltage is applied, output R connects the load immediately. After delay period T has expired, output R disconnects the load.

Function Ht: Wiping contact, additive



As soon as the operating voltage is applied, output R connects the load immediately. At control input Y1 the contact break intervals are accumulated (additive process) and when the preset delay period has expired, output R disconnects the load.

U = Operating voltage

R = Output relay or load

T = Delay

Y1 = Control input

Timers

Status LED

Two LED's show the status of the modules:

- green LED = supply voltage connected
- yellow LED = relay output active (not for ITTO)

Marking

Marking is done on a removable tag or on the marking area. The function is printed on the **front** of the module.


Control lamp for verifying contact

A control lamp can be wired parallel to input Y1 to show the status of control input.


Assembly

Mount direct onto DIN TS 35 mounting rails.

on DIN rail



on panel using M4 screws



Approvals and standards

This relay has a high resistance to interference. The housing material is self-extinguishing (UL94/V0).

Manufacturing to IEC/VDE and UL/CSA approvals permit worldwide usage.


- IEC 255 static measuring relays
- IEC529 testers and test procedures
- IEC 664 regulations for high-voltage fuses for motor circuits
- IEC 801 EMC compatibility
- VDE 0110 insulation coordination for low-voltage electrical equipment
- VDE 0435 relays with fixed times

Connection technology

Clamping yoke has the following capacities:

- 2 x 1.5 mm² with ferrule
- 2 x 2.5 mm² without ferrule
- 1 x 4 mm² without ferrule

Dimensions IT




Multifunctional Timers

- Response delay
- Response delay and turn-off delay
- Additive response delay
- Wiping contact with control input
- Wiping function
- Turn-off delay with control input
- Pulse generator (begins in the zero position)
- Pulse generator (begins in the operating position)
- Wiping contact without control input
- Wiping contact, additive

Schematic circuit diagram

ITM

Multifunctional timer relay



Ordering data

Contact	
Time periods	
Repeat accuracy (const. parameter)	
Accuracy of indication acc. to IEC 1812-1	
Input	
Input voltage	
Voltage tolerance	
Duty factor	
Rated power consumption	
Min pulse duration type	
Max. reset time at voltage interruption	
Protection against voltage interruption	

Output

Contact	
Contact material	
Service life	- mechanical
	- electrical
Switching current	- max.
	- min.

Max. switching voltage

Switching current

Status indicators

Voltage applied	
Relay output active	
Approvals	
Standards	

Temperature	- Storage temperature
	- Operating temperature
Clearance/creepage path. acc. to IEC 664/VDE 0110	
Protection category IEC 529	- Terminal block
	- Front

Mounting

Installation category to IEC 664

Connection

- with ferrule	
- without ferrule	

Enclosure material

Weight, typ.

Type	Cat. No.
ITM	8362550000

changeover	
0.1 s - 100 h	
1 s, 10 s, 1 min	
1 h, 10 h, 100 h	

± 0.5%

± 10% (25 °C)

12 V...240 Vac/dc / 50...60 Hz

85 - 110% U_N

100 %

7 VA / 230 V~

≥ 50 ms

≤ 100 ms

> 10 ms

Relay output

2 changeover

AgCdO

5 x 10⁶ switching operations

10⁵ switching operations at 2000 VA resistive load

8 A₀ / changeover contact

100 mA₀

250 V₀

2000 VA / 80 W

green LED

yellow LED

UL / CSA

IEC 529/IEC 664/IEC 801/IEC 255

VDE 0435/VDE 0110

-30°C...+70°C

-20°C...+60°C

4 kV

IP 20

IP 50

DIN rail 35 mm

Category III

2 x 1.5 mm²

2 x 2.5 mm² / 1 x 4 mm²

self extinguishing

110 g

Function A: Response delay




As soon as the operating voltage is applied, the preset delay period T begins. After time period T has expired, output R connects the load.

Function Ac: Response delay and turn-off delay



As soon as operating voltage has been applied and control input Y1 has closed, delay period T begins. After time period T has expired, output R connects the load (delayed response). When control input Y1 is opened, the output disconnects the load after the preset time period has expired (delayed turn-off).

Function At: Additive response delay




As soon as the operating voltage has been applied and delay period T has expired, output R connects the load. At control input Y1 the contact break intervals are accumulated (additive process). As soon as the operating voltage is switched off, the load at output R is disconnected.

Function B: Wiping contact with control input




As soon as the operating voltage has been applied, a pulse (min 50 ms) or a voltage can be applied to control input Y1. Output R connects the load immediately. After delay period T has expired, output R disconnects the load.

Function Bw: Wiping function



The operating voltage must be applied. As soon as a voltage is applied to control input Y1, output R connects the load for the preset time T. After time period T has expired, output R disconnects the load. As soon as the control input is opened, output R once more connects the load for the duration of time period T. After time period T has expired, output R disconnects the load.

Function C: Turn-off delay with control input



As soon as the operating voltage has been applied and control input Y1 has been activated, output R connects the load for an indefinite period of time. When the control input is opened and after the preset time period T has expired, the output disconnects the load.

Function D: Pulse generator (begins in the zero position)



As soon as the operating voltage has been applied, output R simultaneously switches the load alternately between the zero position and operating position for the period of the preset time T. With this function, the cycle begins at the zero position.

Function Di: Pulse generator (begins in the operating position)




As soon as the operating voltage has been applied, output R simultaneously switches the load alternately between the zero position and operating position for the period of the preset time T. With this function, the cycle begins at the operating position.

Function H: Wiping contact without control input



As soon as the operating voltage is applied, output R connects the load immediately. After delay period T has expired, output R disconnects the load.

Function Ht: Wiping contact, additive



As soon as the operating voltage is applied, output R connects the load immediately. At control input Y1 the contact break intervals are accumulated (additive process) and when the preset delay period has expired, output R disconnects the load.

U = Operating voltage

R = Output relay or load

T = Delay

Y1 = Control input

Timers

ITTo

Turn-off delay timer relay **without** control input





ITTW

Turn-off delay timer relay **with** control input



Schematic circuit diagram



Ordering data	Type	Cat. No.	Type	Cat. No.
Contact	ITTo	836260000	ITTW	8362610000
Time periods	Changeover		Changeover	
	0.6 s - 160 s		0.1 s - 100 h	
	(0.06 s - 0.6 s, 0.25 s - 2.5 s,		(0.1 s - 1 s, 1 s - 10 s, 0.1 min - 1 min,	
	2 s - 20 s, 16 s - 160 s)		1 min - 10 min, 0.1 h - 1 h, 1 h - 10h)	
Repeat accuracy (const. parameter)	± 0.5%		± 0.5%	
Anzeigegegnauigkeit gemäß IEC 1812-1	± 10% (25 °C)		± 10% (25 °C)	
Input				
Input voltage	24 Vdc/ 24...240 Vac / 50...60 Hz		24 Vdc/ 24...240 Vac / 50...60 Hz	
Voltage tolerance	85 - 110% U _N		85 - 115% U _N (110% for 240 V)	
Duty factor	100 %		100 %	
Rated power consumption	0.5 W / 30 VA / 230 V~		0.5 W / 24 V- / 1 W / 48 V- / 2 VA / 48 V~	
Min. switch-on time for the supply	-		1.5 VA / 24 V~	
			12 VA / 230 V~	
Min pulse duration type	≥ 50 ms		≥ 50 ms	
Max. reset time at voltage interruption	≤ 100 ms		≤ 100 ms	
Protection against voltage interruption	> 10 ms		> 10 ms	
Output	Relay output		Relay output	
Contact	2 changeover		1 changeover	
Contact material	AgCdO		AgCdO	
Service life	5 x 10 ⁶ switching operations		5 x 10 ⁶ switching operations	
	10 ⁵ switching operations at 1250 VA resistive load		10 ⁵ switching operations at 2000 VA resistive load	
Switching current	8 A ₀ / changeover contact		8 A ₀	
	100 mA ₀		100 mA ₀	
Max. switching voltage	250 V ₀		250 V ₀	
Switching current	1250 VA / 80 W		2000 VA / 80 W	
Status indicators				
Voltage applied	green LED		green LED	
Relay output active	yellow LED		yellow LED	
Approvals	UL / CSA		UL / CSA	
Standards	IEC 529/IEC 664/IEC 801/IEC 255		IEC 529/IEC 664/IEC 801/IEC 255	
	VDE 0435/VDE 0110		VDE 0435/VDE 0110	
Temperature	-30°C...+70°C		-30°C...+70°C	
	-20°C...+60°C		-20°C...+60°C	
Clearance/creepage path. acc. to IEC 664/VDE 0110	4 kV / 2		4 kV / 2	
Protection category IEC 529 - Terminal block	IP 20		IP 20	
	IP 50		IP 50	
Mounting	DIN rail 35 mm		DIN rail 35 mm	
Installation category to IEC 664	Category III		Category III	
Connection				
- with ferrule	2 x 1.5 mm ²		2 x 1.5 mm ²	
- without ferrule	2 x 2.5 mm ² / 1 x 4 mm ²		2 x 2.5 mm ² / 1 x 4 mm ²	
Enclosure material	self extinguishing		self extinguishing	
Weight, typ.	100 g		100 g	

Timers

ITWo

Wiping contact timer relay **without** control input





ITWw

Wiping contact timer relay **with** control input



Schematic circuit diagram



Ordering data

Contact	
Time periods	
Repeat accuracy (const. parameter)	
Accuracy of indication acc. to IEC 1812-1	
Input	
Input voltage	
Voltage tolerance	
Duty factor	
Rated power consumption	
Min pulse duration type	
Max. reset time at voltage interruption	
Protection against voltage interruption	
Output	
Contact	
Contact material	
Service life	- mechanical
	- electrical
Switching current	- max.
	- min.
Max. switching voltage	
Switching current	
Status indicators	
Voltage applied	
Relay output active	
Approvals	
Standards	
Temperature	- Storage temperature
	- Operating temperature
Clearance/creepage path. acc. to IEC 664/VDE 0110	
Protection category IEC 529	- Terminal block
	- Front
Mounting	
Installation category to IEC 664	
Connection	
- with ferrule	
- without ferrule	
Enclosure material	
Weight, typ.	

Type	Cat. No.
ITWo	8362580000
Changeover	
0.1 s - 100 h	
(0.1 - 1 s, 1 s - 10 s, 0.1 min. - 1 min.,	
1 min. - 10 min., 0.1 h - 1 h, 1 h - 10 h, 100 h)	
± 0.5%	
± 10% (25 °C)	
24 Vdc/ 24...240 Vac / 50...60 Hz	
85 - 115% U _N (110% for 240 V)	
100 %	
0.5 W / 24 V-	
1.5 VA / 24 V~	
12 VA / 230 V~	
≥ 50 ms	
≤ 100 ms	
> 10 ms	
Relay output	
1 changeover	
AgCdO	
5 x 10 ⁶ switching operations	
10 ⁵ switching operations at 2000 VA resistive load	
8 A0	
100 mA0	
250 V0	
2000 VA / 80 W	
green LED	
yellow LED	
UL / CSA	
IEC 529/IEC 664/IEC 801/IEC 255	
VDE 0435/VDE 0110	
-30°C...+70°C	
-20°C...+60°C	
4 kV / 2	
IP 20	
IP 50	
DIN rail 35 mm	
Category III	
2 x 1.5 mm ²	
2 x 2.5 mm ² / 1 x 4 mm ²	
self extinguishing	
100 g	

Type	Cat. No.
ITWw	8362590000
Changeover	
0.1 s - 100 h	
(0.1 - 1 s, 1 s - 10 s, 0.1 min. - 1 min.,	
1 min. - 10 min., 0.1 h - 1 h, 1 h - 10 h, 100 h)	
± 0.5%	
± 10% (25 °C)	
24 Vdc/ 24...240 Vac / 50...60 Hz	
85 - 115% U _N (110% for 240 V)	
100 %	
0.5 W / 24 V- / 1 W / 48 V- / 2 VA / 48 V~	
1.5 VA / 24 V~	
12 VA / 230 V~	
≥ 50 ms	
≤ 100 ms	
> 10 ms	
Relay output	
1 changeover	
AgCdO	
5 x 10 ⁶ switching operations	
10 ⁵ switching operations at 2000 VA resistive load	
8 A0	
100 mA0	
250 V0	
2000 VA / 80 W	
green LED	
yellow LED	
UL / CSA	
IEC 529/IEC 664/IEC 801/IEC 255	
VDE 0435/VDE 0110	
-30°C...+70°C	
-20°C...+60°C	
4 kV / 2	
IP 20	
IP 50	
DIN rail 35 mm	
Category III	
2 x 1.5 mm ²	
2 x 2.5 mm ² / 1 x 4 mm ²	
self extinguishing	
100 g	

Timers

ITTT

Pulse generator





ITMF

Multifunction - timer relay



Schematic circuit diagram




Ordering data	Type	Cat. No.	Type	Cat. No.
Contact	ITTT	8324050000	ITMF	8287770000
Time periods	Changeover		Changeover	
	0.1 s - 100 h		0.1 s - 100 h	
	(0.1 - 1 s, 1 s - 10 s, 0.1 min. - 1 min.,		(0.1 - 1 s, 1 s - 10 s, 0.1 min. - 1 min.,	
	1 min. - 10 min., 0.1 h - 1 h, 1 h - 10 h, 100 h)		1 min. - 10 min., 0.1 h - 1 h, 1 h - 10 h, 100 h)	
Repeat accuracy (const. parameter)	± 0.5%		± 0.5%	
Accuracy of indication acc. to IEC 1812-1	± 10% (25 °C)		± 10% (25 °C)	
Input				
Input voltage	24 Vdc/ 24...240 Vac / 50...60 Hz		24 Vdc/ 24...240 Vac / 50...60 Hz	
Voltage tolerance	85 - 115% U _N (110% for 240 V)		85 - 115% U _N (110% for 240 V)	
Duty factor	100 %		100 %	
Rated power consumption	0.5 W / 24 V-		0.5 W / 24 V- / 1 W / 48 V-	
	1.5 VA / 24 V~		1.5 VA / 24 V~ / 2 VA / 48 V~	
	12 VA / 230 V~		12 VA / 230 V~	
Min pulse duration type	≥ 50 ms		≥ 50 ms	
Max. reset time at voltage interruption	≤ 100 ms		≤ 100 ms	
Protection against voltage interruption	> 10 ms		> 10 ms	
Output	Relay output		Relay output	
Contact	1 changeover		1 changeover	
Contact material	AgCdO		AgCdO	
Service life	5 x 10 ⁶ switching operations		5 x 10 ⁶ switching operations	
	10 ⁵ switching operations at 2000 VA resistive load		10 ⁵ switching operations at 2000 VA resistive load	
Switching current	8 A ₀		8 A ₀	
	100 mA ₀		100 mA ₀	
Max. switching voltage	250 V ₀		250 V ₀	
Switching current	2000 VA / 80 W		2000 VA / 80 W	
Status indicators				
Voltage applied	green LED		green LED	
Relay output active	yellow LED		yellow LED	
Approvals	UL / CSA		UL / CSA	
Standards	IEC 529/IEC 664/IEC 801/IEC 255		IEC 529/IEC 664/IEC 801/IEC 255	
	VDE 0435/VDE 0110		VDE 0435/VDE 0110	
Temperature	-30°C...+70°C		-30°C...+70°C	
	-20°C...+60°C		-20°C...+60°C	
Clearance/creepage path. acc. to IEC 664/VDE 0110	4 kV / 2		4 kV / 2	
Protection category IEC 529 - Terminal block	IP 20		IP 20	
	IP 50		IP 50	
Mounting	DIN rail 35 mm		DIN rail 35 mm	
Installation category to IEC 664	Category III		Category III	
Connection				
- with ferrule	2 x 1.5 mm ²		2 x 1.5 mm ²	
- without ferrule	2 x 2.5 mm ² / 1 x 4 mm ²		2 x 2.5 mm ² / 1 x 4 mm ²	
Enclosure material	self extinguishing		self extinguishing	
Weight, typ.	100 g		100 g	

ITR

Response delay timer relay



Schematic circuit diagram




Ordering data

Ordering data	Type	Cat. No.
Contact	ITR	8362570000
Time periods	Changeover	
	0.1 s - 100 h	
	(0.1 - 1 s, 1 s - 10 s, 0.1 min. - 1 min.,	
	1 min. - 10 min., 0.1 h - 1 h, 1 h - 10 h, 100 h)	
Repeat accuracy (const. parameter)	± 0.5%	
Accuracy of indication acc. to IEC 1812-1	± 10% (25 °C)	
Input	24 Vdc/ 24...240 Vac / 50...60 Hz	
Input voltage	85 - 115% U _N (110% for 240 V)	
Voltage tolerance	100 %	
Duty factor	0.5 W / 24 V-	
Rated power consumption	1.5 VA / 24 V~	
	12 VA / 230 V~	
Min pulse duration type	≥ 50 ms	
Max. reset time at voltage interruption	≤ 100 ms	
Protection against voltage interruption	> 10 ms	
Output	Relay output	
Contact	1 changeover	
Contact material	AgCdO	
Service life	5 x 10 ⁶ switching operations	
	10 ⁵ switching operations at 2000 VA resistive load	
Switching current	8 A ₀	
	100 mA ₀	
Max. switching voltage	250 V ₀	
Switching current	2000 VA / 80 W	
Status indicators		
Voltage applied	green LED	
Relay output active	yellow LED	
Approvals	UL / CSA	
Standards	IEC 529/IEC 664/IEC 801/IEC 255	
	VDE 0435/VDE 0110	
Temperature	- Storage temperature	-30°C...+70°C
	- Operating temperature	-20°C...+60°C
Clearance/creepage path. acc. to IEC 664/VDE 0110	4 kV / 2	
Protection category IEC 529 - Terminal block	IP 20	
	IP 50	
Mounting	DIN rail 35 mm	
Installation category to IEC 664	Category III	
Connection		
- with ferrule	2 x 1.5 mm ²	
- without ferrule	2 x 2.5 mm ² / 1 x 4 mm ²	
Enclosure material	self extinguishing	
Weight, typ.	100 g	

Timers

Signal conditioning


DKZ/DKZA timer modules



DKZ

DKZA

- Components for extending short pulses
- Provides PLC versions with switch-on/off delay
- Fixed times






DKZ 24 Vac/dc

DKZA 24 Vac/dc

DKZA 24 Vac/dc


Schematic circuit diagram



Ordering data		Type	Cat. No.	Type	Cat. No.	Type	Cat. No.
For TS 32	Y	DKZ 24 Vac/dc 32	8008130000	DKZA 24 Vdc 32	8008120000	DKZA 24 Vdc 32	8020990000
For TS 35	W	DKZ 24 Vac/dc 35	8008190000	DKZA 24 Vdc 35	8008180000	DKZA 24 Vdc 35	8022110000
Technical data							
Input							
Input voltage		24 Vac/dc ±10 %		24 Vdc ±18 %		24 Vdc ±10 %	
Input nominal current		5.1 mAdc/6.1 mAac ±10 %		6.7 mA ±10 %		6.7 mA ±10 %	
Input current (at first-time power-up)				200 mA ±10 %		200 mA ±10 %	
Input power		130 mW ±10 % / 150 mVA ±10 %		160 mW ±10 %		160 mW	
Switch-on delay		1s					
Switch-off delay		≤ 0.7 ms		50 ms		150 ms	
Min. pulse duration of input voltage				2 ms		2.5 ms	
Output							
Max. output voltage		5...48 Vdc		5...48 Vdc		5...48 Vdc	
Max. output current		20 mA		20 mA		20 mA	
Reverse current, max. (closed-circuit current)		≤ 0.16 mA (at 48 V)		≤ 0.16 mA (at 48 V)		≤ 0.16 mA (at 48 V)	
Max. voltage drop at max. load current		≤ 1 V		≤ 1.6 V		≤ 1.6 V	
Max. switching frequency		0.9 Hz		20 Hz		20 Hz	
Isolation coordinates acc. to DIN VDE 0160, Draft11/94							
Rated voltage		300 V		300 V		300 V	
Rated impulse voltage		4 kV		4 kV		4 kV	
Overvoltage category		III		III		III	
Pollution severity		2		2		2	
Clearance and creepage distances		≥4 mm		≥4 mm		≥4 mm	
Voltage proof, input/output-TS		4 kVeff		4 kVeff		4 kVeff	
Operating temperature	without clearances	-25 °C...+50 °C		-25 °C...+50 °C		-25 °C...+50 °C	
	with clearances	-25 °C...+50 °C		-25 °C...+50 °C		-25 °C...+50 °C	
Storage temperature		-40 °C...+85 °C		-40 °C...+85 °C		-40 °C...+85 °C	
Total width		6 mm		6 mm		6 mm	
Conductor		AWG 22...12		AWG 22...12		AWG 22...12	
Conductor cross-section		0.5...4 mm ²		0.5...4 mm ²		0.5...4 mm ²	
Reverse polarity protection		ja		ja		ja	
Accessories		Type	Cat. No.	Type	Cat. No.	Type	Cat. No.
End plate		AP DKT4	0687560000	AP DKT4	0687560000	AP DKT4	0687560000
Dimensions see		Page 305		Page 305		Page 305	


Timers

Pulse conditioning DKZ/DKZA timer modules




DKZ

DKZA




Schematic circuit diagram


DKZ DK5



DKZ DK5



DKZ DK5



Ordering data

For TS 32

For TS 35

With combi foot TS32/TS 35

Technical data

Input

Supply voltage

Supply current

Control voltage

Control input current

Output

Output voltage

Max. output current

Internal voltage drop

Range of switch-on delay

Type Cat. No.

DKZ DK5 8228680000

Type Cat. No.

DKZ DK5 8243780000

Type Cat. No.

DKZ DK5 8019650000

Isolation coordinates acc. to DIN VDE 0160, Draft11/94

Rated voltage

Rated impulse voltage

Overvoltage category

Pollution severity

Clearance and creepage distances

Voltage proof, input/output-TS

Operating temperature without clearances

Storage temperature

Total width

Conductor

Conductor cross-section

300 V

6 kV

IV

2

≥ 5.5 mm

4 kV_{eff}

-25 °C...+40 °C

-25 °C...+50 °C

-40 °C...+85 °C

6 mm

AWG 22...12

0.5...4 mm²

300 V

6 kV

IV

2

≥ 5.5 mm

4 kV_{eff}

-25 °C...+40 °C

-25 °C...+50 °C

-40 °C...+85 °C

6 mm

AWG 22...12

0.5...4 mm²

300 V

6 kV

IV

2

≥ 5.5 mm

4 kV_{eff}

-25 °C...+40 °C

-25 °C...+50 °C

-40 °C...+85 °C

6 mm

AWG 22...12

0.5...4 mm²

Accessories

End plate

Dimensions see

Type Cat. No.

AP DK5 8268870000

Page 305

Type Cat. No.

AP DK5 8268870000

Page 305


Type Cat. No.

AP DK5 8268870000

Page 305

Timers


Signal conditioning DKZA timer modules




- Components for extending short pulses
- Provides PLC versions with switch-on/off delay
- Fixed times

Schematic circuit diagram


DKZA DK5



DKA DK5



DKZA DK5



Ordering data

For TS 32

For TS 35

With combi foot TS 32/TS 35

Technical data

Input:

Supply voltage

Supply current

Control voltage

Control input current

Min. pulse duration of input voltage

Output:

Output voltage

Max. output current

Internal voltage drop

Range of switch-off delay

Type Cat. No.

DKZA DK5 8228690000

Type Cat. No.

DKZA DK5 8243770000

Type Cat. No.

DKZA DK5 8019630000

Isolation coordinates acc. to DIN VDE 0160, Draft11/94

Rated voltage

Rated impulse voltage

Overvoltage category

Pollution severity

Clearance and creepage distances

Voltage proof input/output-TS

Storage temperature

Operating temperature without clearances
with clearances

Total width

Conductor

Conductor cross-section

300 V

6 kV

IV

2

≥ 5.5 mm

4 kV_{eff}

-25 °C...+40 °C

-25 °C...+50 °C

-40 °C...+85 °C

6 mm

AWG 22...12

0.5...4 mm²

300 V

4 kV_{eff}

IV

2

≥ 5.5 mm

6 kV

-40...+85 °C

-25...+40 °C

-25...+50 °C

6 mm

AWG 22...12

0.5...4 mm²

300 V

4 kV_{eff}

IV

2

≥ 5.5 mm

6 kV

-40...+85 °C

-25...+40 °C

-25...+50 °C

6 mm

AWG 22...12

0.5...4 mm²

Accessories

End plate

Dimensions see

Type Cat. No.

AP DK5 8268870000

Type Cat. No.

AP DK5 8268870000

Type Cat. No.

AP DK5 8268870000


Page 305

Page 305

Page 305


Timers

Turn off delay module MCZ TO





The timer module can be used for extending short pulses and fixed times. Provides PLC versions with switch off delay.

MCZ TO 24 Vdc turn-off delay 50 ms



MCZ TO 24 Vdc turn-off delay 150 ms

Schematic circuit diagram



Ordering data

For TS 35

Type

MCZ TO 24 Vdc turn-off delay 50 ms

Cat. No.

8324590000

Type

MCZ TO 24 Vdc turn-off delay 150 ms

Cat. No.

8286410000

Technical data

Input

Input voltage	24 Vdc $\pm 10\%$
Min. pulse duration	2 ms
Power consumption	6.7 mA $\pm 10\%$
Input power	160 mW
Power consumption when pulse applied	200 mA

Output

Output voltage	5...48 Vdc
Max. output current	20 mA
Max. voltage drop at max. load	≤ 1.6 V
Impulse loading/limiting overload current	200 mA
Reverse current at 48 V (static current)	max. 0,16 mA
Switch-off delay	50 ms
Switching frequency dc	20 Hz

24 Vdc $\pm 10\%$
2.5 ms
6.7 mA $\pm 10\%$
160 mW
200 mA

5...48 Vdc
20 mA
≤ 1.6 V
200 mA
max. 0,16 mA
150 ms
5 Hz

Insulation coordination/safe disconnection to EN 50178

Rated voltage	300 V
Rated impulse voltage	6 kV
Overvoltage category	III
Pollution severity	2
Clearance and creepage distances	≥ 5.5 mm
Voltage proof, input/output mounting rail	4 kVeff / 1 min

Opto coupler to VDE 0884

Ambient temperature	-25 °C...+50 °C
Storage temperature	-40 °C...+85 °C
Conductor	AWG 22...12
Conductor cross-section	1.5 mm ²
Approvals	CE, UL, CSA
Total width	6 mm

300 V
6 kV
III
2
≥ 5.5 mm
4 kVeff / 1 min

to VDE 0884

-25 °C...+50 °C
-40 °C...+85 °C
AWG 22...12
1.5 mm ²
CE, UL, CSA
6 mm

