

## 6 PIN DIP PHOTOTRANSISTOR PHOTOCOUPLER

**4N2X Series**  
**4N3X Series**  
**H11AX Series**

### Features:

- 4N2X series: 4N25, 4N26, 4N27, 4N28
- 4N3X series: 4N35, 4N36, 4N37, 4N38
- H11AX series: H11A1, H11A2, H11A3, H11A4, H11A5
- High isolation voltage between input and output  
(Viso=5000 V rms)
- Creepage distance >7.62 mm
- Operating temperature up to +110°C
- Compact dual-in-line package
- Pb free and RoHS compliant.
- UL approved (No. E214129)
- VDE approved (No. 132249)
- SEMKO approved
- NEMKO approval
- DEMKO approval
- FIMKO approval
- CSA approved
- CQC approved


### Description

The 4N2X, 4N3X, H11AX series of devices each consist of an infrared emitting diode optically coupled to a phototransistor.


They are packaged in a 6-pin DIP package and available in wide-lead spacing and SMD option.

### Applications

- Power supply regulators
- Digital logic inputs
- Microprocessor inputs



Schematic



1. Anode
2. Cathode
3. No Connection
4. Emitter
5. Collector
6. Base

# 6 PIN DIP PHOTOTRANSISTOR PHOTOCOUPLER

**4N2X Series**  
**4N3X Series**  
**H11AX Series**

## Absolute Maximum Ratings ( $T_a=25^{\circ}\text{C}$ )

| Parameter                           |                                                  | Symbol    | Rating   | Unit                   |
|-------------------------------------|--------------------------------------------------|-----------|----------|------------------------|
| Input                               | Forward current                                  | $I_F$     | 60       | mA                     |
|                                     | Peak forward current ( $t = 10\mu\text{s}$ )     | $I_{FM}$  | 1        | A                      |
|                                     | Reverse voltage                                  | $V_R$     | 6        | V                      |
|                                     | Power dissipation ( $T_A = 25^{\circ}\text{C}$ ) | $P_D$     | 100      | mW                     |
|                                     | Derating factor (above $100^{\circ}\text{C}$ )   |           | 3.8      | mW/ $^{\circ}\text{C}$ |
| Output                              | Collector-Emitter voltage                        | $V_{CEO}$ | 80       | V                      |
|                                     | Collector-Base voltage                           | $V_{CBO}$ | 80       | V                      |
|                                     | Emitter-Collector voltage                        | $V_{ECO}$ | 7        | V                      |
|                                     | Emitter-Base voltage                             | $V_{EBO}$ | 7        | V                      |
|                                     | Power dissipation ( $T_A = 25^{\circ}\text{C}$ ) | $P_C$     | 150      | mW                     |
|                                     | Derating factor (above $100^{\circ}\text{C}$ )   |           | 9.0      | mW/ $^{\circ}\text{C}$ |
| Total power dissipation             |                                                  | $P_{tot}$ | 200      | mW                     |
| Isolation voltage <sup>*1</sup>     |                                                  | $V_{iso}$ | 5000     | V <sub>rms</sub>       |
| Operating temperature               |                                                  | $T_{opr}$ | -55~+110 | $^{\circ}\text{C}$     |
| Storage temperature                 |                                                  | $T_{stg}$ | -55~+125 | $^{\circ}\text{C}$     |
| Soldering temperature <sup>*2</sup> |                                                  | $T_{sol}$ | 260      | $^{\circ}\text{C}$     |

### Notes

\*1 AC for 1 minute, R.H.= 40 ~ 60% R.H. In this test, pins 1, 2 & 3 are shorted together, and pins 4, 5 & 6 are shorted together.

\*2 For 10 seconds.

# 6 PIN DIP PHOTOTRANSISTOR PHOTOCOUPLER

**4N2X Series**  
**4N3X Series**  
**H11AX Series**

## Electrical Characteristics (T<sub>a</sub>=25°C unless specified otherwise)

### Input

| Parameter         | Symbol          | Min. | Typ.* | Max. | Unit | Condition             |
|-------------------|-----------------|------|-------|------|------|-----------------------|
| Forward voltage   | V <sub>F</sub>  | -    | 1.2   | 1.5  | V    | I <sub>F</sub> = 10mA |
| Reverse current   | I <sub>R</sub>  | -    | -     | 10   | μA   | V <sub>R</sub> = 6V   |
| Input capacitance | C <sub>in</sub> | -    | 30    | -    | pF   | V = 0, f = 1MHz       |

### Output

| Parameter                           |       | Symbol            | Min. | Typ.* | Max. | Unit | Condition                     |
|-------------------------------------|-------|-------------------|------|-------|------|------|-------------------------------|
| Collector-Base dark current         |       | I <sub>CBO</sub>  | -    | -     | 20   | nA   | V <sub>CB</sub> = 10V         |
| Collector-Emitter dark current      | 4N2X  | I <sub>CEO</sub>  | -    | -     | 50   | nA   | V <sub>CE</sub> = 10V, IF=0mA |
|                                     | H11AX |                   | -    | -     | 50   |      | V <sub>CE</sub> = 60V, IF=0mA |
|                                     | 4N3X  |                   | -    | -     | 50   |      |                               |
| Collector-Emitter breakdown voltage |       | BV <sub>CEO</sub> | 80   | -     | -    | V    | I <sub>C</sub> =1mA           |
| Collector-Base breakdown voltage    |       | BV <sub>CBO</sub> | 80   | -     | -    | V    | I <sub>C</sub> =0.1mA         |
| Emitter-Collector breakdown voltage |       | BV <sub>ECO</sub> | 7    | -     | -    | V    | I <sub>E</sub> =0.1mA         |
| Emitter-Base breakdown voltage      |       | BV <sub>EBO</sub> | 7    | -     | -    | V    | I <sub>E</sub> =0.1mA         |
| Collector-Emitter capacitance       |       | C <sub>CE</sub>   | -    | 8     | -    | pF   | VCE=0V, f=1MHz                |

\* Typical values at T<sub>a</sub> = 25°C

# 6 PIN DIP PHOTOTRANSISTOR PHOTOCOUPLER

**4N2X Series**  
**4N3X Series**  
**H11AX Series**

Transfer Characteristics ( $T_a=25^\circ\text{C}$  unless specified otherwise)







| Parameter                            |                                                           | Symbol        | Min.      | Typ.* | Max. | Unit          | Condition                                                                      |
|--------------------------------------|-----------------------------------------------------------|---------------|-----------|-------|------|---------------|--------------------------------------------------------------------------------|
| Current transfer ratio               | 4N35, 4N36, 4N37                                          | CTR           | 100       | -     | -    | %             | $I_F = 10\text{mA}$ , $V_{CE} = 10\text{V}$                                    |
|                                      | H11A1                                                     |               | 50        | -     | -    |               |                                                                                |
|                                      | H11A5                                                     |               | 30        | -     | -    |               |                                                                                |
|                                      | 4N25, 4N26, 4N38, H11A2, H11A3                            |               | 20        | -     | -    |               |                                                                                |
|                                      | 4N27, 4N28, H11A4                                         |               | 10        | -     | -    |               |                                                                                |
| Collector-Emitter saturation voltage | 4N25, 4N26, 4N27, 4N28                                    | $V_{CE(sat)}$ | -         | -     | 0.5  | V             | $I_F = 50\text{mA}$ , $I_C = 2\text{mA}$                                       |
|                                      | 4N35, 4N36, 4N37                                          |               | -         | -     | 0.3  |               | $I_F = 10\text{mA}$ , $I_C = 0.5\text{mA}$                                     |
|                                      | H11A1, H11A2, H11A3, H11A4, H11A5                         |               | -         | -     | 0.4  |               |                                                                                |
|                                      | 4N38                                                      |               | -         | -     | 1.0  |               | $I_F = 20\text{mA}$ , $I_C = 4\text{mA}$                                       |
| Isolation resistance                 |                                                           | $R_{IO}$      | $10^{11}$ | -     | -    | $\Omega$      | $V_{IO} = 500\text{Vdc}$                                                       |
| Input-output capacitance             |                                                           | $C_{IO}$      | -         | 0.2   | -    | pF            | $V_{IO} = 0$ , $f = 1\text{MHz}$                                               |
| Turn-on time                         | 4N25, 4N26, 4N27, 4N28, H11A1, H11A2, H11A3, H11A4, H11A5 | $T_{on}$      | -         | 3     | 10   | $\mu\text{s}$ | $V_{CC} = 10\text{V}$ , $I_F = 10\text{mA}$ , $R_L = 100\Omega$<br>See Fig. 11 |
|                                      | 4N35, 4N36, 4N37, 4N38                                    |               | -         | 10    | 12   |               | $V_{CC} = 10\text{V}$ , $I_C = 2\text{mA}$ , $R_L = 100\Omega$ , See Fig. 11   |
| Turn-off time                        | 4N25, 4N26, 4N27, 4N28, H11A1, H11A2, H11A3, H11A4        | $T_{off}$     | -         | 3     | 10   | $\mu\text{s}$ | $V_{CC} = 10\text{V}$ , $I_F = 10\text{mA}$ , $R_L = 100\Omega$<br>See Fig. 11 |
|                                      | 4N35, 4N36, 4N37, 4N38                                    |               | -         | 9     | 12   |               | $V_{CC} = 10\text{V}$ , $I_C = 2\text{mA}$ , $R_L = 100\Omega$ , See Fig. 11   |

\* Typical values at  $T_a = 25^\circ\text{C}$

# 6 PIN DIP PHOTOTRANSISTOR PHOTOCOUPLER

**4N2X Series  
4N3X Series  
H11AX Series**

## Typical Performance Curves



# 6 PIN DIP PHOTOTRANSISTOR PHOTOCOUPLER

**4N2X Series  
4N3X Series  
H11AX Series**

**Figure 7. Collector-Emitter Saturation Voltage vs Collector Current**




**Figure 8. Switching Time vs Load Resistance**




**Figure 9. Turn-on Time vs Base-Emitter Resistance**




**Figure 10. Turn-off Time vs Base-Emitter Resistance**





**Figure 11. Switching Time Test Circuit & Waveforms**



LIGHTING FOREVER

## 6 PIN DIP PHOTOTRANSISTOR PHOTOCOUPLER

**4N2X Series**  
**4N3X Series**  
**H11AX Series**

### Order Information

#### Part Number

**4NXXY(Z)-V**

or

**H11AXY(Z)-V**

#### Note

XX = Part no. for 4NXX series (25, 26, 27, 28, 35, 36, 37 or 38)

X = Part no. for H11AX series (1, 2, 3, 4, or 5)

Y = Lead form option (S, S1, M or none)

Z = Tape and reel option (TA, TB or none).

V = VDE safety (optional)


| Option  | Description                                                   | Packing quantity    |
|---------|---------------------------------------------------------------|---------------------|
| None    | Standard DIP-6                                                | 65 units per tube   |
| M       | Wide lead bend (0.4 inch spacing)                             | 65 units per tube   |
| S (TA)  | Surface mount lead form + TA tape & reel option               | 1000 units per reel |
| S (TB)  | Surface mount lead form + TB tape & reel option               | 1000 units per reel |
| S1 (TA) | Surface mount lead form (low profile) + TA tape & reel option | 1000 units per reel |
| S1 (TB) | Surface mount lead form (low profile) + TB tape & reel option | 1000 units per reel |

# 6 PIN DIP PHOTOTRANSISTOR PHOTOCOUPLER


**4N2X Series**  
**4N3X Series**  
**H11AX Series**

## Package Drawings (Dimensions in mm)

### Standard DIP Type




### Option M Type




# 6 PIN DIP PHOTOTRANSISTOR PHOTOCOUPLER

**4N2X Series**  
**4N3X Series**  
**H11AX Series**

## Option S Type



## Option S1 Type






LIGHTING FOREVER


## 6 PIN DIP PHOTOTRANSISTOR PHOTOCOUPLER

4N2X Series  
4N3X Series  
H11AX Series

Recommended pad layout for surface mount leadform



### Device Marking



### Notes


|      |                           |
|------|---------------------------|
| EL   | denotes Everlight         |
| 4N35 | denotes Device Number     |
| Y    | denotes 1 digit Year code |
| WW   | denotes 2 digit Week code |
| V    | denotes VDE (optional)    |

# 6 PIN DIP PHOTOTRANSISTOR PHOTOCOUPLER

**4N2X Series**  
**4N3X Series**  
**H11AX Series**


## Tape & Reel Packing Specifications

**Option TA**




Direction of feed from reel

**Option TB**



Direction of feed from reel

## Tape dimensions



| Dimension No.  | A        | B        | D0      | D1         | E        | F       |
|----------------|----------|----------|---------|------------|----------|---------|
| Dimension (mm) | 10.4±0.1 | 7.52±0.1 | 1.5±0.1 | 1.5+0.1/-0 | 1.75±0.1 | 7.5±0.1 |

| Dimension No.  | P0       | P1       | P2      | t         | W        | K       |
|----------------|----------|----------|---------|-----------|----------|---------|
| Dimension (mm) | 4.0±0.15 | 16.0±0.1 | 2.0±0.1 | 0.35±0.03 | 16.0±0.2 | 4.5±0.1 |




LIGHTING FOREVER

## 6 PIN DIP PHOTOTRANSISTOR PHOTOCOUPLER

4N2X Series  
4N3X Series  
H11AX Series

### Solder Reflow Temperature Profile



## **6 PIN DIP PHOTOTRANSISTOR PHOTOCOUPLER**

**4N2X Series  
4N3X Series  
H11AX Series**

---

### **DISCLAIMER**

1. Above specification may be changed without notice. EVERLIGHT will reserve authority on material change for above specification.
2. When using this product, please observe the absolute maximum ratings and the instructions for use as outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
3. These specification sheets include materials protected under copyright of EVERLIGHT Corporation. Reproduction in any form is prohibited without the specific consent of EVERLIGHT.