

**FEATURES**

- \* 0.4-INCH (10.0-mm) DIGIT HEIGHT.
- \* CONTINUOUS UNIFORM SEGMENTS.
- \* LOW POWER REQUIREMENT.
- \* EXCELLENT CHARACTERS APPEARANCE.
- \* HIGH BRIGHTNESS & HIGH CONTRAST.
- \* WIDE VIEWING ANGLE.
- \* SOLID STATE RELIABILITY.
- \* CATEGORIZED FOR LUMINOUS INTENSITY.


**DESCRIPTION**

The LTD-4608E is a 0.4-inch (10.0-mm) digit height dual digit seven-segment display. This device utilizes red orange LED chips, which are made from GaAsP on a transparent GaP substrate, and has a gray face and white segments.

**DEVICE**


| <b>PART NO.</b> | <b>DESCRIPTION</b>  |
|-----------------|---------------------|
| RED ORANGE      | Duplex Common Anode |
| LTD-4608E       | Rt. Hand Decimal    |

## PACKAGE DIMENSIONS



NOTES: All dimensions are in millimeters. Tolerance is  $\pm 0.25$ -mm (0.01") unless otherwise noted.

## INTERNAL CIRCUIT DIAGRAM



**PIN CONNECTION**

| No. | CONNECTION             |
|-----|------------------------|
| 1   | CATHODE C              |
| 2   | CATHODE D.P.           |
| 3   | CATHODE E              |
| 4   | COMMON ANODE (DIGIT 2) |
| 5   | CATHODE D              |
| 6   | CATHODE F              |
| 7   | CATHODE G              |
| 8   | CATHODE B              |
| 9   | COMMON ANODE (DIGIT 1) |
| 10  | CATHODE A              |

ABSOLUTE MAXIMUM RATING AT  $T_A=25^\circ\text{C}$ 

| PARAMETER  | MAXIMUM RATING                             | UNIT                 |
|--|--|----------------------|
| Power Dissipation Per Segment  | 75   | mW                   |
| Peak Forward Current Per Segment<br>( 1/10 Duty Cycle, 0.1ms Pulse Width ) | 100  | mA                   |
| Continuous Forward Current Per Segment                                     | 25   | mA                   |
| Derating Linear From $25^\circ\text{C}$ Per Segment                        | 0.33                                       | mA/ $^\circ\text{C}$ |
| Reverse Voltage Per Segment  | 5  | V                    |
| Operating Temperature Range  | $-35^\circ\text{C}$ to $+85^\circ\text{C}$ |                      |
| Storage Temperature Range  | $-35^\circ\text{C}$ to $+85^\circ\text{C}$ |                      |
| Solder Temperature 1/16 inch Below Seating Plane for 3 Seconds             | $260^\circ\text{C}$                        |                      |

ELECTRICAL / OPTICAL CHARACTERISTICS AT  $T_A=25^\circ\text{C}$ 

| PARAMETER                         | SYMBOL          | MIN. | TYP. | MAX. | UNIT           | TEST CONDITION    |
|-----------------------------------|-----------------|------|------|------|----------------|-------------------|
| Average Luminous Intensity        | $I_v$           | 800  | 2200 |      | $\mu\text{cd}$ | $I_F=10\text{mA}$ |
| Peak Emission Wavelength          | $\lambda_p$     |      | 630  |      | nm             | $I_F=20\text{mA}$ |
| Spectral Line Half-Width          | $\Delta\lambda$ |      | 40   |      | nm             | $I_F=20\text{mA}$ |
| Dominant Wavelength               | $\lambda_d$     |      | 621  |      | nm             | $I_F=20\text{mA}$ |
| Forward Voltage Per Segment       | $V_F$           |      | 2.0  | 2.6  | V              | $I_F=20\text{mA}$ |
| Reverse Current Per Segment       | $I_R$           |      |      | 100  | $\mu\text{A}$  | $V_R=5\text{V}$   |
| Luminous Intensity Matching Ratio | $I_v\text{-m}$  |      |      | 2:1  |                | $I_F=10\text{mA}$ |

Note: Luminous intensity is measured with a light sensor and filter combination that approximates the CIE (commision Internationale DE L'clairage) eye-response curve.

## TYPICAL ELECTRICAL / OPTICAL CHARACTERISTIC CURVES

(25°C Ambient Temperature Unless Otherwise Noted)




Fig1. RELATIVE INTENSITY VS. WAVELENGTH




Fig2. RELATIVE LUMINOUS EFFICIENCY (LUMINOUS INTENSITY PER UNIT CURRENT) VS. PEAK CURRENT (REFRESH RATE 1KHz)




Fig3. FORWARD CURRENT VS. FORWARD VOLTAGE




Fig4. RELATIVE LUMINOUS INTENSITY VS. FORWARD CURRENT




Fig5. MAX. ALLOWABLE DC CURRENT VS. AMBIENT TEMPERATURE.




Fig6. MAX. PEAK CURRENT VS. DUTY CYCLE % (REFRESH RATE 1KHz)

NOTE: E=RED ORANGE