




GUARDIAN
Electric Manufacturing

ISO 9001 / AS9100 Certified Company

Woodstock, IL 60098 Ph. (815)334-3600 Fax (815)337-0377

Or visit us at our website www.guardian-electric.com

Model 4 DC Frame Solenoid



Solenoid shown energized and fully seated.

Spring kits are available (consult factory).

Total Weight: 12.6 oz.

Plunger Weight: 1.6 oz.

Model No.	Part No.	Duty Cycle	Voltage	Resistance (Ω)	Power (W)	Current
4-I-12D	A420-065943-00	Intermittent	12VDC	3.96	38.2	3.03 A
4-C-12D	A420-065942-00	Continuous	12VDC	15.8	9.6	759 mA
4-I-24D	A420-065945-00	Intermittent	24VDC	15.8	38.3	1.52 A
4-C-24D	A420-065944-00	Continuous	24VDC	61.3	9.9	392 mA

When ordering, please refer to Part No., as listed above.

Consult factory for custom configurations.

Pull Force (oz.)									Holding Force (oz.)
Stroke (in.)	0.050	0.125	0.250	0.375	0.500	0.625	0.750	1.000	-
Continuous Duty	100	60	20	14	9	5	3	1	155
Intermittent Duty	140	112	97	60	40	27	22	20	181

UL Recognition

Recognized under the 
Component Recognition Program of
Underwriters Laboratories, Inc.

Continuous Duty

100% 'On' Time

Intermittent Duty

25% 'On' Time, (100 Seconds 'On' Max.
Followed By 300 Seconds 'Off' Min.)

RoHS

These parts comply with **RoHS** Directive 2002/95/EC