

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED

© COPYRIGHT

 $\Theta_1 =$

LOC	
-----	--

DIST

REVISIONS

DESCRIPTION

DATE _____

4	APV
---	-----

4	APV
---	-----

[illegible]

REVIS

PER FO

14-000255

5JUL20

K	MN
---	----

K	MN
---	----

1. ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
2. TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD




3 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING

4 PLATING: 0.000381 [.000015] GOLD ON CONTACT AREA,
.00254-.00508 [.0000100-.0000200] MATTE TIN-LEAD
ON SOLDER TAIL, ALL OVER 0.00127 [.000050] NICKEL.

5 HOUSING: LCP, COLOR-BLACK.
POST: COPPER ALLOY.

6 PLATING: 0.000381 [.000015] GOLD ON CONTACT AREA,
.00254-.00508 [.0000100-.0000200] MATTE TIN
ON SOLDER TAIL, ALL OVER 0.00127 [.000050] NICKEL.

7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED PC BOARD MOUNTING DIMENSIONS
FOR .063 [1.60] THICK PC BOARD AND
.012 [.305] STENCIL THICK

		101.19 [3.984]	99.06 [3.900]	39	80	9-146260-0
OBSOLETE		98.65 [3.884]	96.52 [3.800]	38	78	8-146260-9
		96.11 [3.784]	93.98 [3.700]	37	76	8-146260-8
		93.57 [3.684]	91.44 [3.600]	36	74	8-146260-7
		91.03 [3.584]	88.90 [3.500]	35	72	8-146260-6
		88.49 [3.484]	86.36 [3.400]	34	70	8-146260-5
		85.95 [3.384]	83.82 [3.300]	33	68	8-146260-4
		83.41 [3.284]	81.28 [3.200]	32	66	8-146260-3
		80.87 [3.184]	78.74 [3.100]	31	64	8-146260-2
		78.33 [3.084]	76.20 [3.000]	30	62	8-146260-1
		75.79 [2.984]	73.66 [2.900]	29	60	8-146260-0
		73.25 [2.884]	71.12 [2.800]	28	58	7-146260-9
		70.71 [2.784]	68.58 [2.700]	27	56	7-146260-8
		68.17 [2.684]	66.04 [2.600]	26	54	7-146260-7
		65.63 [2.584]	63.5 [2.500]	25	52	7-146260-6
		63.09 [2.484]	60.96 [2.400]	24	50	7-146260-5
		60.55 [2.384]	58.42 [2.300]	23	48	7-146260-4
		58.01 [2.284]	55.88 [2.200]	22	46	7-146260-3
		55.47 [2.184]	53.34 [2.100]	21	44	7-146260-2
		52.93 [2.084]	50.80 [2.000]	20	42	7-146260-1
		50.39 [1.984]	48.26 [1.900]	19	40	7-146260-0
		47.85 [1.884]	45.72 [1.800]	18	38	6-146260-9
		45.31 [1.784]	43.18 [1.700]	17	36	6-146260-8
		42.77 [1.684]	40.64 [1.600]	16	34	6-146260-7
		40.23 [1.584]	38.10 [1.500]	15	32	6-146260-6
		37.69 [1.484]	35.56 [1.400]	14	30	6-146260-5
		35.15 [1.384]	33.02 [1.300]	13	28	6-146260-4
		32.61 [1.284]	30.48 [1.200]	12	26	6-146260-3
		30.07 [1.184]	27.94 [1.100]	11	24	6-146260-2
		27.53 [1.084]	25.40 [1.000]	10	22	6-146260-1
			24.99 [.984]	22.86 [.900]	9	20
OBSOLETE		22.45 [.884]	20.32 [.800]	8	18	5-146260-9
		19.91 [.784]	17.78 [.700]	7	16	5-146260-8
		17.37 [.684]	15.24 [.600]	6	14	5-146260-7
		14.83 [.584]	12.70 [.500]	5	12	5-146260-6
		12.29 [.484]	10.16 [.400]	4	10	5-146260-5
		9.75 [.384]	7.62 [.300]	3	8	5-146260-4
OBSOLETE		7.21 [.284]	5.08 [.200]	2	6	5-146260-3
		4.67 [.184]	2.54 [.100]	1	4	5-146260-2
OBSOLETE		2.13 [.084]	- [-]	0	2	5-146260-1
	PLATING	C	B	A	NO. OF POSITIONS	PART NUMBER

7 OBSOLETE	4	101.19 [3.984]	99.06 [3.900]	39	80	4-146260-0	
	4	98.65 [3.884]	96.52 [3.800]	38	78	3-146260-9	
	4	96.11 [3.784]	93.98 [3.700]	37	76	3-146260-8	
	4	93.57 [3.684]	91.44 [3.600]	36	74	3-146260-7	
	4	91.03 [3.584]	88.90 [3.500]	35	72	3-146260-6	
	4	88.49 [3.484]	86.36 [3.400]	34	70	3-146260-5	
	4	85.95 [3.384]	83.82 [3.300]	33	68	3-146260-4	
	4	83.41 [3.284]	81.28 [3.200]	32	66	3-146260-3	
	4	80.87 [3.184]	78.74 [3.100]	31	64	3-146260-2	
	4	78.33 [3.084]	76.20 [3.000]	30	62	3-146260-1	
	4	75.79 [2.984]	73.66 [2.900]	29	60	3-146260-0	
	4	73.25 [2.884]	71.12 [2.800]	28	58	2-146260-9	
	4	70.71 [2.784]	68.58 [2.700]	27	56	2-146260-8	
	4	68.17 [2.684]	66.04 [2.600]	26	54	2-146260-7	
	4	65.63 [2.584]	63.5 [2.500]	25	52	2-146260-6	
	4	63.09 [2.484]	60.96 [2.400]	24	50	2-146260-5	
	4	60.55 [2.384]	58.42 [2.300]	23	48	2-146260-4	
	4	58.01 [2.284]	55.88 [2.200]	22	46	2-146260-3	
	4	55.47 [2.184]	53.34 [2.100]	21	44	2-146260-2	
	4	52.93 [2.084]	50.80 [2.000]	20	42	2-146260-1	
	4	50.39 [1.984]	48.26 [1.900]	19	40	2-146260-0	
	4	47.85 [1.884]	45.72 [1.800]	18	38	1-146260-9	
	4	45.31 [1.784]	43.18 [1.700]	17	36	1-146260-8	
	4	42.77 [1.684]	40.64 [1.600]	16	34	1-146260-7	
	4	40.23 [1.584]	38.10 [1.500]	15	32	1-146260-6	
	4	37.69 [1.484]	35.56 [1.400]	14	30	1-146260-5	
	4	35.15 [1.384]	33.02 [1.300]	13	28	1-146260-4	
	4	32.61 [1.284]	30.48 [1.200]	12	26	1-146260-3	
	4	30.07 [1.184]	27.94 [1.100]	11	24	1-146260-2	
	4	27.53 [1.084]	25.40 [1.000]	10	22	1-146260-1	
	4	24.99 [.984]	22.86 [.900]	9	20	1-146260-0	
	4	22.45 [.884]	20.32 [.800]	8	18	146260-9	
	4	19.91 [.784]	17.78 [.700]	7	16	146260-8	
4	17.37 [.684]	15.24 [.600]	6	14	146260-7		
4	14.83 [.584]	12.70 [.500]	5	12	146260-6		
7 SUPERCEDED	4	12.29 [.484]	10.16 [.400]	4	10	146260-5	
	7 OBSOLETE	4	9.75 [.384]	7.62 [.300]	3	8	146260-4
		4	7.21 [.284]	5.08 [.200]	2	6	146260-3
		4	4.67 [.184]	2.54 [.100]	1	4	146260-2
4		2.13 [.084]	- [-]	0	2	146260-1	
	PLATING	C	B	A	NO. OF POSITIONS	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 08-05-95 T. HOFFMAN ORC 02-01-96 G. DUBINCZKI APV 02-01-96 G. DUBINCZKI		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0. PLC ± — 1. PLC ± — 2. PLC ± 0.51[.02] 3. PLC ± 0.127[.005] 4. PLC ± 0.012[.0005] ANGLES FINISH ±		PRODUCT SPEC — APPLICATION SPEC	
MATERIAL 		SEE TABLE		WEIGHT —	
				SIZE A1 CASE CODE 00779 DRAWING NO. C=146260	
				RESTRICTED —	
				CUSTOMER DRAWING	
				SCALE 4:1 SHEET 1 of 1 REV G	