

## Duplex Multimode 62.5/125 Fiber Patch Cable (SC/ST), 1M (3-ft.)

MODEL NUMBER: **N304-003**



### Description

Tripp Lite's 3-ft. multimode duplex fiber optic SC/ST patch cable is manufactured from 62.5/125 zipcord fiber. The cable has ST to SC connectors, a PVC jacket and is FDDI and OFNR rated. Duplex multimode fiber is most commonly used in LAN applications.

### Features

- Manufactured from 62.5/125 duplex (zipcord) fiber
- PVC jacket
- Length: 3-ft. Connectors: 2 ST to 2 SC connectors
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze
- Fiber made from glass (not a polymer)
- Color coded shrouds identify transmit and receive
- Duplex multimode fiber is most commonly used in LAN applications where links are typically 10 feet or less
- Fiber optic distributed data interface (FDDI) rated
- OFNR (riser rated)

### Specifications

General Info	
Product Group	NETWORK CABLES
OVERVIEW	
Fiber Type	62.5/125 - OM1
Intended Application	Computer Networking (Fiber)

### Highlights

- Premium PVC 62.5/125 $\mu$ m multimode patch cables
- Attenuation loss meets or exceeds the latest industry standards

### System Requirements

- Any fiber optic hardware or NIC card requiring multimode duplex cable with SC/ST connectors

### Package Includes

- 3-ft. duplex MMF cable ST/SC 62.5/125 fiber

Cable Type	MULTIMODE 62.5/125 FIBER OPTIC
Model Type	SC/ST
Network Speed	1Gbps
<b>INPUT</b>	
Cable Length (ft.)	3
Cable Length (m)	0.91
<b>UPC ASSIGNMENT</b>	
Unit Carton UPC#	037332013248
<b>PHYSICAL</b>	
Color	Orange
Style	Fiber Optic
<b>CONNECTIONS</b>	
Connector A	SC
Connector B	ST
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.