




Shielded Power Inductors-LPS5030



- Very low DCR; excellent current handling
- 4.9 × 4.9 mm footprint; less than 3 mm tall

Designer's Kit C420 contains 3 each of all values

Core material Ferrite

Terminations RoHS compliant silver-palladium-platinum-glass frit. Other terminations available at additional cost.

Weight 226 – 244 mg

Ambient temperature –40°C to +85°C with 1rms current, +85°C to +125°C with derated current

Storage temperature Component: –40°C to +125°C.

Packaging: –40°C to +80°C

Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

Failures in Time (FIT) / Mean Time Between Failures (MTBF) 38 per billion hours / 26,315,789 hours, calculated per Telcordia SR-332

Packaging 750/7" reel; 2500/13" reel Plastic tape: 12 mm wide, 0.32 mm thick, 8 mm pocket spacing, 3.1 mm pocket depth

Recommended pick and place nozzle OD: 5 mm; ID: ≤ 2.5 mm

PCB washing Only pure water or alcohol recommended

Part number ¹	Inductance ² ±20% (μH)	DCR max ³ (Ohms)	SRF typ ⁴ (MHz)	Isat (A) ⁵			Irms (A) ⁶	
				10% drop	20% drop	30% drop	20°C rise	40°C rise
LPS5030-901ML	0.90	0.040	250	3.8	4.0	4.1	2.10	2.80
LPS5030-122ML	1.2	0.043	210	3.5	3.6	3.7	2.00	2.65
LPS5030-172ML	1.7	0.051	190	3.0	3.2	3.3	1.90	2.50
LPS5030-222ML	2.2	0.057	168	2.9	3.1	3.2	1.60	2.15
LPS5030-332ML	3.3	0.066	125	2.3	2.5	2.6	1.40	1.80
LPS5030-472ML	4.7	0.083	84	1.9	2.0	2.0	1.30	1.75
LPS5030-562ML	5.6	0.089	70	1.8	1.8	1.9	1.25	1.65
LPS5030-682ML	6.8	0.099	56	1.6	1.7	1.7	1.20	1.60
LPS5030-822ML	8.2	0.125	45	1.6	1.7	1.7	1.10	1.55
LPS5030-103ML	10.0	0.127	30	1.4	1.4	1.4	1.00	1.50
LPS5030-123ML	12.0	0.155	24	1.3	1.4	1.4	0.95	1.40
LPS5030-153ML	15.0	0.160	32	0.80	0.90	0.90	0.92	1.40
LPS5030-183ML	18.0	0.170	27	0.80	0.82	0.87	0.90	1.30
LPS5030-223ML	22.0	0.190	24	0.70	0.75	0.78	0.88	1.25
LPS5030-333ML	33.0	0.260	19	0.60	0.63	0.64	0.85	1.20
LPS5030-473ML	47.0	0.330	16	0.50	0.53	0.55	0.75	1.00
LPS5030-683ML	68.0	0.440	12	0.40	0.43	0.44	0.65	0.900
LPS5030-823ML	82.0	0.470	11	0.38	0.40	0.40	0.60	0.830
LPS5030-104ML	100	0.600	10	0.27	0.31	0.32	0.55	0.750
LPS5030-124ML	120	0.800	9	0.26	0.29	0.30	0.45	0.660
LPS5030-154ML	150	0.860	7.5	0.22	0.25	0.263	0.42	0.570
LPS5030-224ML	220	1.35	6.0	0.21	0.235	0.245	0.36	0.500
LPS5030-334ML	330	1.80	5.0	0.155	0.155	0.200	0.32	0.420
LPS5030-474ML	470	2.80	4.0	0.117	0.134	0.146	0.28	0.370
LPS5030-564ML	560	3.20	3.6	0.110	0.130	0.140	0.23	0.320
LPS5030-684ML	680	3.80	3.0	0.100	0.120	0.126	0.20	0.290
LPS5030-105ML	1000	5.10	2.5	0.100	0.110	0.110	0.18	0.250
LPS5030-155ML	1500	7.60	2.0	0.068	0.080	0.089	0.15	0.210
LPS5030-185ML	1800	10.0	1.8	0.069	0.081	0.086	0.13	0.170
LPS5030-225ML	2200	11.0	1.6	0.063	0.074	0.080	0.10	0.150
LPS5030-335ML	3300	19.5	1.3	0.056	0.063	0.067	0.090	0.125
LPS5030-475ML	4700	26.0	1.1	0.049	0.056	0.059	0.080	0.110

1. Please specify **termination** and **packaging** codes:

LPS5030-105ML C

Termination: L = RoHS compliant silver-palladium-platinum-glass frit.

Special order:

T = RoHS tin-silver-copper (95.5/4/0.5)
or S = non-RoHS tin-lead (63/37).

Packaging: C = 7" machine-ready reel. EIA-481 embossed plastic tape (750 parts per full reel).

B = Less than full reel. In tape, but not machine ready.

To have a leader and trailer added (\$25 charge), use code letter C instead.

D = 13" machine-ready reel. EIA-481 embossed plastic tape. Factory order only, not stocked (2500 parts per full reel).

- Inductance tested at 100 kHz, 0.1 Vrms, 0 Adc using an Agilent/HP 4263B LCR meter or equivalent.
 - DCR measured on a micro-ohmmeter.
 - SRF measured using Agilent/HP 8753ES or equivalent.
 - DC current at which the inductance drops the specified amount from its value without current.
 - Current that causes the specified temperature rise from 25°C ambient.
 - Electrical specifications at 25°C.
- Refer to Doc 362 "Soldering Surface Mount Components" before soldering.

Coilcraft®

Specifications subject to change without notice.
Please check our website for latest information.

Document 581-1 Revised 10/06/08


1102 Silver Lake Road Cary, Illinois 60013 Phone 847/639-6400 Fax 847/639-1469

E-mail info@coilcraft.com Web <http://www.coilcraft.com>




Shielded SMT Power Inductors – LPS5030 Series



Typical L vs Frequency



Typical L vs Current



Typical Current Derating



Dimensions are in $\frac{\text{inches}}{\text{mm}}$

Coilcraft®

Specifications subject to change without notice.
Please check our website for latest information.

Document 581-2 Revised 10/06/08

1102 Silver Lake Road Cary, Illinois 60013 Phone 847/639-6400 Fax 847/639-1469

E-mail info@coilcraft.com Web <http://www.coilcraft.com>