



S



1. PARTS COMPLY WITH AMP SOLDERABILITY SPEC. NO. 109-11-3

2. CONTACT IS PLATED OVERALL WITH .000050 NICKEL, THEN .000030 GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN ON SOLDER TAIL END.

3. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING-PER D.RENAUD/D.SINISI

350425-2	NYLON	NATURAL	COPPER ALLOY - GOLD	2
350425-1	NYLON -	NATURAL	COPPER ALLOY - PRE-TIN	
ASSEMBLY NO.	HSG.MATL. -	COLOR	PIN MATL. FINISH	

K1		REV PER ECO-10-000445		KK	AEG	09JAN	REQUIRED PER ASSEMBLY		QWS	NUMBER	NAME	REMARKS	ITEM
RESTORED		REV. PER M-7375		SS	QW	8/1/85	6-27-73		9. Schman	MATERIAL AND FINISH		CUSTOMER COPY REFERENCE ONLY	
ECN M-3871		ECN M-3871		SS	QW	8/1/85	6-28-73		9. Schman	SEE TABLE		AMP INCORPORATED	
ECN M-3156		ECN M-3156		SS	QW	8/1/85	6-28-73		9. Schman	WIRE - GAGE - INSULATION		TYPE	
ECN M-3156		ECN M-3156		SS	QW	8/1/85	6-28-73		9. Schman	TOLERANCE DEC. PT		LOC	
ECN M-3156		ECN M-3156		SS	QW	8/1/85	6-28-73		9. Schman	SCALE		REV	
ECN M-3156		ECN M-3156		SS	QW	8/1/85	6-28-73		9. Schman	CIRCUIT MATE-N-LOK		K1	
ECN M-3156		ECN M-3156		SS	QW	8/1/85	6-28-73		9. Schman	P.C. BOARD PIN HEADER			