



**HOW TO ORDER:**

**TABLE I: CONNECTOR DIMENSIONS**

| SHELL SIZE | A THREAD CLASS 2B  | V THREAD CLASS 2A | ØQ MAX.      |
|------------|--------------------|-------------------|--------------|
| 11         | .750-.1P-.2L-D.S.  | 3/4-20 UNEF       | 1.028 (26.1) |
| 13         | .875-.1P-.2L-D.S.  | 7/8-20 UNEF       | 1.141 (29.0) |
| 15         | 1.062-.1P-.2L-D.S. | 1-20 UNEF         | 1.263 (32.1) |
| 17         | 1.125-.1P-.2L-D.S. | 1 1/8-18 UNEF     | 1.387 (35.2) |
| 19         | 1.312-.1P-.2L-D.S. | 1 1/4-18 UNEF     | 1.513 (38.4) |
| 23         | 1.500-.1P-.2L-D.S. | 1 7/16-18 UNEF    | 1.703 (43.3) |
| 25         | 1.625-.1P-.2L-D.S. | 1 9/16-18 UNEF    | 1.825 (46.4) |
| 29         | 1.812-.1P-.2L-D.S. | 1 7/8-16 UN       | 2.143 (54.4) |
| 33         | 2.000-.1P-.2L-D.S. | 2 1/16-16 UNS     | 2.329 (59.2) |

**NOTES:**

1. INTERPRET PER MIL-STD-100.
2. SEE MIL-C-28840 FOR ADDITIONAL DESIGN DETAILS.

 GLENAIR NF = CLASS A  
 GLENAIR ZU = CLASS B