


THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC. U.S.A. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.

DWG. NO.	ZONE	REV.	DESCRIPTION	DATE	APPROV.
X10-0X3		F	ECN 387	06/09/95	C



BUNDLE SPECIFICATION


- NOTES: UNLESS OTHERWISE SPECIFIED.
- 1.0 PACKAGING SPECIFICATION
 - 1.01 USE CLEAR TAPE TO BUNDLE 25 CABLES TOGETHER AT THE MID SECTION.
 - 1.02 PLACE PLASTIC BAG IN SHIPPING BOX AND LAY 10 BUNDLE OR 250 PIECES MAX. PER SHIPPING BOX. CLOSE PLASTIC BAG AND SEAL BOX ALONG 3 SURFACES WITH TAPE.

4	431.80	(17.000)	L=13.00" X W=20.00" X H=9.0
5	457.20	(18.000)	L=13.00" X W=20.00" X H=9.0
6	558.80	(22.000)	L=13.00" X W=25.00" X H=9.0
CONDUCTORS NUMBER OF	MILLIMETERS	INCHES	DIMENSION MAX. OUTSIDE SHIPPING BOX
RETRACTED LENGTH 'R'			
TABULATION BLOCK			
THIRD ANGLE PROJECTION		I/O INTERCONNECT	
		SANTA ANA, CALIFORNIA	
UNLESS OTHERWISE NOTED: 1) DIMENSIONS ARE IN MILLIMETER (INCHES) 2) TOLERANCES: XX ± 0.20 (0.008) XXX ± 0.35 (0.250)		DR: GETH WYNN E: 06/09/95 TITLE: 26 AWG (12/0.12 mm) BARE COPP 500 FT EXTENDED, NON-UL, UNSHIELDED, MODULAR CABLE	
CHKD: 		PART NO: 121-X10-0X3	
CHKD: 		CUSTOMER: I/O INTERCONNECT	
CHKD: 		SCALE: NONE	
CHKD:		SHEET 2 OF 2	

A B C D E F G H

THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT, INC. U.S.A. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF I/O INTERCONNECT, INC. OR ITS AFFILIATED SUBSIDIARIES.

DWG. NO.	ZONE	REV.	DESCRIPTION	DATE	APPROV.
X10-0X2		I	ECN 387	06/09/95	CT



BUNDLE SPECIFICATION

NOTES: UNLESS OTHERWISE SPECIFIED.

1.0 PACKAGING SPECIFICATION

- 1.01 USE CLEAR TAPE TO BUNDLE 25 CABLES TOGETHER AT THE MID SECTION.
- 1.02 PLACE PLASTIC BAG IN SHIPPING BOX AND LAY 10 BUNDLE OR 250 PIECES MAX. PER SHIPPING BOX. CLOSE PLASTIC BAG AND SEAL BOX ALONG 3 SURFACES WITH TAPE.

4	863.60	[34.000]	L=13.00' X W=40.00' X H=9.00
6	1117.60	[44.000]	L=13.00' X W=50.00' X H=9.00
8	1270.00	[50.000]	L=13.00' X W=55.00' X H=9.00
CONDUCTORS	MILLIMETERS	INCHES	DIMENSION MAX
NUMBER OF	RETRACTED LENGTH "R"		OUTSIDE SHIPPING BOX

TABULATION BLOCK

THIRD ANGLE PROJECTION		
UNLESS OTHERWISE NOTED: 1) DIMENSIONS ARE IN MILLIMETER (INCHES) 2) TOLERANCES: XX ± 0.20 (0.008) XXX ± 0.35 (0.250)		
I/O INTERCONNECT SANTA ANA, CALIFORNIA		
DR: C. WANG	TITLE: 06/09/95	36 AWG (12/012 MM) BARE COPPER, 14.00 FT EXTENDED, NON-UL, UNSHIELDED, MODULAR CABLE
CHKD: [Signature]	PART NO: 121-X10-0X2	CUSTOMER: I/O INTERCONNECT
SCALE: NONE	SHEET: 2 OF 2	

Open 6/10/95



NOTES: UNLESS OTHERWISE SPECIFIED.

1.1.01 USE CLEAR TAPE TO BUNDLE 25 CABLES TOGETHER AT THE MID SECTION.


- 1.02 PLACE PLASTIC BAG IN SHIPPING BOX AND LAY
10 BUNDLE OR 250 PIECES MAX. PER SHIPPING BOX.
CLOSE PLASTIC BAG AND SEAL BOX ALONG 3 SURFACES
WITH TAPE.

THIRD ANGLE PROJECTION		I/O INTERCONNECT SANTA ANA, CALIFORNIA		121-X10-0X1	
		DR. Cathy Wang C. Wang 06/29/93		TITLE 25 AWG (12/0/12 mm) BARE COPPER 1000 FT EXTENDED, NON-UL, UNSHIELDED, MODULAR CABLE	
UNLESS OTHERWISE NOTED: 1) DIMENSIONS ARE IN MILLIMETER (INCHES) 2) TOLERANCES: XX ± 0.20 (0.008) XXX ± 6.35 (0.250)		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD		CHKD	
		CHKD			

	THIRD ANGLE PROJECTION	 I/O INTERCONNECT SANTA ANA, CALIFORNIA	UNLESS OTHERWISE NOTED: 1) DIMENSIONS ARE IN MILLIMETER (INCHES) 2) TOLERANCES: XX ± 0.20 (0.008) XX ± 0.35 (0.250)
DR: Cathy W. Wang C. Wang 06/29/93	AWG (12/012 MAX) BARE COPPER 10.00 FT EXTENDED, NON-UL, UNSHIELDED, MODULAR CABLE	121-X10-0X1	REV 1 INTERCONNECT
CHECKED: <i>[Signature]</i>	CHECKED: <i>[Signature]</i>	PART NO	CUSTOMER
CHECKED: <i>[Signature]</i>	CHECKED: <i>[Signature]</i>	SCALE: NONE	SHEET 2 OF 2

THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT, INC. USA AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF I/O INTERCONNECT, INC. OR ITS AFFILIATED SUBSIDIARIES.

DWG. NO.	ZONE / REV.	DESCRIPTION	DATE	APPROV.
X10-0X0	D	ECN 387	06/09/95	G.T.



BUNDLE SPECIFICATION



NOTES UNLESS OTHERWISE SPECIFIED.

1.0 PACKAGING SPECIFICATION

1.01 USE CLEAR TAPE TO BUNDLE 25 CABLES TOGETHER AT THE MID SECTION.

1.02 PLACE PLASTIC BAG IN SHIPPING BOX AND LAY

10 BUNDLE OR 250 PIECES MAX. PER SHIPPING BOX.

CLOSE PLASTIC BAG AND SEAL BAG ALONG 3 SURFACES


WITH TAPE

4	533.40	(21.000)	L=13.00" X W=25.00" X H=9.00"
6	609.60	(24.000)	L=13.00" X W=25.00" X H=9.00"
8	711.20	(28.000)	L=13.00" X W=30.00" X H=9.00"
CONDUCTORS	MILLIMETERS	INCHES	DIMENSION MAX.
NUMBER OF	RETRACTED LENGTH "R"		OUTSIDE SHIPPING BOX

TABULATION BLOCK

I/O INTERCONNECT 26 AVG (12/0.12 mm) BARE COPPER 7.00 FT. EXTENDED, NON-UL UNSHIELDED, MODULAR CABLE	
DR: CAVI C. VAG CHKD: <i>Valley</i>	TITLE: SANTA ANA, CALIFORNIA DATE: 06/09/95 PART NO: 121-X10-0X0 CUSTOMER: I/O INTERCONNECT SCALE: NONE SHEET: 2 OF 2

THIRD ANGLE PROJECTION




UNLESS OTHERWISE NOTED:

1) DIMENSIONS ARE IN MILLIMETER (INCHES)


2) TOLERANCES:

XX ± 0.20 (0.008)


X.XX ± 6.35 (0.250)



8 CONDUCTOR CABLE



6 CONDUCTOR CABLE



4 CONDUCTOR CABLE

NOTES: UNLESS OTHERWISE SPECIFIED.

- 1.0 MATERIAL AND SPECIFICATIONS
 - 1.01 CONDUCTORS: 26 AWG (12/012 mm) STRANDED BARE COPPER.
 - 1.02 INSULATION: POLYPROPYLENE
 - 1.03 COLOR: PER CALLOUT
 - 1.04 PACKAGING: (SEE PAGE 2)
- 2.0 ELECTRICAL CHARACTERISTICS
 - 2.01 TEMPERATURE & VOLTAGE RATING: 80°C 30 V
 - 2.02 CONDUCTORS RESISTANCE: 148 OHMS/KM MAX. AT 20°C
 - 2.03 INSULATION RESISTANCE: 100 MEGOHMS/KM MIN. AT 20°C
 - 2.04 CAPACITANCE: 15 PF/FT (MAX)
 - 2.05 DIELECTRIC TEST: AC-500V PER 1 MINUTE

121-410-003	4	SILVER SATIN	[0.55] ± 0.0	14.00 ± 1.0
121-410-013	4	BLACK	[0.55] ± 0.0	14.00 ± 1.0
121-410-023	4	WHITE	[0.55] ± 0.0	14.00 ± 1.0
121-610-003	6	SILVER SATIN	[0.55] ± 0.0	14.00 ± 1.0
121-610-013	6	BLACK	[0.55] ± 0.0	14.00 ± 1.0
121-610-023	6	WHITE	[0.55] ± 0.0	14.00 ± 1.0
121-810-003	8	SILVER SATIN	[0.748 ± 0.0	19.00 ± 1.0
121-810-013	8	BLACK	[0.748 ± 0.0	19.00 ± 1.0
121-810-023	8	WHITE	[0.748 ± 0.0	19.00 ± 1.0
1/0 INTERCONNECT PART NUMBER	NUMBER OF CONDUCTORS	COLOR	Ø "A"	

THIRD ANGLE PROJECTION

UNLESS OTHERWISE NOTED:
1) DIMENSIONS ARE IN MILLIMETER (INCHES)
2) TOLERANCES:
XX ± 0.20 (0.008)
XXX ± 6.35 (0.250)

I/O INTERCONNECT
SANTA ANA, CALIFORNIA

DR: TECH W/NOV TITLE: 26 AWG (12/012 mm) BARE COPP
C. W/NOV 06/09/95 500 FT EXTENDED, NON-UL, UNSHIELDED, MODULAR CABLE

CHD: *Kentley* PART NO: 121-X10-0X3

CHD: *John* CUSTOMER: I/O INTERCONNECT

CHD: *John* SCALE: NONE SHEET 1 OF 1


John

DATE	REV.	DESCRIPTION	DATE	APPROVED
010-013	G	CON BCS	07/15/78	RJ

DATE	REV.	DESCRIPTION	DATE	APPROVED
010-013	G	CON BCS	07/15/78	RJ

DATE	REV.	DESCRIPTION	DATE	APPROVED
010-013	G	CON BCS	07/15/78	RJ

NOTE: DIMENSIONS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC. ALL RIGHTS ARE RESERVED. NO PARTS OR MATERIALS MAY BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM, WITHOUT PERMISSION IN WRITING FROM I/O INTERCONNECT INC. OR ITS APPLICABLE SUBSIDIARIES.



BUNDLE SPECIFICATION

NOTES: UNLESS OTHERWISE SPECIFIED:

- 1.0 MATERIAL AND SPECIFICATIONS
- 1.1 CONDUCTORS: 26 AWG (0.212 mm) STANNED BARE COPPER
- 1.2 INSULATION: POLYPROPYLENE
- 1.3 COLOR: PER CALLOUT
- 1.4 PACKAGING: SEE PAGE 2
- 2.0 ELECTRICAL CHARACTERISTICS
- 2.1 TEMPERATURE & VOLTAGE RATING: 80°C 30 V
- 2.2 CONDUCTORS RESISTANCE: 140 OHMS/KM MAX AT 20°C
- 2.3 INSULATION RESISTANCE: 100 MEGOHMS/KM MIN AT 20°C
- 2.4 CAPACITANCE: 15 PF/FT (500)
- 2.5 DIELECTRIC TEST: AC-500V PER 1 MINUTE
- 3.0 PACKAGING SPECIFICATION
- 3.1 USE CLEAR TAPE TO BUNDLE 25 CABLES TOGETHER AT THE MID SECTION
- 3.2 PLACE PLASTIC BAG IN SHIPPING BOX AND LAY TO BUNDLE OR 250 PILES MAX PER SHIPPING BOX. CLOSE PLASTIC BAG AND SEAL BOX ALONG 3 SURFACES WITH TAPE.

CONDUCTORS NUMBER OF	RETRACTED LENGTH "F"		THICKNESS MM	OUTSIDE SHIPPING BOX
	MILLIMETERS	INCHES		
4	431.00	(17.000)	L=13.00" X W=28.00" X H=9.00"	
6	457.20	(18.000)	L=13.00" X W=28.00" X H=9.00"	
8	508.00	(20.000)	L=13.00" X W=28.00" X H=9.00"	
10	609.60	(24.000)	L=13.00" X W=28.00" X H=9.00"	

THIRD ANGLE PROJECTION	ISOTHERMAL BLOCK
UNLESS OTHERWISE NOTED: 1) DIMENSIONS ARE IN MILLIMETERS (INCHES) 2) TOLERANCES: XX ± 0.20 (0.008) XXX ± 0.25 (0.010)	SANTA ANA, CALIFORNIA 26 AWG (0.212 mm) BARE COPPER 500 FT EXTENDED, NON-IL, UNSHIELDED, MEDICAL CABLE DATE: 07/15/78 REV: 07/15/78 DATE: 07/15/78 REV: 07/15/78 DATE: 07/15/78 REV: 07/15/78 DATE: 07/15/78 REV: 07/15/78

