

# Zener ESD Protection Diode

## Dual Common Anode Zeners for ESD Protection

### DF3A6.8FUT1

These dual monolithic silicon zener diodes are designed for applications requiring transient overvoltage protection capability. They are intended for use in voltage and ESD sensitive equipment such as computers, printers, business machines, communication systems, medical equipment and other applications. Their dual junction common anode design protects two separate lines using only one package. These devices are ideal for situations where board space is at a premium.

#### Features

- Pb-Free Package is Available
- SC-70 Package Allows Two Separate Unidirectional Configurations
- Low Leakage < 1.0  $\mu$ A @ 5.0 V
- Breakdown Voltage: 6.4–7.2 V @ 5.0 mA
- ESD Protection Meeting: 16 kV Human Body Model  
30 kV Contact = IEC61000–4–2
- Peak Power: 24 W @ 1.0 ms (Unidirectional), per Figure 1
- Peak Power: 150 W @ 20  $\mu$ s (Unidirectional), per Figure 2

#### Mechanical Characteristics



- Void Free, Transfer-Molded, Thermosetting Plastic Case
- Corrosion Resistant Finish, Easily Solderable
- Package Designed for Optimal Automated Board Assembly
- Small Package Size for High Density Applications

#### MAXIMUM RATINGS

| Rating                                                                                                          | Symbol          | Value           | Unit        |
|-----------------------------------------------------------------------------------------------------------------|-----------------|-----------------|-------------|
| Steady State Power Dissipation<br>Derate above 25°C (Note 1)                                                    | $P_D$           | 200<br>1.6      | mW<br>mW/°C |
| Thermal Resistance Junction-to-Ambient                                                                          | $R_{\theta JA}$ | 618             | °C/W        |
| Operating Junction and Storage<br>Temperature Range                                                             | $T_J, T_{stg}$  | – 55 to<br>+150 | °C          |
| Peak Power Dissipation @ 1.0 ms<br>(Note 2) @ $T_A = 25^\circ\text{C}$                                          | $P_{PK}$        | 20              | W           |
| Peak Power Dissipation @ 20 $\mu$ s (Note 3)<br>@ $T_A = 25^\circ\text{C}$                                      | $P_{PK}$        | 150             | W           |
| ESD Discharge<br>MIL STD 883C – Method 3015–6<br>IEC61000–4–2, Air Discharge<br>IEC61000–4–2, Contact Discharge | $V_{PP}$        | 16<br>30<br>30  | kV          |


Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

- Mounted on FR-5 Board = 1.0 X 0.75 X 0.062 in.
- Non-repetitive pulse per Figure 1.
- Non-repetitive pulse per Figure 2.



SC-70/SOT-323  
CASE 419  
STYLE 4

#### MARKING DIAGRAM



68 = Specific Device Code  
M = Date Code

#### ORDERING INFORMATION

| Device       | Package            | Shipping <sup>†</sup> |
|--------------|--------------------|-----------------------|
| DF3A6.8FUT1G | SC-70<br>(Pb-Free) | 3000 /<br>Tape & Reel |

#### DISCONTINUED (Note 1)

|             |       |                       |
|-------------|-------|-----------------------|
| DF3A6.8FUT1 | SC-70 | 3000 /<br>Tape & Reel |
|-------------|-------|-----------------------|

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

- DISCONTINUED:** This device is not recommended for new design. Please contact your onsemi representative for information. The most current information on this device may be available on [www.onsemi.com](http://www.onsemi.com).

**Preferred** devices are recommended choices for future use and best overall value.


## DF3A6.8FUT1

### ELECTRICAL CHARACTERISTICS

( $T_A = 25^\circ\text{C}$  unless otherwise noted)

**UNIDIRECTIONAL** (Circuit tied to Pins 1 and 3 or 2 and 3)

| Symbol    | Parameter                                   |
|-----------|---------------------------------------------|
| $V_{RWM}$ | Working Peak Reverse Voltage                |
| $I_R$     | Maximum Reverse Leakage Current @ $V_{RWM}$ |
| $V_{BR}$  | Breakdown Voltage @ $I_T$                   |
| $I_T$     | Test Current                                |
| $I_F$     | Forward Current                             |
| $V_F$     | Forward Voltage @ $I_F$                     |
| $Z_{ZT}$  | Maximum Zener Impedance @ $I_{ZT}$          |
| $Z_{ZK}$  | Maximum Zener Impedance @ $I_{ZK}$          |



### ELECTRICAL CHARACTERISTICS ( $T_A = 25^\circ\text{C}$ unless otherwise noted)

**UNIDIRECTIONAL** (Circuit tied to Pins 1 and 3 or 2 and 3)

| Parameter                     | Symbol   | Conditions                          | Min | Typ | Max | Unit          |
|-------------------------------|----------|-------------------------------------|-----|-----|-----|---------------|
| Forward Voltage               | $V_F$    | $I_F = 10\text{ mA}$                | –   | 0.8 | 0.9 | V             |
| Zener Voltage (Note 4)        | $V_Z$    | $I_{ZT} = 5\text{ mA}$              | 6.4 | 6.8 | 7.2 | V             |
| Operating Resistance (Note 5) | $Z_{ZK}$ | $I_{ZK} = 0.5\text{ mA}$            | –   | –   | 200 | $\Omega$      |
|                               | $Z_{ZT}$ | $I_{ZT} = 5\text{ mA}$              | –   | –   | 50  | $\Omega$      |
| Reverse Current               | $I_{R1}$ | $V_{RWM} = 5\text{ V}$              | –   | –   | 0.5 | $\mu\text{A}$ |
| Clamping Voltage              | $V_C$    | $I_{PP} = 2.0\text{ A}$ (Figure 1)  | –   | –   | 9.6 | V             |
|                               |          | $I_{PP} = 9.37\text{ A}$ (Figure 2) | –   | –   | 16  | V             |
| ESD Protection                |          |                                     |     |     |     | kV            |
| Human Body Model (HBM)        |          |                                     | –   | –   | 16  |               |
| Contact – IEC61000–4–2        |          |                                     | –   | –   | 30  |               |
| Air Discharge                 |          |                                     | –   | –   | 30  |               |

4.  $V_Z$  measured at pulse test current  $I_{ZT}$  at an ambient temperature of  $25^\circ\text{C}$ .

5.  $Z_{ZT}$  and  $Z_{ZK}$  is measured by dividing the AC voltage drop across the device by the AC current supplied. AC frequency = 1.0 kHz.

# TYPICAL CHARACTERISTICS




Figure 1. 10 × 1000 μs Pulse Waveform




Figure 2. 8 × 20 μs Pulse Waveform




Figure 3. Zener Voltage vs. Zener Current




Figure 4. Forward Voltage vs. Forward Current




Figure 5. Capacitance vs. Bias Voltage





Figure 6. Steady State Power Derating Curve




SCALE 4:1

**SC-70 (SOT-323)**  
**CASE 419**  
**ISSUE R**


DATE 11 OCT 2022

## NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH




| DIM | MILLIMETERS |      |      | INCHES    |       |       |
|-----|-------------|------|------|-----------|-------|-------|
|     | MIN.        | NOM. | MAX. | MIN.      | NOM.  | MAX.  |
| A   | 0.80        | 0.90 | 1.00 | 0.032     | 0.035 | 0.040 |
| A1  | 0.00        | 0.05 | 0.10 | 0.000     | 0.002 | 0.004 |
| A2  | 0.70 REF    |      |      | 0.028 BSC |       |       |
| b   | 0.30        | 0.35 | 0.40 | 0.012     | 0.014 | 0.016 |
| c   | 0.10        | 0.18 | 0.25 | 0.004     | 0.007 | 0.010 |
| D   | 1.80        | 2.00 | 2.20 | 0.071     | 0.080 | 0.087 |
| E   | 1.15        | 1.24 | 1.35 | 0.045     | 0.049 | 0.053 |
| e   | 1.20        | 1.30 | 1.40 | 0.047     | 0.051 | 0.055 |
| e1  | 0.65 BSC    |      |      | 0.026 BSC |       |       |
| L   | 0.20        | 0.38 | 0.56 | 0.008     | 0.015 | 0.022 |
| H_E | 2.00        | 2.10 | 2.40 | 0.079     | 0.083 | 0.095 |

**GENERIC**  
**MARKING DIAGRAM**


XX = Specific Device Code  
M = Date Code  
■ = Pb-Free Package

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "■", may or may not be present. Some products may not follow the Generic Marking.



\* For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

**SOLDERING FOOTPRINT**

STYLE 1:  
CANCELLED

STYLE 2:  
PIN 1. ANODE  
2. N.C.  
3. CATHODE

STYLE 3:  
PIN 1. BASE  
2. EMITTER  
3. COLLECTOR

STYLE 4:  
PIN 1. CATHODE  
2. CATHODE  
3. ANODE

STYLE 5:  
PIN 1. ANODE  
2. ANODE  
3. CATHODE

STYLE 6:  
PIN 1. EMITTER  
2. BASE  
3. COLLECTOR

STYLE 7:  
PIN 1. BASE  
2. EMITTER  
3. COLLECTOR

STYLE 8:  
PIN 1. GATE  
2. SOURCE  
3. DRAIN

STYLE 9:  
PIN 1. ANODE  
2. CATHODE  
3. CATHODE-ANODE

STYLE 10:  
PIN 1. CATHODE  
2. ANODE  
3. ANODE-CATHODE

STYLE 11:  
PIN 1. CATHODE  
2. CATHODE  
3. CATHODE

|                         |                        |                                                                                                                                                                                  |
|-------------------------|------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>DOCUMENT NUMBER:</b> | <b>98ASB42819B</b>     | Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| <b>DESCRIPTION:</b>     | <b>SC-70 (SOT-323)</b> | <b>PAGE 1 OF 1</b>                                                                                                                                                               |

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)