







DAUGHTERCARD HOLE PATTERN (CONNECTOR SIDE)

NOTES:

1. MATERIALS: HOUSING - LIQUID CRYSTAL POLYMER (LCP)
GLASS-FILLED, UL 94V-0
TERMINALS - HIGH PERFORMANCE COPPER ALLOY
2. FINISH: SELECTIVE GOLD (Au) IN CONTACT AREA,
SELECTIVE MATTE TIN (Sn) IN TAIL AREA,
NICKEL (Ni) UNDERPLATE OVERALL.
3. REFER TO MOLEX PRODUCT SPEC PS-75710-999 FOR PERFORMANCE SPECIFICATIONS.
4. PRODUCT IS PACKAGED PER PK-70873-607.
5. THIS PART CONFORMS TO CLASS B REQUIREMENTS OF COSMETIC SPEC PS-45499-002.
6. MAPS (MOLEX ADVANCED PLATING SYSTEM).

ADD 50 GOLD EC NO: UCP2014-3112 DRWN:WOLFE 2014/01/28 CHKD:SVANG 2014/01/28 APPR:SMILLER 2014/02/11	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 4:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
				mm	INCH	DRAWN BY DATE MCARRANZA 3/20/06		TITLE I-TRAC DAUGHTERCARD 7 ROW UNGUIDED SIGNAL MODULE molex		
			4 PLACES ± --- ± ---	3 PLACES ± --- ± ---	CHECKED BY DATE JLAURX 3/21/06					
			2 PLACES ± 0.13 ± ---	1 PLACE ± 0.25 ± ---	APPROVED BY DATE JLAURX 3/21/06					
			0 PLACE ± ±							
			ANGULAR ±1/2°		MATERIAL NO.		DOCUMENT NO.			SHEET NO.
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-76020-001			1 OF 2
					SIZE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

MATERIAL NUMBER	# OF COLUMNS	DIM. "A" MAX.	DIM. "B"
76020-*0*4	4	14.80	11.10
76020-*0*6	6	22.20	18.50
76020-*0*0	10	37.00	33.30

76020-*0**

MODULE STYLE AND TAIL PLATING TYPE
0 = UNGUIDED, MATTE TIN (FORMERLY TIN/LEAD)
1 = UNGUIDED, MATTE TIN

POLARIZATION KEY ORIENTATION
0 = NO KEY

OF COLUMNS/PLATING
04 = 4 COL, 30 GOLD
06 = 6 COL, 30 GOLD
10 = 10 COL, 30 GOLD
44 = 4 COL, 10 GOLD (MAPS)
46 = 6 COL, 10 GOLD (MAPS)
40 = 10 COL, 10 GOLD (MAPS)
54 = 4 COL, 50 GOLD
56 = 6 COL, 50 GOLD
50 = 10 COL, 50 GOLD

SEE SHEET 1
EC NO: UCP2014-3112
DRWN:MWLF 2014/01/28
CHKD:SVANG 2014/01/28
APPR:SMILLER 2014/02/11

DESCRIPTION
REV

QUALITY SYMBOLS
▽=0
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)
mm INCH
4 PLACES ± --- ± ---
3 PLACES ± --- ± ---
2 PLACES ± 0.13 ± ---
1 PLACE ± 0.25 ± ---
0 PLACE ± ±
ANGULAR ±1/2°
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE
MM ONLY
DRAWN BY DATE
MCARRANZA 3/20/06
CHECKED BY DATE
JLAURX 3/21/06
APPROVED BY DATE
JLAURX 3/21/06

SCALE
1:1
TITLE
I-TRAC DAUGHTERCARD
7 ROW UNGUIDED
SIGNAL MODULE
molex

DESIGN UNITS
METRIC
THIRD ANGLE PROJECTION

MATERIAL NO.
SEE CHART
DOCUMENT NO.
SD-76020-001
SHEET NO.
2 OF 2

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION