







OBSELETE	4.19 [.165]	60.96 [2.400]	24	68.58 [2.700]	71.12 [2.800]	50	636-5017	9-1437061-3
OBSELETE	2.90 [.114]	60.96 [2.400]	24	68.58 [2.700]	71.12 [2.800]	50	636-5007	9-1437061-1
	2.90 [.114]	48.26 [1.900]	19	55.88 [2.200]	58.42 [2.300]	40	636-4007	7-1437061-9
	2.90 [.114]	40.64 [1.600]	16	48.26 [1.900]	50.80 [2.000]	34	636-3407	7-1437061-1
	4.19 [.165]	30.48 [1.200]	12	38.10 [1.500]	40.64 [1.600]	26	636-2617	5-1437061-7
	OBSELETE	2.90 [.114]	30.48 [1.200]	12	38.10 [1.500]	40.64 [1.600]	26	636-2607
	2.90 [.114]	22.86 [.900]	9	30.48 [1.200]	33.02 [1.300]	20	636-2007	3-1437061-9
	2.90 [.114]	17.78 [.700]	7	25.40 [1.000]	27.94 [1.100]	16	636-1607	3-1437061-1
	4.19 [.165]	15.24 [.600]	6	22.86 [.900]	25.40 [1.000]	14	636-1417	2-1437061-5
	2.90 [.114]	15.24 [.600]	6	22.86 [.900]	25.40 [1.000]	14	636-1407	2-1437061-3
	2.90 [.114]	10.16 [.400]	4	17.78 [.700]	20.32 [.800]	10	636-1007	1-1437061-5
	E	D	C	B	A	NO OF POS	T&B PART NO REF	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. J. GERACE OSMAY06		 Tyco Electronics Corporation Harrisburg, Pa 17105	
		CHK. S. BOLASH OSMAY06			
DIMENSIONS: (IN)[INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		HEADER ASSEMBLY, RIGHT ANGLE, LOW PROFILE, IDC NOT THE LATEST DESIGN	
		0 FRACTIONAL ± 1 DECIMAL ± 2 ANGLES ± 0.1°[.005] 3 ANGLES ± 4 ANGLES ±			
MATERIAL		FINISH		RESTRICTED TO	
				WEIGHT — CUSTOMER DRAWING	
				SIZE: CAGE CODE: DRAWING NO. A1 00779 ©6-1437046 SCALE: 4:1 SHEET 1 OF 1 REV B	