




	13	12	11	10	9	8	7	6	5	4	3	2	1			
J	PART NUMBER	ENGINEERING NUMBER	FINISH LENGTH												J	
	1300061346	105001A01F030	3.00' +1.75" -0 [.9M +44.5 -0]													
	1300061349	105001A01F060	6.00' +2.19" -0 [1.8M +55.6 -0]													
I	1300061353	105001A01F120	12.00' +3.50" -0 [3.7M +88.9 -0]												I	
	1300061356	105001A01F150	15.00' +6.50" -0 [4.6M +165.1 -0]													
	1300061360	105001A01F200	20.00' +6.50" -0 [6.1M +165.1 -0]													
	1300061364	105001A01F250	25.00' +12.50" -0 [7.6M +317.5 -0]													
H	1300061367	105001A01F300	30.00' +12.50" -0 [9.1M +317.5 -0]												H	
G	NOTE 1) MATERIAL: SEE TABLE 2) FINISHES: SEE TABLE 3) WRAP LABEL IS MARKED WITH P/N, DATE CODE, VOLTAGE & AMPERAGE 4) MATES WITH: MINI CHANGE, 5 POLE RECEPTACLE 5) ELECTRICAL DATA: INLINE CORDSET FEMALE A-SIZE WITH FLYING LEADS 16AWG UNSHIELDED POLES: 5 MAX. VOLTAGE: 600V MAX. CURRENT 8A PROTECTION IP67 TEMPERATURE RANGE: -20°C TO 105°C 6) PACKAGING: CABLE ASSEMBLIES ARE BAGGED SEPERATELY IN POLY BAGS WITH BAR CODE LABEL ATTACHED TO OUTSIDE OF BAG. 7)ASSEMBLY IS RoHS COMPLIANT. 8)CERTIFICATION UL RECOGNIZED, FILE NO. E152210 CSA CERTIFIED, FILE NO. LR6837														G	
F															F	
E															E	
D															D	
C															C	
B															B	
A															A	
					6	1	LABEL	PLASTIC FILM	BLACK/YELLOW							
	5	5	CONTACT SOCKET	COPPER ALLOY	GOLD PLATED											
	4	1	INSERT	PVC	YELLOW											
	3	1	COUPLING NUT	ZINC DIE CAST	BLACK E-COATED											
	2	1	OVERMOLD	PVC	YELLOW											
	1	1	CABLE, 16AWG-5 TYPE STOW	PVC	YELLOW											
	ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH											
	13	12	11	10	9	8	7	6	5	4	3	2	1			



P1	
1	WHITE
2	RED
3	GREEN/YELLOW-GND
4	ORANGE
5	BLACK

FEMALE FACE VIEW

WIRING DIAGRAM

RELEASE EC NO: WNA2010-0397 DRWN: BWOODMAN 12/22/09 CH'KD: --- APPR: JFMURPHY 2010/01/05 B	DESCRIPTION REV	QUALITY SYMBOL	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION			
		▽=0 ∇=0		mm	INCH	IN/MM		1:1	INCH			
			4 PLACES	±----	±---	DRAWN BY	DATE	TITLE MINI CHANGE ASSEMBLY 5-POLE FEMALE 90D 16/5AWG PVC				
			3 PLACES	±.005	±.005	TWOLDEGE	2009/07/29					
			2 PLACES	±.013	±.010	CHECKED BY	DATE	MOLEX INCORPORATED				
			1 PLACE	±.025	±.020	BWOODMAN	2009/07/29					
		ANGULAR ±1/2°			JFMURPHY	2010/01/05	DOCUMENT NO. SD-130006-017					
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO. SEE CHART							SHEET NO. 1 OF 1
					SIZE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
					C							