





This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, and that no right is granted to disclose or to use any information in this document.




REVISIONS				
SYM	ECH	DESCRIPTION	DATE	APPROVED
Q	HK1421	RELEASE TO CUSTOMER	06/12/97	NELSON
R	HK1513	"**" TAIL SIZE MODIFIED	06/01/98	Michael Ts
S	HK2043	Revise L&E options&delete three side option	8/24/01	Michael P
T	HK3437	UPDATE DRAWING TO COMPLY WITH RoHS	07/18/05	Michael P



Optional latch and stud




Size 14
P/N: X842-816-14XX-XXX




Size 10 with CPK slot
P/N: 842-816-10XX-XXXS, or
P/N: E842-816-10XX-XXX with date code



Size 10 without CPK slot
P/N: 842-816-10XX-XXX




Size 34 or above
P/N: X842-816-XXXX-XXX



Size 20
P/N: X842-816-20XX-XXX



Size 16
P/N: X842-816-16XX-XXX



Right angle
solder tail

Customer Drawing

Table 1

Latch & Eject	J	H
Short: for use with non strain relief socket	0.425 [10.80]	1.015 [25.78]
Long for use with strain relief socket	0.575 [14.61]	1.135 [28.83]

Table II

Stud	L	M
Short stud 2–56	0.29 [7.4]	0.45 [11.43]
Long stud 2–56	0.36 [9.1]	0.52 [13.21]
Stud M2.5	0.18 [4.6]	0.34 [8.6]

Note: unit in inch [mm]

UNLESS OTHERWISE SPECIFIED			
TOLERANCES			
	U.S.	METRIC	
.X	+/-	.020	0.51
.JXX	+/-	.010	0.25
.JXXX	+/-	.005	0.13
FRACTIONS	+/-		
ANGLES	+/-	2.5°	2.5°
FOR MATERIALS AND FINISHES SEE NOTES			
REMOVE SHARP EDGES			
DIMENSIONS			
U.S.		INCHES	
METRIC		MM	

APPROVAL		DATE
DRAWN ALEX.LEE		07/18/08
CHECKED TSUI		07/18/08
CHECKED		
DRAWING FILE : \\DRAWING\816\CS16.DWG		
ANGLE OF PROJECTION		
		


Amphenol

TITLE	816 Protected Header
-------	----------------------

SIZE	DRAWING NO.
A3	C816-XXXX-XXX

SCALE	NONE
-------	------

SHEET 1 OF 2



This document is the property of Amphenol Corporation and is loaned on the express condition that it is not to be distributed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without the prior express written consent. No right is granted to disclose or to use any information in this document.

ORDERING INFORMATION

E 842 - 816 - XX XX - X XX X

Date code _____
Nil - No date code
E - Date code printed Δ

No. of contact _____

Body & pin configuration
(Refer to Table III)

Lock & Eject (L&E) and mounting stud options

0 - no L&E, no stud
1 - short L&E, no stud
2 - short L&E, short stud
3 - short L&E, long stud
4 - long L&E, no stud
5 - long L&E, short stud
6 - long L&E, long stud
F - long L&E, M2.5 stud


Nil - standard
S - standard with polarizing
key slot for size 10 Δ

Plating
AA - gold flash duplex
19 - 15 ? gold plated duplex
35 - 30 ? gold plated duplex

Table III

Standard product - four side grey	Non-standard product - three side grey (specific quantity required)	K
30 - straight solder tail, for 0.062" [1.6 mm] PCB	20 - obsolete	0.109 ± 0.007 [2.61 ± 0.34] coined tail
31 - straight solder tail, for 0.125" [3.2 mm] PCB	21 - obsolete	0.171 ± 0.009 [4.14 ± 0.36] coined tail
32 - right angle solder tail, for 0.062" [1.6 mm] PCB	22 - obsolete	0.109 ± 0.007 [2.61 ± 0.34] coined tail
33 - right angle solder tail, for 0.125" [3.2 mm] PCB	23 - obsolete	0.171 ± 0.009 [4.14 ± 0.36] coined tail
37 - straight wire wrap tail	27 - obsolete	0.61 ± 0.015 [15.49 ± 0.38] square tail
39 - right angle wire wrap tail	29 - obsolete	0.61 ± 0.015 [15.49 ± 0.38] square tail

Recommended PCB layout



Notes:

- Connectors purchased under this drawing will mate with MIL-C-83503/7B socket connector with strain relief or without strain relief and Amphenol's 812 connector.
- This assembly is designed to meet requirements of MIL-C-83503.
- Δ The polarizing key slot on this end does not exist on size 10 and 14.
- Δ Prefix "E" only applies to the four-sided version & polarizing key slot is available for all size including size 10.
- Δ Suffix "S" only applies to the size 10 since the polarizing key slot is absent from the standard size 10.
- This connector is both UL and CSA approved.
- Refer to Amphenol 5-816-001 for product specification.
- MATERIAL SHOULD BE FULFILLED AMPHENOL SPEC#SSN001.

Table IV

Size	A	B	C	D	E	F
10	1.26 [32.07]	1.10 [27.94]	0.860 [21.84]	0.708 [17.98]	0.400 [10.16]	4
14	1.46 [37.08]	1.30 [33.02]	1.080 [26.92]	0.908 [23.06]	0.600 [15.24]	6
16	1.56 [39.62]	1.40 [35.56]	1.160 [29.46]	1.008 [25.60]	0.700 [17.78]	7
20	1.76 [44.70]	1.60 [40.64]	1.360 [34.54]	1.208 [30.68]	0.900 [22.86]	9
28	2.06 [52.32]	1.90 [48.26]	1.660 [42.16]	1.508 [38.30]	1.200 [30.40]	12
30	2.26 [57.40]	2.10 [53.34]	1.860 [47.24]	1.708 [43.38]	1.400 [35.56]	14
34	2.46 [62.48]	2.30 [58.42]	2.060 [52.32]	1.908 [48.46]	1.600 [40.64]	16
40	2.76 [70.10]	2.60 [66.04]	2.360 [59.94]	2.208 [56.08]	1.900 [48.26]	18
50	3.26 [82.80]	3.10 [78.74]	2.860 [72.64]	2.708 [68.78]	2.400 [60.96]	24
60	3.76 [95.50]	3.60 [91.44]	3.360 [85.34]	3.208 [81.48]	2.900 [73.66]	28
64	3.96 [100.58]	3.80 [96.52]	3.560 [90.42]	3.408 [86.60]	3.100 [78.74]	31

Customer Drawing

UNLESS OTHERWISE SPECIFIED TOLERANCES U.S. METRIC X +/- .020 0.51 3X +/- .010 0.25 30X +/- .008 0.13 FRACTIONS +/- 2.5 2.5 ANGLES +/- 2.5 2.5	APPROVAL DRAWN ALEXJEE CHECKED TSUN CHECKED	DATE 07/18/04 07/18/04	TITLE 816 Protected Header
FOR MATERIALS AND FINISHES SEE NOTES REMOVE SHARP EDGES	DRAWING FILE: DRAWING\816\816.DWG	ANGLE OF PROJECTION 	SIZE DRAWING NO. A3 C816-XXXX-XXX
DIMENSIONS U.S. INCHES METRIC MM			REY. T
			SCALE NONE SHEET 2 OF 2