





See "Part Drawing" for Details




Part Number	Description
-------------	-------------

[UMS-32-45A-RT](#)


Strap,Adj,Adh Mnt,Blk,2" Max Hold



PART NO.		MAXIMUM BUNDLE DIA.	RADIUS "R"
W/O TAPE	W/TAPE		
UMS-16-45	UMS-16-45A-RT	1 (25.4)	1/2 (12.7)
UMS-24-45	UMS-24-45A-RT	1-1/2 (38.1)	3/4 (19.1)
UMS-32-45	UMS-32-45A-RT	2 (50.8)	1 (25.4)



RICHCO RIVET NO.	PANEL THICKNESS RANGE
SR5045	0.000 TO 0.018
SR5055	0.018 TO 0.058
SR5065	0.058 TO 0.097
SR5075	0.097 TO 0.137
SR5085	0.137 TO 0.176
SR5095	0.176 TO 0.215
SR5105	0.215 TO 0.255



NOTES:

1. MATERIAL: NYLON 6/6 (RMS-45).
2. COLOR: BLACK.
3. FOR MOUNTING USE SNAP RIVETS "SR-SERIES", #6 SCREW OR ACRYLIC ADHESIVE TAPE (RMS-15).

TITLE: UNIVERSAL MOUNTING STRAP					DWG IN IN (MM)	
TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=±1/64 ANG=±1°	FILE # UMS	DWN: P.B.	APP:	FINAL		
	MAT'L: SEE NOTES	DT: 01-18-95	DT:	PART # SEE TABLE	PRINT TYPE CA	
	RE: RICHCO, INC.	RICHCO INC.				

REV	DESCRIPTION	ENGR	DATE
D	SEE CO 200171 FOR CHANGES	SK	04.29.08
C	SEE ECN #551 FOR CHANGES	SM	01.07.03
B	CHANGED TAPE NOTE AND FILE NO.	SM	12.11.01
A	CHANGED RMS-73 TO RMS-45	JB	04.22.96