



P	LTR	DESCRIPTION	DATE	DWN	APV
	B3	REVISED (ECR-11-011518)	02JUN11	SC	WK






RECOMMENDED PCB LAYOUT

PCB TOLERANCE : ± 0.05 

NOTES :

1. MATERIAL :
HOUSING : THERMOPLASTIC, UL 94V-0, COLOR: SEE TABLE.
CONTACT : PHOSPHOR BRONZE, (t=0.25mm).
FRONT SHELL & SPRING : BRASS, (t=0.30mm).
REAR SHELL : SPCC (t=0.30mm).
2. FINISH :
CONTACT : GOLD PLATED(SEE TABLE) ON CONTACT AREA,
100u" MIN. TIN PLATED ON SOLDER TAILS,
50u" MIN. NICKEL UNDERPLATED ALL OVER.
FRONT SHELL: 40u" MIN. NICKEL PLATED OVER 50u" MIN.
CU UNDERPLATED ALL OVER.
REAR SHELL: 100u" MIN. NICKEL PLATED OVER 100u" MIN.
CU UNDERPLATED ALL OVER.
3. TOLERANCE : ±0.30mm.
4. GAP. 0.25mm(MAX.)



	30μ"	BLACK	1734181-6
OBSOLETE	30μ"	WHITE	1734181-5
	5μ"	BLACK	1734181-4
		WHITE	1734181-3
	GOLD FLASH	BLACK	1734181-2
		WHITE	1734181-1
	MIN. GOLD THICKNESS	HSG. COLOR	PART NUMBER


THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	14APR2009
S. CHIEN	
CHK	14APR2009
S. CHIEN	
APVD	14APR2009
W. KODAMA	
PRODUCT SPEC	
108-57113	
QUALIFICATION TEST REPORT	
501-57061	



TE Connectivity

RCPT. ASS'Y TRIPLE STACKED
USB, R/A, A TYPE.

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		S. CHIEN	
MM				APVD 14APR2009	
		0 PLC	± 0.3	PRODUCT SPEC	
		1 PLC	± 0.3	108-57113	
		2 PLC	± 0.3	QUALIFICATION TEST REPORT	
		3 PLC	± -	501-57061	
		4 PLC	± -	WEIGHT - GRAMS	
MATERIAL		FINISH		CUSTOMER DRAWING	
SEE NOTE		SEE NOTE			

SIZE	CAGE CODE	DRAWING NO	RESTRICTED 1
A3	00779	C=1734181	—
		SCALE	SHEET 1 OF 3 REV B3

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG. 2006 .

C

COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1.

NOTES :

1. MATERIAL :


HOUSING : THERMOPLASTIC, UL 94V-0, COLOR: SEE TABLE.
 CONTACT : PHOSPHOR BRONZE, (t=0.25mm).
 FRONT SHELL & SPRING : BRASS, (t=0.30mm).
 REAR SHELL : SPCC (t=0.30mm).

2. FINISH :

CONTACT : GOLD PLATED(SEE TABLE) ON CONTACT AREA,
 100u" MIN. TIN PLATED ON SOLDER TAILS,
 50u" MIN. NICKEL UNDERPLATED ALL OVER.
 FRONT SHELL: 40u" MIN. NICKEL PLATED OVER 50u" MIN.
 CU UNDERPLATED ALL OVER.
 REAR SHELL: 100u" MIN. NICKEL PLATED OVER 100u" MIN.
 CU UNDERPLATED ALL OVER.


3. TOLERANCE : ±0.30mm.

4. GAP. 0.25mm(MAX.)






RECOMMENDED PCB LAYOUT

PCB TOLERANCE : ±0.05



REAR SHELL



OBSOLETE	30μ"	BLACK	1-1734181-2
		WHITE	1-1734181-1
	5μ"	BLACK	1-1734181-0
		WHITE	1734181-9
	GOLD FLASH	BLACK	1734181-8
		WHITE	1734181-7
	MIN. GOLD THICKNESS	HSG. COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE

TE Connectivity

NAME

RCPT. ASS'Y TRIPLE STACKED
USB, R/A, A TYPE.

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C=1734181

SCALE

SHEET

2 of 3

REV B3

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG 2006 .



COPYRIGHT




BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.



LOC
DWDIST
—

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1.			




TRAY





DET.A

PE PAG

DESICCANT



PE BOX



Every 5 trays and mantissa tray by PE packing . it should be fulled by cardboard when less than one carton .

11.53	9.31	1000	100
G.W(KGS)	N.W(KGS)	QUANTITY/BOX	PCS/TRAY

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: MM	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
	ANGLES ± -
MATERIAL	FINISH

DWN	TE Connectivity		
CHK	NAME		
APVD	RCPT. ASS'Y TRIPLE STACKED USB, R/A, A TYPE.		
PRODUCT SPEC	SIZE	CAGE CODE	DRAWING NO
APPLICATION SPEC	A3	00779	C=1734181
WEIGHT	CUSTOMER DRAWING		RESTRICTED TO
SCALE	SHEET	3 of 3	REV B3