

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT

BY

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD




B1

REVISED PER ECO-11-005294


29APR11

RK

HMR



P/N 284392-2 AS SHOWN



MATERIALS AND FINISH

HOUSING : PA 6.6, UL 94-V0, COLOR GREEN.

CLAMP : BRASS, NICKEL PLATED

TERMINAL : BRASS, TIN PLATED

CLAMPING SCREW : M3, BRASS, NICKEL PLATED


2. SUITABLE FOR 1.6-2.4 mm. PC BOARD THICKNESS.

3. END-TO-END STACKABLE W/INTERLOCK WITHOUT LOSS OF CENTERLINE SPACING

4. WIRE SIZE RANGE
14 - 30 AWG

NOT CUMULATIVE TOLERANCE

RECOMMENDED PC BOARD LAYOUT



95.25	25	2-284392-5
91.44	24	2-284392-4
87.63	23	2-284392-3
83.82	22	2-284392-2
80.01	21	2-284392-1
76.20	20	2-284392-0
72.39	19	1-284392-9
68.58	18	1-284392-8
64.77	17	1-284392-7
60.96	16	1-284392-6
57.15	15	1-284392-5
53.34	14	1-284392-4
49.53	13	1-284392-3
45.72	12	1-284392-2
41.91	11	1-284392-1
38.10	10	1-284392-0
34.29	9	284392-9
30.48	8	284392-8
26.67	7	284392-7
22.86	6	284392-6
19.05	5	284392-5
15.24	4	284392-4
11.43	3	284392-3
7.62	2	284392-2
DIM "A"	NO. OF POS	PART NUMBER

DWN 01FEB2002

E. ZANOLINI

CHK 01FEB2002

E. ZANOLINI

APVD 01FEB2002

D. BIEVENOUR

PRODUCT SPEC

108-20166

APPLICATION SPEC

114-20079

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME
TERMINAL BLOCK, PCB MOUNT, STRAIGHT
SIDE ENTRY WIRE, STACKING
W/ INTERLOCK, 3.81mm PITCH

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 00779 C=284392

SCALE 4:1

SHEET 1 OF 1

REV B1