


System No. N/A		MDSM-4R		D10-5277																																													
<table><tr><th colspan="4">ELECTRICAL RATINGS</th></tr><tr><th>CONTACT FORM</th><th colspan="2">WATTS</th><th>A</th></tr><tr><td>CONTACT RATING</td><td colspan="2"></td><td>10</td></tr><tr><td>RATING SENSITIVITY</td><td>AMPERE</td><td>TURNS</td><td>20</td></tr><tr><td rowspan="3">VOLTAGE</td><td>SWITCHING</td><td>VDC-MAX.</td><td>200</td></tr><tr><td>BREAKDOWN</td><td>VDC-MIN.</td><td>250</td></tr><tr><td>ARC-QUENCH</td><td>VDC-MIN.</td><td>200</td></tr><tr><td rowspan="2">CURRENT</td><td>SWITCHING</td><td>AMPERES-MAX.</td><td>0.5</td></tr><tr><td>CARRY</td><td>AMPERES-MAX.</td><td>1.2</td></tr><tr><td rowspan="2">RESISTANCE</td><td>CONTACT, INITIAL</td><td>OHMS-MAX.</td><td>0.10</td></tr><tr><td>INSULATION</td><td>OHMS-MIN.</td><td>10¹⁰</td></tr><tr><td>CAPACITANCE</td><td colspan="2">PICOFARADS-TYP.</td><td>0.2</td></tr></table>				ELECTRICAL RATINGS				CONTACT FORM	WATTS		A	CONTACT RATING			10	RATING SENSITIVITY	AMPERE	TURNS	20	VOLTAGE	SWITCHING	VDC-MAX.	200	BREAKDOWN	VDC-MIN.	250	ARC-QUENCH	VDC-MIN.	200	CURRENT	SWITCHING	AMPERES-MAX.	0.5	CARRY	AMPERES-MAX.	1.2	RESISTANCE	CONTACT, INITIAL	OHMS-MAX.	0.10	INSULATION	OHMS-MIN.	10 ¹⁰	CAPACITANCE	PICOFARADS-TYP.		0.2	SEE REED SWITCH CATALOG FOR DEFINITION OF TERMS	
ELECTRICAL RATINGS																																																	
CONTACT FORM	WATTS		A																																														
CONTACT RATING			10																																														
RATING SENSITIVITY	AMPERE	TURNS	20																																														
VOLTAGE	SWITCHING	VDC-MAX.	200																																														
	BREAKDOWN	VDC-MIN.	250																																														
	ARC-QUENCH	VDC-MIN.	200																																														
CURRENT	SWITCHING	AMPERES-MAX.	0.5																																														
	CARRY	AMPERES-MAX.	1.2																																														
RESISTANCE	CONTACT, INITIAL	OHMS-MAX.	0.10																																														
	INSULATION	OHMS-MIN.	10 ¹⁰																																														
CAPACITANCE	PICOFARADS-TYP.		0.2																																														
 MAGNETIC CHARACTERISTICS <table><tr><td>TEST COIL</td><td>L4989</td></tr><tr><td>STANDARD TOLERANCE</td><td>AMPERE TURNS</td></tr><tr><td>PULL-IN RANGES BEFORE MOD.</td><td>12-23 17-28 22-33 27-38</td></tr></table> PACKAGING TAPE AND REEL -3000/REEL SEE PAGE 2 OF 2 FOR TAPE AND REEL DETAIL. © HAMLIN, Incorporated 1996 This design and print is copyright and is the property of HAMLIN, Inc. It must not be copied or permitted to be copied, nor may its contents be divulged to any third party without the prior written permission from the company.				TEST COIL	L4989	STANDARD TOLERANCE	AMPERE TURNS	PULL-IN RANGES BEFORE MOD.	12-23 17-28 22-33 27-38	<table><tr><th colspan="2">H A M L I N, Inc.</th><th colspan="2">DCR No. A5406</th></tr><tr><td>Dwn.</td><td>RLB</td><td>DATE</td><td>12/17/96</td></tr><tr><td>App'd</td><td>GJ</td><td>DATE</td><td>12/18/96</td></tr></table>		H A M L I N, Inc.		DCR No. A5406		Dwn.	RLB	DATE	12/17/96	App'd	GJ	DATE	12/18/96																										
TEST COIL	L4989																																																
STANDARD TOLERANCE	AMPERE TURNS																																																
PULL-IN RANGES BEFORE MOD.	12-23 17-28 22-33 27-38																																																
H A M L I N, Inc.		DCR No. A5406																																															
Dwn.	RLB	DATE	12/17/96																																														
App'd	GJ	DATE	12/18/96																																														
MDSM-4R																																																	
AD	ADD DIM TO OUTSIDE LEG FORM	A9340	GJ	11/5/01	GJ	11/7/01																																											
REV.	DESCRIPTION OF REVISION	DCR No.	BY	DATE	APP.	DATE																																											

