

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00		L	REVISED PER ECR-13-008204	10DEC2013	KH	TM

- 1

0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN TIN-LEAD IN TIN-LEAD PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
- 2




WIRE RANGE: 3-6mm² [12-10 AWG].
- 3

DIMENSIONS IN BRACKETS ARE IN INCHES.
- 4

0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN TIN IN TIN PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
- 5

THIS CONTACT HAS NO INSULATION BARREL.
- 6

SUPERSEDED BY 1-770003-0.



SECTION A-A
SCALE 10:1

DETAIL A
SCALE 20:1

6	GOLD 4	0.30 [.012] PH BRZ	1-770003-0			
	GOLD 1	0.30 [.012] PH BRZ	770003-4			
	PRE-TIN	0.30 [.012] PH BRZ	770003-3			
	FINISH	MATERIAL	PART NUMBER			
THIS DRAWING IS A CONTROLLED DOCUMENT.						
MENT.	DWN K. WHITAKER	02APR04	 TE Connectivity			
	CHK C. JONES	02APR04				
ESS FIED:	APVD C. JONES	02APR04	NAME			
	PRODUCT SPEC		- PIN, UNIVERSAL MATE-N-LOK(TM) II -			
	APPLICATION SPEC					
-						
	WEIGHT	-	SIZE A2	CAGE CODE 00779	DRAWING NO C-770003	RESTRICTED TO -
CUSTOMER DRAWING				SCALE 4:1	SHEET 1 OF 1	REV L