

Article Number: 596-00625

Thermal Transfer Self-Laminating Label, 1.0" X .75" X 2.25", 1 across, Vinyl, White, 1000/RL



Download drawing

Download spec sheet

Base Data

Local Order Number	596-00625
Type	TAG2T1-100B
Color	White (WH)
Features and Benefits	• Thermal transfer labels are made with high performance materials for long term industrial applications. • Labels can be printed in any standard thermal transfer printer giving the user options for printing and eliminating the need to be dedicated to one printer model. • The labels are available in a wide variety of sizes so that finding a label for a particular application is easy.
Color Marking Field	White (WH)
Product Description	Labels are made with various high performance materials including polyester, metalized polyester, clear polyester, cloth, polyimide and the Durattach label stock. The construction includes an aggressive acrylic adhesive and abrasion and chemical resistant top coatings that are made to accept ink from a thermal transfer printer. The product is supplied on rolls on a 3 cardboard core."
Short Description	Thermal Transfer Self-Laminating Label, 1.0" X .75" X 2.25", 1 across, Vinyl, White, 1000/RL

Product Dimensions

Width W (Imperial)	0.5 "
Width W (Metric)	12.7 mm
Height H (Imperial)	0.5 "
Height H (Metric)	12.7 mm
Height H2 (Imperial)	1.43 "
Height H2 (Metric)	36.5 mm
Bundle Diameter Min. (Imperial)	0.137 "
Bundle Diameter Min. (Metric)	3.5 mm
Bundle Diameter Max. (Imperial)	0.29 "
Bundle Diameter Max. (Metric)	7.6 mm
Horizontal Repeat HR (imperial)	0.66 "
Horizontal Repeat HR (metric)	16.81 mm
Print Method	Thermal Transfer
Thickness T (Metric)	25 µm
Vertical Repeat VR (metric)	41.28 mm
Vertical Repeat VR (imperial)	1.62 "
Width of Liner WL (metric)	25.4 mm
Width of Liner WL (imperial)	1.0 "

Logistics and Packaging

Quantity Per	reel
Package Quantity	1000
Package Quantity (Metric)	1000
Carton Quantity	1000
Labels per Row	1

Material and Specifications

Material	Vinyl
Material Shortcut	VL
Adhesive	Acrylic
Adhesive Shortcut	Acrylic
Adhesive Operating Temperature	-40°F to +194°F (-40°C to +90°C)
Operating Temperature	-40°F to +194°F (-40°C to +90°C)
ROHS Compliant	Yes
Certification/Specification	UL-Recognized
UL Listed (US and Canada)	No
UL Listed (US)	No