

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC
AJ

DIST
16

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	H1	REVISED PER ECO-06-018709	18SEP2006	MC	JH

1 ZINC PER QQ-Z-363

2 PTFE PER MIL-P-19468

3 PHOS BRONZE PER QQ-B-750

4 POLYMETHYLPENTENE GENERAL PURPOSE

5 BRASS PER QQ-B-626

6 TIN PL PER MIL-T-10727, 3.81μm [.000150] MIN THK

7 TIN PL PER MIL-T-10727B TYPE 2, 2.54μm [.000100] MIN THK

8 NICKEL PL PER QQ-N-290, 3.81μm [.000150] MIN THK

9 TIN PL PER MIL-T-10727B TYPE 2, 2.54μm [.000100] MIN THK (POST PLATED)

10 BLACK CHROMATE PLATE OVER ZINC PLATE PER ASTM-B-633

11 BLACK NICKEL PLATE

15.88 [.625]

15.88 [.625]

Ø2.36±0.13
[.093±.005]
4 PLC

11.07±0.10
[.436±.004]

11.07±0.01
[.436±.004]

Ø2.36 [.093] MIN
4 HOLES

Ø9.65 [.380] MIN

RECOMMENDED PANEL CUTOUT

VIEW X

CONTACT

DIELECTRIC

SHELL

12.37
[.487]

23.50 [.925] MAX

3/8-24 UNF-2A

VIEW Y

SAME AS VIEW X EXCEPT AS SHOWN

CONTACT, STAMPED AND FORMED

0.25 MAX
[.010]

23.88 [.940] MAX

OBSOLETE	Y	1	10	4	3	9	226601-6
OBSOLETE	Y	1	11	4	3	9	226601-5
OBSOLETE	X	1	8	4	5	6	226601-4
	Y	1	8	4	3	9	226601-3
OBSOLETE	Y	1	8	4	3	7	226601-2
OBSOLETE	X	1	8	2	5	6	226601-1

VIEW

SHELL

DIELECTRIC

CONTACT

PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
M. SNEED
6-25-91

CHK
R. HENRY
6-25-91

APVD
-

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=226601

RESTRICTED TO
-

SCALE
4:1

SHEET
1 OF 1

REV
H1

tyco
Electronics

Tyco Electronics Corporation
Harrisburg, PA 17105-3608

AMP 1471-9 REV 31MAR2000