

Type 2 surge protection replacement module - VAL-SQ SP 80-347/600Y/ FM - 2804102

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Surge protection device for 347/600 V AC Wye configurations. Uses a compact, NEMA rated enclosure that connects easily to an existing enclosure. Hybrid Sine Wave Tracking provides 80 kA surge protection.

Product Description

Surge protection device for 347/600 V AC Wye configurations with 80 kA protection

Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	3,040.000 g
Custom tariff number	85363010
Country of origin	United States

Technical data

Dimensions

Height	79 mm
Width	250 mm
Depth	122 mm

Ambient conditions

Degree of protection	IP40 / NEMA 1
Ambient temperature (operation)	-40 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	3658 m

General

NEMA power supply system	347/600 V Wye
Mounting type	3/4 inch NPT male
Type	Parallel hybrid
Surge protection fault message	Phase LEDs
	Audible alarm

Type 2 surge protection replacement module - VAL-SQ SP 80-347/600Y/ FM - 2804102

Technical data

General

	Remote indication contact
Direction of action	3L-N & N-GND

Protective circuit

IEC test classification	I
Maximum continuous operating voltage U_c	420 V
Response time t_A	< 1 ns

Connection, protective circuit

Connection method	#10 AWG/5.26 mm ² wires (24 in./61 cm long)
Connection technology	4-wire + Gnd
Conductor cross section AWG min.	10
Conductor cross section AWG max.	10

Remote indication contact

Connection method	#24 AWG/0.205 mm ² wires (24 in./61 cm long)
-------------------	---

Standards and Regulations

Standards/regulations	UL 1449 2 nd edition, February 2007
	UL 1283
	IEEE C62.41
	IEEE C62.45


NEMA / UL data

UL type	type 2
Maximum Surge Current per Phase	80 kA
Short-circuit current rating (SCCR)	22 kA
Maximum Circuit Breaker	30 A

Drawings

Type 2 surge protection replacement module - VAL-SQ SP 80-347/600Y/
FM - 2804102

Circuit diagram



Classifications

eCl@ss

eCl@ss 4.0	27140201
eCl@ss 4.1	27130801
eCl@ss 5.0	27130801
eCl@ss 5.1	27130801
eCl@ss 6.0	27130805
eCl@ss 8.0	27130802
eCl@ss 9.0	27130802

ETIM

ETIM 2.0	EC000941
ETIM 3.0	EC000941
ETIM 4.0	EC000381
ETIM 5.0	EC000381

UNSPSC

UNSPSC 6.01	30212010
UNSPSC 7.0901	39121610
UNSPSC 11	39121610
UNSPSC 12.01	39121610



Type 2 surge protection replacement module - VAL-SQ SP 80-347/600Y/ FM - 2804102

Classifications

UNSPSC

UNSPSC 13.2	39121620
-------------	----------