



JIANGSU CHANGJIANG ELECTRONICS TECHNOLOGY CO., LTD

TO-126 Plastic-Encapsulate Transistors

D882 TRANSISTOR (NPN)

FEATURES

Power dissipation

P_{CM} : 1.25 W ($T_{amb}=25$)

Collector current

I_{CM} : 3 A

Collector-base voltage

$V_{(BR)CBO}$: 40 V

Operating and storage junction temperature range

T_J , T_{stg} : -55 to +150

TO—126

1. EMITTER

2.COLLECTOR

3.BASE

1 2 3


ELECTRICAL CHARACTERISTICS ($T_{amb}=25$ unless otherwise specified)

Parameter	Symbol	Test conditions	MIN	TYP	MAX	UNIT
Collector-base breakdown voltage	$V_{(BR)CBO}$	$I_C=100\mu A$, $I_E=0$	40			V
Collector-emitter breakdown voltage	$V_{(BR)CEO}$	$I_C=10mA$, $I_B=0$	30			V
Emitter-base breakdown voltage	$V_{(BR)EBO}$	$I_E=100\mu A$, $I_C=0$	6			V
Collector cut-off current	I_{CBO}	$V_{CB}=40V$, $I_E=0$			1	μA
Collector cut-off current	I_{CEO}	$V_{CE}=30V$, $I_B=0$			10	μA
Emitter cut-off current	I_{EBO}	$V_{EB}=6V$, $I_C=0$			1	μA
DC current gain	$h_{FE(1)}$	$V_{CE}=2V$, $I_C=1A$	60		400	
	$h_{FE(2)}$	$V_{CE}=2V$, $I_C=100mA$	32			
Collector-emitter saturation voltage	$V_{CE(sat)}$	$I_C=2A$, $I_B=0.2A$			0.5	V
Base-emitter saturation voltage	$V_{BE(sat)}$	$I_C=2A$, $I_B=0.2A$			1.5	V
Transition frequency	f_T	$V_{CE}=5V$, $I_C=0.1mA$ $f=10MHz$	50			MHz

CLASSIFICATION OF $h_{FE(1)}$

Rank	R	O	Y	GR
Range	60-120	100-200	160-320	200-400

TO-126 PACKAGE OUTLINE DIMENSIONS



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	2.500	2.900	0.098	0.114
A1	1.100	1.500	0.043	0.059
b	0.660	0.860	0.026	0.034
b1	1.170	1.370	0.046	0.054
c	0.450	0.600	0.018	0.024
D	7.400	7.800	0.291	0.307
E	10.600	11.000	0.417	0.433
e	2.290TYP		0.090TYP	
e1	4.480	4.680	0.176	0.184
L	15.300	15.700	0.602	0.618
L1	2.100	2.300	0.083	0.091
P	3.900	4.100	0.154	0.161
ϕ	3.000	3.200	0.118	0.126