


1.5 AMP LOW DROPOUT POSITIVE ADJUSTABLE REGULATOR APPROVED TO DESC DRAWING 5962-89981



Three Terminal, Positive Adjustable Low Dropout Voltage Regulator In Hermetic Packages

FEATURES

- Similar To Industry Standard LT1086
- Approved To DESC Standardized Military Drawing Number 5962-89981
- Adjustable Output Voltage
- Built In Thermal Overload Protection
- Short Circuit Current Limiting
- Maximum Output Voltage Tolerance is Guaranteed To $\pm 1\%$
- Guaranteed Dropout Voltage At Multiple Current Levels
- TO-257 Available in Isolated and Non-Isolated Packages

DESCRIPTION

This three terminal positive adjustable voltage regulator is designed to provide 1.5A with higher efficiency than conventional voltage regulators. This device is designed to operate to 1 Volt input to output differential and the dropout voltage is specified as a function of load current. Supplied in easy-to-use hermetic TO-257, TO-3 and TO-39 packages, this device is ideally suited for Military applications where small size and high reliability is required.

ABSOLUTE MAXIMUM RATINGS @ 25°C

Power Dissipation (P_d)	Internally Limited
Input - Output Voltage Differential	35 V
Operating Junction Temperature Range	- 55°C to + 150°C
Storage Temperature Range	- 65°C to + 150°C
Lead Temperature (Soldering 10 seconds)	300°C
Thermal Resistance:	
θ_{JC} (TO-257, Isolated)	4.2°C/W
θ_{JA}	42°C/W
θ_{JC} (TO-3)	3.0°C/W
θ_{JA} (TO-3)	35°C/W
θ_{JC} (TO-39)	40°C/W
θ_{JA} (TO-39)	140°C/W
Maximum Output Current	1.5 A
Recommended Operating Conditions:	
Output Voltage Range	.33V to 15 V
Ambient Operating Temperature Range (T_A)	- 55°C to + 125°C
Input Voltage Range	5V to 25 V

3.3

OM1860STM OM1860NKM OM1860NHM


ELECTRICAL CHARACTERISTICS -55°C ≤ T_A ≤ 125°C (unless otherwise specified)

Parameter	Symbol	Test Conditions	Min.	Max.	Unit
Reference Voltage	V _{REF}	V _{IN} - V _{OUT} = 3.0 V, T _A = 25° C I _{OUT} = 10 mA	1.238	1.262	V
		1.5 V ≤ V _{IN} - V _{OUT} ≤ 25 V, 10 mA ≤ I _{OUT} ≤ 1.0 A	• 1.220	1.270	V
Line Regulation (Note 1)	$\frac{\Delta V_{OUT}}{\Delta V_{IN}}$	1.5 V ≤ V _{IN} - V _{OUT} ≤ 15 V, I _{OUT} = 10 mA, T _A = 25° C		0.2	%
		15 V ≤ V _{IN} - V _{OUT} ≤ 35 V, I _{OUT} = 10 mA	•	0.5	%
Load Regulation (Note 1)	$\frac{\Delta V_{OUT}}{\Delta I_{OUT}}$	V _{IN} - V _{OUT} = 3.0 V, T _A = 25° C 10 mA ≤ I _{OUT} ≤ 1.0 A		0.8	%
			•	1.0	%
Dropout Voltage	V _{DO}	I _{OUT} = 1.0 A, ΔV _{REF} = 1%	•	1.5	V
Thermal Regulation	-	30 ms pulse, T _A = +25° C		0.04	%/W
Ripple Rejection	$\frac{\Delta V_{IN}}{\Delta V_{OUT}}$	f = 120 Hz, C _{Adj} = 25 μF, C _{OUT} = 25 μF (tantalum), I _{OUT} = 1.0 A, V _{IN} - V _{OUT} = 3.0 V	•	60	dB
Adjust Pin Current	I _{Adj}	1.5 V ≤ V _{IN} - V _{OUT} ≤ 25 V, 10 mA ≤ I _{OUT} ≤ 1.0 A	•	120	μA
Adjust Pin Current Change	ΔI _{Adj}	1.5 V ≤ V _{IN} - V _{OUT} ≤ 25 V, 10 mA ≤ I _{OUT} ≤ 1.0 A	•	5.0	μA
Minimum Load Current	I _{Min}	V _{IN} - V _{OUT} = 25 V	•	10	mA
Current Limit	I _{Lim}	V _{IN} - V _{OUT} ≤ 5.0 V	•	1.5	A
		V _{IN} - V _{OUT} = 25 V	•	0.075	A
Temperature Stability (Note 2)	$\frac{\Delta V_{OUT}}{\Delta T}$	-55° C ≤ T _J ≤ +125° C	•	1.5	%
Long Term Stability (Note 2)	$\frac{\Delta V_{OUT}}{\Delta T}$	T _A = +125° C, t = 1000 hrs		1.0	%


Notes:

- Line and Load Regulation are measured at a constant junction temperature using a low duty cycle pulse technique. Although power dissipation is internally limited, regulation is guaranteed up to the maximum power dissipation of 15 W. Power dissipation is determined by the input/output differential voltage and the output current. Guaranteed maximum power dissipation will not be available over the full input/output voltage range.
- Guaranteed by design, characterization or correlation to other tested parameters.
- The • denotes the specifications which apply over the full operating temperature range.


3.3




LOAD REGULATION




SHORT CIRCUIT CURRENT




ADJUSTMENT PIN CURRENT




RIPPLE REJECTION VS. CURRENT



TEMPERATURE STABILITY




MINIMUM OPERATING CURRENT



TYPICAL APPLICATIONS


1.2V - 15V Adjustable Regulator



*NEEDED IF DEVICE IS FAR FROM FILTER CAPACITORS


$$^{\dagger} V_{OUT}=1.25V\left(1+\frac{R_2}{R_1}\right)$$

5V Regulator with Shutdown



MECHANICAL OUTLINE

OM1860STM




PIN OUT

- 1 Adjust
- 2 V_{OUT}
- 3 V_{IN}
- 4 Isolated

NOTES

- Case is metal/hermetically sealed
- Isolated Tab


MECHANICAL OUTLINE TO-3 OM1860NKM



PIN OUT

- | | |
|------|-----------|
| 1 | Adjust |
| 2 | V_{IN} |
| Case | V_{OUT} |

MECHANICAL OUTLINE TO-39



OM1860NHM TO-39

- | | |
|-------|--------|
| Pin 1 | Adjust |
| Pin 2 | Input |
| Case | Output |

