


RECOMMENDED PANEL MOUNTING


PANEL THICKNESS	X
0.75-1.25	19.2
1.25-2.00	19.4
2.00-3.00	19.6






SWITCH FUNCTION	
POS. 1	POS. 2
OFF	ON
OFF	1-2

SPST

RED ACTUATOR

9.30
[.366 in]2.00
[.079 in].80
[.031 in]10.00
[.394 in]

BLACK HOUSING

4.75
[.187 in]10.90
[.429 in]21.00
[.827 in]15.00
[.591 in]14.80
[.583 in]17.90
[.705 in]8.20
[.323 in]19.20
[.756 in]6.50
[.256 in]13.00
[.512 in]

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=± 0.4
X.XX=± 0.25
3. MECHANICAL LIFE: 30,000
4. ELECTRICAL LIFE: 10,000
5. CONTACT RESISTANCE: 20 mΩ
6. INSULATION RESISTANCE: 1000 MΩ
7. OPERATING TEMPERATURE: -10°C TO 55°C
8. CONTACT RATING: 15A-250 VAC, 125VAC, UL APPROVED
10A 250VAC, VDE APPROVED
9. DIELECTRIC STRENGTH: 1500V FOR 1 MIN
10. LAMP: NEON, 125VAC
11. ▲ DENOTES CRITICAL PARAMETER
12. 2002/95/EC (RoHS) COMPLIANT.
13. OPERATING FORCE: 750±100grams



D	21294	MODEL HAD FOUR TERMINALS	11/5/13	EBP
C	17722	ADDED NOTE # 13	9/27/07	BF
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE PB1973CBLKRILEF1

SCALE 1.5

DATE 9/27/2007

DR BF

DWG M197301

REV D