



PRODUCT NUMBER

20020619-XXXXXXLF

20020619-□□□□A0□LF

PITCH
M : 7.62 mm

POLES

02: 2 POLES
03: 3 POLES
04: 4 POLES
:

16: 16 POLES

LF : DENOTED ROHS COMPATIBLE

1 : STANDARD PRODUCT
W/ BOX PACKING

HOUSING CODE

CODE	COLOR	AVAILABILITY
1	GREEN(RAL 6018/T)	STANDARD
2	BLACK	ON REQUEST ONLY
3	GREY(RAL 7004/P)	ON REQUEST ONLY
4	BLUE(RAL 5015/A)	ON REQUEST ONLY

PROPERTY TABLE

FCI SERIES NAME	07-762
PITCH (mm)	7.62
VOLTAGE RATING (VAC)	300
CURRENT RATING (A)	32
WITHSTANDING VOLTAGE (kV)	1.6
OPERATING TEMP. (°C)	-40~+115
SOLDERING TEMP. (°C)	250±10 (5 sec.)
POLES AVAILABLE	02~16
SAFETY CERTIFICATE	

NOTES:

1. MATERIALS

1-1 HOUSING: THERMALPLASTIC RESIN, UL 94V-0 RATED.

1-2 TERMINAL: COPPER ALLOY, TIN PLATED.

2. PRODUCTION SPECIFICATION REFER TO FCI GS-12-625.

3. BOXED PACKAGING.

DETAILED PRODUCT PACKING SPECIFICATION REFER TO FCI GS-14-1394.




4. FCI, SAFETY CERTIFICATE LOGO AND SERIES NAME TO BE SHOWN ON PRODUCT SURFACE.

5. THE PRODUCTS WHERE THE PART NUMBER END IN "LF" MEET THE EUROPEAN UNION DIRECTIVE AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

6. RECOMENDED SOLDERING PROCESS BY WAVE SOLDER.

mat'l. code				surface ASME Y14.5		tolerance ASME Y14.5		projection 		product family TERMINAL BLOCK																																																																																																																																																																																																																																																																																																																																																																																																																																																																																								
ltr	ecn no	dr	date	tolerances unless otherwise specified										title																																																																																																																																																																																																																																																																																																																																																																																																																																																																																				
A	T10-0062	WL	050710	angles		X.±0.5[.020]					TERMINAL BLOCK																																																																																																																																																																																																																																																																																																																																																																																																																																																																																							
B	T10-0155	WL	093010	X.X±0.3[.012]				PLUGGABLE, SOCKET, POWER, R/A																																																																																																																																																																																																																																																																																																																																																																																																																																																																																										
C	T10-0187	WL	121410	X'±1"	X.XX±0.1[.004]				scale	W/FLANGE																																																																																																																																																																																																																																																																																																																																																																																																																																																																																								
D	T-004860	WL	080411	dr	WENDY CHEN	042610					dwg no	sheet 1 of 2					size																																																																																																																																																																																																																																																																																																																																																																																																																																																																																	
				enrg	JASON HSU	042610					20020619																																																																																																																																																																																																																																																																																																																																																																																																																																																																																							
				chr	GARY HSIEH	042610					A.																																																																																																																																																																																																																																																																																																																																																																																																																																																																																							
				appd	JOSEPH HSIA	042610					type	CUSTOMER Drawing																																																																																																																																																																																																																																																																																																																																																																																																																																																																																						
sheet index	revision	sheet	D	D																																																																																																																																																																																																																																																																																																																																																																																																																																																																																														

PRODUCT NUMBER	SERIES NAME	PITCH
20020619-MXXXXXXLF	07-762	7.62 mm



N = Number of poles


$$\text{Dim A} = (N-1) \times 7.62 \left[\begin{smallmatrix} .300 \\ .900 \end{smallmatrix} \right] + 22.86 \left[\begin{smallmatrix} .300 \\ .900 \end{smallmatrix} \right]$$

$$\text{Dim B} = (N-1) \times 7.62 \left[\begin{smallmatrix} .300 \\ .900 \end{smallmatrix} \right]$$

$$\text{Dim C} = (N+1) \times 7.62 \left[\begin{smallmatrix} .300 \\ .900 \end{smallmatrix} \right]$$

$$\text{Dim D} = (N+1) \times 7.62 \left[\begin{smallmatrix} .300 \\ .900 \end{smallmatrix} \right]$$

Poles	Dim A	Dim B	Dim C	Dim D
2-4p	±0.15	±0.06		
5-8p	±0.25	±0.10		
9-12p	±0.35	±0.14		
13-16p	±0.40	±0.16		



mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection 	product family TERMINAL BLOCK	
ltr	ecn no	dr	date	tolerances unless otherwise specified			title	
D				angles	linear	MM [INCH]	TERMINAL BLOCK PLUGGABLE, SOCKET, POWER, R/A W/FLANGE	
				X±0.5	X.X±0.3	scale	dwg no	
				X'±1"	X.XX±0.1		sheet 2 of 2	
				dr	WENDY CHEN	042610	20020619	
				enr	JASON HSU	042610	A4	
				chr	GARY HSIEH	042610	type	
				appd	JOSEPH HSIA	042610	CUSTOMER Drawing	
sheet index	revision sheet							