



- 1
- 2
- 3
- 4
- 5
- 6
- 7
- CONNECTOR IS DESIGNED FOR FLAT RIBBON CABLE ON 1.27 CENTERS.
FOR CABLE REQUIREMENTS SEE TE APPLICATION SPECIFICATION 114-19022.
- THESE RECEPTACLE CONNECTORS MATE WITH 0.64±0.05mm SQUARE OR ROUND POSTS ON 2.54mm GRID.
- MARK INDICATING FIRST CABLE POSITION REFERRING TO CONTACT POSITION.
- THERE IS NO POLARIZATION-SLOT AT THIS END IN 6, 10 AND 14 POS CONNECTORS.
- THESE CONNECTORS CAN BE USED IN CONJUNCTION WITH STRAIN-RELIEF COVERS OF PARTNR: 100103.
- THERE IS NO POLARIZATION-SLOT AT THIS END IN 6 POS CONNECTORS.
- PRODUCT SPECIFICATION 108-19033.



③ RECEPTACLE CONTACT	PHOSPHORBRONZE Cu Sn6	AT CONTACT-PLACE: 0,8μ GOLD AT WIRING END: 2,5μ TIN ENTIRE UNDERCOATING:1,27μ NICKEL
② COVER	THERMOPLASTIC POLYESTER GF UL 94 -V0	GREY RAL 7032 ONLY FOR REF.
① HOUSING		
COMPONENT NAME	MATERIAL	PLATING / COLOUR

	500	85,9	64	32	6-215915-4	D
	500	80,8	60	30	6-215915-0	D
	500	68,1	50	25	5-215915-0	D
OBSOLETE	—1500	60,5	44	22	4-215915-4	D
	750	55,4	40	20	4-215915-0	D
	1500	47,8	34	17	3-215915-4	D
OBSOLETE	—1500	42,7	30	15	3-215915-0	D
	1500	37,6	26	13	2-215915-6	D
	1500	30,0	20	10	2-215915-0	D
	1500	24,9	16	8	1-215915-6	D
	1500	22,4	14	7	1-215915-4	D
	1500	17,3	10	5	1-215915-0	D
OBSOLETE	—1500	14,8	8	4	0-215915-8	B
	1500	12,2	6	3	0-215915-6	D
OBSOLETE	—1500	9,7	4	2	0-215915-4	B
	QUANTITY PER REEL	DIM."C"	"B" CABLE POS.	"A" DUAL POS.	PARTNUMBER ④	PART REV.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.HOGEVEEN 02-02-88	TE Connectivity			
DIMENSIONS: mm		CHK R.VERSTIJNEN 03-02-88	NAME			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD L.V.SOEST 03-02-88	AMP-LATCH MIL-TYPE RECEPT. CONN. ASS'Y 14,9 PRE-ASSEMBLED 0.8μm SELECTIVE GOLDPLATE ④			
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH		PRODUCT SPEC — APPLICATION SPEC — WEIGHT —	SIZE A2	CAGE CODE 00779	DRAWING NO C-215915	RESTRICTED TO —
CUSTOMER DRAWING			SCALE 5:1	SHEET 1 of 1	REV E	