




REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN.	APVD.
	A8	REVISED PER ECO-15-003872	25MAR2015	DD	DS


- 1 ACCEPTS #3 SELF TAPPING THREAD FORMING SCREWS OR METRIC EQUIVALENT. DRIVE TO 0.6-0.8 N-m.
- 2 DATE CODE TO BE BRANDED IN THIS LOCATION PER TE SPEC 102-60. USE 5 DIGIT CODE: FIRST 2 DIGITS = YEAR, SECOND 2 DIGITS = WEEK, LAST DIGIT = DAY.
- 3 MATERIALS: HEADER HOUSING - GLASS FILLED PBT
PINS - TIN OR GOLD PLATED BRASS
GASKET - SILICONE
- 4 HOUSING COLORS ARE MECHANICALLY KEYED TO MATE ONLY WITH IDENTICALLY COLORED PLUG ASSEMBLIES.
5. HEADER MATES TO PLUG ASSEMBLY 776273 WHICH USES REELED TERMINAL 770520 OR LOOSE PIECE TERMINAL 770854

776262-1 & 1-776262-1 SHOWN


BLUE	DURAGOLD	1-776262-5
GRAY	DURAGOLD	1-776262-4
NATURAL	DURAGOLD	1-776262-2
BLACK	DURAGOLD	1-776262-1
BLUE	TIN	776262-5
GRAY	TIN	776262-4
NATURAL	TIN	776262-2
BLACK	TIN	776262-1
HEADER COLOR 4		PLATING
		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. STRAUSSER 03MAR2010	TE Connectivity ASSEMBLY, HEADER, 14 POSITION, VERTICAL, AMPSEAL WITH FLANGE SEAL	
		CHK D. STRAUSSER 22MAR2010		
DIMENSIONS:		APVD D. STRAUSSER 27APR2010	NAME	
mm		PRODUCT SPEC	SIZE	
		108-1329	CAGE CODE	
		APPLICATION SPEC	DRAWING NO	
		114-16016	RESTRICTED TO	
MATERIAL		WEIGHT	A100779C=776262	
		CUSTOMER DRAWING	SCALE 4:1	
			SHEET 1 OF 2	
			REV A8	


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-




RECOMMENDED P.C. BOARD LAYOUT
FOR 1.57 THICK P.C. BOARD




RECOMMENDED MOUNTING HOLE LAYOUT
FOR 5.0 MAX THICK PANEL




SECTION A-A
OPTIONAL CONSTRUCTION IF PANEL
THICKNESS IS GREATER THAN 2.0




SECTION A-A
OPTIONAL CONSTRUCTION IF PANEL
THICKNESS IS GREATER THAN 2.0





776262-2 & 1-776262-2
KEY LOCATION
SCALE 2:1



776262-4 & 1-776262-4
KEY LOCATION
SCALE 2:1



776262-5 & 1-776262-5
KEY LOCATION
SCALE 2:1



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. STRAUSSER CHK D. STRAUSSER APVD D. STRAUSSER	03MAR2010 22MAR2010 27APR2010	TE Connectivity	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
mm		0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.13 3 PLC ±0.13 4 PLC ±0.13 ANGLES ±4° FINISH		PRODUCT SPEC 108-1329 APPLICATION SPEC 114-16016	
MATERIAL		WEIGHT		RESTRICTED TO	
-		-		A100779C=776262	
-		CUSTOMER DRAWING		SCALE 2:1 SHEET 2 OF 2 REV A8	