



MARKETING SALES DRAWING
 DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
 DIMENSIONS IN METRIC - []

Electrical Testing
 per Tusonix standard
 test plans and Mil-Std-202
 Test Methods.



NOTES:

1. Operating temperature range: -55°C to +125°C.
2. Gold plated case and lead.
3. Epoxy sealed on opposite end from glass seal.
4. Max. recommended soldering temperature: 260°C.
See installation recommendations.
5. Recommended mounting hole: .135 [3.43] dia.
6. Solder preform available for mounting.
7. Tusonix Standard part number: 4300-024.
Tusonix RoHS compliant part number: 4300-024 LF.
Customer must specify Standard or RoHS part number when ordering.
8. RoHS compliant part marked with additional dark green dot for identification.

Cx (pF)		TOL.	DC WORKING VOLTAGE		DC CURRENT (AMPS)	DWV (VDC)	I.R. MIN. @ 100 (VDC.)	MIN. NO LOAD INSERTION LOSS (dB) @ 25° C PER MIL-STD-220					COLOR CODE
			85°C	125°C				1 MHz	10 MHz	100 MHz	1GHz	10 GHz	
5,000		GMV	150	100	5	250	10 G	---	15	30	40	50	YELLOW

REVISION RECORD	Original Release	0	YELLOW WAS BLUE-BLUE 15,30,40,50 WERE 35,45,70& -- L.E. 06-04-02	1	ADDED NOTES 7 & 8. S.M. 05-23-05	2	TUSONIX TUCSON, ARIZONA	--TOLERANCES-- Unless Otherwise Specified	Title SOLDER MOUNT EMI FILTER		
	C.O. 20020213-4-01					DECIMAL ± NOTED					
						ANGLES ± 		Drawn	S.M. 02-14-02	Scale	5 X
	20020604-1-02							Approved	T.C. 02-14-02		
	20050511-2-25							A	4300-024		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix:](#)

[4300-024LF](#)