






LOC		DIST		REVISIONS				
AD	00	P	LYR	DESCRIPTION	DATE	DWN	APVD	
			B	REVISED PER ECO-11-025276	22DEC11	KH	DY	



- 1 MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- 2 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.
- 3 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD
ON PCB TAILS, NICKEL OVERALL.



UNGUIDED
BACKPLANE HOLE PATTERN
(CONNECTOR SIDE)



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. K. SHOBER 21DEC2010	 TE Connectivity	
DIMENSIONS:		CHK J. EABY 21DEC2010		
mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 9 PLC ±.01 2 PLC ±0.25 2 PLC ±0.13 3 PLC ±. 4 PLC ±. ANGLES ±. FINISH SEE TABLE	APVD J. EABY 21DEC2010	NAME IMPACT, 3 PAIR, 10 COLUMN, HEADER
			PRODUCT SPEC -	UNGUIDED, RIGHT END WALL SIGNAL MODULE, 0.39 PTH
			APPLICATION SPEC	SIZE CAGE CODE DRAWING NO
			WEIGHT -	A100779C=2007791
MATERIAL		CUSTOMER DRAWING	SCALE 6:1	SHEET 1 OF 2
			REV B	

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		-		SEE SHEET 1	-	-	-

	5.5	2007791-6
	4.9	2007791-5
	4.5	2007791-4
	5.5	2007791-3
	4.9	2007791-2
	4.5	2007791-1
FINISH	DIM M	PART NUMBER

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. K. SHOBER 21DEC2010			
CHK J. EABY 21DEC2010		NAME			
APVD J. EABY 21DEC2010		PRODUCT SPEC		IMPACT, 3 PAIR, 10 COLUMN, HEADER	
APPLICATION SPEC		UNGUIDED, RIGHT END WALL		SIGNAL MODULE, 0.39 PTH	
SIZE		CAGE CODE		DRAWING NO	
A100779		C=2007791		RESTRICTED TO	
WEIGHT		CUSTOMER DRAWING		SCALE 5:1	
SHEET 2		OF 2		REV B	