





TYPE DIM.	POS. 4	POS. 6		POS. 8		
	4 CKTS.	4 CKTS.	6 CKTS.	4 CKTS.	6 CKTS.	8 CKTS.
A	(11.18) / .440	(13.21) / .520	(13.21) / .520	(15.24) / .600	(15.24) / .600	(15.24) / .600
C $(\pm 0.05) / \pm .002$	(7.62) / .300	(10.16) / .400	(10.16) / .400	(11.43) / .450	(11.43) / .450	(11.43) / .450
B $(\pm 0.05) / \pm .002$	(3.81) / .150	(3.81) / .150	(6.35) / .250	(3.81) / .150	(6.35) / .250	(8.89) / .350


P.C.B. MOUNTING PATTERNS - SEE FROM COMPONENT SIDE

FOR SMT JACK TYPE (SURFACE MOUNT)



FOR ALL VERSIONS, CIRCUIT 1 ALWAYS ON THE LEFT SIDE

FOR STANDARD JACK TYPE (THROUGH HOLE)



NOTE:

FOR CONVECTION SOLDERING: DIA 3.25±0.05 / .128±.002
FOR WAVE SOLDERING: DIA 3.20±0.10 / .126±.004

EC NO: MG2005-0106 DRWN: MARTIN 2004/10/12 CHKD: FCARABET 2004/10/12 APPR: KNOLLER 2004/10/13	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION
		4 PLACES	± ---	± ---	DRAWN BY FB	DATE 2004/09/25	TITLE R/A LOW PROFILE JACK PC JACK 4,6,8 CKT SIZE SMT AND STANDARD VERSION	
REV	DESCRIPTION	3 PLACES	± ---	± .006	CHECKED BY	DATE	MOLEX INCORPORATED	SHEET NO. 3 OF 9
		2 PLACES	± 0.15	± .010	APPROVED BY	DATE		
REV	DESCRIPTION	1 PLACE	± 0.25	± ---	MATERIAL NO.	DOCUMENT NO.	SDA-95001	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION
		ANGULAR	± ---°	± ---°	SEE CHART SHEETS 4.5&6	SIZE A3		

STANDARD PACKAGING OPEN TRAY ,SEE PACKAGING SPEC PK95001 SHEET 1

PART NO FOR JACK ASSEMBLY

STANDARD VERSION

SPECIAL VERSION HIGH TEMPERATURE

HOUSING SIZE	LOADED CONTACTS	PLATING	POLYESTER FIBER GLASS FILED 94V0,COLOR BLACK.								POLYAMIDE FIBER GLASS FILLED COLOR BLACK			
			NO KEY	TOOLED	KEY	TOOLED		TOOLED		TOOLED	NO KEY	TOOLED	KEY	TOOLED
			NOT RIBBED		NOT RIBBED						NOT RIBBED		NOT RIBBED	
4	4	2	9500I-244I	X	9500I-2442						9500I-844I	X		
6	4	2	9500I-264I	X	9500I-2642						9500I-864I	X		
6	6	2	9500I-266I	X	9500I-2662						9500I-866I	X		
8	4	2	9500I-284I		9500I-2842									
8	6	2	9500I-286I	X	9500I-2862									
8	8	2	9500I-288I	X	9500I-2882	X					9500I-888I	X		

EC NO: MG2005-0106 DRWN:TMARTIN 2004/10/12 CHKD:FCARABET 2004/10/12 APPR:KNOLLER 2004/10/13		QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE MM ONLY	SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION
4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± --- ± --- 1 PLACE ± --- ± --- ANGULAR ± ---°		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWN BY DP DATE 1989/06/01	CHECKED BY FB DATE 1989/06/01	TITLE LOW PROFILE R/A JACK STANDARD AND SMT VERSION STABDARD OPEN TRAY VERS	
MATERIAL NO. SEE CHART		APPROVED BY JB DATE 1989/06/01		DOCUMENT NO. SDA-95001		SHEET NO. 4 OF 9	
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							