


REV.	DATE	DESCRIPTION
NC	09/19/02	INITIAL RELEASE



1. CRIMPED FERRULE
HEX CRIMP SIZE .213"
2. CONTACT PIN TO SOLDER

				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS	APPROVALS	DATE	Amphenol - Connex CONNECTOR CORPORATION				
8					DIMENSIONS IN [] ARE IN INCHES FOR CUSTOMER REFERENCE ONLY	DRAWN					G.R.S.
7				UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .XXX = ± 0.005" .XX = ± 0.010" .X = ± 0.020"		CHECKED		TITLE SMA CRIMP JACK (FOR TIMES LMR-200)			
6					ISSUED						
5					DO NOT SCALE DRAWING			SIZE	FSCM NO.	DWG. NO.	REV.
4	FERRULE	COPPER	GOLD			A	99001	132236.DWG	NC		
3	CONTACT PIN	BER. COPPER	GOLD								
2	INSULATOR	TEFLON	NATURAL								
1	BODY	BRASS	GOLD								
	DESCRIPTION	MATERIAL	FINISH				SCALE	NA	PART NO.	SHEET	1 OF 1