


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C3	REVISED PER ECO-16-009052	24MAY2017	DD	MT

D

C

B

A



1. FINISH : PLATE 0.000100-0.000200 THK TIN IN LOCALIZED TIN PLATE AREA, ALL OVER 0.000030-0.000070 THK NICKEL.
2. CONTACT WILL BE LUBED WITH LUBRICANT PER P/N 22014-4.
3. WIRE RANGE: 18-14 AWG SXL, GXL, AND TXL WIRE WITH INSL DIAMETERS OF 0.077-0.155 INCHES.
4. PLATE 0.000030 MIN THK SELECT GOLD IN LOCALIZED PLATE AREA.
5. PLATE .000100-.000200 THK TIN PER 112-65-1 IN LOCALIZED TIN PLATE AREA. ALL OVER .000040-.000080 THK NICKEL PER 112-25-2

5	638112-3
1 4	638112-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JL MCNEAL 9-30-97	TE Connectivity			
DIMENSIONS: INCHES		CHK —				
		APVD W. LONG 10-1-97	NAME			
		PRODUCT SPEC	PIN CONTACT, WIRE-TO-WIRE			
		APPLICATION SPEC	—			
		FINISH	—			
MATERIAL BODY: 0.014 THK COPPER ALLOY		WEIGHT 0.000000	SIZE A2	CAGE CODE 00779	DRAWING NO C=638112	RESTRICTED TO —
		CUSTOMER DRAWING	SCALE 10:1	SHEET 1 of 1	REV C3	