


DO NOT
SCALE FROM
THIS PRINTDESIGNED AND DIMENSIONED
IN MILLIMETERS [INCHES]

TABLE 1

No. OF POS.	
-005, -010, -011, -013, -020, -025, -030, -035	0.10 [0.004]
-040, -049, -050, -060	0.12 [0.005]
-070, -075, -100	0.15 [0.006]

TABLE 5

POSITION	"A"	"B"	"C"	"D"	"H"
-005	10.00 [0.394]	8.20 [0.323]	3.200 [0.1260]	6.80 [0.268]	3.00 [0.128]
-010	14.00 [0.551]	12.20 [0.480]	7.200 [0.2835]	10.80 [0.425]	5.00 [0.197]
-011	14.80 [0.583]	13.00 [0.512]	8.000 [0.3150]	11.60 [0.457]	5.40 [0.212]
-013	16.40 [0.648]	14.80 [0.575]	9.600 [0.3780]	13.20 [0.520]	6.20 [0.244]
-020	22.00 [0.866]	20.20 [0.796]	15.200 [0.5984]	18.80 [0.740]	9.00 [0.354]
-025	26.00 [1.024]	24.20 [0.953]	19.200 [0.7559]	22.80 [0.898]	11.00 [0.433]
-030	30.00 [1.181]	28.20 [1.110]	23.200 [0.9134]	26.80 [0.805]	13.00 [0.512]
-035	34.00 [1.339]	32.20 [1.268]	27.200 [0.10709]	30.80 [0.1213]	15.00 [0.590]
-040	38.00 [1.496]	36.20 [1.425]	31.200 [0.12283]	34.80 [0.1370]	17.00 [0.669]
-049	45.20 [1.780]	43.40 [1.709]	38.400 [0.15118]	42.00 [0.1654]	20.60 [0.811]
-050	46.00 [1.811]	44.20 [1.740]	39.20 [0.1543]	42.80 [0.1685]	21.00 [0.827]
-060	54.00 [2.126]	52.20 [2.055]	47.20 [0.1858]	50.80 [0.2000]	25.00 [0.984]
-070	62.00 [2.441]	60.20 [2.370]	55.20 [0.2173]	58.80 [0.2315]	29.00 [1.142]
-075	66.00 [2.598]	64.20 [2.528]	59.20 [0.2331]	62.80 [0.2472]	31.00 [1.220]
-100	86.00 [3.386]	84.20 [3.315]	79.20 [0.3118]	82.80 [0.3260]	41.00 [1.614]

FIG 1
(ERM8-030-02.0-X-DV-XX SHOWN)
(SOME CENTER FEATURES REMOVED FOR CLARITY)

ERM8-XXX-XX.X-X-DV-XXXX-TR

No OF POSITIONS
(PER ROW)

-005, -010, -011, -013, -020, -025, -030,
-035, -040, -049, -050, -060, -070, -075, -100
(-100 AVAILABLE ON -09.0 LEAD STYLE ONLY
SEE NOTE 8)

AD

LEAD STYLE

-02.0 = 2mm
-05.0 = 5mm
-08.0 = 8mm
-09.0 = 9mm
***-15.0 = 15mm

PLATING SPECIFICATION

-L: 10 μ " LIGHT SELECTIVE GOLD
IN CONTACT AREA,
MATTE TIN ON TAIL
-S: 30 μ " SELECTIVE GOLD
IN CONTACT AREA,
MATTE TIN ON TAIL

ROW SPECIFICATION

-DV: DOUBLE VERTICAL

** = NOT RELEASED FOR PRODUCTION
*** = NOT TOOLED

TAPE & REEL
(STANDARD PACKAGING)
(SEE NOTES 4 & 7)

OPTIONS

- K: POLYIMIDE FILM PAD
(FOR -EGP & EGPS OPTIONS
USE K-DOT-157-250-005)
(FOR ALL OTHER OPTIONS USE K-500-300)
- DS: DIFFERENTIAL PAIR (HOT SWAP)
(AVAILABLE ONLY ON -05.0 LEAD STYLE)
(SEE TABLE 4 FOR POSITION AVAILABILITY)
- L: LATCHES
(AVAILABLE ONLY ON -05.0, -08.0, -09.0 &
***-15.0 LEAD STYLES. -L ON -08.0 & -09.0
NOT TOOLED)
(SEE TABLE FOR AVAILABILITY)
(NOT AVAILABLE WITH -EGP, -L2, -W, -EGP, -EGPS
OPTIONS)
- *** -L2: LATCHES WITH LONG WELD TAB
(AVAILABLE ONLY ON -05.0, -08.0 & -09.0
LEAD STYLES)(NOT AVAILABLE WITH -L, -E, -W,
-EGP AND -EGPS OPTIONS)
- *** -E: EXTENDED GUIDE POSTS, WITH LONG WELD TAB
(AVAILABLE ONLY ON -05.0, -08.0 & -09.0
LEAD STYLES, NOT AVAILABLE WITH -L OPTION,
SEE NOTE 6)
- *** -W: WELD TAB (AVAILABLE ONLY ON -05.0, -08.0 & -09.0
LEAD STYLES)
- EGP: EXTENDED GUIDE POSTS
(AVAILABLE ONLY ON -05.0 LEAD STYLE)
(NOT AVAILABLE WITH -L OPTION)
- EGPS: EXTENDED GUIDE POST SHIELD
(AVAILABLE ONLY ON -05.0 LEAD STYLE)
(NOT AVAILABLE WITH -L OPTION)
(-10, -20, -25, & -30 POSITIONS ONLY)

NOTES:

- (C) REPRESENTS A CRITICAL DIMENSION.
- BURR ALLOWANCE: 0.038 [0.0015] MAX.
- MINIMUM PUSHOUT FORCE: TERMINAL 2.22 N [0.5 LB.], WELD TAB 4.45 N [1 LB.]
- FOR QUANTITY UP TO 49 PIECES, NO LEADER, TRAILER, OR
EIA-481-D REEL WILL BE SUPPLIED. FOR QUANTITY OF 50-124
PIECES, NO LEADER OR TRAILER WILL BE SUPPLIED.
- "F" DIMENSION DOES NOT APPLY TO -EGP & -EGPS OPTION, SEE FIG. 5 & 6.
- NOTE DELETED.
- TR PACKAGING NOT AVAILABLE ON THE 100 POSITION.
- NOT AVAILABLE WITH -L, -L2, -E OR -W OPTIONS.

AD

TABLE 6

HEIGHT	"E"	"F"	"G"
-02.0	1.605 [0.0632]	5.965 [0.2348]	5.04 [0.198]
-05.0	4.605 [0.1813]	8.905 [0.3506]	7.98 [0.314]
-08.0	7.605 [0.2994]	11.905 [0.4687]	10.98 [0.432]
-09.0	8.605 [0.3411]	12.905 [0.5081]	11.98 [0.472]
***-15.0	14.605 [0.5750]	18.905 [0.7443]	17.98 [0.708]

(** = NOT TOOLED)

TABLE 8

OPTION	"N"
NONE	3.40 [0.134]
-W, -L, -L2, -EGP	4.90 [0.193]

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN
MILLIMETERS [INCHES].

TOLERANCES ARE:

DECIMALS ANGLES
X.X: ± 0.3 [0.01] 2°
X.XX: ± 0.13 [0.005]
X.XXX: ± 0.050 [0.0020]

MATERIAL: DO NOT SCALE DRAWING

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

SHEET SCALE: 2:1

INSULATOR: LCP, COLOR: BLACK

TERMINAL: PHOS BRONZE

LATCH: BeCu

SHIELD: PHOS BRONZE

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150

PHONE: 812-944-6733 FAX: 812-948-5047

e-Mail: info@SAMTEC.com code 55322




DESCRIPTION: 0.8MM EDGE RATE TERMINAL ASSEMBLY

DWG. NO.

ERM8-XXX-XX.X-X-DV-XXXX-TR



BY: KNOWLDEN 9/27/2005 SHEET 1 OF 6

REVISION AD



DETAIL 'R'
SCALE 4 : 1

BOTTOM VIEW
(ERM8-030-09.0-X-DV-XX SHOWN)
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)



SECTION "P"-P"





FIG 3
-DS WITH -L OR -L2 OPTIONS
(-DS AVAILABLE ON -05.0 LEADSTYLE ONLY)
(-L AVAILABLE ON -05.0, -08.0, -09.0 & ***-15.0 LEAD STYLES ONLY.
-L ON -08.0 & -09.0 NOT TOOLED)
(ERM8-025-05.0-X-DV-DS-L SHOWN)
(SAME AS FIG 1, EXCEPT AS SHOWN)
(SOME CENTER FEATURES REMOVED FOR CLARITY)

AD

TABLE 7				
POSITION	"J"	"K"	"L"	"M"
-005	13.00 [.512]	8.90 [.350]	10.00 [.394]	4.50 [.177]
-010	17.00 [.669]	12.90 [0.508]	14.00 [.551]	6.50 [.256]
-011	17.80 [.701]	13.70 [0.539]	14.80 [.583]	6.90 [.271]
-013	19.40 [.764]	15.30 [0.602]	16.40 [.646]	7.75 [.303]
-020	25.00 [.984]	20.90 [0.823]	22.00 [.866]	10.50 [.413]
-025	29.00 [1.142]	24.90 [0.980]	26.00 [1.024]	12.50 [.492]
-030	33.00 [1.299]	28.90 [1.138]	30.00 [1.181]	14.50 [.571]
-035	37.00 [1.457]	32.90 [1.295]	34.00 [1.339]	16.50 [.649]
-040	41.00 [1.614]	36.90 [1.453]	38.00 [1.496]	18.50 [.728]
-049	48.20 [1.889]	44.10 [1.736]	45.20 [1.780]	22.10 [.870]
-050	49.00 [1.929]	44.90 [1.768]	46.00 [1.811]	22.50 [.886]
-060	57.00 [2.244]	52.90 [2.083]	54.00 [2.126]	26.50 [1.043]
-070	65.00 [2.559]	60.90 [2.398]	62.00 [2.441]	30.50 [1.201]
-075	69.00 [2.717]	64.90 [2.555]	66.00 [2.598]	32.50 [1.279]

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 2:1







samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322

DESCRIPTION: 0.8MM EDGE RATE TERMINAL ASSEMBLY

DWG. NO. ERM8-XXX-XX.X-X-DV-XXXX-TR

BY: KNOWLDEN 9/27/2005 SHEET 2 OF 6



PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING





SHEET SCALE: 2:1

Samtec
520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322

DESCRIPTION:
0.8MM EDGE RATE TERMINAL ASSEMBLY

DWG. NO.
ERM8-XXX-XX.X-X-DV-XXXX-TR

BY: KNOWLDEN 9/27/2005 SHEET 3 OF 6



SECTION "B"- "B"

TABLE 9

No. OF POS.	"P"	"Q"	"R"
-10	18.0 [0.71]	17.00 [0.669]	16.36 [0.644]
-20	26.0 [1.02]	25.00 [0.984]	24.36 [0.959]
-25	30.0 [1.18]	29.00 [1.142]	28.36 [1.117]
-30	34.0 [1.34]	33.00 [1.299]	32.36 [1.274]

FIG 6
-EGPS OPTIONS
(AVAILABLE ON -05.0 LEAD STYLE ONLY)
(ERM8-030-05.0-X-DV-EGPS SHOWN)
(SAME AS FIG 5, EXCEPT AS SHOWN)

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 3:1




Samtec
520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322

DESCRIPTION: 0.8MM EDGE RATE TERMINAL ASSEMBLY

DWG. NO.

ERM8-XXX-XX.X-X-DV-XXXX-TR



BY: KNOWLDEN9/27/2005 SHEET 4 OF 6



SECTION 'T'-T'

SECTION "S"-S"

FIG 7
 (**ERM8-030-15.0-X-DV SHOWN)
 (SOME CENTER FEATURES REMOVED FOR CLARITY)
 ***NOT TOOLED



SECTION "U"-U"

FIG 8
 (**ERM8-030-15.0-X-DV-L SHOWN)
 (SAME AS FIG. 7, EXCEPT AS SHOWN)
 ***NOT TOOLED

PROPRIETARY NOTE
 THIS DOCUMENT CONTAINS INFORMATION
 CONFIDENTIAL AND PROPRIETARY TO
 SAMTEC, INC. AND SHALL NOT BE REPRODUCED
 OR TRANSFERRED TO OTHER DOCUMENTS OR
 DISCLOSED TO OTHERS OR USED FOR ANY
 PURPOSE OTHER THAN THAT WHICH IT WAS
 OBTAINED WITHOUT THE EXPRESSED WRITTEN
 CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING







SHEET SCALE: 2:1

samtec
 520 PARK EAST BLVD, NEW ALBANY, IN 47150
 PHONE: 812-944-6733 FAX: 812-948-5047
 e-Mail: info@SAMTEC.com code 55322

DESCRIPTION: 0.8MM EDGE RATE TERMINAL ASSEMBLY

DWG. NO. ERM8-XXX-XX.X-X-DV-XXXX-TR

BY: KNOWLDEN 9/27/2005 SHEET 5 OF 6



PROPRIETARY NOTE
 THIS DOCUMENT CONTAINS INFORMATION
 CONFIDENTIAL AND PROPRIETARY TO
 SAMTEC, INC. AND SHALL NOT BE REPRODUCED
 OR TRANSFERRED TO OTHER DOCUMENTS OR
 DISCLOSED TO OTHERS OR USED FOR ANY
 PURPOSE OTHER THAN THAT WHICH IT WAS
 OBTAINED WITHOUT THE EXPRESSED WRITTEN
 CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 2:1

Samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
 PHONE: 812-944-6733 FAX: 812-948-5047
 e-Mail: info@SAMTEC.com code 55322

DESCRIPTION: 0.8MM EDGE RATE TERMINAL ASSEMBLY

DWG. NO.

ERM8-XXX-XX.X-X-DV-XXXX-TR

BY: KNOWLDEN 9/27/2005 **SHEET 6 OF 6**