

**Tenergy Corporation**

436 Kato Terrace

Fremont CA 94539

Tel: 510-687-0388 Fax: 510-687-0328

**TENERGY 18650 2200mAh Li-Ion Cell**

|                           |                                 |                                                                                     |
|---------------------------|---------------------------------|-------------------------------------------------------------------------------------|
| <b>Product Name:</b>      | Tenergy Lithium Ion 18650 Cell  |  |
| <b>Product Number:</b>    | 30003                           |                                                                                     |
| <b>Battery Model:</b>     | 18650 2200mAh                   |                                                                                     |
| <b>Battery Chemistry:</b> | Lithium Ion Rechargeable        |                                                                                     |
| <b>Dimension:</b>         | Max Diameter ( $\phi$ ): 18.3mm |                                                                                     |
|                           | Max Height (H): 65.0mm          |                                                                                     |

**1. Scope**

The specification describes the technology parameters and testing standard for the lithium ion rechargeable cell supplied by TENERGY CORPORATION.

**2. References**

This specification is referenced GB/T18287-2000, UL1642, IEC61960-1:2000.

**3. Basic characteristics**

|                                |                                                          |
|--------------------------------|----------------------------------------------------------|
| 3.1 Capacity                   | Nominal Capacity : 2200mAh (0.2C <sub>A</sub> Discharge) |
|                                | Minimum Capacity: 2100mAh (0.2C <sub>A</sub> Discharge)  |
| 3.2 Nominal Voltage            | 3.7V                                                     |
| 3.3 Internal impedance         | $\leq 80\text{m}\Omega$ (with PTC)                       |
| 3.4 Discharge Cut-off Voltage  | 3.0V                                                     |
| 3.5 Max Charge Voltage         | 4.20 $\pm$ 0.02V                                         |
| 3.6 Standard Charge Current    | 0.5C <sub>A</sub>                                        |
| 3.7 Rapid Charge Current       | 1C <sub>A</sub>                                          |
| 3.8 Standard Discharge Current | 0.5C <sub>A</sub>                                        |
| 3.9 Rapid Discharge Current    | 1C <sub>A</sub>                                          |

Specifications and data are subject to change without notice. Contact Tenergy for latest information.

©2009 Tenergy Corporation. All rights reserved.

**Tenergy Corporation**

436 Kato Terrace

Fremont CA 94539

Tel: 510-687-0388 Fax: 510-687-0328

|                            |                         |
|----------------------------|-------------------------|
| 3.10 Max Discharge Current | 2.0 C <sub>A</sub>      |
| 3.11 Weight                | 45±1g                   |
| 3.12 Max. Dimension        | Diameter(φ): 18.3mm     |
|                            | Height (H): 65.0mm      |
| 3.13 Operating Temperature | Charge 0 ~ 45℃          |
|                            | Discharge -20 ~ 60℃     |
| 3.14 Storage Temperature   | Within 1 month -5 ~ 35℃ |
|                            | Within 6 months 0 ~ 35℃ |

**4. Standard Conditions for Test**

Unless specified, all tests should be conducted within one month after the delivery under the following conditions: Ambient Temperature: 25±5℃; Relative Humidity: 65±20%

|                         |                                                                                                                   |
|-------------------------|-------------------------------------------------------------------------------------------------------------------|
| 4.1 Standard Charge:    | Constant Current and Constant Voltage (CC/CV)<br>Current = 1100mA<br>End-up Voltage = 4.2 V<br>End Current = 22mA |
| 4.2 Standard Discharge: | Constant Current (CC)<br>Current = 1100mA<br>End Voltage = 3.0V                                                   |

**5. Characteristics**

※In this section, the Standard Conditions of Tests see the part 4.

**5.1 Electrical Performances**

| Item                        | Test procedure                                                                                                                                         | Requirements   |
|-----------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|----------------|
| 5.1.1 Nominal Voltage       | The average value of the working voltage in the whole discharge progress.                                                                              | 3.7V           |
| 5.1.2 Discharge Performance | The discharge capacity of the cell, which is measured at 1C <sub>5</sub> A (or 0.5CA) current discharge to 3.0V within 1 hour after completely charge. | ≥57(or 120)min |

Specifications and data are subject to change without notice. Contact Tenergy for latest information.

©2009 Tenergy Corporation. All rights reserved.

**Tenergy Corporation**

436 Kato Terrace

Fremont CA 94539

Tel: 510-687-0388 Fax: 510-687-0328

|                          |                                                                                                                                                                                                                                                                                                |                          |
|--------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------|
| 5.1.3 Capacity Retention | After 28 days storage at $25\pm 5^{\circ}\text{C}$ after completed charge, the residual capacity is above 90%.                                                                                                                                                                                 | Capacity $\geq$ 1980mAh  |
| 5.1.4 Cycle Life         | After 300 cycles in 100% DOD charge and discharge at 0.5CA current, the residual discharge capacity is above 60% of nominal capacity.                                                                                                                                                          | $\geq$ 300 cycles        |
| 5.1.5 Storage            | (Within 3 months after manufactured) after standard charged 40-50% capacity and stored at ambient temperature $25\pm 5^{\circ}\text{C}$ 、 $65\pm 20\%\text{RH}$ for 12 months, the storage expiry and the cell completely charged, the cell is discharged at 0.2 CA current discharge to 3.0V. | Discharge time $\geq$ 4h |
|                          |                                                                                                                                                                                                                                                                                                |                          |

**5.2 safety Performances**

|                     |                                                                                                                                                                      |                        |
|---------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------|
| 5.2.1 Short Circuit | The cell is to be short-circuited by connecting the positive and negative terminals of the cell directly with copper wire with a resistance less than $0.05\Omega$ . | No fire, no explosion. |
| 5.2.2 Impact Test   | Impacting of a cell on a hard surface following a hammer of 10 kilograms free fall from 1m height.                                                                   | No fire, no explosion. |

**Tenergy Corporation**

436 Kato Terrace

Fremont CA 94539

Tel: 510-687-0388 Fax: 510-687-0328

|                              |                                                                                                                                                                                                                                                                                                                                                                                                          |                        |
|------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------|
| 5.2.3 Overcharge<br>(3C/10V) | The cell that connect with the thermocouple is put in the fume hood, the positive and negative terminals are connected by a permanent constant electrical source, regulate current to 3 CA and voltage to 10 V. Then charge the cell until voltage is 10 V, current about 0A. Monitor the temperature change of cell when the temperature of cell is about lower 10°C than peak value, the test is over. | No fire, no explosion. |
| 5.2.4 Thermal shock          | After standard charging, heat cell to 150±2°C at rate of 5±2°C/min and keep 10 minutes.                                                                                                                                                                                                                                                                                                                  | No fire, no explosion. |

**5.3 Environmental tests**

|                                    |                                                                                                                                                                                                                                                                                                         |                        |
|------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------|
| 5.3.1 High temperature performance | The fully charged cell is put in the surroundings of 55±2°C for 2 hours, and then it is discharged to the 2.75V at 1CA current rate.                                                                                                                                                                    | Capacity≥2160mAh       |
| 5.3.2 Low temperature performance  | The charged cell is put 16-24 hours at -20±2°C and then discharge to 2.75V at 0.2 CA current rate.                                                                                                                                                                                                      | Capacity≥1680mAh       |
| 5.3.3 Vibration Test               | After standard charging, the cell is fixed on the platform and be subjected to vibrate on following frequency 10~55Hz and amplitude vibration for 30 minutes with direction of X, Y. Vibration Frequency: 10~30Hz, vibration amplitude 0.38mm. Vibration Frequency: 30~55Hz, vibration amplitude 0.19mm |                        |
| 5.3.4 Drop Test                    | The cell is to be dropped from a height of 1m to hard board in X、Y、Z directions for twice respectively. Then discharge the cell at 1CA                                                                                                                                                                  | No fire, no explosion. |

Specifications and data are subject to change without notice. Contact Tenergy for latest information.

©2009 Tenergy Corporation. All rights reserved.

**Tenergy Corporation**

436 Kato Terrace

Fremont CA 94539

Tel: 510-687-0388 Fax: 510-687-0328

|  |                                                                                                                   |  |
|--|-------------------------------------------------------------------------------------------------------------------|--|
|  | current rate to 3.0V, and undertake more than three circles of standard charge and discharge at 1CA current rate. |  |
|--|-------------------------------------------------------------------------------------------------------------------|--|

**6. Packing**

Keep the cells at the half-fully charged state before packing.

**7. Transportation:**

Violent shaking, bumping, rain and flaring sun shall be forbidden during the transportation.

Keep the cells at the half-fully charged state.

**8. Storage**

Please keep the cell in the cool and dry environment: Within 1 month  $-5 \sim 35^{\circ}\text{C}$  or Within 6 months,  $0 \sim 35^{\circ}\text{C}$ , Relative humidity  $\leq 75\%$ , Keep the cells at the half-fully charged state.

9. Warranty period of this product is 6 months from leaving plant.

10. We will not guarantee against any accidents occurring due to usage against this specification.

11. The information in this specification subject to change without prior notice.

12. The information contained in this document is for reference only and should not be used as a basis for product guarantee or warranty. For applications other than those described here, please consult TENERGY CORP directly.

**13. Caution:**

13.1 Please read the specification carefully before testing or using the cell, as improper handling of Lithium-ion cell may result in loss of efficiency, heating ignition, electrolyte leakage or even explosion.

13.2 While testing the cell of charging and discharging, please use the testing equipment special for Li-ion cell. Do NOT use the ordinary source of constant current and constant voltage, which fails to restrict charge and discharge to cell in order to



prevent the cell from being overcharged and over-discharged, triggering cell malfunction or explosion.

13.3 When charging and discharging to the cell or packing it into the equipment, do NOT reverse the terminals of cathode and anode or it will make the cell overcharging and over-discharging, causing the cell to lose efficiency seriously and even explode.

13.4 Do NOT weld the cell directly, do not disassembly the cell.

13.5 Do NOT put the cell together with such metal products as necklace, hairpin, coin or screw in the pocket or in the bag; neither store them together. Do NOT connect the positive and negative electrode directly with such conductive materials as metal, or it may make the cell short-circuit.

13.6 Do NOT beat, throw or trample the cell. Do NOT put the cell into the washing machine or the high-pressure container.

13.7 Do NOT put the cell close to heat source, for instance, fire, heater etc. Do NOT use the cell under the circumstance of burning sun or the temperature exceeding 60°C, or it may cause the cell to generate heat, heating ignition and loss of efficiency.

13.8 Do NOT get the cell wet or throw the cell into water. When not use, it should be placed in the dry and low temperature environment.

13.9 While using, testing or preserving the cell, if you find the battery become hot , distribute smell , change color, deform or any other abnormality, please stop using or testing immediately, and attempt to isolate and keep away from the cell.

13.10 If the cell leaks, the electrolyte gets into the eyes, do not rub eyes, instead, rinse the eyes with plenty of water, and seek medical service. If the electrolyte gets onto the skin or clothe, wash it with plenty of water immediately.




## Tenergy Corporation

436 Kato Terrace


Fremont CA 94539

Tel: 510-687-0388 Fax: 510-687-0328


### Performance Curve




Charge: CC/CV 0.5CmA, 4.2V, 20mA cut off at RT.



Charge: CC/CV 0.5CmA, 4.2V, 20mA cut off at RT  
Discharge: 3.0V cut off at RT.



Charge: CC/CV 0.5CmA, 4.2V, 20mA cut off  
Discharge: 3.0V cut off



Charge: CC/CV 0.5CmA, 4.2V, 20mA cut off at RT  
Discharge: CC 0.5CmA, 3.0 V cut off at RT.

#### Note:

CC represent constant current

CV represent constant voltage

1C represent multiple current

RT represent room temperature

Specifications and data are subject to change without notice. Contact Tenergy for latest information.

©2009 Tenergy Corporation. All rights reserved.