

10 9 8 7 6 5 4 3 2 1

NOTES:

1. MATERIAL:

HSG: PCT, 30% GLASS FILLED,UL 94V-0,
COLOUR BLACK.
PIN: 0.50MM SQ PHOSPHOR BRONZE 510

2. PLATING:

***5 - 0.05um MIN - 0.25um MAX GOLD IN CONTACT AREA,
2.00um MIN TIN IN SOLDERTAIL AREA, BOTH OVER
1.25um MIN NICKEL OVERALL

***6 - 0.38um MIN GOLD IN CONTACT AREA,
2.00um MIN TIN IN SOLDERTAIL AREA, BOTH OVER
1.25um MIN NICKEL OVERALL

***7 - 0.76um MIN GOLD IN CONTACT AREA,
2.00um MIN TIN IN SOLDERTAIL AREA, BOTH OVER
1.25um MIN NICKEL OVERALL

***8 - 2.54um MIN TIN OVER
1.25um MIN NICKEL OVERALL

3. 12 CKT USED FOR ILLUSTRATION ONLY
4. PART TO BE PACKED IN POCKET TRAY/TUBE (SEE TABLE).
5. PRODUCT SPEC PS-87761-100 APPLIES.
6. RECOMMENDED PCB BOARD THK 1.60±0.10 MM.


7. MATING LENGTH: 1 - 4.00MM
2 - 3.50MM
3 - 3.06MM
4 - 5.75MM

8. PART NUMBERS THAT ARE UNAVAILABLE IN THIS SD:
87760-0646, 87760-1046, 87760-1446, 87760-2446, 87760-4046.
(REFER TO SD-87760-133 FOR THESE PART NUMBERS)




LEGEND:

87760 - * * * *

PLATING OPTION 2
(SEE NOTE 2)
MATING OPTION 7




RECOMMENDED PCB LAYOUT



DETAIL Z

SHT 3, +87760-5516 EC NO: S2013-0842 DRW:NATSEE 2013/05/31 CHKD:SKANG 2013/06/28 APPR:MLONG 2013/07/08			DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION				
								MM ONLY		NTS	METRIC					
				$F_A=0$ $F_G=0$ $F_P=0$		mm	INCH	DRAWN BY DATE		TITLE MGRID, 2MM DUAL ROW HDR. R/A						
					4 PLACES	± ---	± ---	KSEE 2003/10/15								
					3 PLACES	± ---	± ---	CHECKED BY DATE								
					2 PLACES	± 0.2	± ---	KCL ING 2003/12/02								
					1 PLACE	± ---	± ---	APPROVED BY DATE								
				0 PLACE	±	±	SKTOH 2003/12/11		molex							
				ANGULAR ± 3 °			MATERIAL NO.						DOCUMENT NO.		SHEET NO.	
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE TABLE						SD-87760-109		1 OF 3	
A16			REV				SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								

9 8 7 6 5 4 3 2 1

	10	9	8	7	6	5	4	3	2	1																																																																
	PART NUMBER	VOID PIN LOCATION	CKT SIZE	A	B	M	T	PACKAGING TYPE																																																																		
F	87760-04**	-	04	2.00	4.00	REFER TO NOTE 7.	2.60	TRAY	 PART IN TUBE																																																																	
	87760-06** 	-	06	4.00	6.00																																																																					
	87760-08**	-	08	6.00	8.00																																																																					
	87760-10** 	-	10	8.00	10.00																																																																					
	87760-12** 	-	12	10.00	12.00																																																																					
	87760-14** 	-	14	12.00	14.00																																																																					
E	87760-16**	-	16	14.00	16.00																																																																					
	87760-18**	-	18	16.00	18.00																																																																					
	87760-20**	-	20	18.00	20.00																																																																					
	87760-22**	-	22	20.00	22.00																																																																					
	87760-24** 	-	24	22.00	24.00																																																																					
D	87760-26**	-	26	24.00	26.00																																																																					
	87760-28**	-	28	26.00	28.00																																																																					
	87760-30**	-	30	28.00	30.00																																																																					
	87760-32**	-	32	30.00	32.00																																																																					
	87760-34**	-	34	32.00	34.00																																																																					
	87760-36**	-	36	34.00	36.00																																																																					
	87760-38**	-	38	36.00	38.00																																																																					
C	87760-40** 	-	40	38.00	40.00																																																																					
	87760-42**	-	42	40.00	42.00																																																																					
	87760-44**	-	44	42.00	44.00																																																																					
	87760-46**	-	46	44.00	46.00																																																																					
	87760-48**	-	48	46.00	48.00																																																																					
	87760-50**	-	50	48.00	50.00																																																																					
B																																																																										
A	<table><tr><td rowspan="5">SHT 3, +87760-5516 EC NO: S2013-0842 DRWN:ATSEE 2013/05/31 CHKD:SKANG 2013/06/28 APPR:MLONG 2013/07/08</td><td rowspan="5">DESCRIPTION REV</td><td>QUALITY SYMBOLS</td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td colspan="2">THIRD ANGLE PROJECTION</td></tr><tr><td rowspan="4"> </td><td></td><td>mm</td><td>INCH</td><td>DRAWN BY KSEE</td><td>DATE 2003/10/15</td><td rowspan="4">TITLE MGRID, 2MM DUAL ROW HDR. R/A</td><td rowspan="4">DOCUMENT NO. SD-87760-109</td><td rowspan="4">SHEET NO. 2 OF 3</td></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td><td>CHECKED BY</td><td>DATE</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± ---</td><td>KCL ING</td><td>2003/12/02</td></tr><tr><td>2 PLACES</td><td>± 0.2</td><td>± ---</td><td>APPROVED BY</td><td>DATE</td></tr><tr><td>1 PLACE</td><td>± ---</td><td>± ---</td><td>SKTOH</td><td>2003/12/11</td><td colspan="2">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr><tr><td colspan="2">A16</td><td></td><td colspan="2">ANGULAR ± 3 °</td><td colspan="2">SEE TABLE</td><td colspan="2"></td><td colspan="2"></td></tr><tr><td colspan="2"></td><td></td><td colspan="2">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td colspan="2"></td><td colspan="2"></td><td colspan="2"></td></tr></table>										SHT 3, +87760-5516 EC NO: S2013-0842 DRWN:ATSEE 2013/05/31 CHKD:SKANG 2013/06/28 APPR:MLONG 2013/07/08	DESCRIPTION REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		 		mm	INCH	DRAWN BY KSEE	DATE 2003/10/15	TITLE MGRID, 2MM DUAL ROW HDR. R/A	DOCUMENT NO. SD-87760-109	SHEET NO. 2 OF 3	4 PLACES	± ---	± ---	CHECKED BY	DATE	3 PLACES	± ---	± ---	KCL ING	2003/12/02	2 PLACES	± 0.2	± ---	APPROVED BY	DATE	1 PLACE	± ---	± ---	SKTOH	2003/12/11	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		A16			ANGULAR ± 3 °		SEE TABLE									DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS							
SHT 3, +87760-5516 EC NO: S2013-0842 DRWN:ATSEE 2013/05/31 CHKD:SKANG 2013/06/28 APPR:MLONG 2013/07/08	DESCRIPTION REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																																																																	
		 		mm	INCH	DRAWN BY KSEE	DATE 2003/10/15	TITLE MGRID, 2MM DUAL ROW HDR. R/A	DOCUMENT NO. SD-87760-109	SHEET NO. 2 OF 3																																																																
			4 PLACES	± ---	± ---	CHECKED BY	DATE																																																																			
			3 PLACES	± ---	± ---	KCL ING	2003/12/02																																																																			
			2 PLACES	± 0.2	± ---	APPROVED BY	DATE																																																																			
1 PLACE	± ---	± ---	SKTOH	2003/12/11	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																					
A16			ANGULAR ± 3 °		SEE TABLE																																																																					
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS																																																																							
tb_frame_A3_P_AM_T Rev. G 2012/01/11	9	8	7	6	5	4	3	2	1																																																																	

	10	9	8	7	6	5	4	3	2	1																																				
F	PART NUMBER	VOID PIN LOCATIONS	CKT SIZE	A	B	M	T	PACKAGING TYPE																																						
	87760-5116	5, 6 & 26	50	48.00	50.00	REFER TO NOTE 7.	2.60	TUBE																																						
	87760-531*	-	24	22.00	24.00		1.50	TRAY																																						
	87760-5216	-	04	2.00	4.00		2.60	TUBE																																						
	87760-5416	-	20	18.00	20.00																																									
	87760-5248	-	28	26.00	28.00																																									
E	87760-5516	5, 6, 7, 8, 9, 10, 15, 16, 17, 18, 19, 20, 25, 26, 27, 28, 29, 30	34	32.00	34.00																																									
D																																														
C																																														
B																																														
A	<table><tr><td rowspan="5">SHT 3, +87760-5516 EC NO: S2013-0842 DRWN:ATSEE 2013/05/31 CHKD:SKANG 2013/06/28 APPR:WLONG 2013/07/08</td><td rowspan="5">DESCRIPTION REV</td><td>QUALITY SYMBOLS</td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td rowspan="5"> THIRD ANGLE PROJECTION</td></tr><tr><td rowspan="4"> </td><td rowspan="4">F_a=0 F_a=0 F_a=0</td><td rowspan="4">4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE</td><td rowspan="4">± --- ± --- ± 0.2 ± --- ±</td><td rowspan="4">mm INCH</td><td rowspan="4">DRAWN BY KSEE CHECKED BY KCLING APPROVED BY SKTOH</td><td rowspan="4">DATE 2003/10/15 DATE 2003/12/02 DATE 2003/12/11</td><td rowspan="4">TITLE MGRID, 2MM DUAL ROW HDR. R/A</td></tr><tr><td colspan="2">ANGULAR ± 3 °</td><td rowspan="3">DOCUMENT NO. SD-87760-109</td><td rowspan="3">SHEET NO. 3 OF 3</td></tr><tr><td colspan="2">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td></tr><tr><td colspan="2">SIZE A3 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr><tr><td colspan="2">A16</td><td colspan="8"></td></tr></table>										SHT 3, +87760-5516 EC NO: S2013-0842 DRWN:ATSEE 2013/05/31 CHKD:SKANG 2013/06/28 APPR:WLONG 2013/07/08	DESCRIPTION REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	 	F _a =0 F _a =0 F _a =0	4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE	± --- ± --- ± 0.2 ± --- ±	mm INCH	DRAWN BY KSEE CHECKED BY KCLING APPROVED BY SKTOH	DATE 2003/10/15 DATE 2003/12/02 DATE 2003/12/11	TITLE MGRID, 2MM DUAL ROW HDR. R/A	ANGULAR ± 3 °		DOCUMENT NO. SD-87760-109	SHEET NO. 3 OF 3	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		A16									
SHT 3, +87760-5516 EC NO: S2013-0842 DRWN:ATSEE 2013/05/31 CHKD:SKANG 2013/06/28 APPR:WLONG 2013/07/08	DESCRIPTION REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																																					
		 	F _a =0 F _a =0 F _a =0	4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE	± --- ± --- ± 0.2 ± --- ±	mm INCH	DRAWN BY KSEE CHECKED BY KCLING APPROVED BY SKTOH	DATE 2003/10/15 DATE 2003/12/02 DATE 2003/12/11		TITLE MGRID, 2MM DUAL ROW HDR. R/A																																				
													ANGULAR ± 3 °		DOCUMENT NO. SD-87760-109	SHEET NO. 3 OF 3																														
													DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS																																	
											SIZE A3 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																			
A16																																														
	fb_frame_A3_P_AM_T Rev. G 2012/01/11	9	8	7	6	5	4	3	2	1																																				