

## Two Outputs PCI-Express Clock Generator

### Features


- 25 MHz Crystal or Clock Input
- Two sets of Differential PCI-Express Clocks
- Pin Selectable Output Frequencies
- Supports HCSL or LVDS Compatible Output Levels
- Spread Spectrum Capability on all Output Clocks with Pin Selectable Spread Range
- 16-pin TSSOP Package
- Operating Voltage 3.3V
- Commercial and Industrial Operating Temperature Range

### Functional Description

CY24293 is a two output PCI-Express clock generator device intended for networking applications. The device takes 25 MHz crystal or clock input and provides two pairs of differential outputs at 25 MHz, 100 MHz, 125 MHz, or 200 MHz for HCSL, and 25 MHz or 100 MHz for the LVDS signaling standard.


The device incorporates Lexmark Spread Spectrum profile for maximum electromagnetic interference (EMI) reduction. The spread type and amount can be selected using select pins.

### Logic Block Diagram



## Pinouts

**Figure 1. Pin Diagram - CY24293 16-Pin TSSOP**



**Table 1. Pin Definitions - CY24293 16-Pin TSSOP**

| Pin Number | Pin Name    | Pin Type | Description                                                                                         |
|------------|-------------|----------|-----------------------------------------------------------------------------------------------------|
| 1          | S0          | Input    | Frequency select pin. Has internal weak pull up. Refer to <a href="#">Table 2</a> .                 |
| 2          | S1          | Input    | Frequency select pin. Has internal weak pull up. Refer to <a href="#">Table 2</a> .                 |
| 3          | SS0         | Input    | Spread Spectrum Select pin 0. Has internal weak pull up. Refer to <a href="#">Table 3</a> .         |
| 4          | XIN/EXCLKIN | Input    | Crystal or clock input. 25 MHz fundamental mode crystal or clock input.                             |
| 5          | XOUT        | Output   | Crystal output. 25 MHz fundamental mode crystal input. Float for clock input.                       |
| 6          | OE          | Input    | High true output enable pin. When set low, PCI-E outputs are tri-stated. Has internal weak pull up. |
| 7          | GNDX        | Power    | Ground                                                                                              |
| 8          | SS1         | Input    | Spread Spectrum Select pin 1. Has internal weak pull up. Refer to <a href="#">Table 3</a> .         |
| 9          | IREF        | Output   | Current set for all differential clock drivers. Connect 475Ω resistor to ground.                    |
| 10         | PCIE1N      | Output   | Differential PCI-Express complementary clock output. Tristated when disabled.                       |
| 11         | PCIE1P      | Output   | Differential PCI-Express true clock output. Tristated when disabled.                                |
| 12         | VDDO        | Input    | 3.3V Power supply for output driver and analog circuits.                                            |
| 13         | GNDO        | Power    | Ground                                                                                              |
| 14         | PCIE0N      | Output   | Differential PCI-Express complementary clock output. Tristated when disabled.                       |
| 15         | PCIE0P      | Output   | Differential PCI-Express true clock output. Tristated when disabled.                                |
| 16         | VDDX        | Input    | 3.3V Power supply for oscillator and digital circuits.                                              |

**Table 2. Output Selection Table**

| S1 | S0 | PCIE0[N,P], PCIE1[N,P] |
|----|----|------------------------|
| 0  | 0  | 25 MHz                 |
| 0  | 1  | 100 MHz                |
| 1  | 0  | 125 MHz                |
| 1  | 1  | 200 MHz                |

**Table 3. Spread Selection Table**

| SS1 | SS0 | Spread%   |
|-----|-----|-----------|
| 0   | 0   | No Spread |
| 0   | 1   | -0.5%     |
| 1   | 0   | -0.75%    |
| 1   | 1   | No Spread |

## Application Information

### Crystal Recommendations

CY24293 requires a parallel resonance crystal. Substituting a series resonance crystal causes the CY24293 to operate at the wrong frequency and violate the ppm specification. For most applications, there is a 300 ppm frequency shift between series and parallel crystals due to incorrect loading.

**Table 4. Crystal Recommendations**

| Frequency | Cut      | Load Cap | Eff Series Rest (max) | Drive (max) | Tolerance (max) | Stability (max) | Aging (max) |
|-----------|----------|----------|-----------------------|-------------|-----------------|-----------------|-------------|
| 25.00 MHz | Parallel | 16 pF    | 30 $\Omega$           | 1.0 mW      | 30 ppm          | 10 ppm          | 5 ppm/yr.   |

### Crystal Loading

Crystal loading plays a critical role in achieving low ppm performance. To realize low ppm performance, consider the total capacitance the crystal sees to calculate the appropriate capacitive loading (CL).


Figure 2 shows a typical crystal configuration using two trim capacitors. It is important to note that the trim capacitors in series with the crystal are not parallel. It is a common misconception that load capacitors are in parallel with the crystal and must be approximately equal to the load capacitance of the crystal. This is not true.

### Calculating Load Capacitors

In addition to the standard external trim capacitors, trace capacitance and pin capacitance must also be considered to correctly calculate crystal loading.

As mentioned in the previous section, the capacitance on each side of the crystal is in series with the crystal. This means the total capacitance on each side of the crystal must be twice the specified crystal load capacitance (CL). While the capacitance on each side of the crystal is in series with the crystal, trim capacitors (Ce1, Ce2) must be calculated to provide equal capacitive loading on both sides.

**Figure 2. Crystal Loading Example**



Use the following formulas to calculate the trim capacitor values for Ce1 and Ce2:

#### Load capacitance (each side)

$$C_e = 2 * CL - (C_s + C_i)$$

#### Total capacitance (as seen by the crystal)

$$CL_e = \frac{1}{\left(\frac{1}{C_{e1} + C_{s1} + C_{i1}} + \frac{1}{C_{e2} + C_{s2} + C_{i2}}\right)}$$

CL..... Crystal load capacitance

CLe..... Actual loading seen by crystal using standard value trim capacitors

Ce..... External trim capacitors

Cs..... Stray capacitance (terraced)

Ci..... Internal capacitance

### Current Source (Iref) Reference Resistor

If the board target trace impedance (Z) is 50 $\Omega$ , then for  $R_{REF} = 475\Omega$  (1%), provides IREF of 2.32 mA. The output current (IOH) is equal to 6\*IREF.

### Output Termination

The PCI-Express differential clock outputs of the CY24293 are open source drivers and require an external series resistor and a resistor to ground. These resistor values and their allowable locations are explained in the section [PCI-Express Layout Guidelines](#) on page 4. The CY24293 can also be configured for LVDS compatible voltage levels. Refer to the section [LVDS Compatible Layout Guidelines](#) on page 5.

## PCB Layout Recommendations

For optimum device performance and the lowest phase noise, the following guidelines must be observed:

1. Each 0.01  $\mu\text{F}$  decoupling capacitor must be mounted on the component side of the board as close to the VDD pin as possible.
2. No vias must be used between the decoupling capacitor and the VDD pin.
3. The PCB trace to the VDD pin and the ground via must be kept as short as possible. Distance of the ferrite bead and bulk decoupling from the device is less critical.

4. An optimum layout is one with all components on the same side of the board, minimizing vias through other signal layers (any ferrite beads and bulk decoupling capacitors can be mounted on the back). Other signal traces must be routed away from the CY24293. This includes signal traces just underneath the device, or on layers adjacent to the ground plane layer used by the device.

## Decoupling Capacitors

The decoupling capacitors of 0.01  $\mu\text{F}$  must be connected between VDD and GND as close to the device as possible. Do not share ground vias between components. Route power from the power source through the capacitor pad and then into the CY24293 pin.

## PCI-Express Layout Guidelines

### HCSL Compatible Layout Guidelines


**Table 5. Common Recommendations for Differential Routing**

| Differential Routing <sup>[1]</sup>               | Dimension or Value | Unit     |
|---------------------------------------------------|--------------------|----------|
| L1 length, route as non-coupled 50 $\Omega$ trace | 0.5 max            | inch     |
| L2 length, route as non-coupled 50 $\Omega$ trace | 0.2 max            | inch     |
| L3 length, route as non-coupled 50 $\Omega$ trace | 0.2 max            | inch     |
| $R_S$                                             | 33                 | $\Omega$ |
| $R_T$                                             | 49.9               | $\Omega$ |

**Table 6. Differential Routing for PCI-Express Load or Connector**

| Differential Routing <sup>[1]</sup>                                    | Dimension or Value | Unit |
|------------------------------------------------------------------------|--------------------|------|
| L4 length, route as coupled microstrip 100 $\Omega$ differential trace | 2 to 32            | inch |
| L4 length, route as coupled stripline 100 $\Omega$ differential trace  | 1.8 to 30          | inch |

**Figure 3. PCI-Express Device Routing**



### Note

1. Refer to Figure 3.

## LVDS Compatible Layout Guidelines


**Table 7. Common Recommendations for Differential Routing**

| Differential Routing <sup>[2]</sup>      | Dimension or Value | Unit |
|------------------------------------------|--------------------|------|
| L1 length, route as noncoupled 50Ω trace | 0.5 max            | inch |
| L2 length, route as noncoupled 50Ω trace | 0.2 max            | inch |
| L3 length, route as noncoupled 50Ω trace | 0.2 max            | inch |
| R <sub>P</sub>                           | 100                | Ω    |
| R <sub>Q</sub>                           | 150                | Ω    |
| R <sub>S</sub>                           | 33                 | Ω    |
| R <sub>T</sub>                           | 49.9               | Ω    |

**Table 8. LVDS Device Differential Routing**

| Differential Routing <sup>[2]</sup>                            | Dimension or Value | Unit |
|----------------------------------------------------------------|--------------------|------|
| L4 length, route as coupled microstrip 100Ω differential trace | 2 to 32            | inch |
| L4 length, route as coupled stripline 100Ω differential trace  | 1.8 to 30          | inch |

**Figure 4. LVDS Device Routing**



**Note**

2. Refer to Figure 4.

## Absolute Maximum Ratings

Exceeding maximum ratings may shorten the useful life of the device. User guidelines are not tested.

**Table 9. Absolute Maximum Ratings**

| Parameter          | Description                       | Condition                   | Min            | Max                  | Unit |
|--------------------|-----------------------------------|-----------------------------|----------------|----------------------|------|
| V <sub>DD</sub>    | Supply voltage                    |                             | -0.5           | 4.6                  | V    |
| V <sub>IN</sub>    | Input voltage                     | Relative to V <sub>SS</sub> | -0.5           | V <sub>DD</sub> +0.5 | V    |
| T <sub>S</sub>     | Temperature, Storage              | Non Functional              | -65            | +150                 | °C   |
| T <sub>J</sub>     | Temperature, Junction             | Non Functional              | -65            | +150                 | °C   |
| ESD <sub>HBM</sub> | ESD Protection (Human Body Model) | JEDEC EIA/JESD22-A114-E     | 2000           | –                    | V    |
| UL-94              | Flammability rating               |                             | V-0 at 1/8 in. |                      |      |
| MSL                | Moisture sensitivity level        |                             | 3              |                      |      |

## Recommended Operation Conditions

| Parameter       | Description                                                                                              | Min  | Typ | Max | Unit |
|-----------------|----------------------------------------------------------------------------------------------------------|------|-----|-----|------|
| V <sub>DD</sub> | Supply voltage                                                                                           | 3.0  | –   | 3.6 | V    |
| T <sub>AC</sub> | Commercial ambient temperature                                                                           | 0    | –   | +70 | °C   |
| T <sub>AI</sub> | Industrial ambient temperature                                                                           | -40  | –   | +85 | °C   |
| t <sub>PU</sub> | Power up time for all V <sub>DD</sub> to reach minimum specified voltage (power ramps must be monotonic) | 0.05 | –   | 500 | ms   |

## DC Electrical Characteristics

Unless otherwise stated, V<sub>DD</sub> = 3.3V ±0.3V, ambient temperature = -40°C to +85°C Industrial, 0°C to +70°C Commercial

| Parameter <sup>[3]</sup> | Description                                   | Condition                                                       | Min  | Typ  | Max                  | Unit |
|--------------------------|-----------------------------------------------|-----------------------------------------------------------------|------|------|----------------------|------|
| V <sub>IL</sub>          | Input low voltage                             |                                                                 | -0.3 | –    | 0.8                  | V    |
| V <sub>IH</sub>          | Input high voltage                            |                                                                 | 2.0  | –    | V <sub>DD</sub> +0.3 | V    |
| V <sub>OL</sub>          | Output low voltage of PCIE0[P/N], PCIE1[P/N]  | HCSL termination (R <sub>S</sub> = 33Ω, R <sub>T</sub> = 49.9Ω) | -0.2 | 0    | 0.05                 | V    |
| V <sub>OH</sub>          | Output high voltage of PCIE0[P/N], PCIE1[P/N] | HCSL termination (R <sub>S</sub> = 33Ω, R <sub>T</sub> = 49.9Ω) | 0.65 | 0.71 | 0.85                 | V    |
| I <sub>DD</sub>          | Operating supply current                      | No load, OE = 1                                                 | –    | 45   | 60                   | mA   |
| I <sub>DDOD</sub>        | Output disabled current                       | OE = 0                                                          | –    | –    | 50                   | mA   |
| C <sub>IN</sub>          | Input capacitance                             | All input pins                                                  | –    | 5    | –                    | pF   |
| R <sub>PU</sub>          | Pull up resistance                            | S0, S1, SS0, SS1, OE                                            | –    | 70k  | –                    | Ω    |

### Note

3. Parameters are guaranteed by design and characterization. Not 100% tested in production


## AC Electrical Characteristics

Unless otherwise stated: VDD = 3.3V  $\pm$ 0.3V, ambient temperature = -40°C to +85°C Industrial, 0°C to +70°C Commercial, Outputs HCSL terminated.

| Parameter <sup>[3]</sup> | Description                                                           | Condition                                                           | Min  | Typ  | Max  | Unit |
|--------------------------|-----------------------------------------------------------------------|---------------------------------------------------------------------|------|------|------|------|
| F <sub>IN</sub>          | Input clock frequency (crystal or external clock)                     |                                                                     | –    | 25   | –    | MHz  |
| F <sub>OUT</sub>         | Output frequency                                                      | HCSL Termination                                                    | –    | –    | 200  | MHz  |
|                          |                                                                       | LVDS Termination                                                    | –    | –    | 100  | MHz  |
| F <sub>ERR</sub>         | Frequency synthesis error                                             |                                                                     | –    | 0    | –    | ppm  |
| T <sub>CCJ</sub>         | Cycle-to-cycle jitter <sup>[4]</sup>                                  |                                                                     | –    | –    | 75   | ps   |
| SP <sub>MOD</sub>        | Spread modulation frequency                                           |                                                                     | –    | 32   | –    | kHz  |
| T <sub>DC</sub>          | Output clock duty cycle <sup>[4,6]</sup>                              |                                                                     | 45   | 50   | 55   | %    |
| T <sub>OEH</sub>         | Output enable time                                                    | OE going high to differential outputs becoming valid                | –    | –    | 200  | ns   |
| T <sub>OEL</sub>         | Output disable time                                                   | OE going low to differential outputs becoming invalid               | –    | –    | 200  | ns   |
| T <sub>LOCK</sub>        | Clock stabilization from power up                                     | Measured from 90% of the applied power supply level                 | –    | 1    | 2    | ms   |
| T <sub>R</sub>           | Output rise time <sup>[4,5]</sup>                                     | Measured from 0.175V to 0.525V                                      | 130  | –    | 700  | ps   |
| T <sub>F</sub>           | Output fall time <sup>[4,5]</sup>                                     | Measured from 0.525V to 0.175V                                      | 130  | –    | 700  | ps   |
| DT <sub>R</sub>          | Rise time variation <sup>[4,5]</sup>                                  | For a given frequency, Max(T <sub>R</sub> ) - Min (T <sub>R</sub> ) | –    | –    | 125  | ps   |
| DT <sub>F</sub>          | Fall time variation <sup>[4,5]</sup>                                  | For a given frequency, Max(T <sub>F</sub> ) - Min (T <sub>F</sub> ) | –    | –    | 125  | ps   |
| T <sub>OSKEW</sub>       | Output skew <sup>[6]</sup>                                            | Measured at V <sub>CROSS</sub> point                                | –    | –    | 50   | ps   |
| V <sub>CROSS</sub>       | Absolute crossing point voltage <sup>[6,7]</sup>                      |                                                                     | 0.25 | 0.35 | 0.55 | V    |
| V <sub>Xdelta</sub>      | Variation of V <sub>CROSS</sub> over all clock edges <sup>[6,8]</sup> |                                                                     | –    | –    | 140  | mV   |

## Test and Measurement Setup

**Figure 5. Test Load Configuration for Differential Output Signals**



### Notes


- Measured with Cload = 4 pF max. (scope probe + trace load)
- Measurement taken from a differential waveform.
- Measured at crossing point where the instantaneous voltage value of the rising edge of PCIEP equals the falling edge of PCIEEN.
- Refers to the total variation from the lowest crossing point to the highest, regardless of which edge is crossing. Refers to all crossing points for this measurement.
- Refers to the difference between the PCIEP rising edge V<sub>CROSS</sub> average value and the PCIEEN rising edge V<sub>CROSS</sub> average value.

## Ordering Information

| Part Number    | Type                     | Production Flow           |
|----------------|--------------------------|---------------------------|
| <b>Pb-free</b> |                          |                           |
| CY24293ZXC     | 16-pin TSSOP             | Commercial, 0°C to 70°C   |
| CY24293ZXCT    | 16-pin TSSOP tape & reel | Commercial, 0°C to 70°C   |
| CY24293ZXI     | 16-pin TSSOP             | Industrial, -40°C to 85°C |
| CY24293ZXIT    | 16-pin TSSOP tape & reel | Industrial, -40°C to 85°C |

## Package Dimensions

**Figure 6. 16-Pin TSSOP 4.40 mm Body Package**





DIMENSIONS IN MM[INCHES] MIN.  
MAX.

REFERENCE JEDEC MO-153

PACKAGE WEIGHT 0.05gms

| PART #   |                |
|----------|----------------|
| Z16.173  | STANDARD PKG.  |
| ZZ16.173 | LEAD FREE PKG. |



51-85091 \*A

## Document History Page

| Document Title: CY24293 Two Outputs PCI-Express Clock Generator<br>Document Number: 001-46117 |         |                 |                 |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
|-----------------------------------------------------------------------------------------------|---------|-----------------|-----------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| REV.                                                                                          | ECN NO. | Orig. of Change | Submission Date | Description of Change                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| **                                                                                            | 2490167 | PYG/DPF/AESA    | See ECN         | New Data Sheet                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| *A                                                                                            | 2507681 | DPF/AESA        | 05/23/2008      | Added Note 1: Parameters are guaranteed by design and characterization. Not 100% tested in production.<br>Added Note 2 for Duty cycle spec in the AC Elect. Characteristics.<br>Added HCSL termination in Condition for $V_{OL}$ , $V_{OH}$ DC Elect. Char.<br>Added $V_{Xdelta}$ value of 140 mV in the Differential 100 MHz HCSL output.<br>Changed Cload from 2 pF to 4 pF in Note 2.<br>Added internal weak Pull ups for S0, S1, SS0, SS1 and OE pins.<br>Updated $T_{OEH}$ and $T_{OEL}$ to 200 ns (max.).<br>Updated data sheet template |
| *B                                                                                            | 2621901 | CXQ/AESA        | 12/19/2008      | Updated $I_{DD}$ spec in DC Electrical Characteristics.<br>Added max spec for $I_{DDOD}$ DC Electrical Characteristics.<br>Added $R_{PU}$ in DC Electrical Characteristics.<br>Replaced $T_{REFVAR}$ with $DT_R$ and $DT_F$ in AC Electrical Characteristics.<br>Added definitions for rise and fall time variation, crossing point variation in AC Electrical Characteristics.<br>Reduced cycle-to-cycle jitter spec to 75ps in AC Electrical Characteristics.                                                                                |
| *C                                                                                            | 2683343 | CXQ/PYRS        | 04/03/2009      | Removed "Preliminary" from datasheet title and headings<br>Added "max" to crystal ESR spec.<br>Changed "LVDS Down Device" to "LVDS Device" in Table 8 and Figure 4.                                                                                                                                                                                                                                                                                                                                                                            |

## Sales, Solutions, and Legal Information

### Worldwide Sales and Design Support

Cypress maintains a worldwide network of offices, solution centers, manufacturer's representatives, and distributors. To find the office closest to you, visit us at [cypress.com/sales](http://cypress.com/sales).

#### Products

|                  |                                                                |
|------------------|----------------------------------------------------------------|
| PSoC             | <a href="http://psoc.cypress.com">psoc.cypress.com</a>         |
| Clocks & Buffers | <a href="http://clocks.cypress.com">clocks.cypress.com</a>     |
| Wireless         | <a href="http://wireless.cypress.com">wireless.cypress.com</a> |
| Memories         | <a href="http://memory.cypress.com">memory.cypress.com</a>     |
| Image Sensors    | <a href="http://image.cypress.com">image.cypress.com</a>       |

#### PSoC Solutions

|                       |                                                                                          |
|-----------------------|------------------------------------------------------------------------------------------|
| General               | <a href="http://psoc.cypress.com/solutions">psoc.cypress.com/solutions</a>               |
| Low Power/Low Voltage | <a href="http://psoc.cypress.com/low-power">psoc.cypress.com/low-power</a>               |
| Precision Analog      | <a href="http://psoc.cypress.com/precision-analog">psoc.cypress.com/precision-analog</a> |
| LCD Drive             | <a href="http://psoc.cypress.com/lcd-drive">psoc.cypress.com/lcd-drive</a>               |
| CAN 2.0b              | <a href="http://psoc.cypress.com/can">psoc.cypress.com/can</a>                           |
| USB                   | <a href="http://psoc.cypress.com/usb">psoc.cypress.com/usb</a>                           |

© Cypress Semiconductor Corporation, 2008-2009. The information contained herein is subject to change without notice. Cypress Semiconductor Corporation assumes no responsibility for the use of any circuitry other than circuitry embodied in a Cypress product. Nor does it convey or imply any license under patent or other rights. Cypress products are not warranted nor intended to be used for medical, life support, life saving, critical control or safety applications, unless pursuant to an express written agreement with Cypress. Furthermore, Cypress does not authorize its products for use as critical components in life-support systems where a malfunction or failure may reasonably be expected to result in significant injury to the user. The inclusion of Cypress products in life-support systems application implies that the manufacturer assumes all risk of such use and in doing so indemnifies Cypress against all charges.

Any Source Code (software and/or firmware) is owned by Cypress Semiconductor Corporation (Cypress) and is protected by and subject to worldwide patent protection (United States and foreign), United States copyright laws and international treaty provisions. Cypress hereby grants to licensee a personal, non-exclusive, non-transferable license to copy, use, modify, create derivative works of, and compile the Cypress Source Code and derivative works for the sole purpose of creating custom software and or firmware in support of licensee product to be used only in conjunction with a Cypress integrated circuit as specified in the applicable agreement. Any reproduction, modification, translation, compilation, or representation of this Source Code except as specified above is prohibited without the express written permission of Cypress.

Disclaimer: CYPRESS MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARD TO THIS MATERIAL, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. Cypress reserves the right to make changes without further notice to the materials described herein. Cypress does not assume any liability arising out of the application or use of any product or circuit described herein. Cypress does not authorize its products for use as critical components in life-support systems where a malfunction or failure may reasonably be expected to result in significant injury to the user. The inclusion of Cypress' product in a life-support systems application implies that the manufacturer assumes all risk of such use and in doing so indemnifies Cypress against all charges.

Use may be limited by and subject to the applicable Cypress software license agreement.