






JKL PART NO.: 2910F-42



JKL PART NO.: 2910F-47

NOTES:

1. TAB SIZE REFERENCE DIMENSIONS: .244" wide X .30" deep X .016 thick.
KEYSTONE P/N 4470 QUICK-FIT SOCKET MAY BE USED FOR CONTACT.
2. MINIMUM LAMP SIZE 1.20"
3. MINIMUM CONTACT DIAMETER .30"
4. LOCATION OF MOUNTING HOLE. HOLE DIA. : Ø3.5mm REF.
5. BODY MATERIAL: DUPONT FR50
MAX. WITHSTAND TEMPERATURE 130C
MAX. INTERMITTENT TEMPERATURE 180C
MAX. WATTAGE: -42 10W
-47 18W

			METRIC  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- REF. 2 PL +/- REF. ANGLE +/- 0		JKL COMPONENTS CORPORATION TITLE FESTOON HOLDER										
D	ADDED NOTES		8/7/08		DRAWN BY		APPV'D BY	DATE	SIZE	FSCM NO.	DRAWING NO.	2910F					
C	CORR. MATERIAL DESCRIPTION		11/13/07		L. WENGSTROM		L. R.		A	55335							
B	ADD NOTES		8/18/06														
A	ADD PART NO. 2910F-47		6/30/06														
	RELEASED		6/12/06														
REV. NO.	DESCRIPTION/ECO NUMBER		APPV'D DATE		- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		SCALE		NONE		RELEASED DATE	6/12/06	REVISION DATE	8/7/08	REV. NO.	D	SHEET 1 OF 1