



Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sans autorisation écrite de la propriété de FCI. Droits de reproduction FCI.

A FCI

All rights strictly reserved. Reproduction or use to third parties in any form whatsoever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.



SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S33E4PA00**	D09S33E6PA00**
15	39.14	33.32	25.18	24.54	19.18	D15S33E4PA00**	D15S33E6PA00**
25	53.03	47.04	39.12	38.25	33.12	D25S33E4PA00**	D25S33E6PA00**
37	69.32	63.50	55.68	54.71	49.68	D37S33E4PA00**	D37S33E6PA00**

Gold Flash 0,75 µ gold

LF FOR LEAD FREE

REQUIREMENTS

Technical characteristics:
Shell: steel tin plated
Insulators: self-extinguishing thermoplastic, UL class 94V0
Contacts: phosphor bronze, gold (for thickness see table)
over 2 µ mini nickel on active area and flash to 1.5 µ maxi SnPb
over 1 µ mini nickel on termination.
Cycles: 200 min for plating 4.
Cycles: 500 min for plating 6.
Electrical characteristics:
max. current rating: 5A
Test voltage: 1000V
Rated voltage: 300V
Contact resistance: <15mΩ
Shell resistance: <5mΩ
Insulation resistance: >5000MΩ
Climatic characteristics:
Operating temperature range: -55°C +125°C
Dimensions:
in accordance with MIL-C-24308

d	27/7/05	LEAD FREE DETAILS ADDED
INDEX	DATE	REVISION DESCRIPTION

W	Ecn no	Dr	date
d	105-0124	JS	27/7/05

FOR ROHS DETAILS REFER DWG. NO. C01-8646-0000

Dr. JOHN SLEEBA	24/10/89	Product Family	D-SUB	Size	A3	Scale	
Eng. GEORGE VJ	24/10/89	Spec ref		ECN			
Chr. GEORGE VJ	27/7/05	Material					
Appr. K. Somasundaram	27/7/05						
Title		Dwg no		Rev.			
SOCKET CONNECT, DELTA D RIGHT ANGLED		C01-8646-0010		d			
spill without accessories.							
Catalog no		DELTA-D		CUSTOMER COPY		Sheet 1 of 1	