



	CPC1004N	Units
Blocking Voltage (DC)	100	V
Load Current (DC)	300	mA
Max R_{ON}	4	Ω

Features

- Small 4 Pin SOP Package
- Low Drive Power Requirements (TTL/CMOS Compatible)
- No Moving Parts
- High Reliability
- Arc-Free With No Snubbing Circuits
- 1500V_{RMS} Input/Output Isolation
- No EMI/RFI Generation
- Machine Insertable, Wave Solderable
- Tape & Reel Version Available

Applications

- Instrumentation
 - Multiplexers
 - Data Acquisition
 - Electronic Switching
 - I/O Subsystems
 - Meters (Watt-Hour, Water, Gas)
- Medical Equipment—Patient/Equipment Isolation
- Security Systems
- Aerospace
- Industrial Controls
- Reed Relay Replacement

Description

CPC1004N is a miniature low voltage, low on resistance 1-Form-A DC solid state relay in a 4 pin SOP package. The relay uses optically coupled MOSFET technology to provide 1500V of input to output isolation. The efficient MOSFET switch and photovoltaic die use Clare's patented OptoMOS® architecture. The optically-coupled input is controlled by a highly efficient GaAlAs infrared LED. The CPC1004N uses Clare's state of the art double molded vertical construction packaging to produce the world's smallest relay. The CPC1004N is ideal for replacing larger less reliable reed and electromechanical relays.

Approvals


- UL Recognized Component
File #: E76270
- Certified to: EN60950

Ordering Information


Part #	Description
CPC1004N	4 Pin SOP (100/tube)
CPC1004NTR	4 Pin SOP (2,000/reel)

Pin Configuration

CPC1004N Pinout



Switching Characteristics of Normally Open (Form A) Devices



Absolute Maximum Ratings (@ 25° C)

Parameter	Min	Typ	Max	Units
Input Power Dissipation	-	-	70	mW
Input Control Current	-	-	50	mA
Peak (10ms)	-	-	1	A
Reverse Input Voltage	-	-	5	V
Blocking Voltage	-	-	100	V
Total Power Dissipation	-	-	400 ¹	mW
Capacitance				
Input to Output	-	1	-	pF
Isolation Voltage				
Input to Output	1500	-	-	V _{RMS}
Operational Temperature	-40	-	+110	°C
Storage Temperature	-40	-	+125	°C
Soldering Temperature	-	-	+220	°C
(10 Seconds Max.)				

¹ Derate Linearly 3.33 mw / °C

Absolute Maximum Ratings are stress ratings. Stresses in excess of these ratings can cause permanent damage to the device. Functional operation of the device at these or any other conditions beyond those indicated in the operational sections of this data sheet is not implied. Exposure of the device to the absolute maximum ratings for an extended period may degrade the device and effect its reliability.

Electrical Characteristics


Parameter	Conditions	Symbol	Min	Typ	Max	Units
Output Characteristics @ 25°C (Unless Otherwise Specified)						
Load Current (Continuous) ¹ DC		I _L	-	-	300	mA
Load current (Continuous)	T=110°C I _F =10mA				100	mA
Peak Load Current	10ms	I _{LPK}	-	-	350	mA
On-Resistance ²	I _L =300mA	R _{ON}	-	-	4	Ω
Off-State Leakage Current	V _L =100V	I _{LEAK}	-	-	1	μA
Switching Speeds						
Turn-On	I _F =5mA, V _L =10V	T _{ON}	-	-	3	ms
Turn-Off	I _F =5mA, V _L =10V	T _{OFF}	-		1.0	ms
Output Capacitance	50V; f=1MHz	C _{OUT}	-	25	-	pF
Input Characteristics @ 25°C						
Input Control Current	I _L =300mA	I _F	2	-	50	mA
Input Dropout Current	-	I _F	0.3	0.9	-	mA
Input Voltage Drop	I _F =5mA	V _F	0.9	1.2	1.4	V
Reverse Input Voltage	-	V _R	-	-	5	V
Reverse Input Current	V _R =5V	I _R	-	-	10	μA

¹ Load current derates linearly from 300mA @ 25°C to 100mA @ 110°C.


² Measurement taken within 1 second of on time.

PERFORMANCE DATA*


CPC1004N
Typical LED Forward Voltage Drop
 (Ambient Temperature = 25°C)
 $I_F = 5\text{mA}$




CPC1004N
Typical On-Resistance Distribution
 (Ambient Temperature = 25°C)
 (Load Current = 300mA)




CPC1004N
Typical Blocking Voltage Distribution
 (Ambient Temperature = 25°C)




CPC1004N
Typical I_F for Switch Operation
 (Ambient Temperature = 25°C)
 (Load Current = 300mA)




CPC1004N
Typical I_F for Switch Dropout
 (Ambient Temperature = 25°C)
 (Load Current = 300mA)




CPC1004N
Typical Turn-On Time
 (Ambient Temperature = 25°C)
 (Load Current = 300mA; $I_F = 5\text{mA}$)




CPC1004N
Typical Turn-Off Time
 (Ambient Temperature = 25°C)
 (Load Current = 200mA; $I_F = 5\text{mA}$)




CPC1004N
Typical Maximum Load Current vs. Temperature




CPC1004N
Typical Leakage vs. Temperature
 (Measured across Pins 3 & 4) $V_L = \text{max rated}$




CPC1004N
Typical Blocking Voltage vs. Temperature



CPC1004N
Typical Turn-On vs. Temperature
 (Load Current = 200mA)











CPC1004N
Typical Turn-Off vs. Temperature
 (Load Current = 300mA)



*The Performance data shown in the graphs above is typical of device performance. For guaranteed parameters not indicated in the written specifications, please contact our application department.


PERFORMANCE DATA*




*The Performance data shown in the graphs above is typical of device performance. For guaranteed parameters not indicated in the written specifications, please contact our application department.

MECHANICAL DIMENSIONS


4 Pin SOIC Narrow ("N" Suffix)



PC Board Pattern (Top View)



Tape and Reel Packaging for 4 pin SOIC package



Dimensions
mm
(inches)



CLARE

For additional information please visit our website at: www.clare.com

Clare, Inc. makes no representations or warranties with respect to the accuracy or completeness of the contents of this publication and reserves the right to make changes to specifications and product descriptions at any time without notice. Neither circuit patent licenses nor indemnity are expressed or implied. Except as set forth in Clare's Standard Terms and Conditions of Sale, Clare, Inc. assumes no liability whatsoever, and disclaims any express or implied warranty, relating to its products including, but not limited to, the implied warranty of merchantability, fitness for a particular purpose, or infringement of any intellectual property right.

The products described in this document are not designed, intended, authorized or warranted for use as components in systems intended for surgical implant into the body, or in other applications intended to support or sustain life, or where malfunction of Clare's product may result in direct physical harm, injury, or death to a person or severe property or environmental damage. Clare, Inc. reserves the right to discontinue or make changes to its products at any time without notice.

Specification: DS-CPC1004N-R1.0
©Copyright 2002, Clare, Inc.
OptoMOS® is a registered trademark of Clare, Inc.
All rights reserved. Printed in USA.
9/23/02