




1LN1-3-RH (RIGHT HAND)
M
DRAWING NUMBER
ISSUE 86
REPLACES ISSUE 2
FO-80378-003
LMH 5 SEP 61
DRAWN
CHECK
DRAWING
REVISIONS
A CO16227
LMH 5 SEP 61
B CO18546
MBF 14 NOV 63
C CO55988
MAM 31 OCT 84
D CO 76967
J.D.B. 26 OCT 93

MICRO SWITCH
A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
FREDPORT, ILLINOIS
FED. MFR. CODE 91929

SWITCH - ENCLOSED

CATALOG LISTING
1LN1-3-RH
(RIGHT HAND)



NOTE -
DOWEL HOLES WILL ACCEPT .187 MAX DIA DOWEL PINS ON 3.250 X .375 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.		
CHARACTERISTICS	ELECTRICAL DATA	
OPERATING FORCE-----6 LB MAX	CONTACT ARRANGEMENT (SEE CIRCUIT DIAGRAM)	SCALE FULL
RELEASE FORCE-----1 LB MIN	-L25- 10 A-125 OR 250 VAC 1/2 HP-125 VAC RJ	DO NOT SCALE PRINT
DIFFERENTIAL TRAVEL-----.030 MAX		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES
OVERTRAVEL-----.171 MIN		TOLERANCES ARE: ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ±
		WEIGHT